

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P845524

Luminaire Tested: SQ2R-FB-075D-835-UNV-STD-W-4

Issue Date: 6/14/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P845524  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/14/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2R-FB-075D-835-UNV-STD-W-4  
Description: CONTINUA SQ2 RECESSED, BATWING LENS  
750 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3362.6 lumens  
Efficiency: N/A  
Efficacy: 125.9 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 2.99 / 2.56  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 26.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P845524  
CATALOG NUMBER: SQ2R-FB-075D-835-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P845524

CATALOG NUMBER: SQ2R-FB-075D-835-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84				84
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69				69
3	89	78	70	63	87	77	69	63	74	67	62	71	65	60	68	64	59	57				57
4	81	69	60	53	79	67	59	52	65	58	52	63	56	51	60	55	50	48				48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41				41
6	68	54	45	39	66	53	45	38	52	44	38	50	43	38	48	42	37	35				35
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31				31
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27				27
9	54	40	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24				24
10	51	37	29	23	49	37	29	23	36	28	23	35	28	23	34	28	23	21				21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5483	5483	5483
5°	5345	7408	9710
10°	5005	14346	18897
15°	4530	18664	21748
20°	4010	20533	22777
25°	3549	21957	23151
30°	3134	22615	23435
35°	2799	23006	25196
40°	2546	23225	26770
45°	2347	23336	28033
50°	2215	23785	28540
55°	2159	24403	28769
60°	2215	24723	28627
65°	2308	24386	27817
70°	2389	23580	21040
75°	2645	21185	11609
80°	2734	10925	10776
85°	2723	7558	4539

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 55°  
 Luminance: 28769 cd/sqm



TEST NUMBER: P845524

CATALOG NUMBER: SQ2R-FB-075D-835-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.9	1.7
10°-20°	260.6	7.8
20°-30°	458.8	13.6
30°-40°	593.4	17.6
40°-50°	654.5	19.5
50°-60°	610.5	18.2
60°-70°	472.4	14.1
70°-80°	215.9	6.4
80°-90°	40.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	775.4	23.1
0°-40°	1368.8	40.7
0°-60°	2633.8	78.3
0°-90°	3362.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3362.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	340	340	340	340	340	
5°	330	379	457	557	599	31
15°	271	540	1117	1249	1301	76
25°	199	730	1232	1286	1300	91
35°	142	705	1167	1206	1278	89
45°	103	540	1022	1172	1228	80
55°	77	322	867	996	1022	69
65°	60	181	638	715	728	59
75°	42	111	340	183	186	44
85°	15	33	41	28	24	16
90°	0	0	0	0	0	



TEST NUMBER: P845524

CATALOG NUMBER: SQ2R-FB-075D-835-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	339.6	339.6	339.6	339.6	339.6
2.5°	336.3	354.3	373.8	396.7	406.5
5°	329.8	378.7	457.1	556.7	599.1
7.5°	320.0	409.8	612.2	888.1	982.8
10°	305.3	444.0	875.0	1106.8	1152.6
12.5°	289.0	489.8	1039.9	1185.2	1232.5
15°	271.0	540.4	1116.6	1248.9	1301.1
17.5°	253.0	595.9	1160.7	1296.2	1327.2
20°	233.4	654.6	1195.0	1307.6	1325.6
22.5°	215.5	698.7	1219.5	1297.8	1317.4
25°	199.2	729.7	1232.5	1286.4	1299.5
27.5°	182.8	741.2	1227.7	1265.2	1276.6
30°	168.1	737.9	1213.0	1239.1	1257.0
32.5°	155.1	728.1	1191.7	1216.2	1260.3
35°	142.0	705.2	1167.2	1206.4	1278.3
37.5°	130.6	672.6	1136.2	1211.3	1283.2
40°	120.8	635.0	1101.9	1211.3	1270.1
42.5°	111.0	591.0	1062.8	1195.0	1253.8
45°	102.8	540.4	1022.0	1172.1	1227.7
47.5°	94.7	484.9	984.4	1144.4	1186.8
50°	88.2	427.7	946.9	1103.6	1136.2
52.5°	81.6	372.2	909.3	1054.6	1084.0
55°	76.7	321.6	866.9	995.8	1022.0
57.5°	71.8	275.9	821.2	933.8	955.0
60°	68.6	240.0	765.6	865.2	886.5
62.5°	63.7	207.3	703.6	793.4	813.0
65°	60.4	181.2	638.3	715.0	728.1
67.5°	55.5	160.0	569.7	625.3	612.2
70°	50.6	145.3	499.5	515.9	445.7
72.5°	47.3	129.0	422.8	373.8	225.3
75°	42.4	111.0	339.6	182.8	186.1
77.5°	35.9	89.8	249.8	146.9	150.2
80°	29.4	70.2	117.5	114.3	115.9
82.5°	22.9	50.6	71.8	76.7	73.5
85°	14.7	32.7	40.8	27.8	24.5
87.5°	6.5	14.7	8.2	8.2	8.2
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P845524

CATALOG NUMBER: SQ2R-FB-075D-835-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.81	18.49	17.17	18.81	19.12	25.46	27.15	25.83	27.46	27.77
	3H	17.60	19.12	17.97	19.45	19.81	27.15	28.67	27.52	29.00	29.36
	4H	17.93	19.37	18.33	19.71	20.09	27.36	28.80	27.76	29.15	29.52
	6H	18.19	19.52	18.60	19.88	20.27	27.49	28.82	27.90	29.18	29.57
	8H	18.27	19.54	18.69	19.93	20.32	27.52	28.79	27.94	29.18	29.58
	12H	18.32	19.54	18.75	19.92	20.35	27.52	28.74	27.95	29.12	29.55
4H	2H	21.24	22.68	21.64	23.03	23.40	26.00	27.44	26.40	27.78	28.16
	3H	22.26	23.46	22.67	23.85	24.25	27.91	29.11	28.32	29.50	29.90
	4H	22.58	23.66	23.01	24.08	24.51	28.18	29.26	28.61	29.68	30.11
	6H	22.76	23.71	23.21	24.15	24.60	28.37	29.32	28.83	29.76	30.21
	8H	22.80	23.69	23.26	24.13	24.59	28.42	29.30	28.88	29.75	30.21
	12H	22.84	23.63	23.31	24.10	24.57	28.43	29.23	28.91	29.70	30.17
8H	4H	23.82	24.70	24.28	25.14	25.61	28.37	29.25	28.83	29.69	30.16
	6H	24.09	24.83	24.59	25.31	25.79	28.61	29.34	29.10	29.83	30.30
	8H	24.18	24.83	24.69	25.34	25.82	28.68	29.34	29.19	29.84	30.33
	12H	24.24	24.82	24.75	25.31	25.87	28.72	29.29	29.22	29.78	30.34
12H	4H	23.87	24.67	24.35	25.14	25.61	28.36	29.15	28.84	29.63	30.10
	6H	24.20	24.85	24.70	25.36	25.84	28.60	29.26	29.11	29.77	30.25
	8H	24.34	24.92	24.85	25.41	25.97	28.71	29.29	29.22	29.78	30.34