

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P845539

Luminaire Tested: SQ2R-FB-125D-935-UNV-STD-W-4

Issue Date: 6/14/2024

Test Information

Test Method: LM-79-2019
Report Number: P845539
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 6/14/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2R-FB-125D-935-UNV-STD-W-4
Description: CONTINUA SQ2 RECESSED, BATWING LENS
1250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4974.4 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 2.99 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9979
Total Harmonic Distortion (THDi): 0.0523
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P845539
CATALOG NUMBER: SQ2R-FB-125D-935-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P845539

CATALOG NUMBER: SQ2R-FB-125D-935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84				84
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69				69
3	89	78	70	63	87	77	69	63	74	67	62	71	65	60	68	64	59	57				57
4	81	69	60	53	79	67	59	52	65	58	52	63	56	51	60	55	50	48				48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41				41
6	68	54	45	39	66	53	45	38	52	44	38	50	43	38	48	42	37	35				35
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31				31
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27				27
9	54	40	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24				24
10	51	37	29	23	49	37	29	23	36	28	23	35	28	23	34	28	23	21				21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8110	8110	8110
5°	7906	10960	14365
10°	7404	21223	27953
15°	6701	27612	32174
20°	5935	30374	33694
25°	5248	32484	34247
30°	4639	33454	34670
35°	4141	34036	37272
40°	3766	34360	39601
45°	3473	34520	41468
50°	3275	35183	42222
55°	3195	36099	42556
60°	3274	36577	42347
65°	3415	36076	41150
70°	3536	34886	31124
75°	3918	31335	17174
80°	4045	16169	15946
85°	4020	11189	6706

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 55°
 Luminance: 42556 cd/sqm

TEST NUMBER: P845539

CATALOG NUMBER: SQ2R-FB-125D-935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.7	1.7
10°-20°	385.6	7.8
20°-30°	678.7	13.6
30°-40°	877.8	17.6
40°-50°	968.2	19.5
50°-60°	903.1	18.2
60°-70°	698.9	14.1
70°-80°	319.5	6.4
80°-90°	59.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1147.1	23.1
0°-40°	2024.9	40.7
0°-60°	3896.3	78.3
0°-90°	4974.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4974.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	488	560	676	824	886	45
15°	401	799	1652	1848	1925	112
25°	295	1080	1823	1903	1922	135
35°	210	1043	1727	1785	1891	132
45°	152	799	1512	1734	1816	118
55°	114	476	1282	1473	1512	102
65°	89	268	944	1058	1077	88
75°	63	164	502	270	275	65
85°	22	48	60	41	36	24
90°	0	0	0	0	0	



TEST NUMBER: P845539

CATALOG NUMBER: SQ2R-FB-125D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	502.3	502.3	502.3	502.3	502.3
2.5°	497.5	524.1	553.0	586.9	601.3
5°	487.8	560.3	676.2	823.5	886.3
7.5°	473.4	606.2	905.6	1313.8	1453.9
10°	451.6	656.9	1294.5	1637.4	1705.0
12.5°	427.5	724.5	1538.4	1753.3	1823.4
15°	400.9	799.4	1651.9	1847.5	1924.8
17.5°	374.3	881.5	1717.1	1917.6	1963.4
20°	345.4	968.4	1767.8	1934.5	1961.0
22.5°	318.8	1033.6	1804.0	1920.0	1948.9
25°	294.6	1079.5	1823.4	1903.1	1922.4
27.5°	270.5	1096.4	1816.1	1871.7	1888.6
30°	248.8	1091.6	1794.4	1833.0	1859.6
32.5°	229.4	1077.1	1763.0	1799.2	1864.4
35°	210.1	1043.3	1726.8	1784.7	1891.0
37.5°	193.2	995.0	1680.9	1792.0	1898.2
40°	178.7	939.5	1630.2	1792.0	1878.9
42.5°	164.2	874.2	1572.2	1767.8	1854.8
45°	152.1	799.4	1511.8	1734.0	1816.1
47.5°	140.1	717.3	1456.3	1693.0	1755.7
50°	130.4	632.7	1400.7	1632.6	1680.9
52.5°	120.8	550.6	1345.2	1560.1	1603.6
55°	113.5	475.8	1282.4	1473.2	1511.8
57.5°	106.3	408.1	1214.8	1381.4	1412.8
60°	101.4	355.0	1132.7	1280.0	1311.4
62.5°	94.2	306.7	1040.9	1173.7	1202.7
65°	89.4	268.1	944.3	1057.8	1077.1
67.5°	82.1	236.7	842.9	925.0	905.6
70°	74.9	214.9	739.0	763.2	659.3
72.5°	70.0	190.8	625.5	553.0	333.3
75°	62.8	164.2	502.3	270.5	275.3
77.5°	53.1	132.8	369.5	217.4	222.2
80°	43.5	103.8	173.9	169.1	171.5
82.5°	33.8	74.9	106.3	113.5	108.7
85°	21.7	48.3	60.4	41.1	36.2
87.5°	9.7	21.7	12.1	12.1	12.1
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P845539

CATALOG NUMBER: SQ2R-FB-125D-935-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.17	19.85	18.53	20.17	20.48	26.82	28.51	27.19	28.82	29.14
	3H	18.96	20.48	19.33	20.81	21.17	28.51	30.03	28.88	30.36	30.72
	4H	19.29	20.73	19.69	21.07	21.45	28.73	30.16	29.12	30.51	30.88
	6H	19.55	20.88	19.96	21.24	21.63	28.85	30.18	29.26	30.55	30.94
	8H	19.63	20.90	20.05	21.29	21.68	28.88	30.15	29.30	30.54	30.94
	12H	19.68	20.90	20.11	21.28	21.71	28.88	30.10	29.31	30.48	30.91
4H	2H	22.60	24.04	23.00	24.39	24.76	27.36	28.80	27.76	29.14	29.52
	3H	23.62	24.82	24.03	25.22	25.61	29.27	30.47	29.68	30.86	31.26
	4H	23.94	25.02	24.37	25.44	25.87	29.54	30.62	29.97	31.04	31.47
	6H	24.12	25.07	24.57	25.51	25.96	29.73	30.68	30.19	31.12	31.57
	8H	24.16	25.05	24.62	25.49	25.95	29.78	30.66	30.24	31.11	31.57
	12H	24.20	24.99	24.68	25.46	25.93	29.79	30.59	30.27	31.06	31.53
8H	4H	25.18	26.06	25.64	26.50	26.97	29.73	30.61	30.19	31.05	31.52
	6H	25.45	26.19	25.95	26.67	27.15	29.97	30.70	30.46	31.19	31.67
	8H	25.54	26.19	26.05	26.70	27.18	30.04	30.70	30.55	31.20	31.69
	12H	25.60	26.18	26.11	26.67	27.23	30.08	30.65	30.58	31.14	31.70
12H	4H	25.23	26.03	25.71	26.50	26.97	29.72	30.51	30.20	30.99	31.46
	6H	25.56	26.21	26.07	26.72	27.20	29.96	30.62	30.47	31.13	31.61
	8H	25.70	26.28	26.21	26.77	27.33	30.07	30.65	30.58	31.14	31.70