

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P845512

Luminaire Tested: SQ2R-FA-125D-835-UNV-STD-W-4

Issue Date: 6/14/2024

Test Information

Test Method: LM-79-2019
Report Number: P845512
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-11)
Test Lab: INNOVATION CENTER
Issue Date: 6/14/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2R-FA-125D-835-UNV-STD-W-4
Description: CONTINUA SQ2 RECESSED, ASYMMETRIC LENS
1250 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5287.2 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 0.95 / 0.93
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9979
Total Harmonic Distortion (THDi): 0.0523
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P845512
CATALOG NUMBER: SQ2R-FA-125D-835-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P845512

CATALOG NUMBER: SQ2R-FA-125D-835-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88				88
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78				78
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70				70
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63				63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57				57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52				52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48				48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	55	49	46	44				44
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41				41
10	63	51	44	40	61	51	44	40	50	44	40	49	43	39	48	43	39	38				38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	58513	58513	58513	58513
5°	58204	58294	57982	58248
10°	58115	57892	57892	57892
15°	57927	57334	57469	57334
20°	57477	55036	57055	55553
25°	56723	46449	56333	47423
30°	56201	26649	55590	27005
35°	55217	22894	54515	22570
40°	53687	12039	52189	11923
45°	48800	5179	47053	5179
50°	32197	6247	30549	5835
55°	18002	11541	17078	10463
60°	9707	16239	9533	14560
65°	8562	19733	8978	22449
70°	7997	23608	7610	24902
75°	7505	20287	7673	20973
80°	6351	14486	6351	15249
85°	5576	8096	5057	9615

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 48800 cd/sqm

TEST NUMBER: P845512

CATALOG NUMBER: SQ2R-FA-125D-835-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	341.3	6.5
10°-20°	968.5	18.3
20°-30°	1324.8	25.1
30°-40°	1109.5	21.0
40°-50°	621.9	11.8
50°-60°	329.8	6.2
60°-70°	307.5	5.8
70°-80°	226.1	4.3
80°-90°	57.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2634.5	49.8
0°-40°	3744.0	70.8
0°-60°	4695.7	88.8
0°-90°	5287.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5287.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3624	3624	3624	3624	3624	
5°	3591	3597	3578	3594	3591	341
15°	3466	3430	3438	3430	3466	978
25°	3184	2607	3162	2662	3184	1469
35°	2801	1162	2766	1145	2801	1751
45°	2137	227	2061	227	2137	1577
55°	640	410	607	372	640	604
65°	224	516	235	588	224	224
75°	120	325	123	336	120	124
85°	30	44	27	52	30	35
90°	0	0	0	0	0	



TEST NUMBER: P845512

CATALOG NUMBER: SQ2R-FA-125D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	3624.0	3624.0	3624.0	3624.0	3624.0	3624.0	3624.0	3624.0	3624.0	3624.0	3624.0
2.5°	3599.4	3667.7	3607.6	3599.4	3624.0	3618.5	3610.3	3643.1	3588.5	3643.1	3599.4
5°	3591.2	3654.1	3583.0	3563.9	3596.7	3574.8	3593.9	3632.2	3577.5	3626.7	3572.1
7.5°	3574.8	3632.2	3547.5	3533.8	3566.6	3547.5	3555.7	3607.6	3561.1	3593.9	3544.7
10°	3544.7	3593.9	3509.2	3501.0	3531.1	3511.9	3520.1	3574.8	3531.1	3561.1	3511.9
12.5°	3511.9	3547.5	3462.7	3460.0	3484.6	3473.7	3476.4	3520.1	3487.3	3517.4	3470.9
15°	3465.5	3501.0	3416.3	3402.6	3430.0	3419.0	3424.5	3465.5	3438.1	3457.3	3416.3
17.5°	3413.6	3440.9	3358.9	3328.8	3331.6	3345.2	3358.9	3408.1	3380.8	3405.4	3353.4
20°	3345.2	3378.0	3285.1	3208.6	3203.1	3216.8	3285.1	3334.3	3320.6	3348.0	3266.0
22.5°	3266.0	3285.1	3203.1	3061.0	3039.1	3052.8	3192.2	3252.3	3249.6	3266.0	3159.4
25°	3184.0	3205.8	3052.8	2872.4	2607.3	2856.0	3058.3	3162.1	3162.1	3178.5	3044.6
27.5°	3102.0	3107.5	2888.8	1935.0	1672.6	1855.7	2883.3	3052.8	3074.7	3071.9	2875.1
30°	3014.5	2995.4	2489.8	1489.5	1429.4	1467.6	2492.5	2938.0	2981.7	2951.7	2426.9
32.5°	2913.4	2850.5	1675.3	1339.2	1292.7	1325.5	1598.8	2801.4	2886.1	2812.3	1779.2
35°	2801.4	2659.2	1402.0	1210.7	1161.5	1205.3	1391.1	2612.8	2765.8	2590.9	1448.5
37.5°	2686.6	2219.2	1265.4	1030.4	932.0	1014.0	1259.9	2211.0	2631.9	2118.1	1270.9
40°	2547.2	1642.6	1109.6	707.9	571.2	666.9	1101.4	1566.0	2476.1	1689.0	1082.3
42.5°	2361.3	1388.4	836.3	385.4	295.2	347.1	792.6	1366.5	2284.8	1402.0	806.2
45°	2137.2	1235.3	527.5	246.0	226.8	237.8	486.5	1213.5	2060.7	1186.1	538.4
47.5°	1795.6	992.1	358.0	207.7	224.1	207.7	347.1	962.0	1694.5	942.9	358.0
50°	1281.8	735.2	262.4	210.4	248.7	210.4	254.2	710.6	1216.2	778.9	259.6
52.5°	866.4	587.6	202.2	235.0	311.6	240.5	196.8	573.9	822.6	593.1	188.6
55°	639.5	486.5	172.2	303.4	410.0	311.6	172.2	472.8	606.7	467.3	166.7
57.5°	431.8	382.6	169.4	385.4	459.1	393.6	172.2	369.0	412.7	371.7	150.3
60°	300.6	287.0	194.0	415.4	502.9	420.9	196.8	276.0	295.2	273.3	164.0
62.5°	235.0	210.4	243.2	459.1	527.5	442.8	248.7	199.5	248.7	188.6	185.8
65°	224.1	144.9	276.0	456.4	516.5	456.4	278.8	136.7	235.0	147.6	246.0
67.5°	210.4	109.3	270.6	450.9	524.7	456.4	262.4	103.9	202.2	101.1	240.5
70°	169.4	95.7	251.4	461.9	500.1	445.5	251.4	92.9	161.2	90.2	295.2
72.5°	133.9	90.2	229.6	418.2	429.1	401.8	232.3	90.2	136.7	79.3	273.3
75°	120.3	90.2	224.1	341.6	325.2	325.2	218.6	87.5	123.0	82.0	215.9
77.5°	95.7	82.0	194.0	237.8	224.1	224.1	191.3	79.3	90.2	73.8	183.1
80°	68.3	73.8	153.0	164.0	155.8	155.8	147.6	71.1	68.3	68.3	144.9
82.5°	49.2	60.1	109.3	109.3	103.9	101.1	106.6	60.1	49.2	54.7	103.9
85°	30.1	43.7	62.9	51.9	43.7	41.0	60.1	41.0	27.3	41.0	60.1
87.5°	13.7	24.6	10.9	10.9	10.9	10.9	10.9	24.6	13.7	21.9	13.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P845512

CATALOG NUMBER: SQ2R-FA-125D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	3624.0	3624.0	3624.0	3624.0	3624.0	3624.0
2.5°	3588.5	3607.6	3607.6	3596.7	3651.3	3599.4
5°	3558.4	3593.9	3577.5	3577.5	3632.2	3591.2
7.5°	3539.3	3574.8	3558.4	3552.9	3607.6	3574.8
10°	3506.5	3531.1	3520.1	3528.3	3577.5	3544.7
12.5°	3460.0	3490.1	3479.1	3492.8	3536.5	3511.9
15°	3405.4	3430.0	3435.4	3440.9	3492.8	3465.5
17.5°	3320.6	3331.6	3361.6	3391.7	3443.6	3413.6
20°	3216.8	3233.2	3249.6	3315.2	3378.0	3345.2
22.5°	3099.3	3088.3	3132.1	3211.3	3293.3	3266.0
25°	2872.4	2662.0	2894.3	3088.3	3192.2	3184.0
27.5°	2109.9	1803.8	2071.6	2927.1	3091.1	3102.0
30°	1574.2	1448.5	1571.5	2544.4	2976.3	3014.5
32.5°	1352.8	1276.3	1339.2	1784.7	2831.4	2913.4
35°	1205.3	1145.1	1205.3	1448.5	2631.9	2801.4
37.5°	1027.6	912.8	1030.4	1284.5	2227.4	2686.6
40°	721.5	565.7	699.7	1120.5	1683.5	2547.2
42.5°	420.9	314.3	393.6	822.6	1393.8	2361.3
45°	259.6	226.8	248.7	532.9	1180.7	2137.2
47.5°	205.0	210.4	205.0	355.3	940.2	1795.6
50°	194.0	232.3	194.0	259.6	748.8	1281.8
52.5°	215.9	256.9	213.2	191.3	579.4	866.4
55°	237.8	371.7	240.5	166.7	450.9	639.5
57.5°	338.9	410.0	344.4	155.8	369.0	431.8
60°	349.8	450.9	347.1	166.7	270.6	300.6
62.5°	429.1	584.9	429.1	196.8	183.1	235.0
65°	532.9	587.6	538.4	243.2	142.1	224.1
67.5°	508.3	549.3	502.9	251.4	98.4	210.4
70°	497.4	527.5	491.9	297.9	90.2	169.4
72.5°	456.4	453.7	445.5	270.6	79.3	133.9
75°	360.8	336.2	347.1	237.8	82.0	120.3
77.5°	237.8	226.8	229.6	188.6	73.8	95.7
80°	169.4	164.0	161.2	153.0	68.3	68.3
82.5°	114.8	109.3	106.6	109.3	54.7	49.2
85°	57.4	51.9	49.2	68.3	41.0	30.1
87.5°	13.7	13.7	10.9	13.7	19.1	13.7
90°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P845512

CATALOG NUMBER: SQ2R-FA-125D-835-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.12	19.43	18.49	19.74	20.06	16.96	18.27	17.33	18.58	18.90
	3H	18.84	20.01	19.22	20.34	20.71	23.17	24.34	23.55	24.67	25.03
	4H	19.27	20.36	19.67	20.71	21.10	24.46	25.56	24.87	25.91	26.29
	6H	19.64	20.65	20.06	21.02	21.42	25.09	26.10	25.50	26.47	26.86
	8H	19.77	20.73	20.20	21.12	21.53	25.22	26.18	25.65	26.57	26.98
	12H	19.86	20.78	20.29	21.16	21.59	25.28	26.19	25.71	26.58	27.01
4H	2H	18.56	19.66	18.96	20.01	20.39	17.55	18.64	17.95	18.99	19.37
	3H	19.58	20.49	19.99	20.89	21.30	23.92	24.83	24.33	25.23	25.63
	4H	20.15	20.97	20.59	21.39	21.83	25.38	26.20	25.82	26.62	27.06
	6H	20.65	21.36	21.11	21.81	22.27	26.14	26.85	26.60	27.30	27.76
	8H	20.83	21.49	21.29	21.94	22.41	26.31	26.98	26.78	27.42	27.89
	12H	20.96	21.55	21.45	22.03	22.51	26.39	26.98	26.88	27.46	27.94
8H	4H	21.28	21.95	21.75	22.39	22.86	25.53	26.19	26.00	26.64	27.11
	6H	21.91	22.45	22.41	22.94	23.42	26.42	26.97	26.92	27.46	27.94
	8H	22.14	22.63	22.66	23.14	23.63	26.67	27.16	27.19	27.67	28.16
	12H	22.34	22.76	22.85	23.26	23.83	26.81	27.24	27.33	27.73	28.30
12H	4H	21.45	22.04	21.93	22.52	22.99	25.51	26.10	26.00	26.58	27.06
	6H	22.18	22.66	22.70	23.18	23.67	26.43	26.92	26.95	27.43	27.92
	8H	22.50	22.93	23.02	23.42	23.99	26.73	27.16	27.25	27.65	28.22