

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P845599

Luminaire Tested: SQ2R-PP3-075D-935-UNV-STD-W-4

Issue Date: 6/14/2024

Test Information

Test Method: LM-79-2019
Report Number: P845599
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 6/14/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2R-PP3-075D-935-UNV-STD-W-4
Description: CORELITE SQ2R RECESSED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3437.5 lumens
Efficiency: N/A
Efficacy: 128.7 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 26.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P845599

CATALOG NUMBER: SQ2R-PP3-075D-935-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P845599

CATALOG NUMBER: SQ2R-PP3-075D-935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	89	87				
2	101	94	88	82	99	92	86	82	88	84	80	85	81	78	82	79	76	74				
3	93	83	76	70	91	82	75	69	79	73	68	76	71	67	74	69	66	64				
4	86	75	66	60	83	73	66	60	71	64	59	69	63	58	66	61	57	55				
5	79	67	59	52	77	66	58	52	64	57	52	62	56	51	60	55	51	49				
6	73	61	52	46	71	60	52	46	58	51	46	56	50	45	55	49	45	43				
7	68	55	47	41	66	54	46	41	53	46	41	51	45	40	50	44	40	38				
8	63	50	42	37	62	50	42	37	48	41	36	47	41	36	46	40	36	34				
9	59	46	38	33	58	46	38	33	45	38	33	44	37	33	43	37	33	31				
10	56	43	35	30	54	42	35	30	41	35	30	40	34	30	40	34	30	28				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22034	22034	22034
5°	21861	22049	22258
10°	21972	22138	22422
15°	21919	22136	22474
20°	21763	22283	22928
25°	21640	22564	24132
30°	21517	23021	24636
35°	21212	23089	24681
40°	20645	23048	22803
45°	20027	22003	17358
50°	19241	18771	14458
55°	17909	15797	10396
60°	15419	13556	7453
65°	13005	10472	7331
70°	10829	8242	7015
75°	9177	7112	6569
80°	7782	6174	5904
85°	6150	5076	3205

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 22003 cd/sqm

TEST NUMBER: P845599

CATALOG NUMBER: SQ2R-PP3-075D-935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.0	3.8
10°-20°	376.2	10.9
20°-30°	589.5	17.2
30°-40°	728.0	21.2
40°-50°	685.3	19.9
50°-60°	484.5	14.1
60°-70°	275.2	8.0
70°-80°	136.3	4.0
80°-90°	32.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1095.7	31.9
0°-40°	1823.7	53.1
0°-60°	2993.5	87.1
0°-90°	3437.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3437.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1365	1365	1365	1365	1365	
5°	1349	1373	1360	1363	1373	128
15°	1311	1330	1324	1337	1344	370
25°	1215	1246	1267	1317	1355	560
35°	1076	1106	1171	1238	1252	672
45°	877	945	964	818	760	676
55°	636	675	561	424	369	562
65°	340	359	274	193	192	341
75°	147	163	114	107	105	159
85°	33	30	27	22	17	40
90°	0	0	0	0	0	



TEST NUMBER: P845599

CATALOG NUMBER: SQ2R-PP3-075D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1364.7	1364.7	1364.7	1364.7	1364.7
2.5°	1351.7	1376.2	1360.4	1363.2	1366.1
5°	1348.8	1373.3	1360.4	1363.2	1373.3
7.5°	1344.5	1370.5	1357.5	1361.8	1374.8
10°	1340.2	1361.8	1350.3	1357.5	1367.6
12.5°	1327.2	1347.4	1337.3	1347.4	1356.0
15°	1311.3	1330.1	1324.3	1337.3	1344.5
17.5°	1291.1	1312.7	1311.3	1328.6	1334.4
20°	1266.6	1294.0	1296.9	1320.0	1334.4
22.5°	1240.6	1273.8	1279.6	1317.1	1344.5
25°	1214.7	1246.4	1266.6	1317.1	1354.6
27.5°	1184.4	1216.1	1256.5	1312.7	1343.0
30°	1154.1	1184.4	1234.8	1294.0	1321.4
32.5°	1116.6	1148.3	1203.1	1268.0	1292.6
35°	1076.2	1106.5	1171.4	1237.7	1252.2
37.5°	1031.4	1063.2	1136.8	1181.5	1187.2
40°	979.5	1024.2	1093.5	1100.7	1081.9
42.5°	929.0	989.6	1032.9	995.4	895.8
45°	877.1	944.9	963.6	817.9	760.2
47.5°	822.3	890.1	868.4	704.0	663.6
50°	766.0	829.5	747.3	613.1	575.6
52.5°	702.5	757.4	639.1	526.5	464.5
55°	636.2	675.1	561.2	424.1	369.3
57.5°	556.8	585.7	494.8	333.2	264.0
60°	477.5	499.1	419.8	261.1	230.8
62.5°	405.4	424.1	341.9	217.8	212.1
65°	340.4	359.2	274.1	193.3	191.9
67.5°	281.3	301.5	219.3	173.1	171.7
70°	229.4	251.0	174.6	151.5	148.6
72.5°	186.1	206.3	141.4	128.4	126.9
75°	147.1	163.0	114.0	106.8	105.3
77.5°	112.5	124.1	89.4	85.1	83.7
80°	83.7	88.0	66.4	64.9	63.5
82.5°	57.7	54.8	46.2	44.7	41.8
85°	33.2	30.3	27.4	21.6	17.3
87.5°	13.0	13.0	5.8	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P845599

CATALOG NUMBER: SQ2R-PP3-075D-935-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.19	23.71	22.56	24.03	24.34	18.59	20.12	18.96	20.43	20.75
	3H	23.34	24.70	23.71	25.03	25.39	19.75	21.11	20.12	21.44	21.80
	4H	23.71	24.98	24.11	25.33	25.71	20.24	21.51	20.64	21.86	22.24
	6H	23.96	25.13	24.37	25.50	25.89	20.61	21.79	21.03	22.16	22.55
	8H	24.02	25.14	24.45	25.53	25.93	20.72	21.84	21.14	22.23	22.63
	12H	24.06	25.13	24.49	25.51	25.94	20.75	21.82	21.18	22.21	22.64
4H	2H	22.38	23.65	22.78	24.00	24.38	19.39	20.66	19.79	21.01	21.39
	3H	23.75	24.80	24.16	25.20	25.60	20.69	21.75	21.10	22.15	22.55
	4H	24.25	25.19	24.68	25.61	26.05	21.27	22.22	21.71	22.63	23.07
	6H	24.62	25.44	25.08	25.88	26.34	21.75	22.57	22.20	23.01	23.47
	8H	24.72	25.49	25.19	25.94	26.40	21.88	22.65	22.34	23.09	23.56
	12H	24.79	25.47	25.27	25.95	26.42	21.94	22.62	22.42	23.10	23.57
8H	4H	24.31	25.08	24.78	25.52	25.99	21.59	22.36	22.06	22.80	23.27
	6H	24.76	25.40	25.26	25.89	26.37	22.16	22.79	22.65	23.28	23.76
	8H	24.92	25.49	25.44	26.00	26.49	22.34	22.92	22.86	23.43	23.91
	12H	25.03	25.54	25.54	26.03	26.60	22.44	22.95	22.95	23.44	24.01
12H	4H	24.30	24.98	24.78	25.46	25.93	21.63	22.31	22.11	22.79	23.26
	6H	24.75	25.33	25.27	25.84	26.32	22.21	22.78	22.72	23.29	23.78
	8H	24.95	25.46	25.46	25.95	26.51	22.45	22.95	22.96	23.44	24.01