

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P845519

Luminaire Tested: SQ2R-FB-050D-840-UNV-STD-W-4

Issue Date: 6/14/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P845519  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/14/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2R-FB-050D-840-UNV-STD-W-4  
Description: CONTINUA SQ2 RECESSED, BATWING LENS  
500 LUMENS PER FOOT  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2400.4 lumens  
Efficiency: N/A  
Efficacy: 134.9 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 2.99 / 2.56  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 17.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9973  
Total Harmonic Distortion (THDi): 0.0531  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P845519  
CATALOG NUMBER: SQ2R-FB-050D-840-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P845519

CATALOG NUMBER: SQ2R-FB-050D-840-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84	84	84	
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69	69	69	
3	89	78	70	63	87	77	69	63	74	67	62	71	65	60	68	64	59	57	57	57	
4	81	69	60	53	79	67	59	52	65	58	52	63	56	51	60	55	50	48	48	48	
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41	41	41	
6	68	54	45	39	66	53	45	38	52	44	38	50	43	38	48	42	37	35	35	35	
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31	31	31	
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27	27	27	
9	54	40	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24	24	24	
10	51	37	29	23	49	37	29	23	36	28	23	35	28	23	34	28	23	21	21	21	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3914	3914	3914
5°	3815	5289	6932
10°	3572	10242	13490
15°	3234	13324	15525
20°	2864	14658	16259
25°	2533	15675	16527
30°	2237	16144	16731
35°	1999	16425	17986
40°	1817	16579	19110
45°	1676	16657	20011
50°	1580	16978	20374
55°	1543	17419	20535
60°	1579	17651	20434
65°	1647	17410	19859
70°	1704	16834	15021
75°	1890	15122	8291
80°	1953	7801	7689
85°	1945	5391	3242

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 55°  
 Luminance: 20535 cd/sqm



TEST NUMBER: P845519

CATALOG NUMBER: SQ2R-FB-050D-840-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.9	1.7
10°-20°	186.1	7.8
20°-30°	327.5	13.6
30°-40°	423.6	17.6
40°-50°	467.2	19.5
50°-60°	435.8	18.2
60°-70°	337.3	14.1
70°-80°	154.2	6.4
80°-90°	28.8	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	553.5	23.1
0°-40°	977.1	40.7
0°-60°	1880.2	78.3
0°-90°	2400.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2400.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	242	242	242	242	242	
5°	235	270	326	397	428	22
15°	194	386	797	892	929	54
25°	142	521	880	918	928	65
35°	101	504	833	861	912	64
45°	73	386	730	837	876	57
55°	55	230	619	711	730	49
65°	43	129	456	510	520	42
75°	30	79	242	130	133	31
85°	10	23	29	20	18	11
90°	0	0	0	0	0	



TEST NUMBER: P845519

CATALOG NUMBER: SQ2R-FB-050D-840-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	242.4	242.4	242.4	242.4	242.4
2.5°	240.1	252.9	266.9	283.2	290.2
5°	235.4	270.4	326.3	397.4	427.7
7.5°	228.4	292.5	437.0	634.0	701.6
10°	217.9	317.0	624.7	790.1	822.8
12.5°	206.3	349.6	742.4	846.1	879.9
15°	193.5	385.7	797.1	891.5	928.8
17.5°	180.6	425.4	828.6	925.3	947.5
20°	166.7	467.3	853.1	933.5	946.3
22.5°	153.8	498.8	870.6	926.5	940.5
25°	142.2	520.9	879.9	918.3	927.7
27.5°	130.5	529.1	876.4	903.2	911.3
30°	120.0	526.8	865.9	884.5	897.4
32.5°	110.7	519.8	850.7	868.2	899.7
35°	101.4	503.5	833.3	861.2	912.5
37.5°	93.2	480.1	811.1	864.7	916.0
40°	86.2	453.3	786.6	864.7	906.7
42.5°	79.2	421.9	758.7	853.1	895.0
45°	73.4	385.7	729.5	836.8	876.4
47.5°	67.6	346.1	702.7	816.9	847.2
50°	62.9	305.3	675.9	787.8	811.1
52.5°	58.3	265.7	649.1	752.8	773.8
55°	54.8	229.6	618.8	710.9	729.5
57.5°	51.3	197.0	586.2	666.6	681.8
60°	48.9	171.3	546.6	617.7	632.8
62.5°	45.5	148.0	502.3	566.4	580.4
65°	43.1	129.4	455.7	510.4	519.8
67.5°	39.6	114.2	406.7	446.3	437.0
70°	36.1	103.7	356.6	368.3	318.2
72.5°	33.8	92.1	301.8	266.9	160.8
75°	30.3	79.2	242.4	130.5	132.9
77.5°	25.6	64.1	178.3	104.9	107.2
80°	21.0	50.1	83.9	81.6	82.7
82.5°	16.3	36.1	51.3	54.8	52.4
85°	10.5	23.3	29.1	19.8	17.5
87.5°	4.7	10.5	5.8	5.8	5.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P845519

CATALOG NUMBER: SQ2R-FB-050D-840-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.64	17.32	16.00	17.64	17.95	24.29	25.98	24.66	26.29	26.60
	3H	16.43	17.95	16.80	18.27	18.63	25.98	27.50	26.35	27.83	28.18
	4H	16.76	18.19	17.16	18.54	18.92	26.19	27.63	26.59	27.98	28.35
	6H	17.02	18.35	17.43	18.71	19.10	26.32	27.65	26.73	28.01	28.40
	8H	17.10	18.37	17.52	18.75	19.15	26.35	27.62	26.77	28.01	28.41
	12H	17.15	18.37	17.58	18.75	19.18	26.35	27.56	26.78	27.95	28.37
4H	2H	20.07	21.51	20.47	21.85	22.23	24.83	26.27	25.23	26.61	26.99
	3H	21.09	22.29	21.50	22.68	23.08	26.74	27.94	27.14	28.33	28.73
	4H	21.41	22.49	21.84	22.90	23.34	27.01	28.09	27.44	28.51	28.94
	6H	21.59	22.54	22.04	22.98	23.43	27.20	28.15	27.66	28.59	29.04
	8H	21.63	22.52	22.09	22.96	23.42	27.25	28.13	27.71	28.57	29.04
	12H	21.66	22.46	22.14	22.93	23.40	27.26	28.06	27.74	28.53	29.00
8H	4H	22.65	23.53	23.10	23.97	24.43	27.20	28.08	27.66	28.52	28.99
	6H	22.92	23.66	23.42	24.14	24.62	27.44	28.17	27.93	28.66	29.13
	8H	23.01	23.66	23.51	24.17	24.65	27.51	28.17	28.02	28.67	29.16
	12H	23.07	23.65	23.58	24.14	24.70	27.54	28.12	28.05	28.61	29.17
12H	4H	22.70	23.50	23.18	23.97	24.44	27.19	27.98	27.67	28.46	28.93
	6H	23.03	23.68	23.53	24.19	24.67	27.43	28.09	27.94	28.59	29.08
	8H	23.17	23.75	23.68	24.24	24.80	27.54	28.12	28.05	28.61	29.17