

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P845533

Luminaire Tested: SQ2R-FB-100D-935-UNV-STD-W-4

Issue Date: 6/14/2024

Test Information

Test Method: LM-79-2019
Report Number: P845533
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 6/14/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2R-FB-100D-935-UNV-STD-W-4
Description: CONTINUA SQ2 RECESSED, BATWING LENS
1000 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3995.0 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 2.99 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9969
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P845533
CATALOG NUMBER: SQ2R-FB-100D-935-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P845533

CATALOG NUMBER: SQ2R-FB-100D-935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84				
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69				
3	89	78	70	63	87	77	69	63	74	67	62	71	65	60	68	64	59	57				
4	81	69	60	53	79	67	59	52	65	58	52	63	56	51	60	55	50	48				
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41				
6	68	54	45	39	66	53	45	38	52	44	38	50	43	38	48	42	37	35				
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31				
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27				
9	54	40	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24				
10	51	37	29	23	49	37	29	23	36	28	23	35	28	23	34	28	23	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6513	6513	6513
5°	6350	8802	11537
10°	5946	17044	22450
15°	5382	22176	25839
20°	4766	24395	27060
25°	4215	26088	27505
30°	3725	26867	27844
35°	3325	27334	29934
40°	3025	27594	31805
45°	2790	27725	33305
50°	2630	28256	33907
55°	2567	28991	34179
60°	2632	29376	34010
65°	2743	28974	33047
70°	2837	28018	24996
75°	3144	25165	13793
80°	3245	12980	12803
85°	3242	8985	5391

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 55°
 Luminance: 34179 cd/sqm



TEST NUMBER: P845533

CATALOG NUMBER: SQ2R-FB-100D-935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.4	1.7
10°-20°	309.7	7.8
20°-30°	545.1	13.6
30°-40°	705.0	17.6
40°-50°	777.6	19.5
50°-60°	725.3	18.2
60°-70°	561.3	14.1
70°-80°	256.6	6.4
80°-90°	48.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	921.2	23.1
0°-40°	1626.2	40.7
0°-60°	3129.2	78.3
0°-90°	3995.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3995.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	403	403	403	403	403	
5°	392	450	543	661	712	37
15°	322	642	1327	1484	1546	90
25°	237	867	1464	1528	1544	109
35°	169	838	1387	1433	1519	106
45°	122	642	1214	1393	1459	95
55°	91	382	1030	1183	1214	82
65°	72	215	758	850	865	70
75°	50	132	403	217	221	52
85°	18	39	48	33	29	19
90°	0	0	0	0	0	



TEST NUMBER: P845533

CATALOG NUMBER: SQ2R-FB-100D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	403.4	403.4	403.4	403.4	403.4
2.5°	399.6	420.9	444.2	471.3	483.0
5°	391.8	450.0	543.1	661.4	711.8
7.5°	380.2	486.8	727.3	1055.1	1167.6
10°	362.7	527.6	1039.6	1315.0	1369.3
12.5°	343.3	581.9	1235.5	1408.1	1464.4
15°	322.0	642.0	1326.7	1483.8	1545.8
17.5°	300.6	707.9	1379.0	1540.0	1576.9
20°	277.4	777.8	1419.8	1553.6	1574.9
22.5°	256.0	830.1	1448.9	1542.0	1565.2
25°	236.6	867.0	1464.4	1528.4	1543.9
27.5°	217.2	880.6	1458.6	1503.2	1516.7
30°	199.8	876.7	1441.1	1472.1	1493.5
32.5°	184.3	865.0	1415.9	1445.0	1497.3
35°	168.7	837.9	1386.8	1433.3	1518.7
37.5°	155.2	799.1	1349.9	1439.2	1524.5
40°	143.5	754.5	1309.2	1439.2	1509.0
42.5°	131.9	702.1	1262.7	1419.8	1489.6
45°	122.2	642.0	1214.2	1392.6	1458.6
47.5°	112.5	576.1	1169.6	1359.6	1410.1
50°	104.7	508.2	1124.9	1311.1	1349.9
52.5°	97.0	442.2	1080.3	1253.0	1287.9
55°	91.2	382.1	1029.9	1183.1	1214.2
57.5°	85.3	327.8	975.6	1109.4	1134.6
60°	81.5	285.1	909.7	1028.0	1053.2
62.5°	75.6	246.3	836.0	942.6	965.9
65°	71.8	215.3	758.4	849.5	865.0
67.5°	65.9	190.1	676.9	742.9	727.3
70°	60.1	172.6	593.5	612.9	529.5
72.5°	56.2	153.2	502.3	444.2	267.7
75°	50.4	131.9	403.4	217.2	221.1
77.5°	42.7	106.7	296.8	174.6	178.4
80°	34.9	83.4	139.6	135.8	137.7
82.5°	27.2	60.1	85.3	91.2	87.3
85°	17.5	38.8	48.5	33.0	29.1
87.5°	7.8	17.5	9.7	9.7	9.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P845533

CATALOG NUMBER: SQ2R-FB-100D-935-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.41	19.09	17.77	19.41	19.72	26.06	27.75	26.43	28.06	28.37
	3H	18.20	19.72	18.57	20.04	20.40	27.75	29.27	28.12	29.59	29.95
	4H	18.53	19.96	18.93	20.31	20.69	27.96	29.40	28.36	29.75	30.12
	6H	18.79	20.12	19.20	20.48	20.87	28.09	29.42	28.50	29.78	30.17
	8H	18.87	20.14	19.29	20.52	20.92	28.12	29.39	28.54	29.78	30.17
	12H	18.92	20.14	19.35	20.52	20.95	28.12	29.33	28.55	29.72	30.14
4H	2H	21.84	23.28	22.24	23.62	24.00	26.60	28.03	27.00	28.38	28.76
	3H	22.86	24.06	23.27	24.45	24.85	28.50	29.71	28.91	30.10	30.50
	4H	23.18	24.26	23.61	24.67	25.11	28.78	29.86	29.21	30.28	30.71
	6H	23.36	24.31	23.81	24.75	25.20	28.97	29.92	29.43	30.36	30.81
	8H	23.40	24.29	23.86	24.73	25.19	29.02	29.90	29.48	30.34	30.81
	12H	23.43	24.23	23.91	24.70	25.17	29.03	29.83	29.51	30.30	30.77
8H	4H	24.42	25.30	24.87	25.74	26.20	28.97	29.85	29.43	30.29	30.76
	6H	24.69	25.42	25.19	25.91	26.39	29.21	29.94	29.70	30.43	30.90
	8H	24.78	25.43	25.28	25.94	26.42	29.28	29.94	29.79	30.44	30.93
	12H	24.84	25.42	25.35	25.91	26.47	29.31	29.89	29.82	30.38	30.94
12H	4H	24.47	25.27	24.95	25.74	26.21	28.96	29.75	29.44	30.23	30.70
	6H	24.80	25.45	25.30	25.96	26.44	29.20	29.86	29.71	30.36	30.85
	8H	24.94	25.52	25.45	26.01	26.57	29.31	29.89	29.82	30.38	30.94