

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P845525

Luminaire Tested: SQ2R-FB-075D-840-UNV-STD-W-4

Issue Date: 6/14/2024

Test Information

Test Method: LM-79-2019
Report Number: P845525
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 6/14/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2R-FB-075D-840-UNV-STD-W-4
Description: CONTINUA SQ2 RECESSED, BATWING LENS
750 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3462.8 lumens
Efficiency: N/A
Efficacy: 129.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 2.99 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 26.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P845525
CATALOG NUMBER: SQ2R-FB-075D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P845525

CATALOG NUMBER: SQ2R-FB-075D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84				84
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69				69
3	89	78	70	63	87	77	69	63	74	67	62	71	65	60	68	64	59	57				57
4	81	69	60	53	79	67	59	52	65	58	52	63	56	51	60	55	50	48				48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41				41
6	68	54	45	39	66	53	45	38	52	44	38	50	43	38	48	42	37	35				35
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31				31
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27				27
9	54	40	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24				24
10	51	37	29	23	49	37	29	23	36	28	23	35	28	23	34	28	23	21				21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5646	5646	5646
5°	5504	7629	10000
10°	5155	14773	19459
15°	4665	19221	22397
20°	4131	21144	23455
25°	3654	22613	23840
30°	3229	23288	24134
35°	2884	23692	25947
40°	2622	23918	27569
45°	2418	24030	28866
50°	2281	24493	29391
55°	2224	25129	29624
60°	2280	25462	29479
65°	2376	25112	28646
70°	2459	24283	21668
75°	2726	21815	11959
80°	2817	11251	11102
85°	2797	7781	4668

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 55°
 Luminance: 29624 cd/sqm

TEST NUMBER: P845525

CATALOG NUMBER: SQ2R-FB-075D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.6	1.7
10°-20°	268.4	7.8
20°-30°	472.5	13.6
30°-40°	611.1	17.6
40°-50°	674.0	19.5
50°-60°	628.7	18.2
60°-70°	486.5	14.1
70°-80°	222.4	6.4
80°-90°	41.6	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	798.5	23.1
0°-40°	1409.6	40.7
0°-60°	2712.3	78.3
0°-90°	3462.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3462.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	350	350	350	350	350	
5°	340	390	471	573	617	32
15°	279	556	1150	1286	1340	78
25°	205	752	1269	1325	1338	94
35°	146	726	1202	1242	1316	92
45°	106	556	1052	1207	1264	82
55°	79	331	893	1026	1052	71
65°	62	187	657	736	750	61
75°	44	114	350	188	192	45
85°	15	34	42	29	25	16
90°	0	0	0	0	0	



TEST NUMBER: P845525

CATALOG NUMBER: SQ2R-FB-075D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	349.7	349.7	349.7	349.7	349.7
2.5°	346.3	364.8	385.0	408.5	418.6
5°	339.6	390.0	470.7	573.3	617.0
7.5°	329.5	422.0	630.4	914.6	1012.1
10°	314.4	457.3	901.1	1139.8	1186.9
12.5°	297.6	504.4	1070.9	1220.5	1269.3
15°	279.1	556.5	1149.9	1286.1	1339.9
17.5°	260.6	613.6	1195.3	1334.9	1366.8
20°	240.4	674.2	1230.6	1346.6	1365.1
22.5°	221.9	719.5	1255.8	1336.5	1356.7
25°	205.1	751.5	1269.3	1324.8	1338.2
27.5°	188.3	763.3	1264.2	1302.9	1314.7
30°	173.2	759.9	1249.1	1276.0	1294.5
32.5°	159.7	749.8	1227.3	1252.5	1297.9
35°	146.3	726.3	1202.0	1242.4	1316.4
37.5°	134.5	692.6	1170.1	1247.4	1321.4
40°	124.4	654.0	1134.8	1247.4	1308.0
42.5°	114.3	608.6	1094.5	1230.6	1291.1
45°	105.9	556.5	1052.4	1207.1	1264.2
47.5°	97.5	499.3	1013.8	1178.5	1222.2
50°	90.8	440.5	975.1	1136.5	1170.1
52.5°	84.1	383.3	936.4	1086.0	1116.3
55°	79.0	331.2	892.7	1025.5	1052.4
57.5°	74.0	284.1	845.6	961.6	983.5
60°	70.6	247.1	788.5	891.0	912.9
62.5°	65.6	213.5	724.6	817.1	837.2
65°	62.2	186.6	657.3	736.4	749.8
67.5°	57.2	164.8	586.7	643.9	630.4
70°	52.1	149.6	514.4	531.3	459.0
72.5°	48.8	132.8	435.4	385.0	232.0
75°	43.7	114.3	349.7	188.3	191.7
77.5°	37.0	92.5	257.2	151.3	154.7
80°	30.3	72.3	121.0	117.7	119.4
82.5°	23.5	52.1	74.0	79.0	75.7
85°	15.1	33.6	42.0	28.6	25.2
87.5°	6.7	15.1	8.4	8.4	8.4
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P845525

CATALOG NUMBER: SQ2R-FB-075D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.91	18.59	17.27	18.91	19.22	25.56	27.25	25.93	27.56	27.88
	3H	17.70	19.22	18.07	19.55	19.91	27.25	28.77	27.63	29.10	29.46
	4H	18.03	19.47	18.43	19.81	20.19	27.47	28.90	27.86	29.25	29.62
	6H	18.29	19.62	18.70	19.98	20.37	27.59	28.92	28.00	29.29	29.68
	8H	18.37	19.64	18.79	20.03	20.43	27.62	28.89	28.05	29.28	29.68
	12H	18.42	19.64	18.85	20.02	20.45	27.62	28.84	28.05	29.22	29.65
4H	2H	21.35	22.78	21.74	23.13	23.50	26.10	27.54	26.50	27.88	28.26
	3H	22.36	23.56	22.77	23.96	24.36	28.01	29.21	28.42	29.61	30.00
	4H	22.68	23.76	23.11	24.18	24.61	28.28	29.37	28.71	29.78	30.21
	6H	22.86	23.81	23.32	24.25	24.70	28.48	29.42	28.93	29.86	30.32
	8H	22.91	23.79	23.36	24.23	24.70	28.52	29.41	28.98	29.85	30.31
	12H	22.94	23.73	23.42	24.21	24.67	28.54	29.33	29.01	29.80	30.27
8H	4H	23.92	24.80	24.38	25.24	25.71	28.47	29.35	28.93	29.80	30.26
	6H	24.20	24.93	24.69	25.42	25.89	28.71	29.45	29.21	29.93	30.41
	8H	24.28	24.93	24.79	25.44	25.92	28.79	29.44	29.29	29.95	30.43
	12H	24.35	24.92	24.85	25.41	25.97	28.82	29.40	29.32	29.89	30.45
12H	4H	23.98	24.77	24.45	25.24	25.71	28.46	29.26	28.94	29.73	30.20
	6H	24.30	24.96	24.81	25.46	25.95	28.71	29.36	29.21	29.87	30.35
	8H	24.45	25.02	24.95	25.51	26.07	28.81	29.39	29.32	29.88	30.44