

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P845635

Luminaire Tested: SQ2R-PR1-125D-935-UNV-STD-W-4

Issue Date: 6/14/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P845635  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/14/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2R-PR1-125D-935-UNV-STD-W-4  
Description: CORELITE SQ2R RECESSED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS  
1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5700.0 lumens  
Efficiency: N/A  
Efficacy: 115.9 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.33 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 49.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9979  
Total Harmonic Distortion (THDi): 0.0523  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P845635  
CATALOG NUMBER: SQ2R-PR1-125D-935-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P845635

CATALOG NUMBER: SQ2R-PR1-125D-935-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	110	106	102	99	108	104	101	97	100	97	94	96	94	92	92	91	89	87			87	
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	80	77	75			75	
3	93	84	77	71	91	82	76	70	80	74	69	77	72	68	74	70	67	65			65	
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	62	58	56			56	
5	80	68	60	53	78	67	59	53	65	58	53	63	57	52	61	56	52	50			50	
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			44	
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			39	
8	64	51	43	38	63	51	43	38	49	42	38	48	42	37	47	41	37	35			35	
9	60	47	40	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			32	
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			29	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	38253	38253	38253
5°	38203	38438	38908
10°	38605	39595	40189
15°	38593	38795	39117
20°	37969	38550	39837
25°	37860	38936	41475
30°	37820	39802	41874
35°	37462	40653	38985
40°	36598	39144	34307
45°	34632	34356	27131
50°	31483	28087	21049
55°	27668	23113	16383
60°	23941	18484	13491
65°	20669	15316	11809
70°	18586	13567	10489
75°	17024	11753	9644
80°	14821	9428	9428
85°	10745	8503	4483

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 37497 cd/sqm



TEST NUMBER: P845635

CATALOG NUMBER: SQ2R-PR1-125D-935-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	228.8	4.0
10°-20°	662.6	11.6
20°-30°	1024.6	18.0
30°-40°	1233.7	21.6
40°-50°	1107.5	19.4
50°-60°	739.4	13.0
60°-70°	429.5	7.5
70°-80°	220.8	3.9
80°-90°	53.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1915.9	33.6
0°-40°	3149.6	55.3
0°-60°	4996.5	87.7
0°-90°	5700.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5700.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2369	2369	2369	2369	2369	
5°	2357	2398	2372	2376	2401	225
15°	2309	2405	2321	2328	2340	649
25°	2125	2212	2186	2265	2328	981
35°	1901	1918	2062	2024	1978	1186
45°	1517	1642	1505	1270	1188	1161
55°	983	1022	821	635	582	883
65°	541	553	401	326	309	546
75°	273	266	188	159	155	289
85°	58	46	46	31	24	72
90°	0	0	0	0	0	



TEST NUMBER: P845635

CATALOG NUMBER: SQ2R-PR1-125D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2369.2	2369.2	2369.2	2369.2	2369.2
2.5°	2357.1	2393.3	2359.5	2361.9	2369.2
5°	2357.1	2398.2	2371.6	2376.4	2400.6
7.5°	2357.1	2412.6	2398.2	2415.1	2446.5
10°	2354.7	2424.7	2415.1	2417.5	2451.3
12.5°	2340.2	2424.7	2378.8	2374.0	2388.5
15°	2308.8	2405.4	2320.9	2328.1	2340.2
17.5°	2258.1	2359.5	2275.0	2299.1	2318.5
20°	2209.8	2308.8	2243.6	2277.4	2318.5
22.5°	2166.3	2265.3	2214.6	2265.3	2325.7
25°	2125.2	2212.2	2185.6	2265.3	2328.1
27.5°	2084.2	2139.7	2156.6	2267.7	2318.5
30°	2028.6	2062.5	2134.9	2229.1	2246.0
32.5°	1968.3	1985.2	2105.9	2144.6	2113.2
35°	1900.6	1917.6	2062.5	2023.8	1977.9
37.5°	1823.4	1852.3	1975.5	1876.5	1825.8
40°	1736.4	1794.4	1857.2	1688.1	1627.7
42.5°	1630.2	1731.6	1700.2	1473.2	1395.9
45°	1516.7	1642.2	1504.6	1270.3	1188.2
47.5°	1383.8	1519.1	1299.3	1086.8	1011.9
50°	1253.4	1357.3	1118.2	922.6	838.0
52.5°	1120.6	1188.2	963.6	768.0	693.1
55°	982.9	1021.6	821.1	635.2	582.0
57.5°	854.9	881.5	695.5	528.9	487.8
60°	741.4	758.3	572.4	449.2	417.8
62.5°	637.6	649.7	473.4	381.6	359.8
65°	541.0	553.0	400.9	326.0	309.1
67.5°	461.3	468.5	340.5	280.1	263.2
70°	393.7	396.1	287.4	234.3	222.2
72.5°	333.3	328.4	236.7	195.6	188.4
75°	272.9	265.7	188.4	159.4	154.6
77.5°	214.9	207.7	140.1	128.0	128.0
80°	159.4	149.7	101.4	101.4	101.4
82.5°	108.7	94.2	72.5	72.5	70.0
85°	58.0	45.9	45.9	31.4	24.2
87.5°	19.3	19.3	7.2	7.2	7.2
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P845635

CATALOG NUMBER: SQ2R-PR1-125D-935-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	23.37	24.86	23.73	25.18	25.49	20.10	21.59	20.46	21.91	22.22
	3H	24.65	25.98	25.03	26.31	26.67	21.21	22.55	21.59	22.87	23.24
	4H	25.13	26.38	25.53	26.73	27.11	21.64	22.89	22.04	23.24	23.62
	6H	25.47	26.63	25.89	27.00	27.39	22.00	23.15	22.41	23.52	23.91
	8H	25.57	26.67	26.00	27.06	27.46	22.10	23.20	22.53	23.59	23.99
	12H	25.62	26.67	26.05	27.05	27.48	22.13	23.18	22.56	23.56	23.99
4H	2H	23.52	24.77	23.92	25.12	25.50	20.74	21.99	21.14	22.34	22.72
	3H	25.05	26.08	25.46	26.48	26.88	22.06	23.09	22.47	23.50	23.90
	4H	25.67	26.59	26.10	27.01	27.45	22.59	23.52	23.02	23.93	24.37
	6H	26.15	26.95	26.61	27.40	27.86	23.06	23.86	23.52	24.31	24.77
	8H	26.29	27.04	26.76	27.49	27.96	23.19	23.94	23.65	24.39	24.86
	12H	26.37	27.04	26.86	27.52	27.99	23.24	23.91	23.72	24.39	24.86
8H	4H	25.73	26.49	26.20	26.93	27.40	22.94	23.69	23.40	24.14	24.60
	6H	26.30	26.92	26.80	27.42	27.89	23.49	24.11	23.99	24.61	25.08
	8H	26.50	27.06	27.01	27.57	28.06	23.68	24.24	24.19	24.75	25.24
	12H	26.63	27.12	27.14	27.62	28.18	23.77	24.26	24.28	24.75	25.32
12H	4H	25.72	26.39	26.20	26.87	27.34	22.98	23.65	23.46	24.13	24.60
	6H	26.29	26.85	26.80	27.36	27.85	23.55	24.11	24.07	24.62	25.11
	8H	26.52	27.02	27.04	27.51	28.08	23.78	24.28	24.30	24.77	25.34