

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P845501

Luminaire Tested: SQ2R-FA-075D-840-UNV-STD-W-4

Issue Date: 6/14/2024

Test Information

Test Method: LM-79-2019
Report Number: P845501
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-11)
Test Lab: INNOVATION CENTER
Issue Date: 6/14/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2R-FA-075D-840-UNV-STD-W-4
Description: CONTINUA SQ2 RECESSED, ASYMMETRIC LENS
750 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3252.3 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 0.95 / 0.93
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 26.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P845501
CATALOG NUMBER: SQ2R-FA-075D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P845501

CATALOG NUMBER: SQ2R-FA-075D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88				88
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78				78
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70				70
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63				63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57				57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52				52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48				48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	55	49	46	44				44
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41				41
10	63	51	44	40	61	51	44	40	50	44	40	49	43	39	48	43	39	38				38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	35992	35992	35992	35992
5°	35804	35858	35668	35832
10°	35749	35611	35611	35611
15°	35632	35268	35351	35268
20°	35357	33854	35096	34172
25°	34892	28572	34652	29172
30°	34571	16393	34196	16611
35°	33965	14083	33535	13884
40°	33025	7406	32104	7335
45°	30019	3185	28944	3185
50°	19806	3843	18791	3589
55°	11074	7099	10505	6435
60°	5971	9988	5864	8958
65°	5268	12138	5524	13811
70°	4919	14526	4683	15319
75°	4616	12483	4722	12901
80°	3905	8908	3905	9382
85°	3427	4983	3112	5910

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30019 cd/sqm



TEST NUMBER: P845501

CATALOG NUMBER: SQ2R-FA-075D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.9	6.5
10°-20°	595.8	18.3
20°-30°	814.9	25.1
30°-40°	682.5	21.0
40°-50°	382.5	11.8
50°-60°	202.9	6.2
60°-70°	189.2	5.8
70°-80°	139.1	4.3
80°-90°	35.6	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1620.6	49.8
0°-40°	2303.1	70.8
0°-60°	2888.5	88.8
0°-90°	3252.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3252.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2229	2229	2229	2229	2229	
5°	2209	2212	2201	2211	2209	210
15°	2132	2110	2115	2110	2132	601
25°	1959	1604	1945	1638	1959	904
35°	1723	714	1701	704	1723	1077
45°	1315	140	1268	140	1315	970
55°	393	252	373	229	393	372
65°	138	318	145	362	138	138
75°	74	200	76	207	74	76
85°	18	27	17	32	18	21
90°	0	0	0	0	0	



TEST NUMBER: P845501

CATALOG NUMBER: SQ2R-FA-075D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	2229.2	2229.2	2229.2	2229.2	2229.2	2229.2	2229.2	2229.2	2229.2	2229.2	2229.2
2.5°	2214.1	2256.1	2219.2	2214.1	2229.2	2225.9	2220.8	2241.0	2207.4	2241.0	2214.1
5°	2209.1	2247.7	2204.0	2192.3	2212.4	2199.0	2210.8	2234.3	2200.7	2230.9	2197.3
7.5°	2199.0	2234.3	2182.2	2173.8	2193.9	2182.2	2187.2	2219.2	2190.6	2210.8	2180.5
10°	2180.5	2210.8	2158.6	2153.6	2172.1	2160.3	2165.4	2199.0	2172.1	2190.6	2160.3
12.5°	2160.3	2182.2	2130.1	2128.4	2143.5	2136.8	2138.5	2165.4	2145.2	2163.7	2135.1
15°	2131.7	2153.6	2101.5	2093.1	2109.9	2103.2	2106.5	2131.7	2114.9	2126.7	2101.5
17.5°	2099.8	2116.6	2066.2	2047.7	2049.4	2057.8	2066.2	2096.4	2079.6	2094.8	2062.8
20°	2057.8	2077.9	2020.8	1973.7	1970.3	1978.8	2020.8	2051.0	2042.6	2059.4	2009.0
22.5°	2009.0	2020.8	1970.3	1882.9	1869.5	1877.9	1963.6	2000.6	1998.9	2009.0	1943.4
25°	1958.6	1972.0	1877.9	1766.9	1603.8	1756.8	1881.2	1945.1	1945.1	1955.2	1872.8
27.5°	1908.1	1911.5	1777.0	1190.3	1028.9	1141.5	1773.6	1877.9	1891.3	1889.6	1768.6
30°	1854.3	1842.6	1531.6	916.2	879.3	902.8	1533.2	1807.3	1834.2	1815.7	1492.9
32.5°	1792.1	1753.5	1030.6	823.8	795.2	815.4	983.5	1723.2	1775.3	1729.9	1094.4
35°	1723.2	1635.8	862.4	744.8	714.5	741.4	855.7	1607.2	1701.4	1593.8	891.0
37.5°	1652.6	1365.1	778.4	633.8	573.3	623.7	775.0	1360.1	1619.0	1302.9	781.7
40°	1566.9	1010.4	682.6	435.4	351.4	410.2	677.5	963.3	1523.2	1039.0	665.7
42.5°	1452.5	854.0	514.4	237.0	181.6	213.5	487.5	840.6	1405.5	862.4	495.9
45°	1314.7	759.9	324.5	151.3	139.5	146.3	299.3	746.4	1267.6	729.6	331.2
47.5°	1104.5	610.3	220.2	127.8	137.9	127.8	213.5	591.8	1042.3	580.0	220.2
50°	788.5	452.2	161.4	129.5	153.0	129.5	156.3	437.1	748.1	479.1	159.7
52.5°	532.9	361.5	124.4	144.6	191.7	147.9	121.0	353.0	506.0	364.8	116.0
55°	393.4	299.3	105.9	186.6	252.2	191.7	105.9	290.8	373.2	287.5	102.6
57.5°	265.6	235.4	104.2	237.0	282.4	242.1	105.9	227.0	253.9	228.6	92.5
60°	184.9	176.5	119.4	255.5	309.3	258.9	121.0	169.8	181.6	168.1	100.9
62.5°	144.6	129.5	149.6	282.4	324.5	272.4	153.0	122.7	153.0	116.0	114.3
65°	137.9	89.1	169.8	280.8	317.7	280.8	171.5	84.1	144.6	90.8	151.3
67.5°	129.5	67.2	166.4	277.4	322.8	280.8	161.4	63.9	124.4	62.2	147.9
70°	104.2	58.8	154.7	284.1	307.7	274.0	154.7	57.2	99.2	55.5	181.6
72.5°	82.4	55.5	141.2	257.2	263.9	247.1	142.9	55.5	84.1	48.8	168.1
75°	74.0	55.5	137.9	210.1	200.1	200.1	134.5	53.8	75.7	50.4	132.8
77.5°	58.8	50.4	119.4	146.3	137.9	137.9	117.7	48.8	55.5	45.4	112.6
80°	42.0	45.4	94.1	100.9	95.8	95.8	90.8	43.7	42.0	42.0	89.1
82.5°	30.3	37.0	67.2	67.2	63.9	62.2	65.6	37.0	30.3	33.6	63.9
85°	18.5	26.9	38.7	31.9	26.9	25.2	37.0	25.2	16.8	25.2	37.0
87.5°	8.4	15.1	6.7	6.7	6.7	6.7	6.7	15.1	8.4	13.4	8.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P845501

CATALOG NUMBER: SQ2R-FA-075D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	2229.2	2229.2	2229.2	2229.2	2229.2	2229.2
2.5°	2207.4	2219.2	2219.2	2212.4	2246.1	2214.1
5°	2188.9	2210.8	2200.7	2200.7	2234.3	2209.1
7.5°	2177.1	2199.0	2188.9	2185.5	2219.2	2199.0
10°	2157.0	2172.1	2165.4	2170.4	2200.7	2180.5
12.5°	2128.4	2146.9	2140.1	2148.6	2175.5	2160.3
15°	2094.8	2109.9	2113.2	2116.6	2148.6	2131.7
17.5°	2042.6	2049.4	2067.9	2086.3	2118.3	2099.8
20°	1978.8	1988.8	1998.9	2039.3	2077.9	2057.8
22.5°	1906.5	1899.7	1926.6	1975.4	2025.8	2009.0
25°	1766.9	1637.5	1780.4	1899.7	1963.6	1958.6
27.5°	1297.9	1109.6	1274.3	1800.5	1901.4	1908.1
30°	968.4	891.0	966.7	1565.2	1830.8	1854.3
32.5°	832.2	785.1	823.8	1097.8	1741.7	1792.1
35°	741.4	704.4	741.4	891.0	1619.0	1723.2
37.5°	632.1	561.5	633.8	790.2	1370.2	1652.6
40°	443.8	348.0	430.4	689.3	1035.6	1566.9
42.5°	258.9	193.3	242.1	506.0	857.4	1452.5
45°	159.7	139.5	153.0	327.8	726.3	1314.7
47.5°	126.1	129.5	126.1	218.6	578.3	1104.5
50°	119.4	142.9	119.4	159.7	460.6	788.5
52.5°	132.8	158.0	131.1	117.7	356.4	532.9
55°	146.3	228.6	147.9	102.6	277.4	393.4
57.5°	208.5	252.2	211.8	95.8	227.0	265.6
60°	215.2	277.4	213.5	102.6	166.4	184.9
62.5°	263.9	359.8	263.9	121.0	112.6	144.6
65°	327.8	361.5	331.2	149.6	87.4	137.9
67.5°	312.7	337.9	309.3	154.7	60.5	129.5
70°	306.0	324.5	302.6	183.2	55.5	104.2
72.5°	280.8	279.1	274.0	166.4	48.8	82.4
75°	221.9	206.8	213.5	146.3	50.4	74.0
77.5°	146.3	139.5	141.2	116.0	45.4	58.8
80°	104.2	100.9	99.2	94.1	42.0	42.0
82.5°	70.6	67.2	65.6	67.2	33.6	30.3
85°	35.3	31.9	30.3	42.0	25.2	18.5
87.5°	8.4	8.4	6.7	8.4	11.8	8.4
90°	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P845501

CATALOG NUMBER: SQ2R-FA-075D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.43	17.74	16.80	18.05	18.37	15.28	16.58	15.64	16.90	17.21
	3H	17.15	18.32	17.53	18.65	19.02	21.48	22.65	21.86	22.98	23.34
	4H	17.58	18.68	17.98	19.03	19.41	22.78	23.87	23.18	24.22	24.60
	6H	17.96	18.97	18.37	19.34	19.73	23.40	24.41	23.82	24.78	25.18
	8H	18.09	19.04	18.52	19.43	19.84	23.54	24.49	23.97	24.89	25.29
	12H	18.17	19.09	18.60	19.47	19.90	23.59	24.51	24.02	24.89	25.32
4H	2H	16.87	17.97	17.27	18.32	18.70	15.86	16.95	16.26	17.30	17.69
	3H	17.89	18.80	18.30	19.20	19.61	22.23	23.14	22.64	23.54	23.95
	4H	18.46	19.28	18.90	19.70	20.14	23.69	24.51	24.13	24.93	25.38
	6H	18.96	19.67	19.42	20.12	20.58	24.45	25.16	24.91	25.61	26.07
	8H	19.14	19.80	19.61	20.25	20.72	24.62	25.29	25.09	25.74	26.21
	12H	19.27	19.86	19.76	20.34	20.82	24.71	25.29	25.19	25.78	26.25
8H	4H	19.59	20.26	20.06	20.70	21.17	23.84	24.51	24.31	24.95	25.42
	6H	20.22	20.76	20.72	21.26	21.74	24.74	25.28	25.24	25.77	26.25
	8H	20.45	20.94	20.97	21.45	21.94	24.98	25.47	25.50	25.98	26.47
	12H	20.65	21.07	21.16	21.57	22.14	25.13	25.55	25.64	26.05	26.62
12H	4H	19.76	20.35	20.25	20.83	21.30	23.82	24.41	24.31	24.89	25.37
	6H	20.49	20.98	21.01	21.49	21.98	24.74	25.23	25.26	25.74	26.23
	8H	20.81	21.24	21.33	21.73	22.30	25.04	25.47	25.56	25.96	26.54