

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855520

Luminaire Tested: SQ2-PH1-100D-830-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P855520  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PH1-100D-830-UNV-STD-W-4  
Description: CORELITE SQ2 SURFACE LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5097.9 lumens  
Efficiency: N/A  
Efficacy: 135.6 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P855520  
CATALOG NUMBER: SQ2-PH1-100D-830-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P855520

CATALOG NUMBER: SQ2-PH1-100D-830-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	91	81	73	67	89	80	72	67	77	71	65	74	69	64	72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	55	64	59	55	53
5	77	65	56	50	75	64	55	49	62	54	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	48	43	54	48	43	53	47	42	40
7	66	53	45	39	65	52	44	38	51	43	38	49	43	38	48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28	39	32	28	38	32	28	26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	37213	37213	37213
5°	37426	35188	34015
10°	36564	32036	30919
15°	36729	30131	30315
20°	35419	29203	30558
25°	34769	29065	29847
30°	34015	28989	30091
35°	33758	28657	35272
40°	33786	28473	27963
45°	33798	27389	24085
50°	33325	27929	22584
55°	32904	30308	21667
60°	32576	26553	20324
65°	32004	21532	17677
70°	30232	18321	12628
75°	26949	13818	9576
80°	22027	8963	8963
85°	13801	8133	6095

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 33798 cd/sqm



TEST NUMBER: P855520

CATALOG NUMBER: SQ2-PH1-100D-830-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	202.8	4.0
10°-20°	533.4	10.5
20°-30°	782.2	15.3
30°-40°	947.2	18.6
40°-50°	931.5	18.3
50°-60°	810.9	15.9
60°-70°	563.7	11.1
70°-80°	267.3	5.2
80°-90°	58.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1518.4	29.8
0°-40°	2465.7	48.4
0°-60°	4208.0	82.5
0°-90°	5097.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5097.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2305	2305	2305	2305	2305	
5°	2309	2307	2171	2103	2099	217
15°	2197	1957	1803	1790	1814	613
25°	1952	1660	1632	1682	1675	898
35°	1713	1385	1454	1579	1790	1073
45°	1480	1096	1200	1241	1055	1138
55°	1169	854	1077	776	770	1044
65°	838	587	564	463	463	823
75°	432	299	222	158	154	458
85°	74	49	44	35	33	102
90°	0	0	0	0	0	



TEST NUMBER: P855520

CATALOG NUMBER: SQ2-PH1-100D-830-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2304.8	2304.8	2304.8	2304.8	2304.8
2.5°	2299.5	2323.6	2269.7	2248.6	2245.1
5°	2309.2	2307.1	2171.1	2103.0	2098.7
7.5°	2267.1	2200.6	2038.1	1963.0	1959.6
10°	2230.2	2129.5	1954.0	1885.9	1885.9
12.5°	2221.5	2062.4	1885.5	1835.3	1845.5
15°	2197.3	1957.1	1802.6	1790.0	1813.6
17.5°	2117.5	1858.9	1738.1	1766.9	1794.3
20°	2061.4	1806.2	1699.6	1752.7	1778.5
22.5°	2014.0	1755.4	1671.4	1729.7	1743.5
25°	1951.7	1660.1	1631.5	1681.8	1675.4
27.5°	1877.2	1572.7	1591.6	1622.5	1626.3
30°	1824.5	1520.0	1554.9	1586.2	1614.0
32.5°	1773.6	1458.9	1514.5	1588.7	1652.7
35°	1712.7	1384.6	1453.9	1579.3	1789.5
37.5°	1648.7	1297.0	1393.0	1498.4	1565.4
40°	1603.0	1234.2	1350.9	1481.1	1326.7
42.5°	1554.0	1185.1	1287.7	1455.9	1195.2
45°	1480.2	1096.4	1199.5	1241.3	1054.8
47.5°	1393.4	1027.6	1139.9	1035.2	962.3
50°	1326.7	981.5	1111.9	946.2	899.1
52.5°	1261.8	933.8	1092.5	873.0	841.2
55°	1168.9	853.6	1076.7	776.2	769.7
57.5°	1070.2	772.1	952.2	692.0	703.0
60°	1008.8	719.3	822.3	642.2	629.4
62.5°	943.9	668.1	701.3	579.1	566.2
65°	837.7	586.8	563.6	462.7	462.7
67.5°	721.0	502.3	456.6	378.7	327.2
70°	640.4	447.4	388.1	301.9	267.5
72.5°	554.4	388.8	317.9	247.4	207.9
75°	432.0	299.1	221.5	157.8	153.5
77.5°	312.3	215.4	149.1	117.1	117.6
80°	236.9	163.9	96.4	94.3	96.4
82.5°	166.7	112.6	71.9	75.0	75.4
85°	74.5	48.8	43.9	35.0	32.9
87.5°	15.8	14.0	8.8	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P855520

CATALOG NUMBER: SQ2-PH1-100D-830-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	23.73	25.33	24.10	25.64	25.95	22.41	24.00	22.77	24.31	24.63
	3H	25.81	27.24	26.19	27.57	27.93	23.49	24.92	23.87	25.25	25.61
	4H	26.58	27.92	26.97	28.27	28.65	23.74	25.08	24.14	25.43	25.81
	6H	27.10	28.34	27.51	28.71	29.10	23.92	25.16	24.33	25.53	25.92
	8H	27.24	28.43	27.67	28.82	29.22	23.97	25.16	24.40	25.55	25.95
	12H	27.31	28.44	27.74	28.83	29.26	23.99	25.13	24.42	25.51	25.94
4H	2H	24.19	25.54	24.59	25.89	26.26	23.13	24.48	23.53	24.83	25.20
	3H	26.37	27.48	26.78	27.88	28.28	24.38	25.50	24.79	25.90	26.30
	4H	27.21	28.22	27.64	28.63	29.07	24.68	25.69	25.11	26.11	26.54
	6H	27.83	28.71	28.29	29.15	29.61	24.93	25.81	25.39	26.25	26.71
	8H	28.02	28.84	28.48	29.28	29.75	25.00	25.82	25.46	26.27	26.73
	12H	28.12	28.86	28.60	29.33	29.80	25.04	25.78	25.53	26.26	26.73
8H	4H	27.28	28.10	27.74	28.55	29.01	24.95	25.77	25.42	26.22	26.68
	6H	27.96	28.64	28.46	29.13	29.61	25.26	25.93	25.75	26.42	26.90
	8H	28.20	28.80	28.71	29.31	29.80	25.36	25.97	25.88	26.48	26.97
	12H	28.34	28.88	28.85	29.37	29.93	25.44	25.98	25.95	26.47	27.03
12H	4H	27.27	28.00	27.75	28.48	28.95	24.98	25.72	25.47	26.20	26.67
	6H	27.94	28.55	28.45	29.06	29.55	25.29	25.90	25.80	26.41	26.89
	8H	28.21	28.75	28.72	29.24	29.80	25.44	25.98	25.95	26.47	27.03