

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855546

Luminaire Tested: SQ2-FB-075D-830-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855546
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FB-075D-830-UNV-STD-W-4
Description: CORELITE SQ2 SURFACE LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3352.4 lumens
Efficiency: N/A
Efficacy: 125.6 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 26.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855546
CATALOG NUMBER: SQ2-FB-075D-830-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855546

CATALOG NUMBER: SQ2-FB-075D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84				84
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69				69
3	89	78	70	63	87	77	69	63	74	67	61	71	65	60	68	63	59	57				57
4	81	69	60	53	79	67	59	52	65	57	52	63	56	51	60	55	50	48				48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	43	54	48	43	41				41
6	68	54	45	39	66	53	45	38	52	44	38	50	43	38	48	42	37	35				35
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31				31
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27				27
9	54	40	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24				24
10	51	37	29	23	49	37	29	23	36	28	23	35	28	23	34	28	23	21				21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5478	5478	5478
5°	5340	7402	9702
10°	5000	14332	18880
15°	4527	18648	21728
20°	4009	20515	22756
25°	3545	21937	23129
30°	3132	22592	23415
35°	2797	22984	25172
40°	2546	23204	26744
45°	2347	23315	28005
50°	2213	23762	28514
55°	2159	24380	28743
60°	2212	24703	28598
65°	2308	24363	27794
70°	2384	23561	21017
75°	2645	21166	11603
80°	2734	10925	10767
85°	2723	7558	4520

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 29000 cd/sqm



TEST NUMBER: P855546

CATALOG NUMBER: SQ2-FB-075D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	1.7
10°-20°	259.5	7.7
20°-30°	456.5	13.6
30°-40°	590.9	17.6
40°-50°	651.7	19.4
50°-60°	608.5	18.2
60°-70°	470.3	14.0
70°-80°	216.9	6.5
80°-90°	41.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	772.8	23.1
0°-40°	1363.6	40.7
0°-60°	2623.8	78.3
0°-90°	3352.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3352.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	339	339	339	339	339	
5°	330	377	457	557	599	31
15°	271	534	1116	1249	1300	75
25°	199	717	1231	1286	1298	91
35°	142	692	1166	1207	1277	89
45°	103	530	1021	1172	1226	80
55°	77	316	866	996	1021	69
65°	60	178	638	715	728	59
75°	42	109	339	183	186	44
85°	15	32	41	28	24	16
90°	0	0	0	0	0	



TEST NUMBER: P855546

CATALOG NUMBER: SQ2-FB-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	339.3	339.3	339.3	339.3	339.3
2.5°	336.6	350.7	366.7	385.1	392.8
5°	329.5	377.3	456.7	557.2	598.6
7.5°	316.7	414.0	664.1	932.9	1015.8
10°	305.0	440.6	874.2	1106.9	1151.6
12.5°	291.9	476.0	1006.0	1169.5	1215.4
15°	270.8	533.9	1115.6	1248.9	1299.9
17.5°	248.9	599.1	1166.5	1298.0	1325.7
20°	233.3	644.7	1194.0	1306.9	1324.4
22.5°	218.9	678.8	1213.5	1299.1	1317.9
25°	199.0	717.3	1231.4	1285.5	1298.3
27.5°	179.8	727.3	1223.6	1259.1	1271.5
30°	168.0	724.6	1211.8	1238.4	1255.9
32.5°	157.6	716.7	1194.9	1220.5	1258.5
35°	141.9	692.1	1166.1	1207.0	1277.1
37.5°	128.6	652.6	1128.4	1211.8	1279.4
40°	120.8	623.1	1100.9	1211.5	1268.9
42.5°	112.8	588.4	1069.6	1198.5	1255.9
45°	102.8	530.2	1021.1	1172.4	1226.5
47.5°	93.3	464.6	976.0	1136.1	1175.6
50°	88.1	419.8	946.0	1103.3	1135.2
52.5°	82.9	376.3	916.0	1064.2	1093.4
55°	76.7	315.9	866.1	995.5	1021.1
57.5°	71.1	264.1	809.3	919.8	940.5
60°	68.5	236.0	765.0	864.9	885.6
62.5°	64.6	210.3	715.4	807.5	827.0
65°	60.4	178.4	637.7	714.7	727.5
67.5°	54.5	154.7	555.3	602.3	578.3
70°	50.5	143.0	499.1	513.9	445.2
72.5°	47.9	130.3	437.8	398.9	269.1
75°	42.4	109.3	339.3	182.7	186.0
77.5°	34.6	84.7	223.1	140.3	143.3
80°	29.4	69.2	117.5	114.2	115.8
82.5°	24.2	53.8	81.0	84.1	81.9
85°	14.7	32.2	40.8	27.7	24.4
87.5°	5.2	11.6	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P855546

CATALOG NUMBER: SQ2-FB-075D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.73	18.42	17.10	18.73	19.05	25.47	27.15	25.83	27.47	27.78
	3H	17.52	19.04	17.90	19.37	19.73	27.15	28.67	27.53	29.00	29.36
	4H	17.86	19.29	18.25	19.64	20.01	27.37	28.80	27.76	29.15	29.52
	6H	18.12	19.45	18.53	19.81	20.20	27.49	28.82	27.90	29.19	29.58
	8H	18.20	19.47	18.62	19.86	20.25	27.52	28.79	27.95	29.18	29.58
	12H	18.25	19.47	18.68	19.85	20.28	27.52	28.74	27.95	29.12	29.55
4H	2H	21.23	22.66	21.62	23.01	23.38	26.01	27.44	26.40	27.79	28.16
	3H	22.23	23.44	22.64	23.83	24.23	27.91	29.11	28.32	29.50	29.90
	4H	22.55	23.64	22.98	24.05	24.48	28.18	29.27	28.61	29.68	30.11
	6H	22.73	23.68	23.19	24.12	24.57	28.38	29.32	28.83	29.76	30.22
	8H	22.77	23.66	23.23	24.10	24.57	28.42	29.31	28.88	29.75	30.21
	12H	22.81	23.60	23.29	24.08	24.54	28.43	29.23	28.91	29.70	30.17
8H	4H	23.80	24.68	24.26	25.12	25.59	28.37	29.25	28.83	29.69	30.16
	6H	24.07	24.81	24.57	25.29	25.77	28.61	29.35	29.10	29.83	30.31
	8H	24.15	24.81	24.66	25.32	25.80	28.68	29.34	29.19	29.85	30.33
	12H	24.22	24.80	24.73	25.29	25.85	28.72	29.29	29.22	29.78	30.34
12H	4H	23.86	24.65	24.33	25.12	25.59	28.36	29.16	28.84	29.63	30.10
	6H	24.18	24.83	24.68	25.34	25.82	28.60	29.26	29.11	29.77	30.25
	8H	24.32	24.90	24.83	25.39	25.95	28.71	29.29	29.22	29.78	30.34