

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855567

Luminaire Tested: SQ2-F-075D-840-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855567
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-F-075D-840-UNV-STD-W-4
Description: CORELITE SQ2 SURFACE LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3464.0 lumens
Efficiency: N/A
Efficacy: 129.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 26.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855567
CATALOG NUMBER: SQ2-F-075D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855567

CATALOG NUMBER: SQ2-F-075D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84				84
2	99	90	84	78	96	89	82	77	85	80	75	82	77	73	79	75	72	70				70
3	90	79	71	65	88	78	70	64	75	68	63	72	66	62	69	65	61	59				59
4	82	70	61	55	80	69	61	54	66	59	54	64	58	53	62	57	52	50				50
5	76	63	54	47	74	62	53	47	60	52	46	58	51	46	56	50	45	43				43
6	70	57	48	41	68	56	47	41	54	46	41	52	45	40	50	44	40	38				38
7	65	51	42	36	63	50	42	36	49	41	36	47	41	36	46	40	35	33				33
8	60	47	38	32	59	46	38	32	45	37	32	43	37	32	42	36	32	30				30
9	56	43	35	29	55	42	34	29	41	34	29	40	33	29	39	33	29	27				27
10	53	40	32	26	52	39	31	26	38	31	26	37	31	26	36	30	26	24				24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19922	19922	19922
5°	19781	19836	19998
10°	19735	19790	19928
15°	19614	19671	19868
20°	19498	19527	19699
25°	19319	19319	19436
30°	19121	19121	19182
35°	18889	18821	18954
40°	18638	18567	18638
45°	18347	18274	18347
50°	18073	17904	17947
55°	17652	17605	17512
60°	17208	17102	16992
65°	16699	16504	16313
70°	15711	15635	15314
75°	14785	14473	14055
80°	13129	12822	12357
85°	10578	9652	9022

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 18463 cd/sqm

TEST NUMBER: P855567

CATALOG NUMBER: SQ2-F-075D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.6	3.4
10°-20°	333.3	9.6
20°-30°	501.4	14.5
30°-40°	600.0	17.3
40°-50°	619.0	17.9
50°-60°	558.5	16.1
60°-70°	426.2	12.3
70°-80°	245.0	7.1
80°-90°	63.9	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	951.4	27.5
0°-40°	1551.4	44.8
0°-60°	2728.9	78.8
0°-90°	3464.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3464.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1234	1234	1234	1234	1234	
5°	1220	1237	1224	1226	1234	116
15°	1173	1188	1177	1182	1189	331
25°	1084	1096	1084	1086	1091	499
35°	958	965	955	958	962	599
45°	804	809	800	802	804	620
55°	627	630	625	622	622	561
65°	437	436	432	429	427	430
75°	237	235	232	227	225	250
85°	57	54	52	47	49	68
90°	0	0	0	0	0	



TEST NUMBER: P855567

CATALOG NUMBER: SQ2-F-075D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1233.9	1233.9	1233.9	1233.9	1233.9
2.5°	1225.9	1240.3	1228.6	1231.4	1232.6
5°	1220.5	1237.0	1223.9	1225.8	1233.9
7.5°	1210.4	1228.2	1213.8	1217.0	1226.2
10°	1203.7	1220.2	1207.1	1208.9	1215.5
12.5°	1192.9	1209.5	1196.3	1199.5	1206.1
15°	1173.4	1188.2	1176.8	1182.1	1188.6
17.5°	1151.0	1166.7	1154.0	1158.4	1164.0
20°	1134.8	1147.9	1136.5	1138.4	1146.5
22.5°	1114.6	1127.8	1117.6	1118.1	1125.1
25°	1084.4	1095.8	1084.4	1086.2	1091.0
27.5°	1049.7	1059.6	1049.7	1051.5	1055.7
30°	1025.6	1035.3	1025.6	1027.2	1028.9
32.5°	998.6	1007.1	997.2	999.1	1003.3
35°	958.3	964.8	954.9	958.3	961.6
37.5°	915.2	920.2	911.8	913.6	916.6
40°	884.3	889.2	880.9	882.7	884.3
42.5°	853.3	857.0	848.6	850.4	853.3
45°	803.5	808.6	800.3	801.9	803.5
47.5°	753.2	756.1	749.1	747.8	750.9
50°	719.5	721.2	712.8	712.9	714.5
52.5°	683.3	684.9	679.2	676.5	678.1
55°	627.1	630.4	625.4	622.1	622.1
57.5°	570.6	573.5	567.2	565.6	565.2
60°	532.9	534.6	529.6	527.8	526.2
62.5°	495.3	495.6	490.5	488.9	487.3
65°	437.1	435.5	432.0	428.6	427.0
67.5°	371.9	373.5	370.2	364.8	364.8
70°	332.8	334.5	331.2	324.4	324.4
72.5°	295.2	294.3	292.2	286.8	284.1
75°	237.0	235.4	232.0	226.9	225.3
77.5°	178.9	177.3	175.5	169.1	170.5
80°	141.2	139.6	137.9	132.9	132.9
82.5°	107.6	104.7	102.9	97.9	97.9
85°	57.1	53.8	52.1	47.1	48.7
87.5°	16.1	14.8	13.4	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P855567

CATALOG NUMBER: SQ2-F-075D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.16	23.80	22.53	24.12	24.43	22.08	23.72	22.45	24.04	24.35
	3H	23.99	25.48	24.37	25.80	26.16	23.87	25.36	24.25	25.68	26.04
	4H	24.68	26.08	25.08	26.43	26.81	24.53	25.93	24.93	26.28	26.65
	6H	25.19	26.49	25.60	26.85	27.24	25.01	26.30	25.42	26.67	27.06
	8H	25.35	26.59	25.78	26.98	27.38	25.15	26.39	25.57	26.78	27.18
	12H	25.45	26.64	25.88	27.02	27.45	25.23	26.42	25.66	26.80	27.23
4H	2H	22.80	24.20	23.19	24.54	24.92	22.73	24.13	23.13	24.48	24.86
	3H	24.85	26.02	25.26	26.42	26.82	24.74	25.92	25.15	26.31	26.71
	4H	25.67	26.73	26.10	27.15	27.58	25.53	26.59	25.96	27.00	27.44
	6H	26.30	27.23	26.76	27.67	28.13	26.12	27.05	26.58	27.49	27.95
	8H	26.51	27.38	26.97	27.82	28.29	26.31	27.18	26.77	27.62	28.09
	12H	26.65	27.43	27.13	27.91	28.37	26.42	27.20	26.90	27.68	28.15
8H	4H	25.98	26.85	26.44	27.29	27.76	25.85	26.72	26.31	27.16	27.63
	6H	26.73	27.45	27.22	27.94	28.42	26.57	27.29	27.06	27.78	28.25
	8H	27.01	27.66	27.52	28.16	28.65	26.81	27.46	27.32	27.97	28.45
	12H	27.21	27.78	27.72	28.27	28.83	26.98	27.56	27.49	28.05	28.61
12H	4H	26.01	26.79	26.49	27.27	27.74	25.89	26.67	26.37	27.15	27.62
	6H	26.78	27.43	27.29	27.94	28.42	26.62	27.27	27.13	27.78	28.26
	8H	27.11	27.69	27.62	28.18	28.74	26.93	27.50	27.43	27.99	28.55