

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855538

Luminaire Tested: SQ2-FB-125D-840-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855538
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FB-125D-840-UNV-STD-W-4
Description: CORELITE SQ2 SURFACE LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5784.8 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855538
CATALOG NUMBER: SQ2-FB-125D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855538

CATALOG NUMBER: SQ2-FB-125D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84				84
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69				69
3	89	78	70	63	87	77	69	63	74	67	61	71	65	60	68	63	59	57				57
4	81	69	60	53	79	67	59	52	65	57	52	63	56	51	60	55	50	48				48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	43	54	48	43	41				41
6	68	54	45	39	66	53	45	38	52	44	38	50	43	38	48	42	37	35				35
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31				31
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27				27
9	54	40	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24				24
10	51	37	29	23	49	37	29	23	36	28	23	35	28	23	34	28	23	21				21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9452	9452	9452
5°	9214	12772	16741
10°	8629	24733	32577
15°	7809	32179	37496
20°	6916	35398	39268
25°	6116	37857	39913
30°	5407	38988	40404
35°	4827	39665	43438
40°	4390	40042	46152
45°	4048	40231	48327
50°	3818	41003	49205
55°	3724	42069	49596
60°	3817	42625	49351
65°	3981	42044	47958
70°	4121	40655	36269
75°	4566	36519	20012
80°	4714	18847	18587
85°	4687	13042	7818

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 50045 cd/sqm

TEST NUMBER: P855538

CATALOG NUMBER: SQ2-FB-125D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	1.7
10°-20°	447.7	7.7
20°-30°	787.7	13.6
30°-40°	1019.6	17.6
40°-50°	1124.5	19.4
50°-60°	1049.9	18.1
60°-70°	811.5	14.0
70°-80°	374.3	6.5
80°-90°	71.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1333.5	23.1
0°-40°	2353.1	40.7
0°-60°	4527.5	78.3
0°-90°	5784.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5784.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	585	585	585	585	585	
5°	568	651	788	961	1033	53
15°	467	921	1925	2155	2243	130
25°	343	1238	2125	2218	2240	158
35°	245	1194	2012	2083	2204	154
45°	177	915	1762	2023	2116	137
55°	132	545	1494	1718	1762	119
65°	104	308	1100	1233	1255	102
75°	73	189	585	315	321	75
85°	25	56	70	48	42	28
90°	0	0	0	0	0	



TEST NUMBER: P855538

CATALOG NUMBER: SQ2-FB-125D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	585.4	585.4	585.4	585.4	585.4
2.5°	581.0	605.1	632.7	664.5	677.7
5°	568.5	651.1	788.0	961.3	1032.9
7.5°	546.6	714.4	1146.1	1609.8	1752.9
10°	526.3	760.2	1508.6	1910.0	1987.0
12.5°	503.8	821.4	1736.0	2018.1	2097.4
15°	467.2	921.2	1925.1	2155.1	2243.2
17.5°	429.5	1033.8	2012.9	2239.8	2287.7
20°	402.5	1112.5	2060.2	2255.1	2285.4
22.5°	377.7	1171.3	2094.0	2241.6	2274.2
25°	343.3	1237.8	2125.0	2218.3	2240.4
27.5°	310.1	1255.1	2111.5	2172.8	2194.2
30°	290.0	1250.4	2091.2	2136.9	2167.2
32.5°	271.9	1236.7	2061.9	2106.2	2171.7
35°	244.9	1194.3	2012.4	2082.7	2203.8
37.5°	221.8	1126.1	1947.0	2091.0	2207.7
40°	208.3	1075.2	1899.8	2090.6	2189.7
42.5°	194.7	1015.4	1845.8	2068.1	2167.2
45°	177.3	914.8	1761.9	2022.9	2116.5
47.5°	160.9	801.7	1684.2	1960.4	2028.7
50°	152.0	724.4	1632.4	1903.9	1958.9
52.5°	143.0	649.4	1580.6	1836.2	1886.9
55°	132.3	545.1	1494.5	1717.8	1761.9
57.5°	122.7	455.7	1396.6	1587.0	1622.8
60°	118.2	407.2	1320.0	1492.5	1528.3
62.5°	111.4	363.0	1234.4	1393.4	1426.9
65°	104.2	307.8	1100.5	1233.2	1255.3
67.5°	94.0	266.9	958.1	1039.3	998.0
70°	87.3	246.8	861.2	886.6	768.3
72.5°	82.7	224.8	755.4	688.4	464.4
75°	73.2	188.8	585.4	315.4	320.8
77.5°	59.7	146.0	385.0	242.2	247.1
80°	50.7	119.5	202.7	197.1	199.9
82.5°	41.6	92.9	139.6	145.1	141.2
85°	25.3	55.6	70.4	47.7	42.2
87.5°	9.0	20.0	11.3	11.3	11.3
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P855538

CATALOG NUMBER: SQ2-FB-125D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.63	20.31	18.99	20.63	20.94	27.36	29.05	27.73	29.36	29.68
	3H	19.42	20.94	19.79	21.27	21.63	29.04	30.57	29.42	30.89	31.25
	4H	19.75	21.19	20.15	21.54	21.91	29.26	30.70	29.66	31.04	31.42
	6H	20.01	21.34	20.42	21.71	22.10	29.39	30.72	29.80	31.08	31.47
	8H	20.09	21.36	20.52	21.75	22.15	29.42	30.69	29.84	31.08	31.47
	12H	20.15	21.37	20.58	21.75	22.18	29.42	30.63	29.84	31.02	31.44
4H	2H	23.12	24.56	23.52	24.90	25.28	27.90	29.34	28.30	29.68	30.06
	3H	24.13	25.33	24.54	25.73	26.13	29.80	31.00	30.21	31.40	31.80
	4H	24.45	25.53	24.88	25.95	26.38	30.08	31.16	30.51	31.57	32.01
	6H	24.63	25.58	25.08	26.02	26.47	30.27	31.22	30.72	31.66	32.11
	8H	24.67	25.56	25.13	26.00	26.46	30.32	31.20	30.78	31.64	32.11
	12H	24.70	25.50	25.18	25.97	26.44	30.33	31.12	30.81	31.60	32.07
8H	4H	25.69	26.58	26.15	27.02	27.48	30.26	31.15	30.72	31.59	32.05
	6H	25.97	26.70	26.46	27.19	27.66	30.51	31.24	31.00	31.73	32.20
	8H	26.05	26.71	26.56	27.21	27.70	30.58	31.24	31.09	31.74	32.23
	12H	26.12	26.69	26.62	27.18	27.74	30.61	31.19	31.12	31.68	32.24
12H	4H	25.75	26.55	26.23	27.02	27.49	30.26	31.05	30.74	31.53	31.99
	6H	26.07	26.73	26.58	27.24	27.72	30.50	31.16	31.01	31.66	32.15
	8H	26.22	26.80	26.72	27.29	27.85	30.61	31.19	31.11	31.68	32.24