

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853778

Luminaire Tested: SQ2-FA-050D-940-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P853778  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-FA-050D-940-UNV-STD-W-4  
Description: CORELITE SQ2 SURFACE LED LUMINAIRE  
DOWNLIGHT 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2048.4 lumens  
Efficiency: N/A  
Efficacy: 115.1 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 0.95 / 0.95  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 17.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P853778  
CATALOG NUMBER: SQ2-FA-050D-940-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P853778

CATALOG NUMBER: SQ2-FA-050D-940-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF  | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |    |    | 20 |     |
| RC  | 80  |     |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |    |    | 10 | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0  |     |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    | 100 |
| 1   | 111 | 107 | 104 | 101 | 108 | 105 | 102 | 99  | 101 | 98  | 96  | 97  | 95  | 93  | 93  | 92  | 90  | 88  |    |    |    | 88  |
| 2   | 103 | 97  | 91  | 87  | 101 | 95  | 90  | 86  | 92  | 87  | 84  | 88  | 85  | 82  | 86  | 83  | 80  | 78  |    |    |    | 78  |
| 3   | 96  | 88  | 81  | 76  | 94  | 86  | 80  | 75  | 84  | 78  | 74  | 81  | 77  | 73  | 79  | 75  | 72  | 70  |    |    |    | 70  |
| 4   | 90  | 80  | 73  | 68  | 88  | 79  | 72  | 67  | 77  | 71  | 66  | 74  | 70  | 65  | 72  | 68  | 65  | 63  |    |    |    | 63  |
| 5   | 84  | 74  | 66  | 61  | 82  | 73  | 66  | 61  | 71  | 65  | 60  | 69  | 64  | 59  | 67  | 62  | 59  | 57  |    |    |    | 57  |
| 6   | 79  | 68  | 61  | 55  | 77  | 67  | 60  | 55  | 65  | 59  | 55  | 64  | 58  | 54  | 62  | 58  | 54  | 52  |    |    |    | 52  |
| 7   | 74  | 63  | 56  | 50  | 73  | 62  | 55  | 50  | 61  | 55  | 50  | 59  | 54  | 50  | 58  | 53  | 49  | 48  |    |    |    | 48  |
| 8   | 70  | 59  | 51  | 46  | 69  | 58  | 51  | 46  | 57  | 50  | 46  | 56  | 50  | 46  | 54  | 49  | 46  | 44  |    |    |    | 44  |
| 9   | 66  | 55  | 48  | 43  | 65  | 54  | 47  | 43  | 53  | 47  | 43  | 52  | 46  | 42  | 51  | 46  | 42  | 41  |    |    |    | 41  |
| 10  | 63  | 51  | 44  | 40  | 61  | 51  | 44  | 40  | 50  | 44  | 39  | 49  | 43  | 39  | 48  | 43  | 39  | 38  |    |    |    | 38  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    | 90°   | 180°  | 270°  |
|-----|-------|-------|-------|-------|
| 0°  | 22646 | 22646 | 22646 | 22646 |
| 5°  | 22527 | 22561 | 22441 | 22545 |
| 10° | 22492 | 22405 | 22405 | 22405 |
| 15° | 22420 | 22190 | 22243 | 22190 |
| 20° | 22246 | 21301 | 22082 | 21500 |
| 25° | 21953 | 17977 | 21802 | 18355 |
| 30° | 21752 | 10314 | 21515 | 10452 |
| 35° | 21370 | 8862  | 21100 | 8736  |
| 40° | 20778 | 4660  | 20198 | 4616  |
| 45° | 18888 | 2005  | 18212 | 2005  |
| 50° | 12461 | 2419  | 11823 | 2258  |
| 55° | 6967  | 4467  | 6609  | 4051  |
| 60° | 3759  | 6284  | 3688  | 5635  |
| 65° | 3312  | 7637  | 3477  | 8688  |
| 70° | 3097  | 9139  | 2946  | 9640  |
| 75° | 2901  | 7854  | 2969  | 8116  |
| 80° | 2455  | 5607  | 2455  | 5904  |
| 85° | 2149  | 3131  | 1964  | 3724  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18888 cd/sqm



TEST NUMBER: P853778

CATALOG NUMBER: SQ2-FA-050D-940-UNV-STD-W-4

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 132.0  | 6.4       |
| 10°-20°   | 374.5  | 18.3      |
| 20°-30°   | 510.6  | 24.9      |
| 30°-40°   | 429.1  | 20.9      |
| 40°-50°   | 243.7  | 11.9      |
| 50°-60°   | 129.3  | 6.3       |
| 60°-70°   | 119.0  | 5.8       |
| 70°-80°   | 87.4   | 4.3       |
| 80°-90°   | 22.8   | 1.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1017.0 | 49.7      |
| 0°-40°    | 1446.1 | 70.6      |
| 0°-60°    | 1819.1 | 88.8      |
| 0°-90°    | 2048.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2048.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 90°  | 180° | 270° | 360° | Flux |
|-----|------|------|------|------|------|------|
| 0°  | 1403 | 1403 | 1403 | 1403 | 1403 |      |
| 5°  | 1390 | 1392 | 1385 | 1391 | 1390 | 132  |
| 15° | 1341 | 1328 | 1331 | 1328 | 1341 | 378  |
| 25° | 1232 | 1009 | 1224 | 1030 | 1232 | 568  |
| 35° | 1084 | 450  | 1070 | 443  | 1084 | 677  |
| 45° | 827  | 88   | 798  | 88   | 827  | 605  |
| 55° | 248  | 159  | 235  | 144  | 248  | 238  |
| 65° | 87   | 200  | 91   | 227  | 87   | 87   |
| 75° | 46   | 126  | 48   | 130  | 46   | 48   |
| 85° | 12   | 17   | 11   | 20   | 12   | 13   |
| 90° | 0    | 0    | 0    | 0    | 0    |      |



TEST NUMBER: P853778

CATALOG NUMBER: SQ2-FA-050D-940-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    | 112.5° | 135°   | 157.5° | 180°   | 202.5° | 225°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1402.6 | 1402.6 | 1402.6 | 1402.6 | 1402.6 | 1402.6 | 1402.6 | 1402.6 | 1402.6 | 1402.6 | 1402.6 |
| 2.5°  | 1395.0 | 1415.7 | 1397.5 | 1395.2 | 1402.6 | 1401.0 | 1398.4 | 1408.2 | 1391.6 | 1408.2 | 1395.0 |
| 5°    | 1389.9 | 1413.7 | 1386.7 | 1379.6 | 1392.0 | 1383.8 | 1391.0 | 1405.3 | 1384.6 | 1403.2 | 1382.5 |
| 7.5°  | 1381.2 | 1402.3 | 1370.0 | 1365.4 | 1377.6 | 1370.4 | 1373.4 | 1393.3 | 1376.0 | 1388.2 | 1369.4 |
| 10°   | 1371.9 | 1390.6 | 1358.2 | 1355.3 | 1366.6 | 1359.4 | 1362.4 | 1383.2 | 1366.6 | 1378.0 | 1359.2 |
| 12.5° | 1361.8 | 1376.3 | 1343.8 | 1342.5 | 1352.3 | 1347.5 | 1348.9 | 1366.3 | 1353.1 | 1364.5 | 1346.5 |
| 15°   | 1341.3 | 1354.7 | 1322.2 | 1317.2 | 1327.5 | 1323.4 | 1325.4 | 1341.0 | 1330.7 | 1337.9 | 1322.2 |
| 17.5° | 1315.9 | 1326.6 | 1294.3 | 1279.1 | 1279.5 | 1284.7 | 1294.3 | 1313.1 | 1303.8 | 1313.3 | 1291.1 |
| 20°   | 1294.7 | 1307.1 | 1271.4 | 1241.8 | 1239.7 | 1244.9 | 1271.4 | 1290.4 | 1285.2 | 1295.5 | 1264.0 |
| 22.5° | 1270.2 | 1278.4 | 1246.1 | 1196.0 | 1188.9 | 1194.1 | 1242.7 | 1265.1 | 1263.2 | 1270.2 | 1231.0 |
| 25°   | 1232.3 | 1240.6 | 1181.5 | 1109.4 | 1009.1 | 1103.2 | 1183.6 | 1223.8 | 1223.8 | 1230.1 | 1178.4 |
| 27.5° | 1193.8 | 1194.0 | 1087.2 | 712.5  | 628.5  | 686.9  | 1085.7 | 1172.9 | 1182.8 | 1179.7 | 1078.1 |
| 30°   | 1166.7 | 1159.5 | 963.6  | 576.0  | 553.2  | 567.7  | 964.7  | 1137.5 | 1154.0 | 1142.7 | 939.3  |
| 32.5° | 1135.4 | 1114.9 | 711.5  | 529.5  | 510.9  | 523.7  | 688.0  | 1095.5 | 1124.4 | 1099.8 | 738.7  |
| 35°   | 1084.2 | 1030.4 | 542.6  | 468.2  | 449.6  | 466.1  | 538.4  | 1012.5 | 1070.5 | 1004.3 | 560.6  |
| 37.5° | 1029.0 | 819.0  | 477.7  | 372.9  | 332.8  | 364.8  | 475.4  | 810.3  | 1006.6 | 791.5  | 477.3  |
| 40°   | 985.8  | 643.5  | 429.5  | 272.8  | 221.1  | 257.3  | 426.3  | 613.9  | 958.3  | 660.5  | 418.9  |
| 42.5° | 928.3  | 565.3  | 344.8  | 173.3  | 135.6  | 158.6  | 330.7  | 552.2  | 899.1  | 572.3  | 333.4  |
| 45°   | 827.2  | 485.9  | 204.2  | 95.0   | 87.8   | 91.9   | 188.3  | 476.9  | 797.6  | 466.6  | 208.4  |
| 47.5° | 655.2  | 370.6  | 131.2  | 80.8   | 88.6   | 80.8   | 127.1  | 358.8  | 618.8  | 358.2  | 131.0  |
| 50°   | 496.1  | 289.2  | 101.5  | 81.8   | 96.3   | 81.8   | 98.4   | 279.4  | 470.7  | 305.2  | 100.5  |
| 52.5° | 367.5  | 241.7  | 82.9   | 89.7   | 115.7  | 91.3   | 80.6   | 235.3  | 348.9  | 246.3  | 78.5   |
| 55°   | 247.5  | 189.6  | 66.6   | 118.3  | 158.7  | 121.4  | 66.6   | 184.1  | 234.8  | 182.1  | 64.5   |
| 57.5° | 157.0  | 141.0  | 67.5   | 152.1  | 181.1  | 155.0  | 68.5   | 135.9  | 150.6  | 136.6  | 59.2   |
| 60°   | 116.4  | 111.2  | 75.1   | 161.5  | 194.6  | 163.6  | 76.2   | 107.0  | 114.2  | 106.0  | 63.5   |
| 62.5° | 96.0   | 87.6   | 90.3   | 174.9  | 202.2  | 170.4  | 92.2   | 83.5   | 99.9   | 80.0   | 70.2   |
| 65°   | 86.7   | 56.7   | 106.8  | 177.2  | 199.9  | 177.2  | 107.9  | 53.7   | 91.0   | 57.9   | 95.2   |
| 67.5° | 78.3   | 42.1   | 103.2  | 176.0  | 201.2  | 176.4  | 100.7  | 40.1   | 75.1   | 39.1   | 97.3   |
| 70°   | 65.6   | 37.7   | 97.3   | 179.1  | 193.6  | 172.9  | 97.3   | 36.6   | 62.4   | 35.5   | 114.2  |
| 72.5° | 54.6   | 35.8   | 90.5   | 165.4  | 171.6  | 159.2  | 91.4   | 35.6   | 54.8   | 32.0   | 107.5  |
| 75°   | 46.5   | 35.2   | 86.7   | 132.1  | 125.9  | 125.9  | 84.6   | 34.2   | 47.6   | 32.1   | 83.6   |
| 77.5° | 34.9   | 31.2   | 71.9   | 86.2   | 81.4   | 81.4   | 70.7   | 30.1   | 33.2   | 28.2   | 67.9   |
| 80°   | 26.4   | 28.5   | 59.2   | 63.4   | 60.3   | 60.3   | 57.1   | 27.5   | 26.4   | 26.4   | 56.1   |
| 82.5° | 20.5   | 24.2   | 45.7   | 46.5   | 44.2   | 43.4   | 44.4   | 24.0   | 20.5   | 22.2   | 43.4   |
| 85°   | 11.6   | 16.8   | 24.3   | 20.0   | 16.9   | 15.9   | 23.3   | 15.7   | 10.6   | 15.7   | 23.3   |
| 87.5° | 4.2    | 7.5    | 3.4    | 3.4    | 3.4    | 3.4    | 3.4    | 7.5    | 4.2    | 6.7    | 4.2    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



TEST NUMBER: P853778

CATALOG NUMBER: SQ2-FA-050D-940-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

|       | 247.5° | 270°   | 292.5° | 315°   | 337.5° | 360°   |
|-------|--------|--------|--------|--------|--------|--------|
| 0°    | 1402.6 | 1402.6 | 1402.6 | 1402.6 | 1402.6 | 1402.6 |
| 2.5°  | 1391.7 | 1397.5 | 1397.5 | 1394.1 | 1410.7 | 1395.0 |
| 5°    | 1377.5 | 1391.0 | 1384.8 | 1384.6 | 1405.4 | 1389.9 |
| 7.5°  | 1367.6 | 1380.2 | 1374.4 | 1373.2 | 1393.7 | 1381.2 |
| 10°   | 1357.3 | 1366.6 | 1362.5 | 1365.6 | 1384.3 | 1371.9 |
| 12.5° | 1343.0 | 1354.0 | 1349.8 | 1354.6 | 1371.7 | 1361.8 |
| 15°   | 1318.2 | 1327.5 | 1329.6 | 1331.7 | 1351.6 | 1341.3 |
| 17.5° | 1277.3 | 1281.8 | 1292.2 | 1306.8 | 1327.5 | 1315.9 |
| 20°   | 1245.1 | 1251.3 | 1257.6 | 1283.1 | 1307.1 | 1294.7 |
| 22.5° | 1208.6 | 1206.5 | 1221.0 | 1250.9 | 1280.9 | 1270.2 |
| 25°   | 1109.9 | 1030.3 | 1118.2 | 1195.3 | 1235.4 | 1232.3 |
| 27.5° | 772.8  | 670.6  | 761.0  | 1103.3 | 1187.6 | 1193.8 |
| 30°   | 608.2  | 560.6  | 607.2  | 984.8  | 1152.2 | 1166.7 |
| 32.5° | 540.0  | 507.3  | 535.6  | 749.5  | 1107.7 | 1135.4 |
| 35°   | 466.0  | 443.2  | 466.0  | 560.6  | 1020.1 | 1084.2 |
| 37.5° | 373.0  | 326.4  | 372.1  | 484.5  | 824.6  | 1029.0 |
| 40°   | 277.9  | 219.0  | 269.6  | 433.7  | 659.0  | 985.8  |
| 42.5° | 185.2  | 141.1  | 175.2  | 341.4  | 570.0  | 928.3  |
| 45°   | 100.2  | 87.8   | 96.1   | 206.3  | 465.2  | 827.2  |
| 47.5° | 78.6   | 83.1   | 78.6   | 130.1  | 355.9  | 655.2  |
| 50°   | 75.4   | 89.9   | 75.4   | 100.5  | 294.4  | 496.1  |
| 52.5° | 82.2   | 97.5   | 81.4   | 79.3   | 240.3  | 367.5  |
| 55°   | 93.2   | 143.9  | 94.2   | 64.5   | 176.2  | 247.5  |
| 57.5° | 132.7  | 161.8  | 134.1  | 61.1   | 135.7  | 157.0  |
| 60°   | 136.3  | 174.5  | 135.2  | 64.5   | 105.0  | 116.4  |
| 62.5° | 161.2  | 216.0  | 161.0  | 73.8   | 78.0   | 96.0   |
| 65°   | 206.7  | 227.4  | 208.8  | 94.1   | 55.7   | 86.7   |
| 67.5° | 196.2  | 210.9  | 194.2  | 100.9  | 38.4   | 78.3   |
| 70°   | 192.8  | 204.2  | 190.7  | 115.3  | 35.6   | 65.6   |
| 72.5° | 179.9  | 181.3  | 176.1  | 106.8  | 32.0   | 54.6   |
| 75°   | 139.4  | 130.1  | 134.2  | 92.0   | 32.1   | 46.5   |
| 77.5° | 86.7   | 82.9   | 83.6   | 70.2   | 28.3   | 34.9   |
| 80°   | 65.5   | 63.5   | 62.4   | 59.2   | 26.4   | 26.4   |
| 82.5° | 48.6   | 46.5   | 45.5   | 45.7   | 22.2   | 20.5   |
| 85°   | 22.2   | 20.1   | 19.1   | 26.4   | 15.8   | 11.6   |
| 87.5° | 4.2    | 4.2    | 3.4    | 4.2    | 5.9    | 4.2    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



TEST NUMBER: P853778

CATALOG NUMBER: SQ2-FA-050D-940-UNV-STD-W-4

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |       |       |       |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7   | 0.5   | 0.5   | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3   | 0.5   | 0.3   | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2   | 0.2   | 0.2   | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |       |       |       |       |
| X=2H            | Y=2H | 14.84            | 16.15 | 15.21 | 16.46 | 16.78 | 13.70          | 15.01 | 14.06 | 15.32 | 15.64 |
|                 | 3H   | 15.57            | 16.74 | 15.95 | 17.07 | 17.43 | 19.87          | 21.05 | 20.25 | 21.38 | 21.74 |
|                 | 4H   | 15.99            | 17.09 | 16.40 | 17.44 | 17.82 | 21.17          | 22.26 | 21.57 | 22.61 | 23.00 |
|                 | 6H   | 16.36            | 17.38 | 16.78 | 17.75 | 18.14 | 21.79          | 22.80 | 22.21 | 23.17 | 23.57 |
|                 | 8H   | 16.49            | 17.45 | 16.92 | 17.84 | 18.25 | 21.93          | 22.89 | 22.36 | 23.28 | 23.68 |
|                 | 12H  | 16.58            | 17.49 | 17.01 | 17.88 | 18.31 | 21.98          | 22.90 | 22.41 | 23.28 | 23.71 |
| 4H              | 2H   | 15.28            | 16.37 | 15.68 | 16.72 | 17.11 | 14.27          | 15.37 | 14.67 | 15.72 | 16.10 |
|                 | 3H   | 16.30            | 17.21 | 16.71 | 17.62 | 18.02 | 20.62          | 21.54 | 21.04 | 21.94 | 22.34 |
|                 | 4H   | 16.87            | 17.69 | 17.31 | 18.11 | 18.56 | 22.08          | 22.91 | 22.52 | 23.32 | 23.77 |
|                 | 6H   | 17.37            | 18.08 | 17.83 | 18.53 | 18.99 | 22.84          | 23.55 | 23.30 | 24.00 | 24.46 |
|                 | 8H   | 17.54            | 18.21 | 18.01 | 18.65 | 19.13 | 23.01          | 23.68 | 23.48 | 24.12 | 24.60 |
|                 | 12H  | 17.68            | 18.27 | 18.16 | 18.75 | 19.22 | 23.09          | 23.68 | 23.58 | 24.17 | 24.64 |
| 8H              | 4H   | 18.00            | 18.66 | 18.47 | 19.11 | 19.58 | 22.23          | 22.90 | 22.70 | 23.34 | 23.81 |
|                 | 6H   | 18.62            | 19.16 | 19.12 | 19.66 | 20.14 | 23.12          | 23.67 | 23.62 | 24.16 | 24.64 |
|                 | 8H   | 18.85            | 19.34 | 19.37 | 19.85 | 20.34 | 23.37          | 23.86 | 23.89 | 24.37 | 24.86 |
|                 | 12H  | 19.04            | 19.47 | 19.56 | 19.96 | 20.53 | 23.51          | 23.94 | 24.03 | 24.43 | 25.01 |
| 12H             | 4H   | 18.16            | 18.75 | 18.65 | 19.23 | 19.71 | 22.21          | 22.80 | 22.70 | 23.28 | 23.76 |
|                 | 6H   | 18.89            | 19.38 | 19.41 | 19.89 | 20.38 | 23.13          | 23.62 | 23.65 | 24.13 | 24.62 |
|                 | 8H   | 19.21            | 19.64 | 19.72 | 20.13 | 20.70 | 23.43          | 23.86 | 23.95 | 24.35 | 24.92 |