

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855521

Luminaire Tested: SQ2-PH1-075D-840-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855521
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PH1-075D-840-UNV-STD-W-4
Description: CORELITE SQ2 SURFACE LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3908.3 lumens
Efficiency: N/A
Efficacy: 146.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 26.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855521
CATALOG NUMBER: SQ2-PH1-075D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855521

CATALOG NUMBER: SQ2-PH1-075D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	91	81	73	67	89	80	72	67	77	71	65	74	69	64	72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	55	64	59	55	53
5	77	65	56	50	75	64	55	49	62	54	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	48	43	54	48	43	53	47	42	40
7	66	53	45	39	65	52	44	38	51	43	38	49	43	38	48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	28530	28530	28530
5°	28691	26976	26075
10°	28032	24558	23704
15°	28159	23099	23239
20°	27153	22386	23426
25°	26657	22283	22882
30°	26077	22223	23068
35°	25882	21969	27039
40°	25901	21827	21439
45°	25912	20998	18466
50°	25551	21411	17314
55°	25225	23237	16608
60°	24974	20360	15581
65°	24539	16504	13551
70°	23174	14044	9682
75°	20661	10593	7342
80°	16885	6881	6881
85°	10578	6243	4668

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25912 cd/sqm

TEST NUMBER: P855521

CATALOG NUMBER: SQ2-PH1-075D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	4.0
10°-20°	409.0	10.5
20°-30°	599.6	15.3
30°-40°	726.2	18.6
40°-50°	714.1	18.3
50°-60°	621.7	15.9
60°-70°	432.2	11.1
70°-80°	204.9	5.2
80°-90°	45.2	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1164.1	29.8
0°-40°	1890.2	48.4
0°-60°	3226.0	82.5
0°-90°	3908.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3908.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1767	1767	1767	1767	1767	
5°	1770	1769	1664	1612	1609	166
15°	1685	1500	1382	1372	1390	470
25°	1496	1273	1251	1289	1284	688
35°	1313	1061	1115	1211	1372	822
45°	1135	841	920	952	809	872
55°	896	654	826	595	590	801
65°	642	450	432	355	355	631
75°	331	229	170	121	118	351
85°	57	37	34	27	25	78
90°	0	0	0	0	0	



TEST NUMBER: P855521

CATALOG NUMBER: SQ2-PH1-075D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1767.0	1767.0	1767.0	1767.0	1767.0
2.5°	1762.9	1781.3	1740.1	1723.9	1721.2
5°	1770.2	1768.6	1664.4	1612.2	1608.8
7.5°	1738.0	1687.0	1562.5	1504.9	1502.3
10°	1709.8	1632.5	1497.9	1445.8	1445.8
12.5°	1703.0	1581.1	1445.4	1407.0	1414.9
15°	1684.6	1500.5	1381.9	1372.3	1390.3
17.5°	1623.4	1425.1	1332.5	1354.5	1375.5
20°	1580.3	1384.7	1302.9	1343.7	1363.4
22.5°	1544.0	1345.8	1281.4	1326.0	1336.6
25°	1496.3	1272.7	1250.8	1289.4	1284.4
27.5°	1439.0	1205.7	1220.2	1243.8	1246.7
30°	1398.7	1165.3	1192.0	1216.0	1237.3
32.5°	1359.8	1118.4	1161.0	1218.0	1266.9
35°	1313.1	1061.4	1114.6	1210.7	1371.8
37.5°	1263.9	994.3	1067.9	1148.7	1200.0
40°	1228.9	946.2	1035.6	1135.5	1017.2
42.5°	1191.3	908.5	987.2	1116.1	916.2
45°	1134.8	840.6	919.6	951.7	808.7
47.5°	1068.2	787.8	873.9	793.6	737.7
50°	1017.2	752.5	852.4	725.5	689.3
52.5°	967.4	715.9	837.6	669.2	644.9
55°	896.1	654.4	825.5	595.1	590.0
57.5°	820.4	591.9	730.0	530.5	539.0
60°	773.4	551.5	630.5	492.4	482.5
62.5°	723.6	512.2	537.6	443.9	434.1
65°	642.3	449.8	432.0	354.7	354.7
67.5°	552.7	385.0	350.0	290.3	250.8
70°	490.9	343.0	297.5	231.4	205.1
72.5°	425.0	298.1	243.8	189.6	159.4
75°	331.2	229.2	169.8	121.0	117.7
77.5°	239.4	165.1	114.3	89.7	90.1
80°	181.6	125.6	74.0	72.4	74.0
82.5°	127.7	86.4	55.1	57.5	57.8
85°	57.1	37.4	33.7	26.8	25.2
87.5°	12.1	10.8	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P855521

CATALOG NUMBER: SQ2-PH1-075D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.81	24.40	23.18	24.72	25.03	21.49	23.08	21.85	23.39	23.70
	3H	24.89	26.32	25.27	26.65	27.01	22.57	24.00	22.95	24.33	24.69
	4H	25.65	27.00	26.05	27.35	27.72	22.82	24.16	23.22	24.51	24.89
	6H	26.17	27.42	26.58	27.78	28.17	23.00	24.24	23.41	24.61	25.00
	8H	26.32	27.50	26.74	27.89	28.29	23.05	24.24	23.47	24.62	25.02
	12H	26.39	27.52	26.82	27.90	28.33	23.07	24.21	23.50	24.59	25.02
4H	2H	23.27	24.62	23.67	24.96	25.34	22.21	23.56	22.61	23.90	24.28
	3H	25.44	26.56	25.85	26.96	27.36	23.45	24.57	23.86	24.97	25.37
	4H	26.29	27.29	26.72	27.71	28.15	23.76	24.77	24.19	25.18	25.62
	6H	26.91	27.79	27.37	28.23	28.69	24.01	24.89	24.46	25.33	25.78
	8H	27.10	27.92	27.56	28.36	28.83	24.08	24.90	24.54	25.34	25.81
	12H	27.20	27.93	27.68	28.41	28.88	24.12	24.86	24.60	25.33	25.80
8H	4H	26.36	27.18	26.82	27.62	28.09	24.03	24.85	24.49	25.29	25.76
	6H	27.04	27.72	27.54	28.21	28.68	24.33	25.01	24.83	25.50	25.98
	8H	27.27	27.88	27.78	28.39	28.87	24.44	25.05	24.95	25.56	26.04
	12H	27.42	27.95	27.93	28.45	29.01	24.52	25.05	25.03	25.55	26.11
12H	4H	26.35	27.08	26.83	27.56	28.03	24.06	24.80	24.54	25.27	25.74
	6H	27.02	27.63	27.53	28.14	28.62	24.37	24.98	24.88	25.48	25.97
	8H	27.29	27.82	27.79	28.31	28.88	24.52	25.05	25.03	25.55	26.11