

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854033

Luminaire Tested: SQ2-PH1-075D-940-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P854033  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PH1-075D-940-UNV-STD-W-4  
Description: CORELITE SQ2 SURFACE LED LUMINAIRE  
DOWNLIGHT 750 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3547.3 lumens  
Efficiency: N/A  
Efficacy: 132.9 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 26.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P854033  
CATALOG NUMBER: SQ2-PH1-075D-940-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P854033

CATALOG NUMBER: SQ2-PH1-075D-940-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85				85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72				72
3	91	81	73	67	89	80	72	67	77	71	65	74	69	64	72	67	63	61				61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	55	64	59	55	53				53
5	77	65	56	50	75	64	55	49	62	54	49	60	53	48	58	52	48	46				46
6	72	59	50	44	70	58	49	43	56	48	43	54	48	43	53	47	42	40				40
7	66	53	45	39	65	52	44	38	51	43	38	49	43	38	48	42	38	36				36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32				32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29				29
10	54	41	34	28	53	41	33	28	40	33	28	39	32	28	38	32	28	26				26

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	25893	25893	25893
5°	26042	24485	23668
10°	25443	22291	21515
15°	25558	20966	21093
20°	24646	20319	21263
25°	24195	20225	20769
30°	23670	20171	20939
35°	23489	19941	24541
40°	23509	19812	19458
45°	23519	19059	16760
50°	23189	19432	15714
55°	22894	21090	15077
60°	22666	18477	14141
65°	22269	14984	12302
70°	21036	12751	8790
75°	18752	9613	6662
80°	15323	6239	6239
85°	9615	5650	4242

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 23519 cd/sqm



TEST NUMBER: P854033

CATALOG NUMBER: SQ2-PH1-075D-940-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.1	4.0
10°-20°	371.2	10.5
20°-30°	544.3	15.3
30°-40°	659.1	18.6
40°-50°	648.2	18.3
50°-60°	564.2	15.9
60°-70°	392.3	11.1
70°-80°	186.0	5.2
80°-90°	41.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1056.6	29.8
0°-40°	1715.7	48.4
0°-60°	2928.1	82.5
0°-90°	3547.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3547.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1604	1604	1604	1604	1604	
5°	1607	1605	1511	1463	1460	151
15°	1529	1362	1254	1246	1262	426
25°	1358	1155	1135	1170	1166	625
35°	1192	964	1012	1099	1245	746
45°	1030	763	835	864	734	792
55°	813	594	749	540	536	727
65°	583	408	392	322	322	573
75°	301	208	154	110	107	319
85°	52	34	30	24	23	71
90°	0	0	0	0	0	



TEST NUMBER: P854033

CATALOG NUMBER: SQ2-PH1-075D-940-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1603.7	1603.7	1603.7	1603.7	1603.7
2.5°	1600.1	1616.8	1579.3	1564.6	1562.2
5°	1606.8	1605.3	1510.7	1463.3	1460.3
7.5°	1577.5	1531.2	1418.2	1365.9	1363.6
10°	1551.9	1481.7	1359.6	1312.3	1312.3
12.5°	1545.7	1435.0	1312.0	1277.0	1284.2
15°	1529.0	1361.9	1254.3	1245.5	1261.9
17.5°	1473.4	1293.5	1209.4	1229.4	1248.5
20°	1434.4	1256.8	1182.6	1219.6	1237.5
22.5°	1401.4	1221.5	1163.1	1203.6	1213.1
25°	1358.1	1155.1	1135.3	1170.3	1165.8
27.5°	1306.2	1094.3	1107.5	1128.9	1131.6
30°	1269.6	1057.7	1081.9	1103.7	1123.1
32.5°	1234.2	1015.1	1053.8	1105.5	1149.9
35°	1191.7	963.5	1011.7	1098.9	1245.1
37.5°	1147.2	902.5	969.3	1042.6	1089.2
40°	1115.4	858.8	940.0	1030.6	923.2
42.5°	1081.3	824.6	896.0	1013.0	831.6
45°	1030.0	762.9	834.7	863.8	734.0
47.5°	969.6	715.0	793.2	720.3	669.6
50°	923.2	683.0	773.6	658.4	625.6
52.5°	878.0	649.7	760.2	607.4	585.3
55°	813.3	594.0	749.2	540.1	535.6
57.5°	744.6	537.3	662.6	481.4	489.2
60°	701.9	500.5	572.2	446.9	437.9
62.5°	656.8	464.9	488.0	402.9	394.0
65°	582.9	408.3	392.2	322.0	322.0
67.5°	501.7	349.5	317.7	263.5	227.7
70°	445.6	311.3	270.1	210.0	186.2
72.5°	385.8	270.6	221.3	172.1	144.7
75°	300.6	208.1	154.1	109.8	106.8
77.5°	217.3	149.9	103.8	81.5	81.8
80°	164.8	114.1	67.1	65.6	67.1
82.5°	116.0	78.4	50.0	52.2	52.5
85°	51.9	34.0	30.5	24.4	22.9
87.5°	11.0	9.8	6.1	6.1	6.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P854033

CATALOG NUMBER: SQ2-PH1-075D-940-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.47	24.07	22.84	24.38	24.69	21.15	22.74	21.51	23.05	23.37
	3H	24.55	25.98	24.93	26.31	26.67	22.23	23.66	22.61	23.99	24.35
	4H	25.32	26.66	25.71	27.01	27.38	22.48	23.82	22.88	24.17	24.55
	6H	25.84	27.08	26.25	27.45	27.84	22.66	23.90	23.07	24.27	24.66
	8H	25.98	27.17	26.41	27.56	27.96	22.71	23.90	23.14	24.29	24.69
	12H	26.05	27.18	26.48	27.57	28.00	22.73	23.87	23.16	24.25	24.68
4H	2H	22.93	24.28	23.33	24.63	25.00	21.87	23.22	22.27	23.57	23.94
	3H	25.11	26.22	25.52	26.62	27.02	23.12	24.24	23.53	24.64	25.04
	4H	25.95	26.96	26.38	27.37	27.81	23.42	24.43	23.85	24.85	25.28
	6H	26.57	27.45	27.03	27.89	28.35	23.67	24.55	24.13	24.99	25.45
	8H	26.76	27.58	27.22	28.02	28.49	23.74	24.56	24.20	25.01	25.47
	12H	26.86	27.60	27.34	28.07	28.54	23.78	24.52	24.27	25.00	25.47
8H	4H	26.02	26.84	26.48	27.29	27.75	23.69	24.51	24.16	24.96	25.42
	6H	26.70	27.38	27.20	27.87	28.35	24.00	24.67	24.49	25.16	25.64
	8H	26.94	27.54	27.45	28.05	28.54	24.10	24.71	24.62	25.22	25.71
	12H	27.08	27.62	27.59	28.11	28.67	24.18	24.72	24.69	25.21	25.77
12H	4H	26.01	26.74	26.49	27.22	27.69	23.73	24.46	24.21	24.94	25.41
	6H	26.68	27.29	27.19	27.80	28.29	24.03	24.64	24.54	25.15	25.63
	8H	26.95	27.49	27.46	27.98	28.54	24.18	24.72	24.69	25.21	25.77