

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854198

Luminaire Tested: SQ2-PR1-050D-940-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854198
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PR1-050D-940-UNV-STD-W-4
Description: CORELITE SQ2 SURFACE LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2496.3 lumens
Efficiency: N/A
Efficacy: 140.2 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 17.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854198
CATALOG NUMBER: SQ2-PR1-050D-940-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854198

CATALOG NUMBER: SQ2-PR1-050D-940-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	101	97	100	97	94	96	94	92	92	90	89				87	
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	80	77				75	
3	93	84	77	71	91	82	76	70	80	74	69	77	72	68	74	70	67				65	
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58				56	
5	80	68	60	53	78	67	59	53	65	58	53	63	57	52	61	56	52				50	
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46				44	
7	69	56	48	42	67	55	47	42	54	47	42	52	46	41	51	45	41				39	
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37				35	
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34				32	
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31				29	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16755	16755	16755
5°	16733	16835	17041
10°	16908	17343	17602
15°	16903	16991	17133
20°	16631	16885	17448
25°	16582	17054	18166
30°	16565	17434	18340
35°	16409	17804	17075
40°	16029	17144	15026
45°	15168	15047	11883
50°	13790	12303	9218
55°	12118	10123	7175
60°	10485	8096	5909
65°	9051	6709	5173
70°	8139	5943	4593
75°	7455	5147	4223
80°	6490	4128	4128
85°	4705	3724	1964

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 16397 cd/sqm



TEST NUMBER: P854198

CATALOG NUMBER: SQ2-PR1-050D-940-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.2	4.0
10°-20°	290.1	11.6
20°-30°	448.4	18.0
30°-40°	539.3	21.6
40°-50°	484.3	19.4
50°-60°	324.4	13.0
60°-70°	188.7	7.6
70°-80°	96.9	3.9
80°-90°	23.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	838.7	33.6
0°-40°	1378.0	55.2
0°-60°	2186.7	87.6
0°-90°	2496.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2496.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1038	1038	1038	1038	1038	
5°	1032	1050	1039	1041	1051	99
15°	1011	1053	1016	1020	1025	284
25°	931	968	957	993	1020	429
35°	832	840	903	886	866	519
45°	664	718	659	556	520	508
55°	430	447	360	278	255	387
65°	237	242	176	143	135	240
75°	120	116	82	70	68	127
85°	25	20	20	14	11	32
90°	0	0	0	0	0	



TEST NUMBER: P854198

CATALOG NUMBER: SQ2-PR1-050D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1037.7	1037.7	1037.7	1037.7	1037.7
2.5°	1033.4	1045.9	1034.3	1035.2	1037.7
5°	1032.4	1050.0	1038.7	1041.1	1051.4
7.5°	1032.2	1057.2	1051.9	1058.3	1071.9
10°	1031.3	1061.3	1057.8	1059.2	1073.6
12.5°	1026.3	1061.2	1045.1	1043.8	1051.6
15°	1011.2	1052.6	1016.5	1019.8	1025.0
17.5°	984.8	1028.0	993.7	1005.3	1015.5
20°	967.9	1010.3	982.7	997.9	1015.5
22.5°	952.6	995.0	972.5	993.8	1018.0
25°	930.8	968.1	957.3	992.8	1019.7
27.5°	908.0	929.9	942.7	990.3	1009.1
30°	888.5	903.0	935.1	976.5	983.7
32.5°	867.4	876.1	924.9	946.5	937.2
35°	832.5	839.7	903.3	886.0	866.3
37.5°	791.0	805.9	854.9	804.9	782.3
40°	760.5	785.4	813.4	738.8	712.9
42.5°	723.3	763.0	758.4	663.4	631.7
45°	664.3	718.1	659.0	555.6	520.4
47.5°	594.7	649.9	553.2	460.9	428.0
50°	549.0	593.5	489.8	403.2	367.0
52.5°	502.4	534.5	435.6	349.2	316.3
55°	430.5	447.1	359.6	277.7	254.9
57.5°	364.5	375.1	293.9	224.3	207.5
60°	324.7	332.0	250.7	196.4	183.0
62.5°	288.3	293.9	216.0	172.8	162.7
65°	236.9	242.1	175.6	142.6	135.4
67.5°	196.1	198.8	144.5	118.5	111.7
70°	172.4	173.5	125.9	102.5	97.3
72.5°	151.3	149.8	108.1	89.0	85.5
75°	119.5	116.4	82.5	69.8	67.7
77.5°	89.3	86.0	58.0	53.7	53.7
80°	69.8	65.7	44.4	44.4	44.4
82.5°	52.0	46.3	34.3	34.3	33.4
85°	25.4	20.2	20.1	13.7	10.6
87.5°	6.8	6.8	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P854198

CATALOG NUMBER: SQ2-PR1-050D-940-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.50	21.99	20.86	22.31	22.62	17.22	18.72	17.59	19.03	19.34
	3H	21.78	23.11	22.15	23.44	23.80	18.33	19.67	18.71	20.00	20.36
	4H	22.26	23.51	22.66	23.86	24.24	18.76	20.01	19.16	20.36	20.74
	6H	22.60	23.76	23.02	24.13	24.52	19.12	20.28	19.54	20.64	21.04
	8H	22.70	23.80	23.13	24.19	24.59	19.23	20.32	19.65	20.71	21.12
	12H	22.75	23.80	23.18	24.18	24.61	19.25	20.30	19.68	20.69	21.12
4H	2H	20.65	21.90	21.05	22.25	22.63	17.86	19.12	18.26	19.47	19.84
	3H	22.18	23.21	22.59	23.61	24.01	19.19	20.22	19.60	20.62	21.02
	4H	22.80	23.72	23.23	24.14	24.58	19.72	20.65	20.15	21.06	21.50
	6H	23.28	24.09	23.74	24.53	24.99	20.18	20.99	20.64	21.43	21.89
	8H	23.42	24.18	23.89	24.62	25.09	20.32	21.07	20.78	21.51	21.98
	12H	23.50	24.18	23.99	24.65	25.13	20.37	21.04	20.85	21.52	21.99
8H	4H	22.86	23.62	23.33	24.06	24.53	20.06	20.82	20.53	21.26	21.73
	6H	23.43	24.05	23.93	24.55	25.02	20.62	21.24	21.12	21.73	22.21
	8H	23.63	24.19	24.15	24.70	25.19	20.80	21.36	21.32	21.87	22.36
	12H	23.76	24.26	24.27	24.75	25.31	20.89	21.39	21.40	21.88	22.45
12H	4H	22.85	23.52	23.33	24.00	24.47	20.11	20.78	20.59	21.26	21.73
	6H	23.42	23.98	23.93	24.49	24.98	20.68	21.24	21.19	21.75	22.24
	8H	23.66	24.15	24.17	24.64	25.21	20.91	21.41	21.42	21.90	22.47