

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P824196

Luminaire Tested: CB2-D-055U-085D-830-1D-UNV-STD-W-4

Issue Date: 4/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P824196
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-13, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 4/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-D-055U-085D-830-1D-UNV-STD-W-4
Description: CORELITE Bryx SLOT LED LUMINAIRE, UPLIGHT DIFFUSER DUST COVER
2-INCH APERTURE
DOWNLIGHT 850 LUMENS PER FOOT
UPLIGHT 550 LUMENS PER FOOT
Light Source: 80 CRI, 3000K CCT LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5131.9 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 44.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P824196

CATALOG NUMBER: CB2-D-055U-085D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P824196

CATALOG NUMBER: CB2-D-055U-085D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	89	94	90	87	83	78	76	74	68	66	64	58	57	56	51
2	92	84	78	73	85	79	73	69	69	65	61	60	57	54	52	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37
4	77	66	58	52	71	62	55	49	54	49	44	48	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	34	30	27	25
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	44	36	30	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23080	23080	23080
5°	22883	22920	23079
10°	22753	22700	22682
15°	22394	22248	22064
20°	22040	21551	21251
25°	21449	20844	20260
30°	20854	19937	19181
35°	20172	19007	18101
40°	19447	18133	17071
45°	18718	17220	16070
50°	18063	16331	15093
55°	17254	15405	14172
60°	16327	14526	13255
65°	15348	13547	12335
70°	14259	12451	11163
75°	12975	11265	10108
80°	11605	9870	9158
85°	8913	8114	6695

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18718 cd/sqm



TEST NUMBER: P824196

CATALOG NUMBER: CB2-D-055U-085D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.6	2.4
10°-20°	347.4	6.8
20°-30°	499.4	9.7
30°-40°	561.4	10.9
40°-50°	542.3	10.6
50°-60°	458.2	8.9
60°-70°	329.1	6.4
70°-80°	179.9	3.5
80°-90°	47.8	0.9
90°-100°	30.9	0.6
100°-110°	127.6	2.5
110°-120°	231.6	4.5
120°-130°	315.1	6.1
130°-140°	363.8	7.1
140°-150°	366.6	7.1
150°-160°	316.4	6.2
160°-170°	214.4	4.2
170°-180°	75.6	1.5
0°-30°	971.4	18.9
0°-40°	1532.8	29.9
0°-60°	2533.2	49.4
0°-90°	3090.0	60.2
90°-120°	390.1	7.6
90°-150°	1435.6	28.0
90°-180°	2042.0	39.8
0°-180°	5131.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1325	1325	1325	1325	1325	
5°	1309	1327	1311	1311	1320	124
15°	1242	1253	1234	1222	1224	350
25°	1116	1117	1085	1060	1054	514
35°	949	938	894	859	851	593
45°	760	744	699	662	652	587
55°	568	547	507	476	467	508
65°	372	358	329	305	299	369
75°	193	181	167	154	150	206
85°	45	42	41	36	34	53
90°	0	0	1	0	1	3
95°	30	26	25	19	19	35
105°	126	124	121	114	113	134
115°	240	239	235	228	227	237
125°	357	360	353	345	346	318
135°	475	481	473	464	467	366
145°	589	596	586	580	584	368
155°	689	696	686	682	687	317
165°	761	769	759	755	762	214
175°	798	806	796	791	792	76
180°	801	801	801	801	801	



TEST NUMBER: P824196

CATALOG NUMBER: CB2-D-055U-085D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1325.1	1325.1	1325.1	1325.1	1325.1
2.5°	1316.1	1332.0	1320.2	1321.9	1324.3
5°	1308.8	1326.7	1310.9	1311.1	1320.0
7.5°	1299.5	1316.4	1296.5	1292.8	1301.1
10°	1286.5	1303.4	1283.5	1276.5	1282.5
12.5°	1269.5	1285.5	1266.4	1255.4	1260.5
15°	1241.9	1252.8	1233.8	1221.6	1223.6
17.5°	1211.8	1218.6	1191.1	1181.0	1179.0
20°	1189.1	1195.1	1162.7	1148.5	1146.5
22.5°	1159.9	1165.1	1131.1	1113.6	1110.8
25°	1116.1	1117.1	1084.6	1060.1	1054.2
27.5°	1070.2	1067.0	1031.0	1002.1	994.3
30°	1036.9	1033.0	991.3	960.7	953.7
32.5°	1001.2	994.1	952.3	919.3	912.3
35°	948.7	937.7	893.9	859.2	851.3
37.5°	892.7	880.3	837.3	799.5	790.6
40°	855.3	841.4	797.5	759.7	750.8
42.5°	818.0	802.5	757.7	719.9	710.2
45°	759.9	744.1	699.1	662.3	652.4
47.5°	704.7	684.5	640.8	604.3	594.4
50°	666.6	644.8	602.7	566.9	557.0
52.5°	627.6	605.0	564.5	530.4	520.5
55°	568.2	547.3	507.3	475.6	466.7
57.5°	509.3	489.3	452.7	422.5	413.8
60°	468.7	451.9	417.0	388.4	380.5
62.5°	429.8	414.5	381.3	355.1	347.2
65°	372.4	358.5	328.7	305.3	299.3
67.5°	316.6	302.7	278.6	257.6	250.8
70°	280.0	266.1	244.5	225.1	219.2
72.5°	245.1	230.4	212.9	195.1	190.7
75°	192.8	180.9	167.4	154.1	150.2
77.5°	146.5	135.0	125.2	115.8	114.9
80°	115.7	105.7	98.4	92.3	91.3
82.5°	86.4	78.9	74.1	69.6	69.4
85°	44.6	41.7	40.6	35.5	33.5
87.5°	13.0	13.0	11.5	9.7	9.9
90°	0.0	0.0	0.6	0.0	0.6
92.5°	7.5	6.5	6.1	4.0	4.6
95°	30.0	26.3	25.0	19.4	19.4
97.5°	56.6	52.9	51.0	45.2	44.0
100°	75.6	71.9	69.9	63.7	62.5
102.5°	95.1	93.3	89.9	83.2	81.9
105°	126.2	124.3	121.2	114.3	113.0
107.5°	158.1	158.5	153.8	148.1	146.4
110°	181.1	180.5	176.7	171.1	169.9



TEST NUMBER: P824196

CATALOG NUMBER: CB2-D-055U-085D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	204.6	203.5	199.7	194.1	192.9
115°	239.8	239.2	234.8	227.9	227.3
117.5°	273.3	275.3	270.1	262.8	262.6
120°	297.3	299.7	293.5	287.3	286.0
122.5°	320.8	323.7	317.5	310.3	310.5
125°	356.6	360.3	352.9	345.4	346.0
127.5°	391.2	395.7	388.8	381.2	382.0
130°	414.7	420.2	412.8	404.7	406.0
132.5°	438.7	444.2	436.8	428.2	430.4
135°	475.3	480.8	472.8	464.1	467.2
137.5°	509.8	515.3	506.5	499.2	502.9
140°	532.7	538.2	529.0	522.2	525.9
142.5°	555.2	561.7	552.0	544.7	549.4
145°	588.9	595.7	586.4	579.7	584.0
147.5°	620.9	627.6	618.3	611.8	616.2
150°	641.4	648.1	638.3	632.8	637.7
152.5°	660.4	668.1	657.8	652.3	658.6
155°	688.9	695.6	685.8	681.5	687.0
157.5°	713.6	721.4	711.6	708.0	712.4
160°	730.1	737.4	727.6	724.0	728.8
162.5°	742.6	750.4	741.1	737.0	742.8
165°	761.3	769.3	759.4	755.2	761.9
167.5°	776.1	784.5	774.6	770.2	777.1
170°	785.1	793.0	782.6	777.7	785.1
172.5°	791.1	799.5	788.6	783.7	788.6
175°	797.5	806.1	795.7	790.7	792.5
177.5°	800.7	807.5	799.2	794.8	800.7
180°	800.7	800.7	800.7	800.7	800.7



TEST NUMBER: P824196
 CATALOG NUMBER: CB2-D-055U-085D-830-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.80	19.75	19.67	20.63	21.75	17.70	18.65	18.57	19.54	20.65
	3H	20.45	21.30	21.33	22.20	23.34	19.24	20.09	20.12	20.98	22.13
	4H	21.09	21.89	21.98	22.79	23.94	19.81	20.62	20.71	21.52	22.67
	6H	21.49	22.23	22.40	23.14	24.31	20.19	20.93	21.10	21.84	23.01
	8H	21.64	22.35	22.56	23.27	24.44	20.33	21.04	21.25	21.96	23.13
	12H	21.72	22.39	22.64	23.31	24.50	20.40	21.07	21.32	21.99	23.18
4H	2H	19.22	20.02	20.12	20.92	22.08	18.35	19.15	19.25	20.05	21.21
	3H	21.10	21.77	22.01	22.70	23.87	20.09	20.76	21.00	21.69	22.86
	4H	21.85	22.46	22.77	23.39	24.58	20.77	21.38	21.69	22.30	23.50
	6H	22.37	22.90	23.31	23.85	25.05	21.25	21.77	22.18	22.72	23.92
	8H	22.58	23.07	23.52	24.02	25.23	21.44	21.93	22.38	22.88	24.09
	12H	22.69	23.13	23.65	24.10	25.31	21.53	21.97	22.49	22.94	24.15
8H	4H	22.01	22.50	22.95	23.45	24.66	21.05	21.54	21.99	22.48	23.69
	6H	22.66	23.06	23.62	24.05	25.26	21.65	22.06	22.62	23.05	24.26
	8H	22.95	23.31	23.92	24.28	25.51	21.93	22.29	22.90	23.27	24.49
	12H	23.13	23.44	24.10	24.41	25.69	22.08	22.40	23.06	23.37	24.65
12H	4H	21.99	22.44	22.95	23.40	24.62	21.05	21.50	22.01	22.46	23.68
	6H	22.69	23.04	23.66	24.02	25.25	21.72	22.08	22.69	23.06	24.28
	8H	23.01	23.32	23.98	24.29	25.57	22.03	22.34	23.00	23.32	24.59