

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P824199

Luminaire Tested: CB2-D-055U-120D-830-1D-UNV-STD-W-4

Issue Date: 4/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P824199
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-13, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 4/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-D-055U-120D-830-1D-UNV-STD-W-4
Description: CORELITE Bryx SLOT LED LUMINAIRE, UPLIGHT DIFFUSER DUST COVER
2-INCH APERTURE
DOWNLIGHT 1200 LUMENS PER FOOT
UPLIGHT 550 LUMENS PER FOOT
Light Source: 80 CRI, 3000K CCT LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6440.7 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P824199

CATALOG NUMBER: CB2-D-055U-120D-830-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P824199

CATALOG NUMBER: CB2-D-055U-120D-830-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	68																												
1	102	98	94	90	96	92	89	86	82	80	77	73	71	70	65	63	62	58																												
2	93	86	79	74	88	81	76	71	73	68	65	65	61	58	57	55	53	49																												
3	85	76	68	62	80	72	65	60	64	59	55	57	53	50	51	48	45	42																												
4	78	67	59	53	74	64	57	51	57	52	47	51	47	43	46	42	39	36																												
5	72	60	52	46	68	57	50	44	52	45	41	46	41	37	41	37	34	32																												
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	38	34	30	28																												
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	35	30	27	25																												
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	32	28	24	22																												
9	54	41	33	28	51	39	32	27	36	30	26	33	27	24	29	25	22	20																												
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	32854	32854	32854
5°	32576	32627	32854
10°	32390	32314	32289
15°	31878	31669	31410
20°	31376	30679	30251
25°	30533	29672	28840
30°	29687	28380	27306
35°	28715	27057	25766
40°	27684	25813	24301
45°	26647	24514	22876
50°	25712	23246	21485
55°	24560	21930	20175
60°	23245	20678	18866
65°	21847	19288	17561
70°	20299	17727	15889
75°	18466	16037	14388
80°	16520	14052	13039
85°	12710	11551	9532

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26647 cd/sqm



TEST NUMBER: P824199

CATALOG NUMBER: CB2-D-055U-120D-830-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.4	2.8
10°-20°	494.5	7.7
20°-30°	711.0	11.0
30°-40°	799.1	12.4
40°-50°	771.9	12.0
50°-60°	652.2	10.1
60°-70°	468.5	7.3
70°-80°	256.1	4.0
80°-90°	68.1	1.1
90°-100°	30.9	0.5
100°-110°	127.6	2.0
110°-120°	231.6	3.6
120°-130°	315.1	4.9
130°-140°	363.8	5.6
140°-150°	366.6	5.7
150°-160°	316.4	4.9
160°-170°	214.4	3.3
170°-180°	75.6	1.2
0°-30°	1382.8	21.5
0°-40°	2182.0	33.9
0°-60°	3606.1	56.0
0°-90°	4398.7	68.3
90°-120°	390.1	6.1
90°-150°	1435.6	22.3
90°-180°	2042.0	31.7
0°-180°	6440.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1886	1886	1886	1886	1886	
5°	1863	1889	1866	1866	1879	177
15°	1768	1783	1756	1739	1742	498
25°	1589	1590	1544	1509	1501	731
35°	1350	1335	1272	1223	1212	844
45°	1082	1059	995	943	929	836
55°	809	779	722	677	664	723
65°	530	510	468	435	426	526
75°	274	258	238	219	214	294
85°	64	59	58	50	48	76
90°	0	0	1	0	1	4
95°	30	26	25	19	19	35
105°	126	124	121	114	113	134
115°	240	239	235	228	227	237
125°	357	360	353	345	346	318
135°	475	481	473	464	467	366
145°	589	596	586	580	584	368
155°	689	696	686	682	687	317
165°	761	769	759	755	762	214
175°	798	806	796	791	792	76
180°	801	801	801	801	801	

TEST NUMBER: P824199

CATALOG NUMBER: CB2-D-055U-120D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1886.3	1886.3	1886.3	1886.3	1886.3
2.5°	1873.6	1896.2	1879.4	1881.8	1885.2
5°	1863.2	1888.6	1866.1	1866.4	1879.1
7.5°	1849.9	1873.9	1845.6	1840.4	1852.2
10°	1831.4	1855.4	1827.1	1817.2	1825.7
12.5°	1807.2	1830.0	1802.8	1787.1	1794.5
15°	1767.9	1783.4	1756.3	1739.1	1741.9
17.5°	1725.1	1734.7	1695.7	1681.2	1678.3
20°	1692.8	1701.2	1655.2	1634.9	1632.1
22.5°	1651.2	1658.5	1610.2	1585.2	1581.3
25°	1588.8	1590.2	1544.0	1509.1	1500.7
27.5°	1523.5	1519.0	1467.7	1426.5	1415.5
30°	1476.1	1470.5	1411.1	1367.6	1357.7
32.5°	1425.3	1415.1	1355.7	1308.6	1298.8
35°	1350.5	1334.9	1272.5	1223.1	1211.8
37.5°	1270.7	1253.2	1191.9	1138.1	1125.4
40°	1217.6	1197.8	1135.3	1081.5	1068.8
42.5°	1164.4	1142.4	1078.6	1024.9	1011.0
45°	1081.8	1059.2	995.2	942.8	928.7
47.5°	1003.2	974.4	912.2	860.2	846.1
50°	948.9	917.9	857.9	807.1	792.9
52.5°	893.5	861.3	803.6	755.1	740.9
55°	808.8	779.2	722.2	677.1	664.4
57.5°	725.1	696.5	644.5	601.4	589.0
60°	667.3	643.3	593.6	552.9	541.6
62.5°	611.8	590.1	542.8	505.6	494.3
65°	530.1	510.3	468.0	434.6	426.1
67.5°	450.6	430.9	396.6	366.6	357.0
70°	398.6	378.9	348.1	320.5	312.0
72.5°	349.0	328.1	303.0	277.8	271.5
75°	274.4	257.5	238.3	219.4	213.8
77.5°	208.6	192.2	178.2	164.9	163.5
80°	164.7	150.5	140.1	131.4	130.0
82.5°	123.1	112.3	105.4	99.1	98.8
85°	63.6	59.3	57.8	50.5	47.7
87.5°	18.5	18.5	16.3	13.9	14.0
90°	0.0	0.0	0.6	0.0	0.6
92.5°	7.5	6.5	6.1	4.0	4.6
95°	30.0	26.3	25.0	19.4	19.4
97.5°	56.6	52.9	51.0	45.2	44.0
100°	75.6	71.9	69.9	63.7	62.5
102.5°	95.1	93.3	89.9	83.2	81.9
105°	126.2	124.3	121.2	114.3	113.0
107.5°	158.1	158.5	153.8	148.1	146.4
110°	181.1	180.5	176.7	171.1	169.9



TEST NUMBER: P824199

CATALOG NUMBER: CB2-D-055U-120D-830-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	204.6	203.5	199.7	194.1	192.9
115°	239.8	239.2	234.8	227.9	227.3
117.5°	273.3	275.3	270.1	262.8	262.6
120°	297.3	299.7	293.5	287.3	286.0
122.5°	320.8	323.7	317.5	310.3	310.5
125°	356.6	360.3	352.9	345.4	346.0
127.5°	391.2	395.7	388.8	381.2	382.0
130°	414.7	420.2	412.8	404.7	406.0
132.5°	438.7	444.2	436.8	428.2	430.4
135°	475.3	480.8	472.8	464.1	467.2
137.5°	509.8	515.3	506.5	499.2	502.9
140°	532.7	538.2	529.0	522.2	525.9
142.5°	555.2	561.7	552.0	544.7	549.4
145°	588.9	595.7	586.4	579.7	584.0
147.5°	620.9	627.6	618.3	611.8	616.2
150°	641.4	648.1	638.3	632.8	637.7
152.5°	660.4	668.1	657.8	652.3	658.6
155°	688.9	695.6	685.8	681.5	687.0
157.5°	713.6	721.4	711.6	708.0	712.4
160°	730.1	737.4	727.6	724.0	728.8
162.5°	742.6	750.4	741.1	737.0	742.8
165°	761.3	769.3	759.4	755.2	761.9
167.5°	776.1	784.5	774.6	770.2	777.1
170°	785.1	793.0	782.6	777.7	785.1
172.5°	791.1	799.5	788.6	783.7	788.6
175°	797.5	806.1	795.7	790.7	792.5
177.5°	800.7	807.5	799.2	794.8	800.7
180°	800.7	800.7	800.7	800.7	800.7



TEST NUMBER: P824199
 CATALOG NUMBER: CB2-D-055U-120D-830-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.68	21.71	21.46	22.52	23.50	19.58	20.61	20.36	21.42	22.40
	3H	22.34	23.27	23.13	24.08	25.10	21.12	22.05	21.92	22.86	23.88
	4H	22.97	23.85	23.79	24.67	25.70	21.70	22.58	22.52	23.40	24.43
	6H	23.38	24.19	24.21	25.02	26.06	22.08	22.89	22.91	23.72	24.76
	8H	23.54	24.31	24.37	25.16	26.20	22.23	23.00	23.06	23.85	24.89
	12H	23.62	24.35	24.46	25.20	26.26	22.29	23.03	23.14	23.87	24.94
4H	2H	21.11	21.99	21.93	22.81	23.83	20.23	21.11	21.05	21.93	22.96
	3H	22.99	23.72	23.82	24.58	25.62	21.98	22.72	22.82	23.57	24.61
	4H	23.75	24.41	24.59	25.27	26.34	22.66	23.33	23.51	24.19	25.25
	6H	24.28	24.85	25.14	25.73	26.80	23.15	23.72	24.01	24.60	25.68
	8H	24.48	25.02	25.35	25.90	26.98	23.34	23.88	24.21	24.76	25.84
	12H	24.60	25.08	25.48	25.98	27.07	23.44	23.92	24.32	24.82	25.91
8H	4H	23.92	24.45	24.78	25.33	26.41	22.95	23.49	23.82	24.36	25.45
	6H	24.56	25.01	25.46	25.93	27.01	23.56	24.01	24.46	24.92	26.01
	8H	24.86	25.25	25.76	26.16	27.26	23.84	24.23	24.74	25.14	26.25
	12H	25.04	25.39	25.94	26.29	27.44	24.00	24.35	24.90	25.25	26.40
12H	4H	23.90	24.39	24.79	25.28	26.37	22.96	23.45	23.85	24.34	25.43
	6H	24.59	24.99	25.50	25.90	27.00	23.63	24.02	24.53	24.93	26.03
	8H	24.92	25.27	25.82	26.17	27.32	23.94	24.29	24.85	25.19	26.35