

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P824198

Luminaire Tested: CB2-D-055U-085D-840-1D-UNV-STD-W-4

Issue Date: 4/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P824198
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-13, G2-2312-242-18)
Test Lab: INNOVATION CENTER
Issue Date: 4/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB2-D-055U-085D-840-1D-UNV-STD-W-4
Description: CORELITE Bryx SLOT LED LUMINAIRE, UPLIGHT DIFFUSER DUST COVER
2-INCH APERTURE
DOWNLIGHT 850 LUMENS PER FOOT
UPLIGHT 550 LUMENS PER FOOT
Light Source: 80 CRI, 4000K CCT LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5524.4 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.15' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 44.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P824198

CATALOG NUMBER: CB2-D-055U-085D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P824198

CATALOG NUMBER: CB2-D-055U-085D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60																				
1	100	96	92	89	94	90	87	83	78	76	74	68	66	64	58	57	56	51																				
2	92	84	78	73	85	79	73	69	69	65	61	60	57	54	52	49	47	43																				
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37																				
4	77	66	58	52	71	62	55	49	54	49	44	48	43	40	41	38	35	32																				
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	34	31	28																				
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	34	30	27	25																				
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22																				
8	56	44	36	30	52	41	34	29	37	31	27	33	28	24	29	25	22	20																				
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18																				
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24844	24844	24844
5°	24633	24671	24845
10°	24493	24435	24416
15°	24107	23948	23751
20°	23727	23200	22876
25°	23088	22439	21808
30°	22449	21461	20649
35°	21713	20459	19485
40°	20934	19519	18376
45°	20151	18535	17299
50°	19444	17580	16247
55°	18572	16583	15256
60°	17578	15637	14268
65°	16518	14585	13279
70°	15349	13403	12013
75°	13964	12127	10875
80°	12488	10622	9860
85°	9612	8733	7194

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20151 cd/sqm



TEST NUMBER: P824198

CATALOG NUMBER: CB2-D-055U-085D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.1	2.4
10°-20°	373.9	6.8
20°-30°	537.6	9.7
30°-40°	604.3	10.9
40°-50°	583.7	10.6
50°-60°	493.2	8.9
60°-70°	354.3	6.4
70°-80°	193.6	3.5
80°-90°	51.5	0.9
90°-100°	33.3	0.6
100°-110°	137.3	2.5
110°-120°	249.3	4.5
120°-130°	339.2	6.1
130°-140°	391.6	7.1
140°-150°	394.6	7.1
150°-160°	340.5	6.2
160°-170°	230.8	4.2
170°-180°	81.4	1.5
0°-30°	1045.7	18.9
0°-40°	1650.0	29.9
0°-60°	2726.9	49.4
0°-90°	3326.3	60.2
90°-120°	419.9	7.6
90°-150°	1545.3	28.0
90°-180°	2198.0	39.8
0°-180°	5524.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1426	1426	1426	1426	1426	
5°	1409	1428	1411	1411	1421	134
15°	1337	1349	1328	1315	1317	377
25°	1201	1202	1168	1141	1135	553
35°	1021	1010	962	925	916	638
45°	818	801	752	713	702	632
55°	612	589	546	512	502	547
65°	401	386	354	329	322	397
75°	208	195	180	166	162	222
85°	48	45	44	38	36	57
90°	0	0	1	0	1	3
95°	32	28	27	21	21	37
105°	136	134	130	123	122	144
115°	258	258	253	245	245	255
125°	384	388	380	372	372	343
135°	512	518	509	500	503	394
145°	634	641	631	624	629	396
155°	742	749	738	734	740	341
165°	820	828	818	813	820	231
175°	858	868	856	851	853	81
180°	862	862	862	862	862	

TEST NUMBER: P824198

CATALOG NUMBER: CB2-D-055U-085D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1426.4	1426.4	1426.4	1426.4	1426.4
2.5°	1416.8	1433.9	1421.2	1423.0	1425.5
5°	1408.9	1428.2	1411.1	1411.3	1421.0
7.5°	1398.9	1417.1	1395.6	1391.7	1400.6
10°	1384.9	1403.1	1381.6	1374.1	1380.5
12.5°	1366.6	1383.9	1363.3	1351.4	1357.0
15°	1336.9	1348.6	1328.1	1315.1	1317.2
17.5°	1304.5	1311.8	1282.2	1271.3	1269.1
20°	1280.1	1286.5	1251.7	1236.3	1234.2
22.5°	1248.6	1254.2	1217.6	1198.7	1195.7
25°	1201.4	1202.5	1167.6	1141.2	1134.8
27.5°	1152.1	1148.6	1109.9	1078.7	1070.4
30°	1116.2	1112.0	1067.1	1034.1	1026.7
32.5°	1077.8	1070.1	1025.1	989.6	982.1
35°	1021.2	1009.5	962.2	924.9	916.4
37.5°	960.9	947.7	901.3	860.7	851.0
40°	920.7	905.8	858.5	817.8	808.2
42.5°	880.5	863.9	815.7	775.0	764.5
45°	818.1	801.0	752.5	713.0	702.3
47.5°	758.6	736.9	689.8	650.5	639.8
50°	717.6	694.1	648.8	610.3	599.6
52.5°	675.6	651.3	607.7	571.0	560.3
55°	611.6	589.2	546.1	512.0	502.4
57.5°	548.3	526.7	487.3	454.8	445.4
60°	504.6	486.4	448.9	418.1	409.6
62.5°	462.7	446.2	410.5	382.3	373.8
65°	400.8	385.9	353.9	328.6	322.2
67.5°	340.8	325.8	299.9	277.3	270.0
70°	301.4	286.5	263.2	242.3	235.9
72.5°	263.9	248.1	229.1	210.0	205.3
75°	207.5	194.7	180.2	165.9	161.6
77.5°	157.7	145.3	134.8	124.7	123.6
80°	124.5	113.8	105.9	99.4	98.3
82.5°	93.1	84.9	79.7	74.9	74.7
85°	48.1	44.9	43.7	38.2	36.0
87.5°	14.0	14.0	12.4	10.5	10.6
90°	0.0	0.0	0.7	0.0	0.7
92.5°	8.1	7.0	6.6	4.3	5.0
95°	32.3	28.3	26.9	20.8	20.8
97.5°	60.9	57.0	54.9	48.6	47.3
100°	81.3	77.4	75.3	68.5	67.2
102.5°	102.3	100.5	96.8	89.5	88.2
105°	135.8	133.8	130.4	123.0	121.7
107.5°	170.2	170.6	165.5	159.4	157.6
110°	195.0	194.3	190.3	184.2	182.9



TEST NUMBER: P824198

CATALOG NUMBER: CB2-D-055U-085D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	220.2	219.1	215.0	208.9	207.6
115°	258.2	257.5	252.8	245.4	244.7
117.5°	294.2	296.3	290.7	282.9	282.6
120°	320.0	322.7	316.0	309.2	307.9
122.5°	345.3	348.5	341.8	334.0	334.3
125°	383.9	387.8	379.9	371.8	372.5
127.5°	421.1	426.0	418.6	410.4	411.2
130°	446.4	452.3	444.4	435.7	437.0
132.5°	472.2	478.1	470.2	461.0	463.4
135°	511.6	517.5	508.9	499.6	502.9
137.5°	548.7	554.7	545.2	537.4	541.3
140°	573.5	579.4	569.4	562.1	566.1
142.5°	597.7	604.7	594.2	586.4	591.4
145°	634.0	641.2	631.3	624.0	628.6
147.5°	668.4	675.6	665.6	658.6	663.3
150°	690.5	697.7	687.1	681.2	686.4
152.5°	710.9	719.2	708.1	702.2	709.0
155°	741.6	748.8	738.2	733.6	739.5
157.5°	768.2	776.6	766.0	762.1	766.8
160°	785.9	793.8	783.2	779.3	784.6
162.5°	799.4	807.8	797.8	793.3	799.6
165°	819.5	828.1	817.5	813.0	820.2
167.5°	835.4	844.5	833.8	829.1	836.5
170°	845.1	853.6	842.4	837.2	845.1
172.5°	851.6	860.6	848.9	843.6	848.9
175°	858.5	867.7	856.5	851.2	853.2
177.5°	861.9	869.3	860.3	855.6	861.9
180°	861.9	861.9	861.9	861.9	861.9



TEST NUMBER: P824198
 CATALOG NUMBER: CB2-D-055U-085D-840-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.06	20.00	19.92	20.89	22.01	17.96	18.90	18.83	19.79	20.91
	3H	20.71	21.56	21.59	22.45	23.60	19.49	20.34	20.37	21.24	22.38
	4H	21.34	22.14	22.24	23.05	24.20	20.07	20.87	20.96	21.77	22.93
	6H	21.75	22.49	22.66	23.40	24.56	20.45	21.18	21.35	22.09	23.26
	8H	21.90	22.60	22.81	23.53	24.70	20.59	21.29	21.50	22.22	23.38
	12H	21.98	22.65	22.90	23.57	24.76	20.65	21.32	21.57	22.24	23.44
4H	2H	19.48	20.28	20.38	21.18	22.34	18.60	19.40	19.50	20.31	21.46
	3H	21.35	22.02	22.27	22.96	24.13	20.35	21.01	21.26	21.95	23.12
	4H	22.10	22.71	23.03	23.64	24.84	21.02	21.63	21.94	22.56	23.76
	6H	22.63	23.15	23.56	24.11	25.30	21.50	22.03	22.44	22.98	24.18
	8H	22.83	23.33	23.77	24.27	25.48	21.69	22.19	22.63	23.13	24.34
	12H	22.95	23.39	23.90	24.35	25.57	21.79	22.23	22.74	23.19	24.41
8H	4H	22.27	22.76	23.20	23.70	24.91	21.30	21.79	22.24	22.74	23.95
	6H	22.91	23.32	23.88	24.31	25.51	21.91	22.32	22.87	23.31	24.51
	8H	23.20	23.56	24.18	24.54	25.77	22.19	22.55	23.16	23.52	24.75
	12H	23.38	23.70	24.36	24.67	25.94	22.34	22.66	23.32	23.63	24.90
12H	4H	22.25	22.69	23.21	23.66	24.87	21.31	21.75	22.27	22.72	23.93
	6H	22.94	23.30	23.91	24.28	25.50	21.97	22.33	22.95	23.31	24.54
	8H	23.26	23.58	24.24	24.55	25.82	22.28	22.60	23.26	23.57	24.85