

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P824318

Luminaire Tested: CB3-0U-030D-840-1D-UNV-STD-W-4

Issue Date: 4/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P824318
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-242-3, G2-2312-242-8)
Test Lab: INNOVATION CENTER
Issue Date: 4/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: CB3-0U-030D-840-1D-UNV-STD-W-4
Description: CORELITE Bryx SLOT LED LUMINAIRE
3-INCH APERTURE
DOWNLIGHT 300 LUMENS PER FOOT
DIRECT ONLY
Light Source: 80 CRI, 4000K CCT LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1140.6 lumens
Efficiency: N/A
Efficacy: 129.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.13 / 1.26
Luminous Opening: Rectangular (W 0.24' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P824318

CATALOG NUMBER: CB3-OU-030D-840-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P824318

CATALOG NUMBER: CB3-OU-030D-840-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	109	105	101	97	107	103	99	96	98	95	93	94	92	90	91	89	87	85				
2	100	92	86	80	97	90	84	79	87	82	77	83	79	76	80	77	74	72				
3	91	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61				
4	84	72	64	58	82	71	63	57	69	62	56	66	60	56	64	59	55	53				
5	78	65	56	50	75	64	56	50	62	55	49	60	54	49	58	53	48	46				
6	72	59	50	44	70	58	50	44	56	49	43	54	48	43	53	47	43	41				
7	67	54	45	39	65	53	45	39	51	44	39	50	43	38	48	43	38	36				
8	62	49	41	35	61	48	40	35	47	40	35	46	39	34	45	39	34	32				
9	58	45	37	32	57	45	37	32	43	36	31	42	36	31	41	35	31	29				
10	55	42	34	29	53	41	34	29	40	33	29	39	33	29	38	33	28	27				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5390	5390	5390
5°	5365	5369	5399
10°	5341	5333	5333
15°	5259	5259	5228
20°	5174	5121	5076
25°	5044	4980	4891
30°	4920	4792	4677
35°	4790	4613	4449
40°	4619	4399	4208
45°	4461	4207	3948
50°	4300	3978	3693
55°	4125	3758	3450
60°	3935	3530	3177
65°	3713	3272	2889
70°	3460	2967	2574
75°	3134	2605	2291
80°	2737	2183	2026
85°	2103	1843	1843

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4461 cd/sqm



TEST NUMBER: P824318

CATALOG NUMBER: CB3-OU-030D-840-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.0	3.9
10°-20°	126.3	11.1
20°-30°	183.5	16.1
30°-40°	208.6	18.3
40°-50°	202.5	17.8
50°-60°	171.0	15.0
60°-70°	121.7	10.7
70°-80°	65.0	5.7
80°-90°	17.2	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	354.7	31.1
0°-40°	563.3	49.4
0°-60°	936.8	82.1
0°-90°	1140.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1140.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	476	476	476	476	476	
5°	472	478	473	472	475	45
15°	449	453	449	446	446	126
25°	404	405	399	394	392	186
35°	347	344	334	324	322	216
45°	279	274	263	250	247	215
55°	209	204	190	178	175	187
65°	139	134	122	111	108	137
75°	72	68	60	53	52	76
85°	16	15	14	14	14	20
90°	0	0	0	0	0	

TEST NUMBER: P824318

CATALOG NUMBER: CB3-OU-030D-840-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	476.4	476.4	476.4	476.4	476.4
2.5°	474.0	478.8	474.5	475.1	476.2
5°	472.4	478.3	472.7	472.1	475.4
7.5°	468.7	474.1	468.3	467.0	469.9
10°	464.9	470.9	464.2	462.6	464.2
12.5°	458.2	464.4	459.1	456.4	457.7
15°	449.0	453.0	449.0	446.3	446.3
17.5°	437.9	442.0	434.5	432.6	431.9
20°	429.7	433.4	425.3	422.6	421.6
22.5°	418.9	422.3	415.6	411.0	409.7
25°	404.0	405.3	398.9	393.5	391.8
27.5°	389.1	389.4	380.6	374.0	371.8
30°	376.6	376.9	366.8	359.7	358.0
32.5°	364.2	363.2	353.5	345.0	343.9
35°	346.8	343.5	334.0	324.1	322.1
37.5°	325.9	323.9	312.7	302.8	299.8
40°	312.7	309.3	297.8	287.9	284.9
42.5°	299.4	295.6	283.7	272.7	269.5
45°	278.8	274.5	262.9	250.3	246.7
47.5°	258.1	253.4	240.6	228.4	224.4
50°	244.3	239.3	226.0	214.1	209.8
52.5°	230.2	225.0	211.7	199.5	196.0
55°	209.1	203.5	190.5	178.2	174.9
57.5°	188.0	182.4	169.5	157.9	154.0
60°	173.9	168.6	156.0	144.4	140.4
62.5°	159.6	154.5	142.2	130.9	127.2
65°	138.7	133.8	122.2	111.2	107.9
67.5°	118.1	113.9	102.4	92.4	89.7
70°	104.6	100.6	89.7	80.5	77.8
72.5°	91.6	87.3	76.9	69.1	67.3
75°	71.7	67.8	59.6	53.4	52.4
77.5°	53.6	50.4	43.2	39.8	39.3
80°	42.0	39.0	33.5	31.1	31.1
82.5°	31.1	28.7	25.1	24.1	24.1
85°	16.2	14.9	14.2	14.2	14.2
87.5°	4.9	4.9	4.6	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P824318

CATALOG NUMBER: CB3-0U-030D-840-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.85	18.43	17.21	18.74	19.06	15.77	17.35	16.14	17.67	17.98
	3H	18.57	19.99	18.94	20.32	20.68	17.23	18.66	17.61	18.99	19.35
	4H	19.23	20.57	19.63	20.92	21.29	17.78	19.12	18.18	19.47	19.85
	6H	19.65	20.89	20.06	21.25	21.64	18.14	19.37	18.55	19.74	20.13
	8H	19.80	20.99	20.23	21.38	21.78	18.28	19.46	18.70	19.85	20.25
	12H	19.89	21.03	20.32	21.41	21.84	18.38	19.51	18.81	19.89	20.32
4H	2H	17.34	18.68	17.74	19.03	19.40	16.48	17.82	16.88	18.17	18.54
	3H	19.29	20.41	19.70	20.81	21.21	18.16	19.28	18.57	19.68	20.08
	4H	20.07	21.08	20.50	21.49	21.93	18.79	19.80	19.23	20.22	20.65
	6H	20.61	21.49	21.06	21.93	22.39	19.25	20.12	19.70	20.57	21.02
	8H	20.81	21.64	21.28	22.08	22.55	19.43	20.25	19.89	20.70	21.16
	12H	20.95	21.68	21.43	22.16	22.63	19.57	20.31	20.05	20.78	21.25
8H	4H	20.25	21.07	20.71	21.51	21.98	19.11	19.93	19.57	20.38	20.84
	6H	20.90	21.58	21.39	22.07	22.54	19.67	20.35	20.16	20.84	21.31
	8H	21.18	21.79	21.69	22.30	22.78	19.92	20.54	20.44	21.04	21.53
	12H	21.37	21.92	21.88	22.41	22.97	20.13	20.67	20.64	21.16	21.73
12H	4H	20.26	20.99	20.74	21.47	21.94	19.15	19.88	19.63	20.36	20.83
	6H	20.92	21.53	21.43	22.04	22.53	19.73	20.34	20.24	20.85	21.34
	8H	21.25	21.79	21.76	22.28	22.85	20.04	20.58	20.55	21.08	21.64