

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855041

Luminaire Tested: SQ2-FA-0U-100D-830-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855041
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FA-0U-100D-830-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4246.7 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 0.95 / 0.95
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855041

CATALOG NUMBER: SQ2-FA-0U-100D-830-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855041

CATALOG NUMBER: SQ2-FA-0U-100D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78				78
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70				70
4	90	80	73	68	88	79	72	67	77	71	66	74	70	65	72	68	65	63				63
5	84	74	66	61	82	73	66	60	71	65	60	69	64	59	67	62	59	57				57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52				52
7	74	63	56	50	73	62	55	50	61	55	50	59	54	50	58	53	49	48				48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44				44
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41				41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38				38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	46950	46950	46950	46950
5°	46704	46775	46525	46738
10°	46630	46452	46452	46452
15°	46481	46004	46114	46004
20°	46118	44161	45782	44575
25°	45514	37269	45202	38051
30°	45095	21382	44607	21669
35°	44305	18370	43741	18112
40°	43079	9662	41876	9569
45°	39155	4156	37755	4156
50°	25834	5014	24513	4682
55°	14446	9258	13706	8397
60°	7792	13030	7650	11683
65°	6869	15836	7205	18013
70°	6420	18944	6104	19978
75°	6014	16282	6157	16831
80°	5095	11623	5095	12236
85°	4465	6484	4057	7725

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 39155 cd/sqm

TEST NUMBER: P855041

CATALOG NUMBER: SQ2-FA-0U-100D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.6	6.4
10°-20°	776.3	18.3
20°-30°	1058.5	24.9
30°-40°	889.5	20.9
40°-50°	505.2	11.9
50°-60°	268.1	6.3
60°-70°	246.8	5.8
70°-80°	181.2	4.3
80°-90°	47.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2108.5	49.7
0°-40°	2998.0	70.6
0°-60°	3771.3	88.8
0°-90°	4246.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4246.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2908	2908	2908	2908	2908	
5°	2882	2886	2871	2884	2882	274
15°	2781	2752	2759	2752	2781	784
25°	2555	2092	2537	2136	2555	1178
35°	2248	932	2219	919	2248	1403
45°	1715	182	1654	182	1715	1254
55°	513	329	487	298	513	494
65°	180	414	189	472	180	181
75°	96	261	99	270	96	99
85°	24	35	22	42	24	28
90°	0	0	0	0	0	



TEST NUMBER: P855041

CATALOG NUMBER: SQ2-FA-0U-100D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	2907.9	2907.9	2907.9	2907.9	2907.9	2907.9	2907.9	2907.9	2907.9	2907.9	2907.9
2.5°	2892.1	2934.9	2897.4	2892.4	2907.9	2904.4	2899.1	2919.3	2885.1	2919.3	2892.1
5°	2881.6	2930.9	2875.0	2860.2	2886.0	2868.8	2883.7	2913.4	2870.6	2909.1	2866.2
7.5°	2863.6	2907.3	2840.3	2830.8	2856.1	2841.1	2847.3	2888.6	2852.6	2877.9	2839.0
10°	2844.2	2882.8	2815.8	2809.8	2833.3	2818.2	2824.6	2867.6	2833.3	2856.9	2817.9
12.5°	2823.2	2853.2	2785.9	2783.3	2803.4	2793.6	2796.4	2832.7	2805.2	2828.9	2791.7
15°	2780.7	2808.5	2741.2	2730.7	2752.2	2743.6	2747.8	2780.1	2758.8	2773.7	2741.2
17.5°	2728.0	2750.3	2683.2	2651.7	2652.6	2663.3	2683.2	2722.4	2703.0	2722.8	2676.7
20°	2684.1	2709.9	2636.0	2574.5	2570.2	2580.9	2636.0	2675.2	2664.5	2685.8	2620.6
22.5°	2633.3	2650.5	2583.3	2479.5	2464.9	2475.7	2576.3	2622.6	2618.8	2633.4	2552.2
25°	2554.8	2572.0	2449.5	2300.1	2092.0	2287.2	2453.9	2537.3	2537.3	2550.2	2443.0
27.5°	2475.0	2475.4	2253.9	1477.2	1303.1	1423.9	2250.9	2431.6	2452.1	2445.7	2235.1
30°	2418.8	2403.9	1997.7	1194.1	1146.9	1176.9	2000.0	2358.2	2392.6	2368.9	1947.3
32.5°	2353.9	2311.5	1475.0	1097.7	1059.2	1085.8	1426.3	2271.1	2331.2	2280.1	1531.6
35°	2247.8	2136.2	1125.0	970.7	932.0	966.4	1116.2	2099.2	2219.2	2082.1	1162.3
37.5°	2133.3	1698.0	990.3	773.1	689.9	756.4	985.5	1679.8	2086.8	1640.8	989.4
40°	2043.9	1334.0	890.4	565.5	458.4	533.3	883.7	1272.8	1986.8	1369.3	868.4
42.5°	1924.6	1171.9	714.9	359.2	281.2	328.8	685.5	1144.9	1864.0	1186.4	691.3
45°	1714.8	1007.3	423.2	197.1	182.0	190.6	390.3	988.7	1653.5	967.4	432.0
47.5°	1358.4	768.3	271.9	167.4	183.7	167.4	263.6	743.9	1282.8	742.5	271.5
50°	1028.5	599.7	210.5	169.5	199.6	169.5	204.0	579.2	975.9	632.8	208.4
52.5°	761.8	501.1	172.0	185.9	239.9	189.3	167.1	487.8	723.3	510.5	162.7
55°	513.2	393.1	138.2	245.3	328.9	251.8	138.2	381.8	486.9	377.5	133.8
57.5°	325.4	292.4	139.9	315.4	375.5	321.4	142.1	281.9	312.3	283.1	122.8
60°	241.3	230.5	155.7	334.9	403.5	339.2	157.8	221.8	236.9	219.7	131.6
62.5°	199.1	181.6	187.2	362.7	419.2	353.2	191.2	173.1	207.0	165.9	145.6
65°	179.8	117.6	221.5	367.3	414.5	367.3	223.6	111.4	188.6	120.0	197.4
67.5°	162.2	87.3	214.0	364.7	417.1	365.6	208.7	83.2	155.7	81.1	201.7
70°	136.0	78.0	201.7	371.3	401.3	358.4	201.7	75.8	129.3	73.6	236.9
72.5°	113.2	74.2	187.7	342.8	355.7	329.9	189.5	73.7	113.6	66.4	222.8
75°	96.4	72.9	179.8	273.8	261.0	261.0	175.5	70.8	98.7	66.5	173.2
77.5°	72.4	64.7	149.1	178.8	168.8	168.8	146.5	62.4	68.9	58.6	140.8
80°	54.8	59.1	122.8	131.4	125.0	125.0	118.4	57.0	54.8	54.8	116.2
82.5°	42.5	50.3	94.7	96.3	91.7	90.0	92.1	49.9	42.5	46.0	89.9
85°	24.1	34.8	50.4	41.5	35.0	32.9	48.3	32.7	21.9	32.7	48.3
87.5°	8.8	15.6	7.0	7.0	7.0	7.0	7.0	15.6	8.8	13.9	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P855041

CATALOG NUMBER: SQ2-FA-0U-100D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	2907.9	2907.9	2907.9	2907.9	2907.9	2907.9
2.5°	2885.3	2897.4	2897.4	2890.3	2924.6	2892.1
5°	2855.9	2883.7	2870.8	2870.6	2913.7	2881.6
7.5°	2835.2	2861.3	2849.3	2846.8	2889.2	2863.6
10°	2813.9	2833.3	2824.7	2831.1	2870.0	2844.2
12.5°	2784.2	2806.9	2798.5	2808.3	2843.8	2823.2
15°	2732.9	2752.2	2756.4	2760.9	2802.1	2780.7
17.5°	2648.0	2657.5	2678.8	2709.1	2752.1	2728.0
20°	2581.4	2594.3	2607.1	2660.1	2709.9	2684.1
22.5°	2505.6	2501.3	2531.3	2593.4	2655.7	2633.3
25°	2301.1	2135.9	2318.2	2478.0	2561.2	2554.8
27.5°	1602.2	1390.4	1577.7	2287.3	2462.1	2475.0
30°	1260.9	1162.3	1258.7	2041.6	2388.8	2418.8
32.5°	1119.4	1051.7	1110.5	1554.0	2296.4	2353.9
35°	966.0	918.9	966.0	1162.3	2114.9	2247.8
37.5°	773.2	676.7	771.6	1004.4	1709.6	2133.3
40°	576.2	454.0	559.0	899.1	1366.3	2043.9
42.5°	383.9	292.5	363.3	707.9	1181.7	1924.6
45°	207.7	182.0	199.2	427.6	964.4	1714.8
47.5°	162.9	172.3	162.9	269.8	737.7	1358.4
50°	156.4	186.4	156.4	208.4	610.3	1028.5
52.5°	170.5	202.2	168.7	164.5	498.0	761.8
55°	193.2	298.3	195.4	133.8	365.2	513.2
57.5°	275.1	335.6	278.0	126.7	281.3	325.4
60°	282.5	361.8	280.4	133.8	217.6	241.3
62.5°	334.1	447.8	333.8	153.1	161.8	199.1
65°	428.6	471.5	432.9	195.1	115.6	179.8
67.5°	406.8	437.2	402.5	209.2	79.5	162.2
70°	399.7	423.2	395.4	239.0	73.8	136.0
72.5°	372.9	375.8	365.2	221.5	66.4	113.2
75°	289.0	269.8	278.4	190.7	66.5	96.4
77.5°	179.7	172.0	173.2	145.6	58.7	72.4
80°	135.9	131.6	129.5	122.8	54.8	54.8
82.5°	100.7	96.4	94.3	94.7	46.0	42.5
85°	45.9	41.7	39.6	54.8	32.7	24.1
87.5°	8.8	8.8	7.0	8.8	12.2	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P855041

CATALOG NUMBER: SQ2-FA-0U-100D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.37	18.68	17.74	19.00	19.31	16.23	17.54	16.60	17.85	18.17
	3H	18.10	19.27	18.48	19.60	19.97	22.41	23.58	22.79	23.91	24.27
	4H	18.52	19.62	18.93	19.97	20.36	23.70	24.80	24.10	25.15	25.53
	6H	18.90	19.91	19.31	20.28	20.67	24.32	25.34	24.74	25.71	26.10
	8H	19.03	19.99	19.46	20.38	20.78	24.46	25.42	24.89	25.81	26.21
	12H	19.11	20.03	19.54	20.41	20.84	24.51	25.43	24.94	25.81	26.24
4H	2H	17.81	18.91	18.21	19.26	19.64	16.80	17.90	17.21	18.25	18.64
	3H	18.83	19.75	19.25	20.15	20.55	23.16	24.07	23.57	24.47	24.88
	4H	19.41	20.23	19.84	20.65	21.09	24.62	25.44	25.05	25.86	26.30
	6H	19.90	20.61	20.36	21.06	21.52	25.37	26.09	25.84	26.53	27.00
	8H	20.08	20.74	20.54	21.19	21.66	25.55	26.21	26.02	26.66	27.13
	12H	20.21	20.80	20.70	21.28	21.76	25.63	26.22	26.11	26.70	27.17
8H	4H	20.53	21.20	21.00	21.64	22.11	24.77	25.43	25.23	25.88	26.35
	6H	21.15	21.69	21.65	22.19	22.67	25.66	26.20	26.16	26.70	27.18
	8H	21.38	21.87	21.90	22.38	22.88	25.90	26.39	26.43	26.91	27.40
	12H	21.58	22.00	22.09	22.50	23.07	26.05	26.47	26.56	26.97	27.54
12H	4H	20.70	21.28	21.18	21.77	22.24	24.75	25.34	25.23	25.82	26.29
	6H	21.42	21.91	21.94	22.42	22.92	25.66	26.15	26.18	26.67	27.16
	8H	21.74	22.17	22.26	22.66	23.24	25.97	26.39	26.48	26.89	27.46