

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853663

Luminaire Tested: SQ2-F-025U-100D-830-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P853663  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2308-131-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-F-025U-100D-830-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5653.0 lumens  
Efficiency: N/A  
Efficacy: 125.6 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P853663

CATALOG NUMBER: SQ2-F-025U-100D-830-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P853663

CATALOG NUMBER: SQ2-F-025U-100D-830-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	84	84	84	80				
1	104	100	95	92	100	95	92	88	88	85	82	80	78	76	74	72	70	67				
2	95	87	80	75	90	83	77	72	76	72	67	70	66	63	64	61	59	56				
3	86	76	68	62	82	73	66	60	67	61	57	62	57	53	57	53	50	47				
4	79	67	59	52	75	65	57	51	60	53	48	55	50	45	51	46	43	40				
5	73	60	51	45	69	58	50	44	53	47	41	49	44	39	46	41	37	34				
6	67	54	45	39	64	52	44	38	48	41	36	45	39	34	41	36	33	30				
7	62	49	40	34	59	47	39	34	44	37	32	41	35	30	38	33	29	27				
8	58	44	36	31	55	43	35	30	40	33	29	37	31	27	35	30	26	24				
9	54	41	33	27	51	39	32	27	37	30	26	34	29	24	32	27	23	21				
10	50	37	30	25	48	36	29	24	34	28	23	32	26	22	30	25	21	19				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	25988	25988	25988
5°	25804	25875	26088
10°	25742	25814	25994
15°	25586	25660	25917
20°	25433	25471	25697
25°	25197	25197	25356
30°	24940	24940	25022
35°	24636	24551	24723
40°	24312	24219	24312
45°	23934	23834	23934
50°	23574	23355	23410
55°	23026	22964	22838
60°	22446	22307	22165
65°	21784	21532	21280
70°	20497	20394	19978
75°	19289	18883	18334
80°	17127	16718	16104
85°	13801	12597	11764

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 24083 cd/sqm



TEST NUMBER: P853663

CATALOG NUMBER: SQ2-F-025U-100D-830-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.2	2.7
10°-20°	434.7	7.7
20°-30°	654.1	11.6
30°-40°	782.6	13.8
40°-50°	807.5	14.3
50°-60°	728.5	12.9
60°-70°	555.9	9.8
70°-80°	319.6	5.7
80°-90°	83.8	1.5
90°-100°	74.0	1.3
100°-110°	230.0	4.1
110°-120°	225.0	4.0
120°-130°	183.7	3.2
130°-140°	150.3	2.7
140°-150°	117.3	2.1
150°-160°	84.6	1.5
160°-170°	51.8	0.9
170°-180°	17.4	0.3
0°-30°	1241.0	22.0
0°-40°	2023.6	35.8
0°-60°	3559.6	63.0
0°-90°	4518.9	79.9
90°-120°	529.0	9.4
90°-150°	980.3	17.3
90°-180°	1134.0	20.1
0°-180°	5653.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1592	1614	1596	1599	1610	151
15°	1531	1550	1535	1542	1550	432
25°	1414	1430	1414	1417	1423	651
35°	1250	1258	1246	1250	1254	782
45°	1048	1055	1044	1046	1048	809
55°	818	822	816	811	811	731
65°	570	568	564	559	557	560
75°	309	307	303	296	294	326
85°	74	70	68	62	64	86
90°	0	1	3	3	3	3
95°	10	30	136	50	33	12
105°	40	57	226	432	413	43
115°	72	85	184	379	444	71
125°	100	111	182	298	350	89
135°	120	133	180	257	289	93
145°	140	151	180	222	242	88
155°	160	166	182	200	206	74
165°	176	177	183	188	190	49
175°	183	183	183	184	183	17
180°	183	183	183	183	183	



TEST NUMBER: P853663

CATALOG NUMBER: SQ2-F-025U-100D-830-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1609.6	1609.6	1609.6	1609.6	1609.6
2.5°	1599.1	1618.0	1602.6	1606.2	1607.9
5°	1592.1	1613.5	1596.5	1598.8	1609.6
7.5°	1578.9	1602.1	1583.4	1587.5	1599.5
10°	1570.1	1591.6	1574.5	1576.9	1585.5
12.5°	1556.1	1577.6	1560.5	1564.6	1573.2
15°	1530.7	1550.0	1535.1	1541.9	1550.5
17.5°	1501.3	1521.8	1505.2	1511.1	1518.3
20°	1480.2	1497.4	1482.4	1484.9	1495.6
22.5°	1453.9	1471.1	1457.9	1458.5	1467.5
25°	1414.4	1429.5	1414.4	1416.8	1423.3
27.5°	1369.3	1382.1	1369.3	1371.6	1377.1
30°	1337.7	1350.6	1337.7	1339.9	1342.1
32.5°	1302.6	1313.8	1300.8	1303.2	1308.7
35°	1249.9	1258.5	1245.6	1250.0	1254.3
37.5°	1193.8	1200.3	1189.4	1191.7	1195.5
40°	1153.5	1159.9	1149.1	1151.3	1153.5
42.5°	1113.1	1117.9	1107.0	1109.3	1113.1
45°	1048.2	1054.7	1043.8	1046.1	1048.2
47.5°	982.4	986.3	977.2	975.5	979.4
50°	938.5	940.7	929.8	929.8	932.0
52.5°	891.2	893.3	886.0	882.5	884.6
55°	818.0	822.2	815.8	811.3	811.3
57.5°	744.3	748.1	739.9	737.7	737.3
60°	695.1	697.3	690.8	688.6	686.4
62.5°	646.0	646.5	639.9	637.7	635.5
65°	570.2	568.0	563.6	559.1	557.0
67.5°	485.0	487.2	482.9	475.9	475.9
70°	434.2	436.3	432.0	423.2	423.2
72.5°	385.1	383.7	381.1	374.0	370.6
75°	309.2	307.1	302.7	296.0	293.9
77.5°	233.4	231.2	229.0	220.7	222.4
80°	184.2	182.0	179.8	173.2	173.2
82.5°	140.3	136.5	134.2	127.6	127.6
85°	74.5	70.3	68.0	61.5	63.5
87.5°	21.0	19.6	18.2	14.7	14.7
90°	0.0	1.1	3.4	3.4	3.4
92.5°	3.6	12.6	42.9	14.0	11.4
95°	10.1	29.8	135.7	50.1	32.6
97.5°	18.4	38.8	224.7	139.9	88.1
100°	24.6	43.3	253.4	237.0	158.1
102.5°	31.0	48.7	248.0	338.4	265.7
105°	40.4	56.8	226.5	432.2	412.6
107.5°	49.7	65.1	205.8	439.5	461.2
110°	56.1	71.3	195.0	429.2	471.9



TEST NUMBER: P853663

CATALOG NUMBER: SQ2-F-025U-100D-830-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	62.3	76.8	189.7	410.6	464.8
115°	71.8	84.9	183.8	379.2	443.9
117.5°	81.0	92.9	181.4	349.3	415.4
120°	86.3	98.4	180.5	332.2	395.7
122.5°	91.7	103.8	181.4	317.7	375.9
125°	99.7	110.7	181.6	298.3	349.7
127.5°	106.3	117.5	181.6	283.7	327.5
130°	109.9	121.9	181.6	275.5	315.0
132.5°	114.3	126.4	180.7	268.3	305.2
135°	120.0	133.1	180.5	257.4	289.2
137.5°	126.4	138.5	180.5	246.6	275.5
140°	130.0	142.1	180.5	239.4	265.7
142.5°	134.5	145.7	180.5	232.1	255.8
145°	140.1	151.1	180.5	222.4	242.2
147.5°	146.9	156.3	181.6	213.4	229.0
150°	151.3	159.0	181.6	208.8	220.8
152.5°	154.9	161.7	181.6	204.3	214.6
155°	160.3	165.8	181.6	199.7	206.2
157.5°	165.6	169.8	181.6	195.6	199.8
160°	169.3	172.5	181.6	192.9	196.2
162.5°	172.0	174.3	181.6	191.1	193.5
165°	176.0	177.1	182.7	188.4	190.5
167.5°	178.4	178.6	181.6	186.8	187.9
170°	179.3	180.5	181.6	185.0	186.1
172.5°	181.1	181.4	182.5	184.1	184.3
175°	182.7	182.7	182.7	183.8	182.7
177.5°	182.7	182.7	182.7	182.7	182.7
180°	182.7	182.7	182.7	182.7	182.7

-----



TEST NUMBER: P853663

CATALOG NUMBER: SQ2-F-025U-100D-830-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.68	22.92	22.33	23.58	24.35	21.60	22.84	22.25	23.50	24.27
	3H	23.49	24.60	24.15	25.27	26.08	23.37	24.48	24.03	25.15	25.96
	4H	24.16	25.21	24.84	25.90	26.71	24.01	25.06	24.69	25.75	26.56
	6H	24.65	25.62	25.34	26.32	27.15	24.47	25.44	25.16	26.13	26.96
	8H	24.80	25.73	25.50	26.44	27.27	24.60	25.52	25.30	26.24	27.07
	12H	24.89	25.77	25.60	26.48	27.34	24.66	25.55	25.37	26.26	27.12
4H	2H	22.27	23.33	22.96	24.01	24.82	22.21	23.26	22.90	23.95	24.76
	3H	24.29	25.17	24.99	25.90	26.73	24.19	25.07	24.88	25.79	26.62
	4H	25.10	25.90	25.81	26.63	27.49	24.96	25.76	25.67	26.48	27.35
	6H	25.71	26.41	26.44	27.16	28.03	25.53	26.23	26.26	26.98	27.85
	8H	25.91	26.56	26.64	27.31	28.19	25.71	26.36	26.44	27.10	27.99
	12H	26.03	26.61	26.79	27.38	28.27	25.80	26.38	26.56	27.16	28.05
8H	4H	25.38	26.03	26.11	26.78	27.66	25.25	25.90	25.99	26.65	27.53
	6H	26.11	26.65	26.88	27.44	28.33	25.95	26.48	26.71	27.27	28.16
	8H	26.38	26.86	27.16	27.65	28.56	26.19	26.67	26.97	27.46	28.36
	12H	26.57	26.99	27.35	27.77	28.73	26.34	26.76	27.12	27.55	28.51
12H	4H	25.39	25.97	26.15	26.75	27.64	25.27	25.85	26.03	26.63	27.51
	6H	26.16	26.64	26.94	27.43	28.33	26.00	26.48	26.78	27.27	28.17
	8H	26.47	26.89	27.25	27.67	28.64	26.28	26.71	27.06	27.49	28.45