

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853702

Luminaire Tested: SQ2-F-0U-125D-830-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P853702  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-F-0U-125D-830-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1250 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5626.2 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 49.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P853702

CATALOG NUMBER: SQ2-F-0U-125D-830-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P853702

CATALOG NUMBER: SQ2-F-0U-125D-830-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84
2	99	90	84	78	96	89	82	77	85	80	75	82	77	73	79	75	72	70
3	90	79	71	65	88	78	70	64	75	68	63	72	66	62	69	65	61	59
4	82	70	61	55	80	69	61	54	66	59	54	64	58	53	62	57	52	50
5	76	63	54	47	74	62	53	47	60	52	46	58	51	46	56	50	45	43
6	70	57	48	41	68	56	47	41	54	46	41	52	45	40	50	44	40	38
7	65	51	42	36	63	50	42	36	49	41	36	47	41	36	46	40	35	33
8	60	47	38	32	59	46	38	32	45	37	32	43	37	32	42	36	32	30
9	56	43	35	29	55	42	34	29	41	34	29	40	33	29	39	33	29	27
10	53	40	32	26	52	39	31	26	38	31	26	37	31	26	36	30	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	32359	32359	32359
5°	32130	32217	32483
10°	32054	32142	32367
15°	31858	31950	32269
20°	31668	31716	31998
25°	31376	31376	31572
30°	31055	31055	31155
35°	30677	30569	30786
40°	30273	30157	30273
45°	29803	29679	29803
50°	29353	29082	29150
55°	28670	28594	28439
60°	27952	27774	27600
65°	27121	26812	26495
70°	25525	25398	24878
75°	24017	23506	22826
80°	21330	20818	20056
85°	17191	15691	14653

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 29985 cd/sqm



TEST NUMBER: P853702

CATALOG NUMBER: SQ2-F-0U-125D-830-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.5	3.4
10°-20°	541.3	9.6
20°-30°	814.4	14.5
30°-40°	974.5	17.3
40°-50°	1005.5	17.9
50°-60°	907.1	16.1
60°-70°	692.2	12.3
70°-80°	398.0	7.1
80°-90°	103.8	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1545.2	27.5
0°-40°	2519.7	44.8
0°-60°	4432.3	78.8
0°-90°	5626.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5626.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2004	2004	2004	2004	2004	
5°	1982	2009	1988	1991	2004	188
15°	1906	1930	1911	1920	1930	538
25°	1761	1780	1761	1764	1772	811
35°	1556	1567	1551	1557	1562	973
45°	1305	1313	1300	1302	1305	1007
55°	1018	1024	1016	1010	1010	911
65°	710	707	702	696	694	698
75°	385	382	377	369	366	406
85°	93	88	85	76	79	111
90°	0	0	0	0	0	



TEST NUMBER: P853702

CATALOG NUMBER: SQ2-F-0U-125D-830-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2004.2	2004.2	2004.2	2004.2	2004.2
2.5°	1991.1	2014.6	1995.5	1999.9	2002.0
5°	1982.4	2009.0	1987.8	1990.8	2004.2
7.5°	1966.0	1994.8	1971.5	1976.7	1991.6
10°	1955.1	1981.8	1960.5	1963.5	1974.2
12.5°	1937.6	1964.3	1943.0	1948.2	1958.8
15°	1905.9	1929.9	1911.4	1919.8	1930.5
17.5°	1869.3	1895.0	1874.3	1881.5	1890.7
20°	1843.1	1864.4	1845.9	1848.8	1862.3
22.5°	1810.4	1831.8	1815.2	1816.0	1827.2
25°	1761.2	1779.9	1761.2	1764.1	1772.2
27.5°	1704.9	1721.0	1704.9	1707.8	1714.7
30°	1665.7	1681.6	1665.7	1668.4	1671.1
32.5°	1621.9	1635.8	1619.8	1622.7	1629.6
35°	1556.4	1567.1	1550.9	1556.6	1561.9
37.5°	1486.5	1494.5	1481.0	1483.9	1488.7
40°	1436.3	1444.3	1430.8	1433.5	1436.3
42.5°	1386.1	1391.9	1378.4	1381.2	1386.1
45°	1305.2	1313.2	1299.8	1302.5	1305.2
47.5°	1223.2	1228.1	1216.7	1214.6	1219.5
50°	1168.6	1171.3	1157.8	1157.8	1160.5
52.5°	1109.7	1112.3	1103.2	1098.9	1101.5
55°	1018.5	1023.8	1015.8	1010.3	1010.3
57.5°	926.8	931.5	921.2	918.5	918.0
60°	865.6	868.2	860.1	857.4	854.7
62.5°	804.5	804.9	796.8	793.9	791.3
65°	709.9	707.2	701.8	696.2	693.5
67.5°	604.0	606.7	601.3	592.6	592.6
70°	540.7	543.3	538.0	527.0	527.0
72.5°	479.5	477.9	474.5	465.7	461.4
75°	385.0	382.4	376.8	368.6	365.9
77.5°	290.6	287.9	285.0	274.7	276.9
80°	229.4	226.7	223.9	215.7	215.7
82.5°	174.8	169.9	167.1	159.0	159.0
85°	92.8	87.5	84.7	76.5	79.1
87.5°	26.2	24.1	21.8	17.5	17.5
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P853702

CATALOG NUMBER: SQ2-F-0U-125D-830-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	23.85	25.49	24.21	25.80	26.12	23.77	25.41	24.13	25.72	26.04
	3H	25.68	27.16	26.05	27.49	27.85	25.56	27.04	25.93	27.37	27.73
	4H	26.37	27.77	26.77	28.12	28.49	26.22	27.62	26.62	27.96	28.34
	6H	26.88	28.17	27.29	28.54	28.93	26.69	27.99	27.10	28.35	28.74
	8H	27.04	28.28	27.46	28.67	29.06	26.83	28.07	27.26	28.46	28.86
	12H	27.14	28.32	27.57	28.71	29.13	26.91	28.10	27.34	28.48	28.91
4H	2H	24.48	25.88	24.88	26.23	26.60	24.42	25.82	24.82	26.17	26.54
	3H	26.54	27.71	26.94	28.11	28.51	26.43	27.60	26.84	28.00	28.40
	4H	27.36	28.42	27.79	28.83	29.27	27.21	28.28	27.64	28.69	29.12
	6H	27.99	28.92	28.44	29.36	29.81	27.81	28.74	28.26	29.18	29.63
	8H	28.20	29.07	28.66	29.51	29.97	27.99	28.86	28.45	29.31	29.77
	12H	28.34	29.12	28.81	29.59	30.06	28.11	28.89	28.59	29.36	29.83
8H	4H	27.67	28.53	28.12	28.98	29.44	27.54	28.41	28.00	28.85	29.32
	6H	28.42	29.14	28.91	29.63	30.10	28.25	28.97	28.74	29.46	29.94
	8H	28.69	29.34	29.20	29.85	30.33	28.50	29.15	29.01	29.65	30.14
	12H	28.90	29.47	29.40	29.96	30.52	28.67	29.24	29.17	29.73	30.29
12H	4H	27.70	28.48	28.18	28.95	29.42	27.58	28.36	28.05	28.83	29.30
	6H	28.47	29.12	28.98	29.62	30.11	28.31	28.96	28.82	29.46	29.95
	8H	28.80	29.37	29.30	29.86	30.42	28.61	29.18	29.12	29.67	30.23