

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855011

Luminaire Tested: SQ2-FB-125U-050D-830-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855011
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FB-125U-050D-830-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7995.7 lumens
Efficiency: N/A
Efficacy: 129.6 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 61.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855011

CATALOG NUMBER: SQ2-FB-125U-050D-830-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855011

CATALOG NUMBER: SQ2-FB-125U-050D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	76	74	63	60	58	47	46	44	32	32	31	24
2	84	77	71	66	75	69	64	60	55	51	48	41	39	37	28	27	26	20
3	77	68	60	55	68	61	55	50	48	43	40	36	33	31	25	23	22	17
4	70	59	52	46	62	53	47	42	42	37	34	32	28	26	22	20	18	14
5	64	53	45	39	57	47	41	35	37	32	29	28	25	22	19	17	16	12
6	59	47	39	33	52	42	35	30	33	28	25	25	22	19	17	15	13	10
7	54	42	34	29	48	38	31	26	30	25	21	23	19	17	16	14	12	9
8	50	38	30	25	45	34	28	23	27	22	19	21	17	15	14	12	10	8
9	46	34	27	22	41	31	25	20	25	20	17	19	15	13	13	11	9	7
10	43	31	24	20	39	28	22	18	23	18	15	17	14	11	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3798	3798	3798
5°	3702	5131	6724
10°	3466	9935	13086
15°	3137	12928	15062
20°	2778	14220	15775
25°	2457	15207	16033
30°	2172	15662	16231
35°	1940	15934	17450
40°	1764	16086	18539
45°	1626	16162	19413
50°	1535	16473	19766
55°	1495	16901	19924
60°	1534	17124	19824
65°	1597	16890	19266
70°	1652	16334	14573
75°	1834	14672	8041
80°	1897	7569	7466
85°	1890	5243	3149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 20104 cd/sqm



TEST NUMBER: P855011

CATALOG NUMBER: SQ2-FB-125U-050D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.4	0.5
10°-20°	179.9	2.2
20°-30°	316.4	4.0
30°-40°	409.6	5.1
40°-50°	451.7	5.6
50°-60°	421.8	5.3
60°-70°	326.0	4.1
70°-80°	150.4	1.9
80°-90°	29.7	0.4
90°-100°	351.6	4.4
100°-110°	1144.6	14.3
110°-120°	1132.3	14.2
120°-130°	925.3	11.6
130°-140°	756.2	9.5
140°-150°	589.0	7.4
150°-160°	424.6	5.3
160°-170°	259.5	3.2
170°-180°	87.6	1.1
0°-30°	535.7	6.7
0°-40°	945.3	11.8
0°-60°	1818.8	22.7
0°-90°	2324.9	29.1
90°-120°	2628.5	32.9
90°-150°	4899.1	61.3
90°-180°	5671.0	70.9
0°-180°	7995.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	235	235	235	235	235	
5°	228	262	317	386	415	21
15°	188	370	773	866	901	52
25°	138	497	854	891	900	63
35°	98	480	808	837	885	62
45°	71	368	708	813	850	55
55°	53	219	600	690	708	48
65°	42	124	442	495	504	41
75°	29	76	235	127	129	30
85°	10	22	28	19	17	11
90°	0	3	8	7	7	3
95°	48	145	644	230	141	55
105°	194	281	1134	2166	2051	207
115°	360	429	924	1904	2240	356
125°	500	557	911	1503	1772	445
135°	604	667	907	1297	1463	466
145°	705	757	904	1117	1223	442
155°	805	832	910	1000	1038	371
165°	878	886	912	946	958	247
175°	916	916	916	922	920	87
180°	919	919	919	919	919	



TEST NUMBER: P855011

CATALOG NUMBER: SQ2-FB-125U-050D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	235.2	235.2	235.2	235.2	235.2
2.5°	233.4	243.1	254.2	266.9	272.3
5°	228.4	261.5	316.6	386.2	414.9
7.5°	219.6	287.0	460.4	646.7	704.2
10°	211.4	305.4	606.0	767.3	798.2
12.5°	202.4	329.9	697.4	810.7	842.6
15°	187.7	370.1	773.4	865.7	901.1
17.5°	172.5	415.3	808.6	899.8	919.0
20°	161.7	446.9	827.6	906.0	918.1
22.5°	151.7	470.6	841.2	900.6	913.6
25°	137.9	497.3	853.6	891.2	900.0
27.5°	124.6	504.3	848.2	872.9	881.4
30°	116.5	502.2	840.1	858.5	870.6
32.5°	109.2	496.8	828.3	846.1	872.4
35°	98.4	479.7	808.4	836.7	885.3
37.5°	89.1	452.4	782.2	840.0	886.9
40°	83.7	431.9	763.2	839.8	879.6
42.5°	78.2	407.9	741.5	830.8	870.6
45°	71.2	367.5	707.8	812.7	850.2
47.5°	64.7	322.0	676.6	787.6	815.0
50°	61.1	291.0	655.8	764.8	786.9
52.5°	57.4	260.8	635.0	737.6	758.0
55°	53.1	219.0	600.4	690.1	707.8
57.5°	49.3	183.1	561.0	637.6	651.9
60°	47.5	163.6	530.3	599.6	613.9
62.5°	44.8	145.9	495.9	559.8	573.2
65°	41.8	123.7	442.1	495.4	504.3
67.5°	37.8	107.2	384.9	417.5	400.9
70°	35.0	99.2	346.0	356.2	308.7
72.5°	33.2	90.3	303.5	276.6	186.6
75°	29.4	75.9	235.2	126.6	128.9
77.5°	24.0	58.7	154.7	97.2	99.3
80°	20.4	47.9	81.4	79.1	80.3
82.5°	16.7	37.3	56.1	58.3	56.8
85°	10.2	22.4	28.3	19.2	17.0
87.5°	3.6	8.7	6.1	5.9	5.9
90°	0.0	3.3	7.9	6.8	6.8
92.5°	16.3	58.5	187.0	61.6	47.5
95°	47.5	144.7	644.4	229.7	141.3
97.5°	89.3	188.4	1093.7	666.1	406.6
100°	116.5	213.7	1262.8	1126.0	730.3
102.5°	147.2	240.9	1242.0	1665.9	1266.7
105°	194.5	280.6	1133.9	2165.7	2050.8
107.5°	245.6	326.6	1031.3	2209.1	2330.9
110°	282.7	356.7	982.4	2155.2	2375.3



TEST NUMBER: P855011

CATALOG NUMBER: SQ2-FB-125U-050D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	313.4	386.6	951.7	2058.1	2341.8
115°	359.5	429.2	923.6	1903.6	2239.6
117.5°	407.0	469.8	912.8	1761.9	2096.4
120°	434.2	496.0	910.1	1674.8	1998.8
122.5°	460.4	521.3	911.0	1599.3	1901.1
125°	499.6	557.2	911.2	1502.9	1771.5
127.5°	533.3	592.2	911.0	1430.7	1654.6
130°	555.0	614.7	910.1	1389.4	1589.5
132.5°	574.0	636.4	909.2	1351.1	1538.8
135°	603.7	666.7	906.7	1297.1	1462.9
137.5°	632.6	696.1	904.2	1242.1	1389.4
140°	653.4	714.2	903.3	1204.9	1344.2
142.5°	673.3	731.5	903.3	1169.3	1293.6
145°	705.4	757.4	904.4	1117.1	1223.2
147.5°	736.6	781.7	906.0	1072.6	1154.7
150°	757.4	797.2	907.8	1046.2	1115.8
152.5°	778.2	811.0	908.7	1025.9	1081.5
155°	804.9	831.5	910.1	1000.3	1037.8
157.5°	830.2	849.2	911.4	981.2	1007.5
160°	845.6	861.1	912.3	969.3	990.3
162.5°	859.2	871.2	912.3	959.2	975.0
165°	878.4	886.2	912.3	946.5	957.5
167.5°	892.0	896.8	912.5	936.9	942.6
170°	901.0	903.3	913.4	930.5	932.7
172.5°	907.3	908.7	915.3	926.8	926.3
175°	915.7	915.7	915.7	922.5	920.2
177.5°	919.1	918.2	917.3	921.7	918.2
180°	919.1	919.1	919.1	919.1	919.1



TEST NUMBER: P855011

CATALOG NUMBER: SQ2-FB-125U-050D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.38	10.09	10.49	11.20	12.74	18.11	18.83	19.23	19.94	21.48
	3H	10.09	10.73	11.22	11.85	13.41	19.72	20.36	20.85	21.48	23.04
	4H	10.39	11.00	11.52	12.12	13.68	19.90	20.50	21.03	21.62	23.19
	6H	10.60	11.15	11.74	12.28	13.85	19.97	20.53	21.11	21.65	23.23
	8H	10.65	11.18	11.79	12.32	13.89	19.97	20.50	21.12	21.64	23.21
	12H	10.67	11.18	11.82	12.31	13.90	19.94	20.44	21.09	21.58	23.17
4H	2H	13.76	14.36	14.90	15.48	17.04	18.54	19.14	19.68	20.26	21.83
	3H	14.67	15.18	15.82	16.33	17.90	20.35	20.85	21.49	22.00	23.57
	4H	14.95	15.42	16.10	16.55	18.15	20.58	21.04	21.73	22.18	23.77
	6H	15.07	15.47	16.23	16.63	18.21	20.71	21.11	21.87	22.27	23.86
	8H	15.09	15.46	16.25	16.61	18.21	20.74	21.11	21.89	22.26	23.86
	12H	15.07	15.41	16.25	16.57	18.18	20.70	21.04	21.87	22.20	23.81
8H	4H	16.11	16.48	17.27	17.63	19.24	20.68	21.05	21.84	22.20	23.81
	6H	16.34	16.65	17.52	17.84	19.44	20.88	21.19	22.06	22.38	23.98
	8H	16.41	16.68	17.59	17.85	19.47	20.94	21.21	22.12	22.38	24.00
	12H	16.43	16.67	17.62	17.83	19.49	20.93	21.16	22.11	22.33	23.98
12H	4H	16.12	16.46	17.29	17.62	19.23	20.63	20.96	21.80	22.13	23.73
	6H	16.43	16.70	17.62	17.87	19.49	20.86	21.13	22.04	22.30	23.92
	8H	16.53	16.77	17.72	17.93	19.59	20.92	21.16	22.11	22.32	23.98