

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855061

Luminaire Tested: SQ2-F-125U-050D-830-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855061
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-F-125U-050D-830-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8001.4 lumens
Efficiency: N/A
Efficacy: 129.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 61.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855061
CATALOG NUMBER: SQ2-F-125U-050D-830-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855061

CATALOG NUMBER: SQ2-F-125U-050D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	60	59	47	46	44	32	32	31	24
2	85	77	71	66	76	70	64	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	17
4	70	60	52	46	63	54	47	42	43	38	34	32	29	26	22	20	19	15
5	64	53	45	39	57	48	41	36	38	33	29	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	25	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	17	14	13	10
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	25	21	25	21	17	20	16	14	14	12	10	8
10	44	32	25	20	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13399	13399	13399
5°	13303	13340	13451
10°	13272	13309	13403
15°	13192	13230	13362
20°	13113	13132	13249
25°	12992	12992	13073
30°	12858	12858	12901
35°	12703	12658	12747
40°	12534	12488	12534
45°	12339	12289	12339
50°	12155	12042	12069
55°	11871	11840	11775
60°	11573	11502	11428
65°	11232	11102	10972
70°	10570	10513	10301
75°	9944	9732	9451
80°	8833	8619	8303
85°	7114	6484	6076

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 12415 cd/sqm



TEST NUMBER: P855061

CATALOG NUMBER: SQ2-F-125U-050D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.4	1.0
10°-20°	224.2	2.8
20°-30°	337.2	4.2
30°-40°	403.5	5.0
40°-50°	416.3	5.2
50°-60°	375.6	4.7
60°-70°	286.6	3.6
70°-80°	164.8	2.1
80°-90°	44.0	0.5
90°-100°	351.6	4.4
100°-110°	1144.6	14.3
110°-120°	1132.3	14.2
120°-130°	925.3	11.6
130°-140°	756.2	9.5
140°-150°	589.0	7.4
150°-160°	424.6	5.3
160°-170°	259.5	3.2
170°-180°	87.6	1.1
0°-30°	639.8	8.0
0°-40°	1043.4	13.0
0°-60°	1835.3	22.9
0°-90°	2330.7	29.1
90°-120°	2628.5	32.9
90°-150°	4899.1	61.2
90°-180°	5671.0	70.9
0°-180°	8001.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	830	830	830	830	830	
5°	821	832	823	824	830	78
15°	789	799	792	795	799	223
25°	729	737	729	730	734	336
35°	644	649	642	644	647	403
45°	540	544	538	539	540	417
55°	422	424	421	418	418	377
65°	294	293	291	288	287	289
75°	159	158	156	153	152	168
85°	38	36	35	32	33	45
90°	0	3	8	7	7	4
95°	48	145	644	230	141	55
105°	194	281	1134	2166	2051	207
115°	360	429	924	1904	2240	356
125°	500	557	911	1503	1772	445
135°	604	667	907	1297	1463	466
145°	705	757	904	1117	1223	442
155°	805	832	910	1000	1038	371
165°	878	886	912	946	958	247
175°	916	916	916	922	920	87
180°	919	919	919	919	919	



TEST NUMBER: P855061

CATALOG NUMBER: SQ2-F-125U-050D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	829.9	829.9	829.9	829.9	829.9
2.5°	824.5	834.2	826.3	828.1	829.0
5°	820.8	831.9	823.1	824.4	829.9
7.5°	814.1	826.0	816.3	818.5	824.7
10°	809.5	820.6	811.8	813.0	817.5
12.5°	802.3	813.4	804.6	806.7	811.1
15°	789.2	799.1	791.5	795.0	799.4
17.5°	774.0	784.7	776.1	779.1	782.9
20°	763.2	772.0	764.3	765.6	771.1
22.5°	749.6	758.4	751.7	752.0	756.6
25°	729.3	737.0	729.3	730.5	733.8
27.5°	706.0	712.6	706.0	707.2	710.0
30°	689.7	696.4	689.7	690.8	692.0
32.5°	671.6	677.4	670.7	671.9	674.8
35°	644.5	648.9	642.2	644.5	646.7
37.5°	615.5	618.8	613.3	614.4	616.4
40°	594.7	598.0	592.5	593.6	594.7
42.5°	573.9	576.4	570.7	571.9	573.9
45°	540.4	543.7	538.2	539.3	540.4
47.5°	506.5	508.6	503.8	502.9	504.9
50°	483.9	485.0	479.4	479.4	480.5
52.5°	459.5	460.6	456.8	455.0	456.1
55°	421.7	424.0	420.6	418.3	418.3
57.5°	383.7	385.8	381.5	380.3	380.1
60°	358.4	359.5	356.2	355.0	353.9
62.5°	333.1	333.3	329.9	328.8	327.7
65°	294.0	292.8	290.6	288.3	287.2
67.5°	250.1	251.2	249.0	245.3	245.3
70°	223.9	225.0	222.7	218.2	218.2
72.5°	198.5	197.9	196.5	192.9	191.1
75°	159.4	158.3	156.0	152.6	151.5
77.5°	120.3	119.2	118.0	113.7	114.6
80°	95.0	93.8	92.7	89.3	89.3
82.5°	72.4	70.3	69.2	65.8	65.8
85°	38.4	36.2	35.0	31.7	32.8
87.5°	10.9	10.6	10.6	8.6	8.6
90°	0.0	3.3	7.9	6.8	6.8
92.5°	16.3	58.5	187.0	61.6	47.5
95°	47.5	144.7	644.4	229.7	141.3
97.5°	89.3	188.4	1093.7	666.1	406.6
100°	116.5	213.7	1262.8	1126.0	730.3
102.5°	147.2	240.9	1242.0	1665.9	1266.7
105°	194.5	280.6	1133.9	2165.7	2050.8
107.5°	245.6	326.6	1031.3	2209.1	2330.9
110°	282.7	356.7	982.4	2155.2	2375.3



TEST NUMBER: P855061

CATALOG NUMBER: SQ2-F-125U-050D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	313.4	386.6	951.7	2058.1	2341.8
115°	359.5	429.2	923.6	1903.6	2239.6
117.5°	407.0	469.8	912.8	1761.9	2096.4
120°	434.2	496.0	910.1	1674.8	1998.8
122.5°	460.4	521.3	911.0	1599.3	1901.1
125°	499.6	557.2	911.2	1502.9	1771.5
127.5°	533.3	592.2	911.0	1430.7	1654.6
130°	555.0	614.7	910.1	1389.4	1589.5
132.5°	574.0	636.4	909.2	1351.1	1538.8
135°	603.7	666.7	906.7	1297.1	1462.9
137.5°	632.6	696.1	904.2	1242.1	1389.4
140°	653.4	714.2	903.3	1204.9	1344.2
142.5°	673.3	731.5	903.3	1169.3	1293.6
145°	705.4	757.4	904.4	1117.1	1223.2
147.5°	736.6	781.7	906.0	1072.6	1154.7
150°	757.4	797.2	907.8	1046.2	1115.8
152.5°	778.2	811.0	908.7	1025.9	1081.5
155°	804.9	831.5	910.1	1000.3	1037.8
157.5°	830.2	849.2	911.4	981.2	1007.5
160°	845.6	861.1	912.3	969.3	990.3
162.5°	859.2	871.2	912.3	959.2	975.0
165°	878.4	886.2	912.3	946.5	957.5
167.5°	892.0	896.8	912.5	936.9	942.6
170°	901.0	903.3	913.4	930.5	932.7
172.5°	907.3	908.7	915.3	926.8	926.3
175°	915.7	915.7	915.7	922.5	920.2
177.5°	919.1	918.2	917.3	921.7	918.2
180°	919.1	919.1	919.1	919.1	919.1

TEST NUMBER: P855061

CATALOG NUMBER: SQ2-F-125U-050D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.66	15.37	15.78	16.48	18.02	14.58	15.29	15.70	16.40	17.94
	3H	16.43	17.06	17.55	18.18	19.74	16.31	16.94	17.43	18.06	19.62
	4H	17.08	17.68	18.21	18.80	20.36	16.93	17.53	18.06	18.65	20.21
	6H	17.54	18.09	18.68	19.22	20.79	17.36	17.91	18.50	19.03	20.60
	8H	17.67	18.20	18.82	19.34	20.91	17.47	18.00	18.62	19.14	20.70
	12H	17.74	18.24	18.89	19.37	20.96	17.52	18.02	18.67	19.15	20.74
4H	2H	15.19	15.79	16.33	16.91	18.47	15.13	15.73	16.27	16.85	18.41
	3H	17.16	17.67	18.31	18.81	20.39	17.06	17.56	18.20	18.70	20.28
	4H	17.95	18.41	19.10	19.54	21.14	17.80	18.27	18.95	19.40	20.99
	6H	18.53	18.92	19.68	20.08	21.67	18.35	18.74	19.50	19.90	21.49
	8H	18.71	19.08	19.87	20.23	21.83	18.51	18.88	19.67	20.03	21.63
	12H	18.81	19.14	19.98	20.30	21.91	18.58	18.91	19.75	20.07	21.68
8H	4H	18.18	18.55	19.34	19.70	21.30	18.05	18.42	19.21	19.57	21.18
	6H	18.89	19.20	20.07	20.39	21.99	18.73	19.03	19.90	20.22	21.82
	8H	19.16	19.42	20.34	20.59	22.21	18.96	19.23	20.15	20.40	22.02
	12H	19.32	19.55	20.50	20.72	22.37	19.09	19.32	20.28	20.49	22.14
12H	4H	18.17	18.50	19.34	19.66	21.27	18.05	18.38	19.22	19.54	21.15
	6H	18.93	19.20	20.12	20.37	21.99	18.77	19.04	19.96	20.21	21.83
	8H	19.22	19.45	20.40	20.62	22.27	19.03	19.27	20.22	20.43	22.09