

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854966

Luminaire Tested: SQ2-PH1-025U-075D-830-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854966
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PH1-025U-075D-830-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4929.0 lumens
Efficiency: N/A
Efficacy: 144.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 34.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854966

CATALOG NUMBER: SQ2-PH1-025U-075D-830-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854966

CATALOG NUMBER: SQ2-PH1-025U-075D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	71	69	66
2	95	87	81	76	90	84	78	73	76	72	68	70	66	63	64	61	59	55
3	87	77	70	64	83	74	67	61	68	62	58	62	57	54	57	53	50	47
4	80	68	60	54	76	66	58	52	60	54	49	55	50	46	51	47	43	40
5	73	61	53	47	70	59	51	45	54	48	43	50	44	40	46	41	38	35
6	68	55	47	41	64	53	45	40	49	42	37	45	40	35	42	37	33	31
7	63	50	42	36	60	48	40	35	44	38	33	41	36	31	38	33	30	27
8	58	46	37	32	56	44	36	31	41	34	30	38	32	28	35	30	27	25
9	54	42	34	29	52	40	33	28	37	31	27	35	29	25	32	28	24	22
10	51	38	31	26	49	37	30	25	35	28	24	32	27	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27679	27679	27679
5°	27835	26172	25298
10°	27196	23825	22997
15°	27318	22410	22547
20°	26344	21720	22727
25°	25860	21618	22199
30°	25299	21559	22380
35°	25109	21313	26233
40°	25130	21176	20799
45°	25138	20372	17915
50°	24787	20773	16799
55°	24473	22542	16113
60°	24228	19753	15116
65°	23805	16011	13150
70°	22480	13629	9394
75°	20044	10274	7124
80°	16383	6676	6676
85°	10263	6058	4520

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25138 cd/sqm



TEST NUMBER: P854966

CATALOG NUMBER: SQ2-PH1-025U-075D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.8	3.1
10°-20°	396.8	8.0
20°-30°	581.8	11.8
30°-40°	704.5	14.3
40°-50°	692.8	14.1
50°-60°	603.1	12.2
60°-70°	419.3	8.5
70°-80°	198.8	4.0
80°-90°	44.3	0.9
90°-100°	74.1	1.5
100°-110°	230.6	4.7
110°-120°	225.6	4.6
120°-130°	184.1	3.7
130°-140°	150.6	3.1
140°-150°	117.6	2.4
150°-160°	84.8	1.7
160°-170°	51.9	1.1
170°-180°	17.5	0.4
0°-30°	1129.3	22.9
0°-40°	1833.9	37.2
0°-60°	3129.8	63.5
0°-90°	3792.1	76.9
90°-120°	530.3	10.8
90°-150°	982.7	19.9
90°-180°	1137.0	23.1
0°-180°	4929.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1714	1714	1714	1714	1714	
5°	1717	1716	1615	1564	1561	161
15°	1634	1456	1341	1331	1349	456
25°	1452	1235	1214	1251	1246	668
35°	1274	1030	1081	1175	1331	798
45°	1101	816	892	923	785	846
55°	869	635	801	577	572	777
65°	623	436	419	344	344	612
75°	321	222	165	117	114	340
85°	55	36	33	26	24	74
90°	0	1	3	3	3	2
95°	10	30	136	50	33	12
105°	40	57	227	433	414	43
115°	72	85	184	380	445	71
125°	100	111	182	299	351	89
135°	120	133	181	258	290	93
145°	140	152	181	223	243	88
155°	161	166	182	200	207	74
165°	176	178	183	189	191	50
175°	183	183	183	184	183	17
180°	183	183	183	183	183	



TEST NUMBER: P854966

CATALOG NUMBER: SQ2-PH1-025U-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1714.3	1714.3	1714.3	1714.3	1714.3
2.5°	1710.3	1728.2	1688.2	1672.4	1669.8
5°	1717.4	1715.9	1614.8	1564.1	1560.9
7.5°	1686.1	1636.7	1515.9	1460.0	1457.5
10°	1658.8	1583.8	1453.2	1402.7	1402.7
12.5°	1652.2	1533.9	1402.3	1365.0	1372.7
15°	1634.3	1455.7	1340.7	1331.3	1348.9
17.5°	1575.0	1382.6	1292.8	1314.1	1334.5
20°	1533.2	1343.4	1264.1	1303.6	1322.7
22.5°	1498.0	1305.7	1243.1	1286.4	1296.7
25°	1451.6	1234.8	1213.5	1250.9	1246.1
27.5°	1396.1	1169.8	1183.8	1206.7	1209.6
30°	1357.0	1130.5	1156.4	1179.7	1200.4
32.5°	1319.2	1085.1	1126.3	1181.6	1229.1
35°	1273.9	1029.8	1081.3	1174.6	1330.9
37.5°	1226.2	964.7	1036.0	1114.5	1164.2
40°	1192.3	918.0	1004.7	1101.6	986.8
42.5°	1155.7	881.4	957.8	1082.8	888.9
45°	1100.9	815.5	892.2	923.3	784.6
47.5°	1036.3	764.3	847.9	770.0	715.7
50°	986.8	730.1	827.0	703.8	668.8
52.5°	938.5	694.6	812.6	649.2	625.7
55°	869.4	634.9	800.8	577.3	572.4
57.5°	796.0	574.3	708.2	514.7	522.9
60°	750.3	535.0	611.7	477.7	468.1
62.5°	702.0	496.9	521.6	430.7	421.2
65°	623.1	436.4	419.1	344.2	344.2
67.5°	536.3	373.6	339.5	281.6	243.3
70°	476.2	332.7	288.7	224.5	199.0
72.5°	412.3	289.2	236.5	184.0	154.7
75°	321.3	222.4	164.7	117.4	114.2
77.5°	232.2	160.2	110.9	87.1	87.4
80°	176.2	121.9	71.8	70.2	71.8
82.5°	123.9	83.8	53.5	55.7	56.1
85°	55.4	36.3	32.7	26.0	24.4
87.5°	11.8	10.7	7.2	7.2	7.2
90°	0.0	1.1	3.4	3.4	3.4
92.5°	3.6	12.6	43.0	14.1	11.4
95°	10.1	29.8	136.0	50.2	32.6
97.5°	18.4	38.9	225.2	140.2	88.3
100°	24.8	43.4	253.9	237.5	158.4
102.5°	31.0	48.8	248.6	339.3	266.4
105°	40.5	57.0	227.0	433.4	413.6
107.5°	49.9	65.2	206.3	440.6	462.3
110°	56.2	71.6	195.5	430.2	473.1



TEST NUMBER: P854966

CATALOG NUMBER: SQ2-PH1-025U-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	62.5	77.0	190.2	411.7	465.9
115°	71.9	85.1	184.3	380.2	445.0
117.5°	81.2	93.3	181.8	350.2	416.5
120°	86.5	98.6	180.9	333.0	396.7
122.5°	91.9	104.0	181.8	318.5	377.0
125°	100.1	111.0	182.0	298.9	350.6
127.5°	106.5	117.7	182.0	284.5	328.3
130°	110.1	122.2	182.0	276.2	315.8
132.5°	114.6	126.7	181.1	269.0	305.8
135°	120.3	133.4	180.9	258.1	289.9
137.5°	126.7	138.8	180.9	247.3	276.2
140°	130.4	142.5	180.9	239.9	266.4
142.5°	134.9	146.1	180.9	232.7	256.4
145°	140.4	151.5	180.9	223.0	242.7
147.5°	147.2	156.7	182.0	213.9	229.5
150°	151.7	159.4	182.0	209.3	221.4
152.5°	155.4	162.1	182.0	204.8	215.0
155°	160.7	166.2	182.0	200.2	206.8
157.5°	166.1	170.3	182.0	196.1	200.2
160°	169.7	173.0	182.0	193.3	196.6
162.5°	172.4	174.8	182.0	191.5	194.0
165°	176.4	177.5	183.2	188.8	191.1
167.5°	178.9	179.1	182.0	187.2	188.4
170°	179.8	180.9	182.0	185.4	186.6
172.5°	181.6	181.8	182.9	184.5	184.7
175°	183.2	183.2	183.2	184.3	183.2
177.5°	183.2	183.2	183.2	183.2	183.2
180°	183.2	183.2	183.2	183.2	183.2

TEST NUMBER: P854966

CATALOG NUMBER: SQ2-PH1-025U-075D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.06	22.22	21.75	22.92	23.75	19.73	20.89	20.42	21.59	22.42
	3H	23.11	24.14	23.81	24.86	25.72	20.79	21.83	21.49	22.54	23.40
	4H	23.85	24.83	24.57	25.55	26.43	21.02	21.99	21.74	22.72	23.59
	6H	24.35	25.25	25.09	25.99	26.88	21.18	22.08	21.91	22.81	23.70
	8H	24.49	25.34	25.23	26.10	26.99	21.22	22.08	21.96	22.83	23.72
	12H	24.54	25.36	25.29	26.11	27.02	21.23	22.04	21.97	22.79	23.71
4H	2H	21.47	22.45	22.20	23.17	24.05	20.41	21.39	21.13	22.11	22.99
	3H	23.61	24.42	24.34	25.18	26.07	21.62	22.43	22.35	23.19	24.08
	4H	24.43	25.17	25.18	25.93	26.85	21.91	22.64	22.66	23.41	24.33
	6H	25.03	25.67	25.80	26.46	27.39	22.13	22.77	22.90	23.56	24.48
	8H	25.21	25.81	25.99	26.59	27.53	22.19	22.79	22.97	23.57	24.51
	12H	25.29	25.83	26.09	26.63	27.58	22.22	22.75	23.01	23.56	24.50
8H	4H	24.47	25.07	25.25	25.85	26.79	22.14	22.74	22.92	23.52	24.46
	6H	25.14	25.63	25.94	26.46	27.40	22.43	22.92	23.23	23.75	24.69
	8H	25.36	25.80	26.18	26.63	27.59	22.53	22.97	23.35	23.80	24.75
	12H	25.49	25.88	26.31	26.69	27.71	22.59	22.98	23.41	23.79	24.81
12H	4H	24.44	24.97	25.23	25.78	26.73	22.16	22.69	22.95	23.50	24.44
	6H	25.11	25.55	25.93	26.38	27.33	22.46	22.90	23.28	23.72	24.68
	8H	25.36	25.74	26.18	26.56	27.58	22.59	22.98	23.41	23.79	24.81