

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855056

Luminaire Tested: SQ2-F-150U-075D-830-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855056
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-14, G2-2308-131-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-F-150U-075D-830-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10128.6 lumens
Efficiency: N/A
Efficacy: 121.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 83.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855056
CATALOG NUMBER: SQ2-F-150U-075D-830-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855056

CATALOG NUMBER: SQ2-F-150U-075D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	82	85	81	78	75	65	62	60	50	48	47	36	35	34	28
2	85	78	72	67	77	71	65	61	56	53	50	43	41	39	31	30	29	23
3	78	69	61	56	70	62	56	51	50	45	42	38	35	33	28	26	24	19
4	71	60	53	47	64	55	48	43	44	39	35	34	31	28	25	22	21	17
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	34	54	44	37	32	35	30	26	27	24	21	20	18	16	13
7	55	43	35	30	50	39	32	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	26	46	36	29	24	29	24	20	23	19	16	17	14	12	10
9	48	36	28	23	43	32	26	22	26	21	18	21	17	15	15	13	11	9
10	44	32	25	21	40	30	23	19	24	19	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19328	19328	19328
5°	19191	19245	19402
10°	19146	19200	19335
15°	19029	19084	19275
20°	18916	18945	19112
25°	18743	18743	18857
30°	18550	18550	18610
35°	18325	18260	18388
40°	18082	18014	18082
45°	17801	17728	17801
50°	17535	17369	17412
55°	17126	17078	16988
60°	16695	16591	16485
65°	16202	16011	15828
70°	15243	15168	14861
75°	14348	14042	13637
80°	12738	12441	11985
85°	10263	9355	8762

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 17911 cd/sqm



TEST NUMBER: P855056

CATALOG NUMBER: SQ2-F-150U-075D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.2	1.1
10°-20°	323.3	3.2
20°-30°	486.5	4.8
30°-40°	582.1	5.7
40°-50°	600.6	5.9
50°-60°	541.8	5.3
60°-70°	413.5	4.1
70°-80°	237.7	2.3
80°-90°	63.2	0.6
90°-100°	417.7	4.1
100°-110°	1367.8	13.5
110°-120°	1352.3	13.4
120°-130°	1105.4	10.9
130°-140°	902.1	8.9
140°-150°	702.0	6.9
150°-160°	505.5	5.0
160°-170°	309.2	3.1
170°-180°	104.5	1.0
0°-30°	923.0	9.1
0°-40°	1505.1	14.9
0°-60°	2647.5	26.1
0°-90°	3361.9	33.2
90°-120°	3137.9	31.0
90°-150°	5847.4	57.7
90°-180°	6767.0	66.8
0°-180°	10128.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1197	1197	1197	1197	1197	
5°	1184	1200	1187	1189	1197	112
15°	1138	1153	1142	1147	1153	321
25°	1052	1063	1052	1054	1058	484
35°	930	936	926	930	933	581
45°	780	784	776	778	780	601
55°	608	612	607	604	604	544
65°	424	422	419	416	414	417
75°	230	228	225	220	219	243
85°	55	52	50	46	47	64
90°	1	3	9	8	9	5
95°	59	170	760	271	176	66
105°	238	339	1358	2580	2451	250
115°	428	512	1103	2279	2676	423
125°	596	664	1087	1798	2112	530
135°	718	794	1078	1550	1748	555
145°	839	901	1076	1334	1461	526
155°	957	988	1083	1193	1239	440
165°	1044	1054	1087	1129	1141	294
175°	1092	1092	1093	1101	1098	104
180°	1096	1096	1096	1096	1096	



TEST NUMBER: P855056

CATALOG NUMBER: SQ2-F-150U-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1197.1	1197.1	1197.1	1197.1	1197.1
2.5°	1189.3	1203.3	1191.9	1194.6	1195.9
5°	1184.1	1200.1	1187.4	1189.2	1197.1
7.5°	1174.3	1191.6	1177.6	1180.7	1189.7
10°	1167.8	1183.8	1171.1	1172.8	1179.3
12.5°	1157.3	1173.4	1160.6	1163.8	1170.1
15°	1138.4	1152.8	1141.7	1146.8	1153.1
17.5°	1116.6	1131.9	1119.6	1123.9	1129.3
20°	1100.9	1113.7	1102.6	1104.4	1112.3
22.5°	1081.3	1094.1	1084.3	1084.7	1091.5
25°	1052.1	1063.1	1052.1	1053.8	1058.5
27.5°	1018.4	1028.0	1018.4	1020.2	1024.2
30°	995.0	1004.5	995.0	996.5	998.2
32.5°	968.8	977.1	967.5	969.3	973.4
35°	929.7	936.1	926.4	929.7	932.9
37.5°	887.9	892.8	884.6	886.3	889.3
40°	857.9	862.7	854.7	856.3	857.9
42.5°	827.9	831.5	823.3	825.0	827.9
45°	779.6	784.4	776.4	778.0	779.6
47.5°	730.7	733.6	726.8	725.5	728.5
50°	698.1	699.6	691.5	691.6	693.2
52.5°	662.9	664.5	658.9	656.3	657.9
55°	608.4	611.6	606.7	603.5	603.5
57.5°	553.6	556.4	550.3	548.7	548.4
60°	517.0	518.6	513.8	512.1	510.5
62.5°	480.5	480.9	475.9	474.3	472.7
65°	424.1	422.5	419.1	415.9	414.3
67.5°	360.8	362.4	359.2	353.9	353.9
70°	322.9	324.5	321.3	314.8	314.8
72.5°	286.4	285.5	283.5	278.3	275.7
75°	230.0	228.4	225.1	220.1	218.6
77.5°	173.6	172.0	170.3	164.1	165.4
80°	137.0	135.5	133.8	128.9	128.9
82.5°	104.4	101.5	99.8	95.0	95.0
85°	55.4	52.2	50.5	45.7	47.3
87.5°	15.8	15.0	14.8	12.0	12.2
90°	1.1	3.3	9.0	7.9	9.0
92.5°	19.1	69.9	214.5	69.8	55.9
95°	58.6	169.8	759.5	270.6	175.8
97.5°	106.4	224.0	1303.0	788.2	488.6
100°	139.7	252.1	1507.6	1346.3	892.4
102.5°	177.6	287.3	1485.1	1983.7	1537.8
105°	237.8	339.1	1357.7	2579.6	2450.7
107.5°	297.0	390.0	1233.5	2635.3	2777.0
110°	335.8	426.1	1174.1	2570.4	2833.7



TEST NUMBER: P855056

CATALOG NUMBER: SQ2-F-150U-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.8	460.4	1138.0	2457.7	2794.9
115°	428.2	511.8	1103.1	2279.4	2676.0
117.5°	482.0	560.2	1089.8	2104.2	2507.0
120°	517.2	591.0	1086.2	2002.1	2394.4
122.5°	548.7	620.7	1086.2	1914.1	2278.0
125°	596.1	664.4	1087.3	1797.5	2111.5
127.5°	636.2	705.7	1086.0	1711.7	1984.8
130°	661.4	731.9	1085.1	1659.7	1906.5
132.5°	683.9	756.2	1082.4	1615.0	1838.9
135°	717.7	793.7	1078.3	1550.3	1747.5
137.5°	753.3	828.6	1075.8	1483.1	1661.3
140°	778.6	851.3	1074.9	1440.4	1609.0
142.5°	803.8	872.2	1074.9	1395.0	1547.7
145°	839.4	901.1	1076.0	1333.6	1461.4
147.5°	876.8	928.1	1077.6	1280.1	1376.7
150°	900.2	945.4	1079.4	1249.1	1330.7
152.5°	923.7	963.5	1080.3	1223.6	1291.0
155°	956.6	988.5	1082.8	1193.2	1239.4
157.5°	986.1	1009.2	1085.3	1169.2	1202.7
160°	1005.0	1023.8	1086.2	1155.5	1182.0
162.5°	1021.3	1036.5	1086.2	1144.5	1163.9
165°	1044.5	1054.4	1087.3	1129.3	1141.4
167.5°	1064.0	1068.9	1088.7	1117.4	1124.1
170°	1074.9	1077.2	1089.6	1111.0	1113.2
172.5°	1083.0	1084.4	1092.3	1106.4	1106.9
175°	1091.9	1091.9	1093.0	1100.8	1098.5
177.5°	1096.3	1095.5	1094.5	1099.9	1096.3
180°	1096.3	1096.3	1096.3	1096.3	1096.3



TEST NUMBER: P855056

CATALOG NUMBER: SQ2-F-150U-075D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.47	17.20	17.56	18.29	19.78	16.39	17.13	17.48	18.21	19.70
	3H	18.24	18.90	19.34	19.99	21.50	18.12	18.78	19.22	19.87	21.38
	4H	18.89	19.52	20.00	20.62	22.13	18.74	19.37	19.85	20.46	21.98
	6H	19.36	19.93	20.47	21.03	22.56	19.17	19.75	20.29	20.85	22.37
	8H	19.49	20.04	20.61	21.15	22.67	19.29	19.84	20.41	20.95	22.47
	12H	19.56	20.08	20.68	21.19	22.73	19.34	19.86	20.46	20.97	22.51
4H	2H	17.00	17.63	18.12	18.73	20.24	16.94	17.57	18.06	18.66	20.18
	3H	18.98	19.50	20.10	20.63	22.15	18.87	19.39	19.99	20.52	22.05
	4H	19.76	20.24	20.89	21.36	22.91	19.62	20.10	20.75	21.21	22.76
	6H	20.35	20.76	21.48	21.89	23.43	20.17	20.58	21.30	21.71	23.25
	8H	20.53	20.92	21.66	22.04	23.60	20.33	20.71	21.46	21.84	23.40
	12H	20.63	20.98	21.78	22.12	23.68	20.40	20.75	21.55	21.89	23.45
8H	4H	20.00	20.39	21.13	21.51	23.07	19.88	20.26	21.01	21.39	22.94
	6H	20.71	21.03	21.87	22.20	23.75	20.55	20.86	21.70	22.04	23.59
	8H	20.98	21.26	22.14	22.41	23.98	20.79	21.06	21.95	22.21	23.79
	12H	21.14	21.39	22.30	22.53	24.14	20.91	21.16	22.08	22.30	23.91
12H	4H	19.99	20.34	21.14	21.48	23.04	19.87	20.22	21.02	21.36	22.92
	6H	20.76	21.03	21.91	22.18	23.76	20.60	20.87	21.76	22.02	23.60
	8H	21.04	21.29	22.20	22.43	24.04	20.86	21.10	22.02	22.25	23.85