

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855017

Luminaire Tested: SQ2-FB-0U-075D-830-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P855017  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-FB-0U-075D-830-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 750 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3352.4 lumens  
Efficiency: N/A  
Efficacy: 125.6 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 26.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P855017

CATALOG NUMBER: SQ2-FB-0U-075D-830-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P855017

CATALOG NUMBER: SQ2-FB-0U-075D-830-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	89	78	70	63	87	77	69	63	74	67	61	71	65	60	68	63	59	57
4	81	69	60	53	79	67	59	52	65	57	52	63	56	51	60	55	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	43	54	48	43	41
6	68	54	45	39	66	53	45	38	52	44	38	50	43	38	48	42	37	35
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27
9	54	40	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24
10	51	37	29	23	49	37	29	23	36	28	23	35	28	23	34	28	23	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5478	5478	5478
5°	5340	7402	9702
10°	5000	14332	18880
15°	4527	18648	21728
20°	4009	20515	22756
25°	3545	21937	23129
30°	3132	22592	23415
35°	2797	22984	25172
40°	2546	23204	26744
45°	2347	23315	28005
50°	2213	23762	28514
55°	2159	24380	28743
60°	2212	24703	28598
65°	2308	24363	27794
70°	2384	23561	21017
75°	2645	21166	11603
80°	2734	10925	10767
85°	2723	7558	4520

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 29000 cd/sqm



TEST NUMBER: P855017

CATALOG NUMBER: SQ2-FB-0U-075D-830-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.8	1.7
10°-20°	259.5	7.7
20°-30°	456.5	13.6
30°-40°	590.9	17.6
40°-50°	651.7	19.4
50°-60°	608.5	18.2
60°-70°	470.3	14.0
70°-80°	216.9	6.5
80°-90°	41.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	772.8	23.1
0°-40°	1363.6	40.7
0°-60°	2623.8	78.3
0°-90°	3352.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3352.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	339	339	339	339	339	
5°	330	377	457	557	599	31
15°	271	534	1116	1249	1300	75
25°	199	717	1231	1286	1298	91
35°	142	692	1166	1207	1277	89
45°	103	530	1021	1172	1226	80
55°	77	316	866	996	1021	69
65°	60	178	638	715	728	59
75°	42	109	339	183	186	44
85°	15	32	41	28	24	16
90°	0	0	0	0	0	



TEST NUMBER: P855017

CATALOG NUMBER: SQ2-FB-0U-075D-830-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	339.3	339.3	339.3	339.3	339.3
2.5°	336.6	350.7	366.7	385.1	392.8
5°	329.5	377.3	456.7	557.2	598.6
7.5°	316.7	414.0	664.1	932.9	1015.8
10°	305.0	440.6	874.2	1106.9	1151.6
12.5°	291.9	476.0	1006.0	1169.5	1215.4
15°	270.8	533.9	1115.6	1248.9	1299.9
17.5°	248.9	599.1	1166.5	1298.0	1325.7
20°	233.3	644.7	1194.0	1306.9	1324.4
22.5°	218.9	678.8	1213.5	1299.1	1317.9
25°	199.0	717.3	1231.4	1285.5	1298.3
27.5°	179.8	727.3	1223.6	1259.1	1271.5
30°	168.0	724.6	1211.8	1238.4	1255.9
32.5°	157.6	716.7	1194.9	1220.5	1258.5
35°	141.9	692.1	1166.1	1207.0	1277.1
37.5°	128.6	652.6	1128.4	1211.8	1279.4
40°	120.8	623.1	1100.9	1211.5	1268.9
42.5°	112.8	588.4	1069.6	1198.5	1255.9
45°	102.8	530.2	1021.1	1172.4	1226.5
47.5°	93.3	464.6	976.0	1136.1	1175.6
50°	88.1	419.8	946.0	1103.3	1135.2
52.5°	82.9	376.3	916.0	1064.2	1093.4
55°	76.7	315.9	866.1	995.5	1021.1
57.5°	71.1	264.1	809.3	919.8	940.5
60°	68.5	236.0	765.0	864.9	885.6
62.5°	64.6	210.3	715.4	807.5	827.0
65°	60.4	178.4	637.7	714.7	727.5
67.5°	54.5	154.7	555.3	602.3	578.3
70°	50.5	143.0	499.1	513.9	445.2
72.5°	47.9	130.3	437.8	398.9	269.1
75°	42.4	109.3	339.3	182.7	186.0
77.5°	34.6	84.7	223.1	140.3	143.3
80°	29.4	69.2	117.5	114.2	115.8
82.5°	24.2	53.8	81.0	84.1	81.9
85°	14.7	32.2	40.8	27.7	24.4
87.5°	5.2	11.6	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P855017

CATALOG NUMBER: SQ2-FB-0U-075D-830-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.73	18.42	17.10	18.73	19.05	25.47	27.15	25.83	27.47	27.78
	3H	17.52	19.04	17.90	19.37	19.73	27.15	28.67	27.53	29.00	29.36
	4H	17.86	19.29	18.25	19.64	20.01	27.37	28.80	27.76	29.15	29.52
	6H	18.12	19.45	18.53	19.81	20.20	27.49	28.82	27.90	29.19	29.58
	8H	18.20	19.47	18.62	19.86	20.25	27.52	28.79	27.95	29.18	29.58
	12H	18.25	19.47	18.68	19.85	20.28	27.52	28.74	27.95	29.12	29.55
4H	2H	21.23	22.66	21.62	23.01	23.38	26.01	27.44	26.40	27.79	28.16
	3H	22.23	23.44	22.64	23.83	24.23	27.91	29.11	28.32	29.50	29.90
	4H	22.55	23.64	22.98	24.05	24.48	28.18	29.27	28.61	29.68	30.11
	6H	22.73	23.68	23.19	24.12	24.57	28.38	29.32	28.83	29.76	30.22
	8H	22.77	23.66	23.23	24.10	24.57	28.42	29.31	28.88	29.75	30.21
	12H	22.81	23.60	23.29	24.08	24.54	28.43	29.23	28.91	29.70	30.17
8H	4H	23.80	24.68	24.26	25.12	25.59	28.37	29.25	28.83	29.69	30.16
	6H	24.07	24.81	24.57	25.29	25.77	28.61	29.35	29.10	29.83	30.31
	8H	24.15	24.81	24.66	25.32	25.80	28.68	29.34	29.19	29.85	30.33
	12H	24.22	24.80	24.73	25.29	25.85	28.72	29.29	29.22	29.78	30.34
12H	4H	23.86	24.65	24.33	25.12	25.59	28.36	29.16	28.84	29.63	30.10
	6H	24.18	24.83	24.68	25.34	25.82	28.60	29.26	29.11	29.77	30.25
	8H	24.32	24.90	24.83	25.39	25.95	28.71	29.29	29.22	29.78	30.34