

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855016

Luminaire Tested: SQ2-FB-0U-125D-830-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855016
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FB-0U-125D-830-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5612.3 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 49.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855016

CATALOG NUMBER: SQ2-FB-0U-125D-830-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855016

CATALOG NUMBER: SQ2-FB-0U-125D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	89	78	70	63	87	77	69	63	74	67	61	71	65	60	68	63	59	57
4	81	69	60	53	79	67	59	52	65	57	52	63	56	51	60	55	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	43	54	48	43	41
6	68	54	45	39	66	53	45	38	52	44	38	50	43	38	48	42	37	35
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27
9	54	40	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24
10	51	37	29	23	49	37	29	23	36	28	23	35	28	23	34	28	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9169	9169	9169
5°	8938	12391	16242
10°	8371	23996	31604
15°	7577	31219	36378
20°	6710	34343	38096
25°	5934	36727	38721
30°	5244	37824	39198
35°	4681	38483	42141
40°	4258	38849	44776
45°	3927	39030	46887
50°	3702	39780	47738
55°	3612	40814	48116
60°	3701	41356	47879
65°	3862	40791	46525
70°	3998	39442	35188
75°	4429	35427	19420
80°	4575	18280	18029
85°	4539	12653	7577

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 48552 cd/sqm

TEST NUMBER: P855016

CATALOG NUMBER: SQ2-FB-0U-125D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	1.7
10°-20°	434.4	7.7
20°-30°	764.2	13.6
30°-40°	989.2	17.6
40°-50°	1091.0	19.4
50°-60°	1018.6	18.1
60°-70°	787.3	14.0
70°-80°	363.2	6.5
80°-90°	69.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1293.7	23.1
0°-40°	2282.9	40.7
0°-60°	4392.5	78.3
0°-90°	5612.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5612.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	568	568	568	568	568	
5°	552	632	764	933	1002	51
15°	453	894	1868	2091	2176	126
25°	333	1201	2062	2152	2174	153
35°	238	1159	1952	2021	2138	149
45°	172	888	1709	1963	2053	133
55°	128	529	1450	1667	1709	116
65°	101	299	1068	1196	1218	99
75°	71	183	568	306	311	73
85°	24	54	68	46	41	27
90°	0	0	0	0	0	



TEST NUMBER: P855016

CATALOG NUMBER: SQ2-FB-0U-125D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	567.9	567.9	567.9	567.9	567.9
2.5°	563.6	587.0	613.8	644.7	657.5
5°	551.5	631.7	764.5	932.7	1002.1
7.5°	530.3	693.1	1111.9	1561.8	1700.6
10°	510.6	737.5	1463.6	1853.0	1927.7
12.5°	488.8	796.9	1684.2	1957.9	2034.8
15°	453.3	893.8	1867.7	2090.8	2176.3
17.5°	416.6	1003.0	1952.8	2173.0	2219.5
20°	390.5	1079.3	1998.8	2187.8	2217.2
22.5°	366.4	1136.4	2031.5	2174.8	2206.3
25°	333.1	1200.9	2061.6	2152.2	2173.5
27.5°	300.9	1217.7	2048.5	2108.0	2128.8
30°	281.3	1213.1	2028.8	2073.1	2102.5
32.5°	263.8	1199.8	2000.4	2043.4	2107.0
35°	237.5	1158.7	1952.4	2020.6	2138.0
37.5°	215.2	1092.5	1889.0	2028.6	2141.9
40°	202.0	1043.1	1843.2	2028.3	2124.4
42.5°	188.9	985.1	1790.7	2006.4	2102.5
45°	172.0	887.6	1709.3	1962.6	2053.4
47.5°	156.1	777.8	1634.0	1902.0	1968.2
50°	147.4	702.8	1583.7	1847.1	1900.5
52.5°	138.7	630.0	1533.5	1781.4	1830.6
55°	128.3	528.8	1449.9	1666.6	1709.3
57.5°	119.1	442.1	1355.0	1539.7	1574.4
60°	114.6	395.0	1280.7	1448.0	1482.7
62.5°	108.1	352.2	1197.6	1351.8	1384.4
65°	101.1	298.6	1067.7	1196.4	1217.8
67.5°	91.2	258.9	929.5	1008.3	968.3
70°	84.7	239.5	835.5	860.2	745.4
72.5°	80.3	218.1	732.9	667.9	450.6
75°	71.0	183.2	567.9	306.0	311.3
77.5°	57.9	141.7	373.6	234.9	239.7
80°	49.2	115.9	196.6	191.2	193.9
82.5°	40.4	90.1	135.5	140.8	137.0
85°	24.5	53.9	68.3	46.2	40.9
87.5°	8.7	19.4	11.0	11.0	11.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P855016

CATALOG NUMBER: SQ2-FB-0U-125D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.52	20.21	18.89	20.52	20.83	27.26	28.94	27.62	29.26	29.57
	3H	19.31	20.84	19.69	21.16	21.52	28.94	30.46	29.32	30.79	31.15
	4H	19.65	21.08	20.05	21.43	21.81	29.16	30.59	29.55	30.94	31.31
	6H	19.91	21.24	20.32	21.60	21.99	29.28	30.61	29.69	30.98	31.37
	8H	19.99	21.26	20.41	21.65	22.05	29.31	30.58	29.74	30.97	31.37
	12H	20.04	21.26	20.47	21.64	22.07	29.31	30.53	29.74	30.91	31.34
4H	2H	23.02	24.45	23.41	24.80	25.17	27.80	29.23	28.19	29.58	29.95
	3H	24.02	25.23	24.43	25.62	26.02	29.70	30.90	30.11	31.30	31.69
	4H	24.34	25.43	24.77	25.84	26.28	29.97	31.06	30.40	31.47	31.90
	6H	24.52	25.47	24.98	25.91	26.36	30.17	31.11	30.62	31.55	32.01
	8H	24.57	25.45	25.02	25.89	26.36	30.21	31.10	30.67	31.54	32.00
	12H	24.60	25.39	25.08	25.87	26.34	30.22	31.02	30.70	31.49	31.96
8H	4H	25.59	26.47	26.05	26.91	27.38	30.16	31.04	30.62	31.48	31.95
	6H	25.86	26.60	26.36	27.08	27.56	30.40	31.14	30.90	31.62	32.10
	8H	25.95	26.60	26.45	27.11	27.59	30.47	31.13	30.98	31.64	32.12
	12H	26.01	26.59	26.52	27.08	27.64	30.51	31.09	31.01	31.58	32.13
12H	4H	25.65	26.44	26.12	26.91	27.38	30.15	30.95	30.63	31.42	31.89
	6H	25.97	26.62	26.47	27.13	27.61	30.39	31.05	30.90	31.56	32.04
	8H	26.11	26.69	26.62	27.18	27.74	30.50	31.08	31.01	31.57	32.13