

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854931

Luminaire Tested: SQ2-PP3-075U-050D-830-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854931
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-11, G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PP3-075U-050D-830-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6074.9 lumens
Efficiency: N/A
Efficacy: 147.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 41.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854931

CATALOG NUMBER: SQ2-PP3-075U-050D-830-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854931

CATALOG NUMBER: SQ2-PP3-075U-050D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	81	72	65	60	74	66	60	55	56	51	48	46	43	40	37	34	33	28
4	74	64	56	51	68	59	52	47	50	45	41	41	37	34	33	30	28	25
5	68	57	49	43	62	53	46	41	45	39	35	37	33	30	30	27	25	21
6	63	51	43	38	58	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17
8	54	42	34	29	49	39	32	28	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	25	30	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17270	17270	17270
5°	17135	17280	17446
10°	17221	17351	17572
15°	17180	17349	17615
20°	17057	17464	17969
25°	16960	17685	18914
30°	16863	18043	19309
35°	16626	18096	19344
40°	16181	18063	17873
45°	15696	17246	13604
50°	15081	14712	11331
55°	14035	12380	8146
60°	12084	10624	5842
65°	10193	8206	5746
70°	8488	6458	5500
75°	7193	5571	5147
80°	6100	4835	4621
85°	4817	3983	2519

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 17246 cd/sqm



TEST NUMBER: P854931

CATALOG NUMBER: SQ2-PP3-075U-050D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.8	1.7
10°-20°	294.7	4.9
20°-30°	461.8	7.6
30°-40°	569.6	9.4
40°-50°	536.3	8.8
50°-60°	379.7	6.3
60°-70°	216.4	3.6
70°-80°	107.1	1.8
80°-90°	26.7	0.4
90°-100°	206.5	3.4
100°-110°	684.6	11.3
110°-120°	679.4	11.2
120°-130°	553.4	9.1
130°-140°	449.8	7.4
140°-150°	349.3	5.7
150°-160°	251.7	4.1
160°-170°	154.1	2.5
170°-180°	52.1	0.9
0°-30°	858.4	14.1
0°-40°	1428.0	23.5
0°-60°	2344.1	38.6
0°-90°	2694.2	44.3
90°-120°	1570.5	25.9
90°-150°	2922.9	48.1
90°-180°	3381.0	55.7
0°-180°	6074.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1070	1070	1070	1070	1070	
5°	1057	1076	1066	1069	1076	101
15°	1028	1042	1038	1048	1054	290
25°	952	976	993	1033	1062	438
35°	844	867	918	970	981	526
45°	687	739	755	640	596	529
55°	499	528	440	332	289	440
65°	267	281	215	152	150	268
75°	115	128	89	84	82	125
85°	26	24	22	17	14	30
90°	0	1	3	4	4	2
95°	29	87	374	134	89	34
105°	120	171	685	1293	1208	126
115°	214	256	552	1148	1343	211
125°	298	332	542	902	1064	265
135°	357	394	537	774	874	277
145°	415	446	536	666	729	260
155°	474	490	539	595	617	218
165°	520	526	542	563	569	147
175°	544	544	545	548	547	52
180°	546	546	546	546	546	



TEST NUMBER: P854931

CATALOG NUMBER: SQ2-PP3-075U-050D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1069.6	1069.6	1069.6	1069.6	1069.6
2.5°	1061.4	1076.5	1066.9	1068.7	1070.5
5°	1057.2	1075.9	1066.2	1068.7	1076.4
7.5°	1053.1	1072.3	1062.8	1066.9	1076.4
10°	1050.4	1067.0	1058.3	1064.2	1071.8
12.5°	1042.2	1057.9	1050.1	1057.7	1064.6
15°	1027.8	1042.1	1037.9	1048.2	1053.8
17.5°	1008.1	1025.6	1025.5	1040.1	1045.8
20°	992.7	1013.7	1016.4	1034.8	1045.8
22.5°	976.4	1001.0	1005.6	1033.2	1052.2
25°	952.0	976.3	992.7	1033.0	1061.7
27.5°	923.5	947.6	981.4	1026.5	1049.2
30°	904.5	927.7	967.8	1014.6	1035.7
32.5°	881.0	905.1	947.9	998.4	1017.6
35°	843.5	866.6	918.1	970.3	981.4
37.5°	800.3	826.6	884.2	913.3	914.0
40°	767.7	802.0	857.0	862.3	848.0
42.5°	736.0	780.0	819.0	795.2	731.3
45°	687.4	739.4	755.3	640.1	595.8
47.5°	635.6	687.0	661.7	536.8	506.3
50°	600.4	649.0	585.7	479.8	451.1
52.5°	560.6	603.9	517.8	425.2	381.5
55°	498.6	528.5	439.8	331.5	289.4
57.5°	424.0	445.0	376.1	248.9	201.7
60°	374.2	390.9	329.0	204.1	180.9
62.5°	329.0	343.8	280.2	177.3	169.1
65°	266.8	281.2	214.8	151.5	150.4
67.5°	212.3	228.1	164.8	132.3	130.9
70°	179.8	196.4	136.8	118.7	116.5
72.5°	152.6	168.4	116.0	104.2	102.9
75°	115.3	127.5	89.3	83.7	82.5
77.5°	83.7	91.4	66.5	63.5	62.4
80°	65.6	68.9	52.0	50.9	49.7
82.5°	49.3	48.2	39.3	38.2	36.2
85°	26.0	23.7	21.5	16.8	13.6
87.5°	8.1	8.4	4.3	3.6	3.6
90°	0.0	1.1	3.4	4.5	4.5
92.5°	9.0	34.9	102.9	33.4	28.0
95°	29.4	86.8	374.2	133.5	89.3
97.5°	54.0	114.2	653.2	380.9	240.8
100°	71.2	128.7	756.3	649.6	430.8
102.5°	90.2	146.0	750.0	992.7	750.0
105°	119.8	170.7	685.1	1292.6	1208.5
107.5°	150.1	195.5	622.9	1323.0	1386.8
110°	167.3	212.7	591.2	1292.9	1422.1



TEST NUMBER: P854931

CATALOG NUMBER: SQ2-PP3-075U-050D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	185.4	229.9	572.2	1239.4	1404.0
115°	213.7	255.6	551.6	1148.5	1343.1
117.5°	241.7	279.0	544.2	1061.7	1265.8
120°	258.9	295.3	541.5	1007.3	1205.2
122.5°	274.3	309.9	541.5	962.6	1145.5
125°	298.5	331.6	541.5	902.4	1063.8
127.5°	318.4	350.8	540.1	856.9	994.9
130°	330.1	364.4	539.2	830.3	954.1
132.5°	341.0	376.2	538.3	808.4	919.8
135°	357.3	393.7	536.9	774.4	873.9
137.5°	374.9	410.0	535.6	741.6	829.3
140°	386.7	420.9	534.7	719.7	800.4
142.5°	397.5	430.9	535.6	697.8	769.6
145°	414.9	445.8	535.8	666.2	729.2
147.5°	433.7	459.5	536.0	639.4	686.2
150°	445.5	468.7	536.9	623.8	663.6
152.5°	456.2	478.6	537.8	611.0	642.8
155°	473.6	490.2	539.2	595.2	617.2
157.5°	490.6	503.5	540.6	584.0	599.6
160°	499.6	510.7	541.5	575.7	587.8
162.5°	508.7	517.2	541.5	570.2	579.7
165°	520.0	525.5	541.5	563.1	568.6
167.5°	530.4	533.3	542.6	556.7	559.6
170°	535.8	536.9	542.6	554.0	555.0
172.5°	539.4	540.6	543.5	551.2	551.4
175°	543.7	543.7	544.9	548.2	547.1
177.5°	546.0	546.0	545.1	546.9	545.1
180°	546.0	546.0	546.0	546.0	546.0



TEST NUMBER: P854931

CATALOG NUMBER: SQ2-PP3-075U-050D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.89	17.68	17.90	18.69	20.04	13.29	14.07	14.30	15.09	16.44
	3H	17.98	18.68	19.00	19.71	21.08	14.38	15.09	15.41	16.11	17.48
	4H	18.32	18.98	19.35	20.01	21.39	14.84	15.51	15.88	16.54	17.92
	6H	18.53	19.14	19.57	20.17	21.56	15.19	15.80	16.23	16.83	18.22
	8H	18.58	19.16	19.63	20.20	21.59	15.27	15.85	16.32	16.90	18.29
	12H	18.59	19.14	19.64	20.18	21.59	15.28	15.83	16.33	16.87	18.29
4H	2H	16.99	17.65	18.03	18.68	20.06	13.99	14.65	15.03	15.68	17.06
	3H	18.29	18.84	19.34	19.90	21.29	15.23	15.78	16.28	16.84	18.23
	4H	18.76	19.26	19.82	20.31	21.73	15.79	16.29	16.84	17.34	18.75
	6H	19.10	19.53	20.16	20.60	22.01	16.22	16.65	17.29	17.72	19.14
	8H	19.19	19.59	20.25	20.65	22.08	16.34	16.74	17.41	17.81	19.23
	12H	19.22	19.58	20.30	20.66	22.09	16.37	16.73	17.45	17.81	19.24
8H	4H	18.77	19.18	19.84	20.24	21.67	16.05	16.46	17.12	17.52	18.95
	6H	19.20	19.54	20.29	20.64	22.06	16.60	16.93	17.68	18.03	19.46
	8H	19.36	19.65	20.45	20.74	22.18	16.78	17.07	17.88	18.16	19.61
	12H	19.44	19.70	20.54	20.78	22.27	16.85	17.11	17.95	18.19	19.68
12H	4H	18.73	19.09	19.81	20.17	21.60	16.06	16.42	17.14	17.50	18.93
	6H	19.19	19.48	20.29	20.57	22.02	16.65	16.94	17.74	18.03	19.47
	8H	19.36	19.62	20.46	20.70	22.18	16.85	17.11	17.95	18.19	19.68