

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855010

Luminaire Tested: SQ2-FB-125U-075D-830-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855010
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FB-125U-075D-830-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8998.3 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 70.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855010
CATALOG NUMBER: SQ2-FB-125U-075D-830-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855010

CATALOG NUMBER: SQ2-FB-125U-075D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37
1	95	91	87	83	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	86	79	73	67	78	71	66	62	58	54	51	46	43	41	34	32	31	26
3	78	69	61	56	71	63	56	51	51	46	42	40	37	34	30	28	26	21
4	71	61	53	47	64	55	48	43	45	40	36	35	32	29	26	24	22	18
5	65	54	45	39	59	49	42	36	40	34	30	31	28	25	23	21	19	15
6	60	48	40	34	54	44	36	31	36	30	26	28	24	21	21	18	16	13
7	55	43	35	29	50	39	32	27	32	27	23	25	21	18	19	16	14	11
8	51	39	31	26	46	35	28	24	29	24	20	23	19	16	17	15	13	10
9	47	35	28	23	43	32	25	21	26	21	18	21	17	14	16	13	11	9
10	44	32	25	20	40	29	23	19	24	19	16	19	15	13	15	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5478	5478	5478
5°	5340	7402	9702
10°	5000	14332	18880
15°	4527	18648	21728
20°	4009	20515	22756
25°	3545	21937	23129
30°	3132	22592	23415
35°	2797	22984	25172
40°	2546	23204	26744
45°	2347	23315	28005
50°	2213	23762	28514
55°	2159	24380	28743
60°	2212	24703	28598
65°	2308	24363	27794
70°	2384	23561	21017
75°	2645	21166	11603
80°	2734	10925	10767
85°	2723	7558	4520

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 29000 cd/sqm



TEST NUMBER: P855010

CATALOG NUMBER: SQ2-FB-125U-075D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	0.6
10°-20°	259.5	2.9
20°-30°	456.5	5.1
30°-40°	590.9	6.6
40°-50°	651.7	7.2
50°-60°	608.5	6.8
60°-70°	470.3	5.2
70°-80°	216.9	2.4
80°-90°	42.4	0.5
90°-100°	350.0	3.9
100°-110°	1139.4	12.7
110°-120°	1127.1	12.5
120°-130°	921.1	10.2
130°-140°	752.8	8.4
140°-150°	586.4	6.5
150°-160°	422.6	4.7
160°-170°	258.3	2.9
170°-180°	87.2	1.0
0°-30°	772.8	8.6
0°-40°	1363.6	15.2
0°-60°	2623.8	29.2
0°-90°	3353.4	37.3
90°-120°	2616.5	29.1
90°-150°	4876.7	54.2
90°-180°	5645.0	62.7
0°-180°	8998.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	339	339	339	339	339	
5°	330	377	457	557	599	31
15°	271	534	1116	1249	1300	75
25°	199	717	1231	1286	1298	91
35°	142	692	1166	1207	1277	89
45°	103	530	1021	1172	1226	80
55°	77	316	866	996	1021	69
65°	60	178	638	715	728	59
75°	42	109	339	183	186	44
85°	15	32	41	28	24	15
90°	0	3	8	7	7	3
95°	47	144	641	229	141	55
105°	194	279	1129	2156	2041	206
115°	358	427	919	1895	2229	354
125°	497	555	907	1496	1764	443
135°	601	664	903	1291	1456	464
145°	702	754	900	1112	1218	440
155°	801	828	906	996	1033	369
165°	874	882	908	942	953	246
175°	912	912	912	918	916	86
180°	915	915	915	915	915	



TEST NUMBER: P855010

CATALOG NUMBER: SQ2-FB-125U-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	339.3	339.3	339.3	339.3	339.3
2.5°	336.6	350.7	366.7	385.1	392.8
5°	329.5	377.3	456.7	557.2	598.6
7.5°	316.7	414.0	664.1	932.9	1015.8
10°	305.0	440.6	874.2	1106.9	1151.6
12.5°	291.9	476.0	1006.0	1169.5	1215.4
15°	270.8	533.9	1115.6	1248.9	1299.9
17.5°	248.9	599.1	1166.5	1298.0	1325.7
20°	233.3	644.7	1194.0	1306.9	1324.4
22.5°	218.9	678.8	1213.5	1299.1	1317.9
25°	199.0	717.3	1231.4	1285.5	1298.3
27.5°	179.8	727.3	1223.6	1259.1	1271.5
30°	168.0	724.6	1211.8	1238.4	1255.9
32.5°	157.6	716.7	1194.9	1220.5	1258.5
35°	141.9	692.1	1166.1	1207.0	1277.1
37.5°	128.6	652.6	1128.4	1211.8	1279.4
40°	120.8	623.1	1100.9	1211.5	1268.9
42.5°	112.8	588.4	1069.6	1198.5	1255.9
45°	102.8	530.2	1021.1	1172.4	1226.5
47.5°	93.3	464.6	976.0	1136.1	1175.6
50°	88.1	419.8	946.0	1103.3	1135.2
52.5°	82.9	376.3	916.0	1064.2	1093.4
55°	76.7	315.9	866.1	995.5	1021.1
57.5°	71.1	264.1	809.3	919.8	940.5
60°	68.5	236.0	765.0	864.9	885.6
62.5°	64.6	210.3	715.4	807.5	827.0
65°	60.4	178.4	637.7	714.7	727.5
67.5°	54.5	154.7	555.3	602.3	578.3
70°	50.5	143.0	499.1	513.9	445.2
72.5°	47.9	130.3	437.8	398.9	269.1
75°	42.4	109.3	339.3	182.7	186.0
77.5°	34.6	84.7	223.1	140.3	143.3
80°	29.4	69.2	117.5	114.2	115.8
82.5°	24.2	53.8	81.0	84.1	81.9
85°	14.7	32.2	40.8	27.7	24.4
87.5°	5.2	12.2	8.1	7.9	7.9
90°	0.0	3.3	7.9	6.8	6.8
92.5°	16.2	58.2	186.1	61.4	47.3
95°	47.3	144.0	641.4	228.7	140.7
97.5°	88.9	187.5	1088.7	663.0	404.7
100°	115.9	212.8	1257.0	1120.9	727.0
102.5°	146.5	239.8	1236.4	1658.3	1260.9
105°	193.6	279.4	1128.7	2155.8	2041.4
107.5°	244.4	325.2	1026.5	2199.0	2320.3
110°	281.3	355.0	977.9	2145.4	2364.4



TEST NUMBER: P855010

CATALOG NUMBER: SQ2-FB-125U-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	311.9	384.8	947.4	2048.7	2331.0
115°	357.8	427.2	919.4	1894.8	2229.3
117.5°	405.1	467.6	908.6	1753.9	2086.8
120°	432.1	493.8	905.9	1667.2	1989.6
122.5°	458.2	519.0	906.8	1592.1	1892.4
125°	497.4	554.6	907.0	1496.1	1763.5
127.5°	530.9	589.5	906.8	1424.2	1647.1
130°	552.5	612.0	905.9	1383.1	1582.2
132.5°	571.4	633.5	905.0	1345.0	1531.8
135°	600.9	663.7	902.6	1291.2	1456.3
137.5°	629.8	692.9	900.1	1236.5	1383.1
140°	650.5	710.9	899.2	1199.4	1338.0
142.5°	670.2	728.1	899.2	1164.0	1287.7
145°	702.2	753.9	900.3	1112.0	1217.6
147.5°	733.3	778.2	901.9	1067.8	1149.4
150°	754.0	793.6	903.6	1041.4	1110.7
152.5°	774.7	807.3	904.5	1021.3	1076.5
155°	801.3	827.6	905.9	995.6	1033.1
157.5°	826.5	845.4	907.2	976.8	1002.9
160°	841.8	857.1	908.1	964.9	985.8
162.5°	855.2	867.2	908.1	954.9	970.5
165°	874.4	882.1	908.1	942.2	953.1
167.5°	887.9	892.8	908.4	932.6	938.3
170°	896.9	899.1	909.3	926.2	928.4
172.5°	903.3	904.5	911.1	922.6	922.2
175°	911.5	911.5	911.5	918.2	916.0
177.5°	914.9	914.0	913.1	917.5	914.0
180°	914.9	914.9	914.9	914.9	914.9



TEST NUMBER: P855010

CATALOG NUMBER: SQ2-FB-125U-075D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.68	12.45	12.73	13.51	14.95	20.41	21.19	21.47	22.25	23.69
	3H	12.40	13.10	13.46	14.17	15.62	22.03	22.72	23.09	23.79	25.25
	4H	12.70	13.36	13.77	14.43	15.89	22.21	22.86	23.28	23.94	25.40
	6H	12.91	13.51	13.99	14.59	16.07	22.29	22.89	23.37	23.97	25.45
	8H	12.96	13.54	14.05	14.63	16.11	22.29	22.87	23.38	23.96	25.43
	12H	12.99	13.54	14.08	14.62	16.12	22.26	22.80	23.35	23.89	25.39
4H	2H	16.06	16.72	17.15	17.80	19.26	20.85	21.50	21.93	22.58	24.04
	3H	16.99	17.54	18.08	18.64	20.12	22.66	23.21	23.75	24.31	25.79
	4H	17.27	17.77	18.36	18.86	20.36	22.90	23.40	23.99	24.49	25.99
	6H	17.39	17.83	18.50	18.94	20.43	23.04	23.47	24.14	24.58	26.07
	8H	17.41	17.82	18.52	18.92	20.43	23.06	23.46	24.16	24.57	26.08
	12H	17.40	17.77	18.52	18.88	20.40	23.03	23.39	24.15	24.51	26.03
8H	4H	18.44	18.84	19.54	19.94	21.45	23.01	23.41	24.11	24.51	26.02
	6H	18.67	19.00	19.80	20.15	21.65	23.21	23.54	24.34	24.69	26.19
	8H	18.74	19.03	19.87	20.16	21.68	23.27	23.56	24.40	24.69	26.21
	12H	18.76	19.02	19.90	20.14	21.70	23.26	23.51	24.39	24.64	26.20
12H	4H	18.45	18.81	19.57	19.93	21.45	22.95	23.32	24.08	24.44	25.95
	6H	18.76	19.05	19.89	20.18	21.71	23.19	23.48	24.32	24.61	26.13
	8H	18.86	19.12	20.00	20.24	21.80	23.25	23.51	24.39	24.63	26.20