

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854946

Luminaire Tested: SQ2-PH1-125U-075D-830-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854946
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PH1-125U-075D-830-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9437.6 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 70.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854946

CATALOG NUMBER: SQ2-PH1-125U-075D-830-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854946

CATALOG NUMBER: SQ2-PH1-125U-075D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	84	87	84	80	77	68	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	64	60	57	53	48	46	43	37	35	34	29
3	80	70	63	58	72	64	58	53	53	49	45	43	39	37	33	31	29	25
4	73	62	55	49	66	57	50	45	47	42	38	38	34	32	29	27	25	21
5	67	55	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	37	32	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27679	27679	27679
5°	27835	26172	25298
10°	27196	23825	22997
15°	27318	22410	22547
20°	26344	21720	22727
25°	25860	21618	22199
30°	25299	21559	22380
35°	25109	21313	26233
40°	25130	21176	20799
45°	25138	20372	17915
50°	24787	20773	16799
55°	24473	22542	16113
60°	24228	19753	15116
65°	23805	16011	13150
70°	22480	13629	9394
75°	20044	10274	7124
80°	16383	6676	6676
85°	10263	6058	4520

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25138 cd/sqm



TEST NUMBER: P854946

CATALOG NUMBER: SQ2-PH1-125U-075D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.8	1.6
10°-20°	396.8	4.2
20°-30°	581.8	6.2
30°-40°	704.5	7.5
40°-50°	692.8	7.3
50°-60°	603.1	6.4
60°-70°	419.3	4.4
70°-80°	198.8	2.1
80°-90°	44.8	0.5
90°-100°	350.0	3.7
100°-110°	1139.4	12.1
110°-120°	1127.1	11.9
120°-130°	921.1	9.8
130°-140°	752.8	8.0
140°-150°	586.4	6.2
150°-160°	422.6	4.5
160°-170°	258.3	2.7
170°-180°	87.2	0.9
0°-30°	1129.3	12.0
0°-40°	1833.9	19.4
0°-60°	3129.8	33.2
0°-90°	3792.7	40.2
90°-120°	2616.5	27.7
90°-150°	4876.7	51.7
90°-180°	5645.0	59.8
0°-180°	9437.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1714	1714	1714	1714	1714	
5°	1717	1716	1615	1564	1561	161
15°	1634	1456	1341	1331	1349	456
25°	1452	1235	1214	1251	1246	668
35°	1274	1030	1081	1175	1331	798
45°	1101	816	892	923	785	846
55°	869	635	801	577	572	777
65°	623	436	419	344	344	612
75°	321	222	165	117	114	340
85°	55	36	33	26	24	74
90°	0	3	8	7	7	4
95°	47	144	641	229	141	55
105°	194	279	1129	2156	2041	206
115°	358	427	919	1895	2229	354
125°	497	555	907	1496	1764	443
135°	601	664	903	1291	1456	464
145°	702	754	900	1112	1218	440
155°	801	828	906	996	1033	369
165°	874	882	908	942	953	246
175°	912	912	912	918	916	86
180°	915	915	915	915	915	



TEST NUMBER: P854946

CATALOG NUMBER: SQ2-PH1-125U-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1714.3	1714.3	1714.3	1714.3	1714.3
2.5°	1710.3	1728.2	1688.2	1672.4	1669.8
5°	1717.4	1715.9	1614.8	1564.1	1560.9
7.5°	1686.1	1636.7	1515.9	1460.0	1457.5
10°	1658.8	1583.8	1453.2	1402.7	1402.7
12.5°	1652.2	1533.9	1402.3	1365.0	1372.7
15°	1634.3	1455.7	1340.7	1331.3	1348.9
17.5°	1575.0	1382.6	1292.8	1314.1	1334.5
20°	1533.2	1343.4	1264.1	1303.6	1322.7
22.5°	1498.0	1305.7	1243.1	1286.4	1296.7
25°	1451.6	1234.8	1213.5	1250.9	1246.1
27.5°	1396.1	1169.8	1183.8	1206.7	1209.6
30°	1357.0	1130.5	1156.4	1179.7	1200.4
32.5°	1319.2	1085.1	1126.3	1181.6	1229.1
35°	1273.9	1029.8	1081.3	1174.6	1330.9
37.5°	1226.2	964.7	1036.0	1114.5	1164.2
40°	1192.3	918.0	1004.7	1101.6	986.8
42.5°	1155.7	881.4	957.8	1082.8	888.9
45°	1100.9	815.5	892.2	923.3	784.6
47.5°	1036.3	764.3	847.9	770.0	715.7
50°	986.8	730.1	827.0	703.8	668.8
52.5°	938.5	694.6	812.6	649.2	625.7
55°	869.4	634.9	800.8	577.3	572.4
57.5°	796.0	574.3	708.2	514.7	522.9
60°	750.3	535.0	611.7	477.7	468.1
62.5°	702.0	496.9	521.6	430.7	421.2
65°	623.1	436.4	419.1	344.2	344.2
67.5°	536.3	373.6	339.5	281.6	243.3
70°	476.2	332.7	288.7	224.5	199.0
72.5°	412.3	289.2	236.5	184.0	154.7
75°	321.3	222.4	164.7	117.4	114.2
77.5°	232.2	160.2	110.9	87.1	87.4
80°	176.2	121.9	71.8	70.2	71.8
82.5°	123.9	83.8	53.5	55.7	56.1
85°	55.4	36.3	32.7	26.0	24.4
87.5°	11.8	11.1	8.1	7.9	7.9
90°	0.0	3.3	7.9	6.8	6.8
92.5°	16.2	58.2	186.1	61.4	47.3
95°	47.3	144.0	641.4	228.7	140.7
97.5°	88.9	187.5	1088.7	663.0	404.7
100°	115.9	212.8	1257.0	1120.9	727.0
102.5°	146.5	239.8	1236.4	1658.3	1260.9
105°	193.6	279.4	1128.7	2155.8	2041.4
107.5°	244.4	325.2	1026.5	2199.0	2320.3
110°	281.3	355.0	977.9	2145.4	2364.4



TEST NUMBER: P854946

CATALOG NUMBER: SQ2-PH1-125U-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	311.9	384.8	947.4	2048.7	2331.0
115°	357.8	427.2	919.4	1894.8	2229.3
117.5°	405.1	467.6	908.6	1753.9	2086.8
120°	432.1	493.8	905.9	1667.2	1989.6
122.5°	458.2	519.0	906.8	1592.1	1892.4
125°	497.4	554.6	907.0	1496.1	1763.5
127.5°	530.9	589.5	906.8	1424.2	1647.1
130°	552.5	612.0	905.9	1383.1	1582.2
132.5°	571.4	633.5	905.0	1345.0	1531.8
135°	600.9	663.7	902.6	1291.2	1456.3
137.5°	629.8	692.9	900.1	1236.5	1383.1
140°	650.5	710.9	899.2	1199.4	1338.0
142.5°	670.2	728.1	899.2	1164.0	1287.7
145°	702.2	753.9	900.3	1112.0	1217.6
147.5°	733.3	778.2	901.9	1067.8	1149.4
150°	754.0	793.6	903.6	1041.4	1110.7
152.5°	774.7	807.3	904.5	1021.3	1076.5
155°	801.3	827.6	905.9	995.6	1033.1
157.5°	826.5	845.4	907.2	976.8	1002.9
160°	841.8	857.1	908.1	964.9	985.8
162.5°	855.2	867.2	908.1	954.9	970.5
165°	874.4	882.1	908.1	942.2	953.1
167.5°	887.9	892.8	908.4	932.6	938.3
170°	896.9	899.1	909.3	926.2	928.4
172.5°	903.3	904.5	911.1	922.6	922.2
175°	911.5	911.5	911.5	918.2	916.0
177.5°	914.9	914.0	913.1	917.5	914.0
180°	914.9	914.9	914.9	914.9	914.9

TEST NUMBER: P854946

CATALOG NUMBER: SQ2-PH1-125U-075D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.88	18.66	18.92	19.70	21.11	16.56	17.33	17.59	18.37	19.78
	3H	19.90	20.59	20.95	21.65	23.07	17.58	18.28	18.63	19.33	20.75
	4H	20.63	21.28	21.69	22.34	23.77	17.79	18.45	18.85	19.50	20.94
	6H	21.11	21.71	22.18	22.77	24.21	17.93	18.54	19.00	19.59	21.04
	8H	21.23	21.80	22.31	22.88	24.32	17.96	18.54	19.04	19.61	21.05
	12H	21.27	21.82	22.35	22.89	24.35	17.96	18.50	19.04	19.57	21.03
4H	2H	18.25	18.90	19.31	19.96	21.39	17.19	17.84	18.25	18.90	20.33
	3H	20.34	20.89	21.42	21.97	23.42	18.36	18.90	19.43	19.99	21.43
	4H	21.16	21.66	22.24	22.73	24.20	18.63	19.13	19.71	20.20	21.67
	6H	21.74	22.17	22.83	23.26	24.72	18.83	19.26	19.92	20.36	21.82
	8H	21.90	22.30	22.99	23.39	24.87	18.89	19.29	19.98	20.38	21.85
	12H	21.97	22.33	23.07	23.43	24.91	18.89	19.25	20.00	20.35	21.84
8H	4H	21.17	21.57	22.26	22.66	24.13	18.84	19.24	19.93	20.33	21.80
	6H	21.81	22.14	22.93	23.28	24.75	19.11	19.44	20.22	20.57	22.04
	8H	22.04	22.33	23.16	23.44	24.93	19.21	19.50	20.33	20.61	22.10
	12H	22.15	22.40	23.27	23.51	25.04	19.25	19.50	20.37	20.61	22.14
12H	4H	21.11	21.48	22.22	22.58	24.06	18.83	19.19	19.94	20.29	21.78
	6H	21.79	22.08	22.91	23.19	24.68	19.14	19.43	20.26	20.54	22.03
	8H	22.02	22.27	23.14	23.38	24.91	19.25	19.50	20.37	20.61	22.14