

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854943

Luminaire Tested: SQ2-PH1-150U-050D-830-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P854943  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-14, G2-2308-131-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PH1-150U-050D-830-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9419.2 lumens  
Efficiency: N/A  
Efficacy: 126.6 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 74.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P854943

CATALOG NUMBER: SQ2-PH1-150U-050D-830-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P854943

CATALOG NUMBER: SQ2-PH1-150U-050D-830-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28				
1	93	89	85	82	83	80	77	74	62	60	58	46	45	44	32	31	30	24				
2	85	78	72	67	76	70	65	61	55	51	48	41	39	37	28	27	26	20				
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17				
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15				
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13				
6	59	48	40	35	53	43	36	32	34	29	26	26	23	20	18	16	14	11				
7	55	43	35	30	49	39	32	28	31	26	23	24	20	18	17	14	13	10				
8	51	39	32	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9				
9	47	35	28	23	42	32	26	22	26	21	18	20	16	14	14	12	10	8				
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19186	19186	19186
5°	19297	18141	17537
10°	18853	16516	15942
15°	18937	15535	15629
20°	18261	15055	15756
25°	17927	14986	15389
30°	17538	14945	15515
35°	17404	14775	18185
40°	17420	14680	14417
45°	17427	14123	12417
50°	17181	14398	11645
55°	16963	15626	11173
60°	16795	13692	10479
65°	16500	11102	9116
70°	15583	9446	6510
75°	13893	7124	4934
80°	11353	4621	4621
85°	7114	4187	3149

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17427 cd/sqm



TEST NUMBER: P854943

CATALOG NUMBER: SQ2-PH1-150U-050D-830-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.6	1.1
10°-20°	275.0	2.9
20°-30°	403.3	4.3
30°-40°	488.4	5.2
40°-50°	480.3	5.1
50°-60°	418.1	4.4
60°-70°	290.7	3.1
70°-80°	137.8	1.5
80°-90°	31.6	0.3
90°-100°	419.2	4.4
100°-110°	1372.5	14.6
110°-120°	1356.9	14.4
120°-130°	1109.2	11.8
130°-140°	905.1	9.6
140°-150°	704.4	7.5
150°-160°	507.2	5.4
160°-170°	310.3	3.3
170°-180°	104.8	1.1
0°-30°	782.9	8.3
0°-40°	1271.3	13.5
0°-60°	2169.6	23.0
0°-90°	2629.7	27.9
90°-120°	3148.5	33.4
90°-150°	5867.2	62.3
90°-180°	6790.0	72.1
0°-180°	9419.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1188	1188	1188	1188	1188	
5°	1191	1189	1119	1084	1082	112
15°	1133	1009	929	923	935	316
25°	1006	856	841	867	864	463
35°	883	714	750	814	923	553
45°	763	565	618	640	544	587
55°	603	440	555	400	397	538
65°	432	303	291	239	239	424
75°	223	154	114	81	79	236
85°	38	25	23	18	17	52
90°	1	3	9	8	9	4
95°	59	170	762	272	176	67
105°	239	340	1362	2588	2459	251
115°	430	514	1107	2287	2685	424
125°	598	667	1091	1804	2119	532
135°	720	796	1082	1556	1754	557
145°	842	904	1080	1338	1466	528
155°	960	992	1086	1197	1244	442
165°	1048	1058	1091	1133	1145	295
175°	1096	1096	1097	1104	1102	104
180°	1100	1100	1100	1100	1100	



TEST NUMBER: P854943

CATALOG NUMBER: SQ2-PH1-150U-050D-830-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1188.3	1188.3	1188.3	1188.3	1188.3
2.5°	1185.6	1198.0	1170.2	1159.4	1157.6
5°	1190.6	1189.4	1119.3	1084.3	1082.0
7.5°	1168.9	1134.6	1050.8	1012.2	1010.3
10°	1149.9	1098.0	1007.4	972.4	972.4
12.5°	1145.3	1063.4	972.1	946.2	951.5
15°	1132.9	1009.1	929.4	922.9	935.0
17.5°	1091.7	958.4	896.1	911.0	925.1
20°	1062.8	931.3	876.2	903.7	917.0
22.5°	1038.4	905.1	861.8	891.7	898.9
25°	1006.3	855.9	841.2	867.1	863.8
27.5°	967.8	810.9	820.6	836.4	838.5
30°	940.7	783.8	801.6	817.8	832.2
32.5°	914.5	752.2	780.8	819.2	852.1
35°	883.0	713.9	749.6	814.3	922.6
37.5°	850.0	668.7	718.2	772.6	807.1
40°	826.5	636.3	696.5	763.6	684.0
42.5°	801.2	611.0	663.9	750.6	616.2
45°	763.2	565.3	618.5	640.1	543.8
47.5°	718.4	529.8	587.7	533.7	496.1
50°	684.0	506.1	573.2	487.9	463.6
52.5°	650.6	481.4	563.3	450.1	433.7
55°	602.6	440.2	555.1	400.1	396.9
57.5°	551.8	398.1	490.9	356.7	362.5
60°	520.1	370.9	424.0	331.2	324.5
62.5°	486.6	344.5	361.6	298.6	291.9
65°	431.9	302.6	290.6	238.6	238.6
67.5°	371.8	259.0	235.4	195.3	168.7
70°	330.1	230.7	200.1	155.6	137.9
72.5°	285.8	200.5	163.9	127.5	107.2
75°	222.7	154.2	114.2	81.4	79.1
77.5°	161.0	111.0	76.9	60.4	60.6
80°	122.1	84.6	49.7	48.6	49.7
82.5°	85.9	58.1	37.1	38.7	38.9
85°	38.4	25.2	22.6	18.1	17.0
87.5°	8.4	7.9	6.3	6.1	6.3
90°	1.1	3.4	9.0	7.9	9.0
92.5°	19.2	70.1	215.3	70.0	56.1
95°	58.8	170.4	762.1	271.5	176.4
97.5°	106.7	224.8	1307.4	790.9	490.2
100°	140.2	252.9	1512.7	1350.9	895.4
102.5°	178.2	288.3	1490.1	1990.5	1543.0
105°	238.6	340.2	1362.3	2588.3	2458.9
107.5°	298.0	391.3	1237.7	2644.2	2786.4
110°	336.9	427.6	1178.0	2579.1	2843.3



TEST NUMBER: P854943

CATALOG NUMBER: SQ2-PH1-150U-050D-830-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	374.0	462.0	1141.8	2465.9	2804.4
115°	429.6	513.7	1106.8	2287.2	2685.1
117.5°	483.7	562.2	1093.4	2111.4	2515.5
120°	519.0	593.0	1089.8	2008.9	2402.4
122.5°	550.6	622.9	1089.8	1920.5	2285.8
125°	598.1	666.6	1091.0	1803.6	2118.7
127.5°	638.4	708.1	1089.6	1717.4	1991.6
130°	663.7	734.4	1088.7	1665.3	1912.9
132.5°	686.3	758.8	1086.0	1620.4	1845.1
135°	720.2	796.4	1081.9	1555.7	1753.5
137.5°	755.9	831.5	1079.4	1488.0	1666.9
140°	781.2	854.2	1078.5	1445.3	1614.4
142.5°	806.5	875.1	1078.5	1399.7	1552.9
145°	842.2	904.2	1079.7	1338.1	1466.3
147.5°	879.8	931.3	1081.2	1284.5	1381.3
150°	903.3	948.6	1083.0	1253.4	1335.2
152.5°	926.8	966.8	1083.9	1227.8	1295.4
155°	959.8	991.9	1086.4	1197.2	1243.6
157.5°	989.4	1012.7	1088.9	1173.2	1206.7
160°	1008.4	1027.3	1089.8	1159.5	1185.9
162.5°	1024.7	1040.0	1089.8	1148.4	1167.8
165°	1048.0	1057.9	1091.0	1133.1	1145.2
167.5°	1067.7	1072.5	1092.3	1121.3	1127.8
170°	1078.5	1080.8	1093.2	1114.8	1117.0
172.5°	1086.7	1088.0	1095.9	1110.2	1110.6
175°	1095.5	1095.5	1096.6	1104.5	1102.3
177.5°	1100.0	1099.1	1098.2	1103.6	1100.0
180°	1100.0	1100.0	1100.0	1100.0	1100.0



TEST NUMBER: P854943

CATALOG NUMBER: SQ2-PH1-150U-050D-830-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.08	15.77	16.21	16.89	18.45	13.76	14.45	14.88	15.56	17.12
	3H	17.10	17.71	18.23	18.84	20.41	14.78	15.39	15.91	16.52	18.09
	4H	17.82	18.40	18.96	19.53	21.11	14.98	15.57	16.13	16.69	18.27
	6H	18.29	18.83	19.45	19.96	21.55	15.12	15.65	16.27	16.78	18.37
	8H	18.41	18.92	19.57	20.07	21.65	15.14	15.66	16.30	16.80	18.38
	12H	18.45	18.94	19.61	20.08	21.68	15.14	15.62	16.30	16.76	18.36
4H	2H	15.44	16.02	16.59	17.15	18.73	14.38	14.96	15.53	16.09	17.67
	3H	17.53	18.01	18.68	19.17	20.76	15.54	16.03	16.70	17.18	18.77
	4H	18.33	18.78	19.49	19.92	21.53	15.81	16.25	16.97	17.40	19.01
	6H	18.91	19.29	20.08	20.46	22.06	16.00	16.39	17.17	17.55	19.15
	8H	19.07	19.43	20.24	20.59	22.20	16.06	16.41	17.22	17.57	19.19
	12H	19.13	19.46	20.32	20.63	22.25	16.06	16.38	17.24	17.55	19.17
8H	4H	18.34	18.70	19.50	19.85	21.47	16.01	16.37	17.17	17.52	19.14
	6H	18.98	19.28	20.17	20.48	22.09	16.27	16.57	17.46	17.77	19.38
	8H	19.21	19.46	20.40	20.64	22.27	16.37	16.63	17.56	17.81	19.44
	12H	19.31	19.54	20.51	20.71	22.38	16.41	16.64	17.60	17.81	19.48
12H	4H	18.28	18.61	19.46	19.77	21.39	16.00	16.32	17.18	17.49	19.11
	6H	18.95	19.21	20.15	20.39	22.02	16.30	16.56	17.49	17.74	19.37
	8H	19.18	19.40	20.37	20.58	22.24	16.41	16.63	17.60	17.81	19.47