

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854863

Luminaire Tested: SQ2-PW1-125U-050D-830-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854863
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PW1-125U-050D-830-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8305.9 lumens
Efficiency: N/A
Efficacy: 134.6 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.22
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 61.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854863

CATALOG NUMBER: SQ2-PW1-125U-050D-830-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854863

CATALOG NUMBER: SQ2-PW1-125U-050D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34	27
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29	24
3	79	70	63	57	70	63	57	52	51	46	43	39	36	34	28	27	25	20
4	72	62	54	49	65	56	50	45	45	40	37	35	32	29	25	24	22	18
5	66	55	47	42	59	50	43	38	40	36	32	31	28	26	23	21	19	16
6	61	49	42	36	55	45	38	33	36	32	28	28	25	22	21	19	17	14
7	56	45	37	32	51	41	34	29	33	28	25	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11
9	49	37	30	25	44	34	27	23	28	23	20	22	18	16	16	14	12	10
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19168	19168	19168
5°	19039	19186	19370
10°	19074	19297	19538
15°	19069	19428	19656
20°	19077	19407	19271
25°	18975	18994	17906
30°	18845	17896	16188
35°	18697	16468	14619
40°	18326	15013	12916
45°	17607	13502	11282
50°	16387	12069	9656
55°	14990	10663	7828
60°	13437	9274	6755
65°	11748	7992	6006
70°	9607	7100	5443
75°	7473	6138	5009
80°	5570	5253	4417
85°	3779	3983	2519

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17607 cd/sqm

TEST NUMBER: P854863

CATALOG NUMBER: SQ2-PW1-125U-050D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.0	1.4
10°-20°	327.5	3.9
20°-30°	482.0	5.8
30°-40°	527.0	6.3
40°-50°	472.8	5.7
50°-60°	352.7	4.2
60°-70°	222.9	2.7
70°-80°	110.4	1.3
80°-90°	26.9	0.3
90°-100°	351.6	4.2
100°-110°	1144.6	13.8
110°-120°	1132.3	13.6
120°-130°	925.3	11.1
130°-140°	756.2	9.1
140°-150°	589.0	7.1
150°-160°	424.6	5.1
160°-170°	259.5	3.1
170°-180°	87.6	1.1
0°-30°	922.6	11.1
0°-40°	1449.6	17.5
0°-60°	2275.0	27.4
0°-90°	2635.2	31.7
90°-120°	2628.5	31.6
90°-150°	4899.1	59.0
90°-180°	5671.0	68.3
0°-180°	8305.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1187	1187	1187	1187	1187	
5°	1175	1194	1184	1185	1195	112
15°	1141	1163	1162	1170	1176	322
25°	1065	1088	1066	1022	1005	490
35°	949	939	836	763	742	592
45°	771	709	591	517	494	591
55°	532	482	379	297	278	476
65°	308	282	209	168	157	305
75°	120	129	98	82	80	132
85°	20	26	22	15	14	26
90°	0	3	8	7	7	3
95°	48	145	644	230	141	55
105°	194	281	1134	2166	2051	207
115°	360	429	924	1904	2240	356
125°	500	557	911	1503	1772	445
135°	604	667	907	1297	1463	466
145°	705	757	904	1117	1223	442
155°	805	832	910	1000	1038	371
165°	878	886	912	946	958	247
175°	916	916	916	922	920	87
180°	919	919	919	919	919	

TEST NUMBER: P854863

CATALOG NUMBER: SQ2-PW1-125U-050D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1187.2	1187.2	1187.2	1187.2	1187.2
2.5°	1179.0	1194.1	1184.5	1185.5	1188.1
5°	1174.7	1193.5	1183.8	1185.1	1195.1
7.5°	1168.9	1187.9	1180.6	1184.7	1194.4
10°	1163.4	1183.3	1177.0	1182.9	1191.7
12.5°	1156.2	1177.0	1172.5	1179.3	1188.1
15°	1140.8	1163.0	1162.3	1170.3	1175.9
17.5°	1123.0	1145.1	1144.0	1146.1	1148.7
20°	1110.3	1132.5	1129.5	1121.6	1121.6
22.5°	1092.2	1116.1	1108.7	1087.1	1080.0
25°	1065.1	1088.2	1066.2	1021.8	1005.1
27.5°	1033.4	1052.2	1007.9	944.7	921.7
30°	1010.8	1025.2	959.9	890.5	868.3
32.5°	987.3	992.8	911.1	838.8	815.0
35°	948.6	938.7	835.5	762.7	741.7
37.5°	902.9	873.3	763.0	686.6	663.5
40°	869.5	827.5	712.3	636.0	612.8
42.5°	832.4	779.8	664.4	588.0	564.0
45°	771.1	709.3	591.3	517.3	494.1
47.5°	702.1	640.6	523.0	451.4	431.5
50°	652.4	592.7	480.5	408.7	384.4
52.5°	601.7	548.2	438.9	365.1	332.0
55°	532.5	481.7	378.8	296.9	278.1
57.5°	461.3	417.3	324.3	250.0	234.5
60°	416.1	377.4	287.2	224.7	209.2
62.5°	372.7	338.4	251.0	201.1	188.4
65°	307.5	282.1	209.2	168.2	157.2
67.5°	244.2	230.1	173.9	138.1	130.7
70°	203.5	199.1	150.4	120.9	115.3
72.5°	168.2	170.0	127.8	104.6	100.9
75°	119.8	128.7	98.4	82.5	80.3
77.5°	81.6	94.9	72.8	61.1	59.2
80°	59.9	73.2	56.5	47.5	47.5
82.5°	41.8	52.5	40.3	35.7	35.7
85°	20.4	25.9	21.5	14.7	13.6
87.5°	5.4	8.7	5.2	4.1	4.1
90°	0.0	3.3	7.9	6.8	6.8
92.5°	16.3	58.5	187.0	61.6	47.5
95°	47.5	144.7	644.4	229.7	141.3
97.5°	89.3	188.4	1093.7	666.1	406.6
100°	116.5	213.7	1262.8	1126.0	730.3
102.5°	147.2	240.9	1242.0	1665.9	1266.7
105°	194.5	280.6	1133.9	2165.7	2050.8
107.5°	245.6	326.6	1031.3	2209.1	2330.9
110°	282.7	356.7	982.4	2155.2	2375.3



TEST NUMBER: P854863

CATALOG NUMBER: SQ2-PW1-125U-050D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	313.4	386.6	951.7	2058.1	2341.8
115°	359.5	429.2	923.6	1903.6	2239.6
117.5°	407.0	469.8	912.8	1761.9	2096.4
120°	434.2	496.0	910.1	1674.8	1998.8
122.5°	460.4	521.3	911.0	1599.3	1901.1
125°	499.6	557.2	911.2	1502.9	1771.5
127.5°	533.3	592.2	911.0	1430.7	1654.6
130°	555.0	614.7	910.1	1389.4	1589.5
132.5°	574.0	636.4	909.2	1351.1	1538.8
135°	603.7	666.7	906.7	1297.1	1462.9
137.5°	632.6	696.1	904.2	1242.1	1389.4
140°	653.4	714.2	903.3	1204.9	1344.2
142.5°	673.3	731.5	903.3	1169.3	1293.6
145°	705.4	757.4	904.4	1117.1	1223.2
147.5°	736.6	781.7	906.0	1072.6	1154.7
150°	757.4	797.2	907.8	1046.2	1115.8
152.5°	778.2	811.0	908.7	1025.9	1081.5
155°	804.9	831.5	910.1	1000.3	1037.8
157.5°	830.2	849.2	911.4	981.2	1007.5
160°	845.6	861.1	912.3	969.3	990.3
162.5°	859.2	871.2	912.3	959.2	975.0
165°	878.4	886.2	912.3	946.5	957.5
167.5°	892.0	896.8	912.5	936.9	942.6
170°	901.0	903.3	913.4	930.5	932.7
172.5°	907.3	908.7	915.3	926.8	926.3
175°	915.7	915.7	915.7	922.5	920.2
177.5°	919.1	918.2	917.3	921.7	918.2
180°	919.1	919.1	919.1	919.1	919.1



TEST NUMBER: P854863

CATALOG NUMBER: SQ2-PW1-125U-050D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.31	16.01	16.42	17.11	18.62	11.80	12.50	12.91	13.59	15.11
	3H	16.62	17.24	17.74	18.35	19.88	12.99	13.61	14.11	14.72	16.25
	4H	16.99	17.58	18.11	18.69	20.22	13.43	14.02	14.56	15.13	16.66
	6H	17.18	17.73	18.32	18.84	20.38	13.74	14.28	14.87	15.39	16.94
	8H	17.21	17.73	18.35	18.85	20.39	13.81	14.33	14.95	15.45	16.99
	12H	17.20	17.69	18.34	18.81	20.37	13.82	14.31	14.96	15.43	16.99
4H	2H	15.40	15.99	16.53	17.09	18.63	12.46	13.05	13.59	14.16	15.70
	3H	16.93	17.42	18.06	18.55	20.10	13.84	14.33	14.97	15.46	17.01
	4H	17.43	17.88	18.57	19.00	20.57	14.38	14.83	15.52	15.95	17.52
	6H	17.75	18.14	18.90	19.28	20.84	14.77	15.16	15.92	16.30	17.86
	8H	17.83	18.19	18.97	19.32	20.90	14.87	15.23	16.02	16.37	17.94
	12H	17.83	18.16	19.00	19.31	20.89	14.89	15.21	16.05	16.36	17.94
8H	4H	17.46	17.81	18.60	18.95	20.53	14.69	15.05	15.84	16.19	17.76
	6H	17.89	18.18	19.05	19.36	20.93	15.19	15.49	16.36	16.67	18.24
	8H	18.03	18.29	19.20	19.45	21.04	15.35	15.61	16.52	16.77	18.36
	12H	18.09	18.32	19.26	19.47	21.10	15.41	15.63	16.58	16.79	18.42
12H	4H	17.41	17.73	18.57	18.88	20.46	14.70	15.02	15.86	16.17	17.75
	6H	17.88	18.13	19.05	19.29	20.89	15.26	15.51	16.43	16.67	18.26
	8H	18.03	18.26	19.21	19.41	21.04	15.43	15.66	16.61	16.82	18.44