

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854896

Luminaire Tested: SQ2-PR1-0U-125D-830-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P854896  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PR1-0U-125D-830-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1250 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6443.9 lumens  
Efficiency: N/A  
Efficacy: 131.0 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 49.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P854896

CATALOG NUMBER: SQ2-PR1-0U-125D-830-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P854896

CATALOG NUMBER: SQ2-PR1-OU-125D-830-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	101	97	100	97	94	96	94	92	92	90	89	87				87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	80	77	75				75
3	93	84	77	71	91	82	76	70	80	74	69	77	72	68	74	70	67	65				65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56				56
5	80	68	60	53	78	67	59	53	65	58	53	63	57	52	61	56	52	50				50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44				44
7	69	56	48	42	67	55	47	42	54	47	42	52	46	41	51	45	41	39				39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35				35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32				32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29				29

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	43250	43250	43250
5°	43193	43459	43990
10°	43648	44768	45439
15°	43634	43863	44227
20°	42929	43586	45041
25°	42806	44023	46893
30°	42761	45002	47344
35°	42356	45965	44078
40°	41378	44257	38788
45°	39155	38845	30675
50°	35595	31757	23800
55°	31282	26134	18522
60°	27070	20899	15255
65°	23370	17318	13352
70°	21012	15338	11858
75°	19251	13288	10905
80°	16755	10656	10656
85°	12153	9615	5076

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 42324 cd/sqm

TEST NUMBER: P854896

CATALOG NUMBER: SQ2-PR1-0U-125D-830-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	258.7	4.0
10°-20°	748.8	11.6
20°-30°	1157.5	18.0
30°-40°	1392.3	21.6
40°-50°	1250.1	19.4
50°-60°	837.5	13.0
60°-70°	487.1	7.6
70°-80°	250.2	3.9
80°-90°	61.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2165.0	33.6
0°-40°	3557.3	55.2
0°-60°	5644.9	87.6
0°-90°	6443.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6443.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2679	2679	2679	2679	2679	
5°	2665	2710	2681	2688	2714	254
15°	2610	2717	2624	2633	2646	733
25°	2403	2499	2471	2563	2632	1108
35°	2149	2168	2332	2287	2236	1340
45°	1715	1854	1701	1434	1343	1312
55°	1111	1154	928	717	658	999
65°	612	625	453	368	350	619
75°	309	300	213	180	175	327
85°	66	52	52	35	27	84
90°	0	0	0	0	0	



TEST NUMBER: P854896

CATALOG NUMBER: SQ2-PR1-0U-125D-830-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2678.7	2678.7	2678.7	2678.7	2678.7
2.5°	2667.8	2699.7	2669.9	2672.3	2678.7
5°	2665.0	2710.4	2681.4	2687.5	2714.2
7.5°	2664.5	2729.1	2715.2	2731.9	2767.1
10°	2662.3	2739.8	2730.6	2734.1	2771.5
12.5°	2649.2	2739.4	2697.8	2694.4	2714.7
15°	2610.4	2717.2	2624.1	2632.6	2645.9
17.5°	2542.1	2653.7	2565.1	2595.2	2621.4
20°	2498.5	2607.9	2536.7	2575.9	2621.4
22.5°	2459.1	2568.6	2510.5	2565.4	2628.0
25°	2402.8	2499.1	2471.1	2562.8	2632.2
27.5°	2343.9	2400.5	2433.5	2556.4	2605.0
30°	2293.6	2331.0	2413.8	2520.8	2539.4
32.5°	2239.0	2261.5	2387.6	2443.3	2419.2
35°	2148.9	2167.7	2332.0	2287.1	2236.3
37.5°	2041.9	2080.4	2206.8	2077.8	2019.6
40°	1963.2	2027.4	2099.8	1907.2	1840.3
42.5°	1867.1	1969.7	1957.8	1712.4	1630.7
45°	1714.8	1853.6	1701.2	1434.2	1343.4
47.5°	1535.1	1677.6	1428.1	1189.7	1104.8
50°	1417.1	1532.0	1264.3	1041.0	947.5
52.5°	1297.1	1379.8	1124.4	901.3	816.4
55°	1111.3	1154.0	928.4	716.8	658.0
57.5°	940.9	968.2	758.5	579.0	535.7
60°	838.3	857.0	647.2	507.1	472.4
62.5°	744.3	758.8	557.6	446.2	419.9
65°	611.7	625.0	453.3	368.3	349.5
67.5°	506.3	513.2	373.0	306.0	288.3
70°	445.1	447.7	324.9	264.6	251.2
72.5°	390.5	386.7	279.0	229.7	220.6
75°	308.6	300.5	213.0	180.1	174.8
77.5°	230.4	221.9	149.6	138.7	138.7
80°	180.2	169.5	114.6	114.6	114.6
82.5°	134.3	119.4	88.4	88.4	86.3
85°	65.6	52.2	51.9	35.3	27.4
87.5°	17.5	17.5	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P854896

CATALOG NUMBER: SQ2-PR1-OU-125D-830-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	23.79	25.29	24.16	25.60	25.92	20.52	22.01	20.88	22.32	22.64
	3H	25.07	26.41	25.45	26.74	27.10	21.63	22.97	22.01	23.29	23.66
	4H	25.55	26.80	25.95	27.15	27.53	22.06	23.31	22.46	23.66	24.04
	6H	25.90	27.05	26.31	27.42	27.81	22.42	23.57	22.83	23.94	24.33
	8H	26.00	27.10	26.42	27.49	27.89	22.52	23.62	22.95	24.01	24.41
	12H	26.05	27.10	26.48	27.48	27.91	22.55	23.60	22.98	23.98	24.41
4H	2H	23.94	25.20	24.34	25.55	25.92	21.16	22.41	21.56	22.76	23.14
	3H	25.47	26.51	25.88	26.91	27.31	22.48	23.52	22.89	23.92	24.32
	4H	26.09	27.02	26.52	27.43	27.87	23.01	23.94	23.44	24.36	24.80
	6H	26.57	27.38	27.03	27.82	28.28	23.48	24.28	23.94	24.73	25.19
	8H	26.72	27.47	27.18	27.92	28.38	23.61	24.36	24.08	24.81	25.28
	12H	26.80	27.47	27.28	27.95	28.42	23.66	24.33	24.14	24.81	25.28
8H	4H	26.16	26.91	26.62	27.36	27.82	23.36	24.11	23.82	24.56	25.03
	6H	26.73	27.35	27.22	27.84	28.32	23.91	24.54	24.41	25.03	25.51
	8H	26.93	27.48	27.44	28.00	28.48	24.10	24.66	24.61	25.17	25.66
	12H	27.05	27.55	27.57	28.04	28.61	24.19	24.68	24.70	25.18	25.74
12H	4H	26.14	26.82	26.63	27.29	27.77	23.40	24.08	23.89	24.55	25.03
	6H	26.71	27.27	27.23	27.78	28.27	23.97	24.53	24.49	25.04	25.53
	8H	26.95	27.45	27.46	27.94	28.50	24.21	24.70	24.72	25.20	25.76