

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854894

Luminaire Tested: SQ2-PR1-100U-075D-830-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854894
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-12, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PR1-100U-075D-830-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8311.2 lumens
Efficiency: N/A
Efficacy: 140.2 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 59.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854894

CATALOG NUMBER: SQ2-PR1-100U-075D-830-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854894

CATALOG NUMBER: SQ2-PR1-100U-075D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46
1	98	93	90	87	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	72	82	76	71	67	64	60	57	53	50	48	43	41	39	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	31	28	26	23
6	64	52	44	39	58	48	41	36	41	36	32	35	31	28	28	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25835	25835	25835
5°	25801	25960	26276
10°	26071	26742	27142
15°	26064	26200	26419
20°	25642	26036	26904
25°	25572	26297	28010
30°	25544	26880	28280
35°	25300	27457	26331
40°	24717	26435	23170
45°	23386	23201	18322
50°	21263	18969	14217
55°	18686	15612	11066
60°	16172	12484	9113
65°	13956	10346	7977
70°	12548	9163	7081
75°	11497	7935	6513
80°	10005	6369	6369
85°	7243	5743	3020

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 25281 cd/sqm



TEST NUMBER: P854894

CATALOG NUMBER: SQ2-PR1-100U-075D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.5	1.9
10°-20°	447.3	5.4
20°-30°	691.4	8.3
30°-40°	831.6	10.0
40°-50°	746.7	9.0
50°-60°	500.3	6.0
60°-70°	291.0	3.5
70°-80°	149.4	1.8
80°-90°	38.2	0.5
90°-100°	299.3	3.6
100°-110°	905.3	10.9
110°-120°	883.8	10.6
120°-130°	722.2	8.7
130°-140°	589.5	7.1
140°-150°	458.9	5.5
150°-160°	330.8	4.0
160°-170°	202.5	2.4
170°-180°	68.4	0.8
0°-30°	1293.2	15.6
0°-40°	2124.9	25.6
0°-60°	3371.8	40.6
0°-90°	3850.4	46.3
90°-120°	2088.5	25.1
90°-150°	3859.1	46.4
90°-180°	4461.0	53.7
0°-180°	8311.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1600	1600	1600	1600	1600	
5°	1592	1619	1602	1605	1621	152
15°	1559	1623	1567	1572	1580	438
25°	1435	1493	1476	1531	1572	662
35°	1284	1295	1393	1366	1336	800
45°	1024	1107	1016	857	802	784
55°	664	689	555	428	393	597
65°	365	373	271	220	209	370
75°	184	180	127	108	104	196
85°	39	31	31	21	16	48
90°	0	2	14	8	7	3
95°	37	118	565	209	132	44
105°	158	221	889	1688	1604	165
115°	280	334	719	1488	1747	277
125°	392	434	709	1175	1383	348
135°	469	519	704	1013	1140	363
145°	548	589	704	872	953	343
155°	624	645	709	782	811	287
165°	683	691	712	739	748	192
175°	714	714	716	721	719	68
180°	717	717	717	717	717	



TEST NUMBER: P854894

CATALOG NUMBER: SQ2-PR1-100U-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1600.1	1600.1	1600.1	1600.1	1600.1
2.5°	1593.5	1612.6	1594.9	1596.2	1600.1
5°	1591.9	1619.0	1601.7	1605.3	1621.2
7.5°	1591.6	1630.2	1621.9	1631.9	1652.9
10°	1590.2	1636.5	1631.1	1633.2	1655.5
12.5°	1582.4	1636.4	1611.5	1609.5	1621.6
15°	1559.3	1623.0	1567.4	1572.5	1580.5
17.5°	1518.5	1585.2	1532.2	1550.2	1565.8
20°	1492.4	1557.8	1515.3	1538.7	1565.8
22.5°	1468.9	1534.3	1499.6	1532.4	1569.7
25°	1435.4	1492.7	1476.1	1530.9	1572.3
27.5°	1400.1	1433.9	1453.6	1527.0	1556.0
30°	1370.1	1392.4	1441.8	1505.7	1516.9
32.5°	1337.4	1350.9	1426.2	1459.4	1445.1
35°	1283.6	1294.8	1393.0	1366.2	1335.9
37.5°	1219.7	1242.7	1318.2	1241.1	1206.3
40°	1172.7	1211.0	1254.2	1139.2	1099.3
42.5°	1115.3	1176.5	1169.4	1022.9	974.0
45°	1024.2	1107.2	1016.1	856.7	802.4
47.5°	917.0	1002.1	853.1	710.6	660.0
50°	846.5	915.1	755.2	621.7	566.0
52.5°	774.7	824.2	671.7	538.4	487.6
55°	663.8	689.4	554.6	428.2	393.1
57.5°	562.0	578.3	453.0	345.9	320.0
60°	500.8	511.8	386.6	302.9	282.2
62.5°	444.6	453.3	333.1	266.5	250.9
65°	365.3	373.3	270.8	219.9	208.8
67.5°	302.4	306.5	222.8	182.7	172.2
70°	265.8	267.5	194.1	158.1	150.0
72.5°	233.3	231.0	166.7	137.3	131.8
75°	184.3	179.5	127.2	107.5	104.4
77.5°	137.7	132.5	89.4	82.9	82.9
80°	107.6	101.3	68.5	68.5	68.5
82.5°	80.3	71.3	52.8	52.8	51.6
85°	39.1	31.2	31.0	21.1	16.3
87.5°	10.4	10.9	6.7	5.5	5.3
90°	0.0	2.1	13.5	7.8	6.8
92.5°	12.6	50.9	182.7	60.6	43.6
95°	37.1	117.5	564.9	208.7	131.6
97.5°	71.8	149.5	890.3	589.1	358.8
100°	93.4	169.3	994.6	961.6	645.8
102.5°	117.7	191.0	973.0	1348.7	1075.2
105°	157.5	221.4	888.9	1688.2	1604.5
107.5°	195.4	256.3	807.8	1721.7	1818.5
110°	220.6	278.8	767.4	1679.5	1855.4



TEST NUMBER: P854894

CATALOG NUMBER: SQ2-PR1-100U-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	244.9	301.4	743.1	1608.5	1831.2
115°	280.2	334.1	719.0	1487.8	1747.4
117.5°	315.2	366.3	710.5	1374.7	1640.6
120°	338.6	387.1	707.8	1308.7	1564.0
122.5°	360.3	406.0	707.8	1250.7	1486.6
125°	391.5	434.5	708.9	1175.0	1382.9
127.5°	417.0	461.4	707.8	1117.8	1295.0
130°	433.1	479.4	707.8	1085.0	1245.6
132.5°	447.6	494.7	706.9	1055.0	1203.2
135°	469.2	518.7	704.4	1013.3	1139.8
137.5°	493.3	540.3	704.4	968.7	1086.0
140°	508.6	554.8	704.4	939.8	1050.9
142.5°	523.9	568.4	703.5	913.3	1010.5
145°	548.0	588.7	704.4	871.6	953.0
147.5°	572.0	606.6	705.7	837.2	899.7
150°	587.4	619.3	706.7	818.1	870.9
152.5°	601.7	630.1	707.6	801.6	844.8
155°	624.5	645.4	708.9	781.5	811.2
157.5°	644.2	661.2	710.3	766.7	787.4
160°	656.0	670.2	711.2	757.6	773.0
162.5°	667.6	678.5	712.0	749.4	762.2
165°	683.0	690.7	712.2	739.4	748.3
167.5°	696.0	700.0	713.5	731.6	735.4
170°	703.3	705.4	714.5	728.0	729.2
172.5°	707.8	709.0	714.5	724.4	724.6
175°	714.5	714.5	715.6	721.2	719.0
177.5°	717.6	716.7	715.8	718.5	716.7
180°	716.7	716.7	716.7	716.7	716.7



TEST NUMBER: P854894

CATALOG NUMBER: SQ2-PR1-100U-075D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.72	18.52	18.72	19.52	20.84	14.45	15.24	15.44	16.24	17.57
	3H	18.95	19.66	19.96	20.67	22.02	15.51	16.22	16.52	17.23	18.58
	4H	19.40	20.07	20.42	21.08	22.44	15.91	16.57	16.93	17.59	18.94
	6H	19.71	20.33	20.74	21.35	22.71	16.23	16.85	17.26	17.87	19.23
	8H	19.79	20.38	20.83	21.41	22.78	16.32	16.90	17.35	17.94	19.30
	12H	19.82	20.38	20.86	21.40	22.79	16.32	16.88	17.36	17.91	19.29
4H	2H	17.79	18.46	18.82	19.48	20.83	15.01	15.68	16.04	16.69	18.05
	3H	19.26	19.81	20.29	20.86	22.22	16.27	16.82	17.30	17.87	19.23
	4H	19.85	20.36	20.89	21.39	22.78	16.77	17.28	17.81	18.31	19.71
	6H	20.30	20.73	21.35	21.79	23.18	17.20	17.64	18.26	18.70	20.08
	8H	20.43	20.84	21.48	21.89	23.29	17.33	17.73	18.38	18.78	20.18
	12H	20.48	20.85	21.55	21.91	23.32	17.34	17.71	18.41	18.78	20.18
8H	4H	19.87	20.28	20.92	21.33	22.73	17.07	17.48	18.13	18.53	19.93
	6H	20.42	20.75	21.49	21.85	23.25	17.61	17.94	18.68	19.03	20.43
	8H	20.62	20.91	21.70	21.99	23.41	17.79	18.09	18.87	19.16	20.58
	12H	20.72	20.98	21.80	22.05	23.51	17.85	18.11	18.94	19.18	20.64
12H	4H	19.83	20.19	20.90	21.26	22.67	17.09	17.45	18.16	18.52	19.92
	6H	20.40	20.70	21.49	21.78	23.19	17.67	17.96	18.75	19.04	20.46
	8H	20.61	20.87	21.70	21.94	23.40	17.87	18.13	18.96	19.20	20.66