

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853665

Luminaire Tested: SQ2-F-025U-125D-930-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853665
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2308-131-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-F-025U-125D-930-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5752.7 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 56.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853665
CATALOG NUMBER: SQ2-F-025U-125D-930-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853665

CATALOG NUMBER: SQ2-F-025U-125D-930-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	115	115	115	115	110	110	110	110	102	102	102	94	94	94	87	87	87	83		
1	105	100	96	92	101	96	93	89	89	86	83	82	80	78	76	74	73	70		
2	95	87	81	75	91	84	78	73	78	73	69	72	68	65	67	64	61	58		
3	87	77	69	62	83	74	67	61	68	62	58	64	59	54	59	55	52	49		
4	80	68	59	53	76	65	58	51	61	54	49	57	51	47	53	48	44	42		
5	73	61	52	45	70	58	50	44	54	48	42	51	45	40	47	42	38	36		
6	67	54	46	39	64	53	44	39	49	42	37	46	40	35	43	38	34	31		
7	62	49	41	35	60	48	40	34	45	38	33	42	36	31	39	34	30	28		
8	58	45	37	31	56	43	36	30	41	34	29	38	32	28	36	31	27	25		
9	54	41	33	28	52	40	32	27	37	31	26	35	29	25	33	28	24	22		
10	51	38	30	25	49	37	29	25	35	28	24	33	27	23	31	26	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27527	27527	27527
5°	27331	27407	27632
10°	27266	27343	27534
15°	27101	27178	27450
20°	26940	26979	27218
25°	26690	26690	26856
30°	26416	26416	26502
35°	26097	26004	26187
40°	25752	25653	25752
45°	25352	25245	25352
50°	24970	24739	24797
55°	24389	24324	24192
60°	23776	23628	23476
65°	23072	22808	22541
70°	21711	21602	21163
75°	20430	19994	19420
80°	18140	17713	17062
85°	14635	13338	12486

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 25507 cd/sqm



TEST NUMBER: P853665

CATALOG NUMBER: SQ2-F-025U-125D-930-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.2	2.8
10°-20°	460.5	8.0
20°-30°	692.8	12.0
30°-40°	829.0	14.4
40°-50°	855.3	14.9
50°-60°	771.6	13.4
60°-70°	588.8	10.2
70°-80°	338.5	5.9
80°-90°	88.7	1.5
90°-100°	63.0	1.1
100°-110°	196.0	3.4
110°-120°	191.7	3.3
120°-130°	156.5	2.7
130°-140°	128.0	2.2
140°-150°	99.9	1.7
150°-160°	72.1	1.3
160°-170°	44.1	0.8
170°-180°	14.9	0.3
0°-30°	1314.5	22.8
0°-40°	2143.5	37.3
0°-60°	3770.4	65.5
0°-90°	4786.4	83.2
90°-120°	450.7	7.8
90°-150°	835.2	14.5
90°-180°	966.0	16.8
0°-180°	5752.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1705	1705	1705	1705	1705	
5°	1686	1709	1691	1694	1705	160
15°	1621	1642	1626	1633	1642	457
25°	1498	1514	1498	1501	1508	690
35°	1324	1333	1319	1324	1329	828
45°	1110	1117	1106	1108	1110	857
55°	866	871	864	859	859	775
65°	604	602	597	592	590	594
75°	328	325	320	314	311	345
85°	79	74	72	65	67	91
90°	0	1	3	3	3	3
95°	9	25	116	43	28	10
105°	34	48	193	368	352	36
115°	61	72	157	323	378	60
125°	85	94	155	254	298	75
135°	102	113	154	219	246	79
145°	119	129	154	190	206	75
155°	137	141	155	170	176	63
165°	150	151	156	160	162	42
175°	156	156	156	157	156	15
180°	156	156	156	156	156	



TEST NUMBER: P853665

CATALOG NUMBER: SQ2-F-025U-125D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1704.9	1704.9	1704.9	1704.9	1704.9
2.5°	1693.8	1713.8	1697.5	1701.2	1703.1
5°	1686.3	1709.0	1691.0	1693.6	1704.9
7.5°	1672.4	1696.9	1677.0	1681.5	1694.2
10°	1663.1	1685.8	1667.8	1670.3	1679.4
12.5°	1648.2	1671.0	1652.9	1657.3	1666.4
15°	1621.3	1641.7	1625.9	1633.1	1642.2
17.5°	1590.2	1612.0	1594.4	1600.6	1608.3
20°	1567.9	1586.0	1570.2	1572.8	1584.1
22.5°	1540.0	1558.2	1544.2	1544.9	1554.4
25°	1498.2	1514.1	1498.2	1500.7	1507.5
27.5°	1450.3	1464.0	1450.3	1452.8	1458.7
30°	1416.9	1430.5	1416.9	1419.3	1421.5
32.5°	1379.7	1391.5	1377.9	1380.3	1386.2
35°	1324.0	1333.1	1319.3	1324.1	1328.6
37.5°	1264.5	1271.3	1259.9	1262.3	1266.4
40°	1221.8	1228.6	1217.1	1219.5	1221.8
42.5°	1179.0	1184.0	1172.5	1175.0	1179.0
45°	1110.3	1117.1	1105.6	1108.0	1110.3
47.5°	1040.6	1044.7	1035.0	1033.3	1037.4
50°	994.1	996.4	984.9	984.9	987.2
52.5°	944.0	946.2	938.4	934.7	937.0
55°	866.4	870.9	864.1	859.4	859.4
57.5°	788.4	792.4	783.7	781.4	780.9
60°	736.3	738.6	731.7	729.3	727.0
62.5°	684.3	684.7	677.8	675.4	673.1
65°	603.9	601.7	597.0	592.3	590.0
67.5°	513.8	516.1	511.5	504.0	504.0
70°	459.9	462.2	457.6	448.3	448.3
72.5°	407.9	406.5	403.7	396.2	392.5
75°	327.5	325.2	320.5	313.5	311.3
77.5°	247.1	244.9	242.5	233.7	235.5
80°	195.1	192.8	190.5	183.5	183.5
82.5°	148.7	144.6	142.2	135.2	135.2
85°	79.0	74.4	72.0	65.1	67.4
87.5°	22.3	20.7	19.2	15.4	15.4
90°	0.0	0.9	2.9	2.9	2.9
92.5°	3.1	10.7	36.5	12.0	9.7
95°	8.6	25.4	115.6	42.6	27.7
97.5°	15.7	33.0	191.4	119.2	75.1
100°	21.0	36.9	215.9	201.9	134.7
102.5°	26.4	41.5	211.3	288.4	226.4
105°	34.4	48.4	192.9	368.3	351.5
107.5°	42.4	55.5	175.4	374.5	393.0
110°	47.8	60.8	166.2	365.7	402.1



TEST NUMBER: P853665

CATALOG NUMBER: SQ2-F-025U-125D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	53.1	65.4	161.6	349.9	396.0
115°	61.1	72.3	156.6	323.1	378.2
117.5°	69.0	79.2	154.5	297.6	354.0
120°	73.5	83.8	153.8	283.0	337.2
122.5°	78.1	88.4	154.5	270.7	320.4
125°	85.0	94.3	154.7	254.1	298.0
127.5°	90.5	100.1	154.7	241.7	279.1
130°	93.6	103.9	154.7	234.8	268.4
132.5°	97.4	107.7	154.0	228.6	260.0
135°	102.2	113.4	153.8	219.3	246.4
137.5°	107.7	118.0	153.8	210.1	234.8
140°	110.8	121.1	153.8	204.0	226.4
142.5°	114.6	124.1	153.8	197.8	218.0
145°	119.4	128.7	153.8	189.5	206.3
147.5°	125.1	133.2	154.7	181.8	195.0
150°	128.9	135.5	154.7	177.9	188.2
152.5°	132.0	137.8	154.7	174.0	182.8
155°	136.6	141.3	154.7	170.1	175.8
157.5°	141.2	144.7	154.7	166.7	170.2
160°	144.2	147.0	154.7	164.4	167.2
162.5°	146.5	148.6	154.7	162.8	164.9
165°	150.0	150.9	155.7	160.5	162.4
167.5°	152.1	152.2	154.7	159.2	160.1
170°	152.8	153.8	154.7	157.6	158.6
172.5°	154.4	154.5	155.5	156.8	157.0
175°	155.7	155.7	155.7	156.6	155.7
177.5°	155.7	155.7	155.7	155.7	155.7
180°	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P853665

CATALOG NUMBER: SQ2-F-025U-125D-930-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.11	23.40	22.72	24.02	24.72	22.03	23.32	22.64	23.94	24.64
	3H	23.92	25.09	24.54	25.71	26.45	23.80	24.97	24.42	25.59	26.33
	4H	24.60	25.70	25.24	26.34	27.09	24.45	25.55	25.09	26.19	26.94
	6H	25.09	26.11	25.75	26.76	27.52	24.91	25.92	25.56	26.57	27.34
	8H	25.24	26.21	25.91	26.88	27.65	25.04	26.01	25.71	26.68	27.45
	12H	25.33	26.26	26.00	26.92	27.72	25.11	26.03	25.78	26.70	27.50
4H	2H	22.71	23.81	23.36	24.45	25.20	22.65	23.75	23.29	24.39	25.14
	3H	24.74	25.66	25.39	26.34	27.11	24.63	25.55	25.29	26.23	27.00
	4H	25.55	26.38	26.22	27.06	27.87	25.40	26.24	26.08	26.92	27.72
	6H	26.16	26.89	26.85	27.60	28.41	25.98	26.71	26.67	27.42	28.23
	8H	26.36	27.04	27.06	27.74	28.57	26.16	26.84	26.85	27.54	28.36
	12H	26.48	27.09	27.20	27.82	28.65	26.25	26.86	26.97	27.60	28.42
8H	4H	25.83	26.51	26.53	27.21	28.04	25.70	26.38	26.40	27.09	27.91
	6H	26.56	27.13	27.29	27.88	28.70	26.40	26.96	27.13	27.71	28.54
	8H	26.84	27.34	27.58	28.09	28.93	26.64	27.15	27.38	27.90	28.74
	12H	27.02	27.47	27.77	28.21	29.11	26.80	27.24	27.54	27.98	28.89
12H	4H	25.84	26.45	26.56	27.19	28.01	25.72	26.33	26.44	27.06	27.89
	6H	26.61	27.12	27.35	27.87	28.71	26.45	26.96	27.19	27.71	28.55
	8H	26.93	27.37	27.67	28.11	29.01	26.74	27.18	27.48	27.92	28.83