

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854862

Luminaire Tested: SQ2-PW1-125U-075D-830-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854862
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PW1-125U-075D-830-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9445.8 lumens
Efficiency: N/A
Efficacy: 133.8 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.22
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 70.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854862

CATALOG NUMBER: SQ2-PW1-125U-075D-830-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854862

CATALOG NUMBER: SQ2-PW1-125U-075D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	42	41	35
2	88	81	75	70	80	74	69	65	61	57	54	49	47	44	38	36	35	30
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	30	26
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	28	26	23
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	51	43	38	57	47	40	35	39	34	30	32	28	25	25	23	21	18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	21	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	23	19	23	19	17	18	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27651	27651	27651
5°	27465	27678	27942
10°	27516	27837	28184
15°	27510	28027	28354
20°	27520	27996	27801
25°	27371	27401	25832
30°	27186	25818	23353
35°	26972	23759	21088
40°	26435	21657	18632
45°	25398	19479	16276
50°	23639	17412	13931
55°	21627	15381	11296
60°	19385	13378	9746
65°	16951	11530	8661
70°	13860	10244	7851
75°	10786	8852	7224
80°	8043	7578	6369
85°	5446	5743	3631

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25398 cd/sqm



TEST NUMBER: P854862

CATALOG NUMBER: SQ2-PW1-125U-075D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.1	1.7
10°-20°	472.5	5.0
20°-30°	695.3	7.4
30°-40°	760.2	8.0
40°-50°	682.0	7.2
50°-60°	508.8	5.4
60°-70°	321.5	3.4
70°-80°	159.3	1.7
80°-90°	38.3	0.4
90°-100°	350.0	3.7
100°-110°	1139.4	12.1
110°-120°	1127.1	11.9
120°-130°	921.1	9.8
130°-140°	752.8	8.0
140°-150°	586.4	6.2
150°-160°	422.6	4.5
160°-170°	258.3	2.7
170°-180°	87.2	0.9
0°-30°	1330.9	14.1
0°-40°	2091.2	22.1
0°-60°	3281.9	34.7
0°-90°	3801.0	40.2
90°-120°	2616.5	27.7
90°-150°	4876.7	51.6
90°-180°	5645.0	59.8
0°-180°	9445.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1713	1713	1713	1713	1713	
5°	1695	1722	1708	1710	1724	161
15°	1646	1678	1677	1688	1696	465
25°	1536	1570	1538	1474	1450	708
35°	1368	1354	1205	1100	1070	853
45°	1112	1023	853	746	713	853
55°	768	695	546	428	401	686
65°	444	407	302	243	227	440
75°	173	186	142	119	116	190
85°	29	37	31	21	20	37
90°	0	3	8	7	7	3
95°	47	144	641	229	141	55
105°	194	279	1129	2156	2041	206
115°	358	427	919	1895	2229	354
125°	497	555	907	1496	1764	443
135°	601	664	903	1291	1456	464
145°	702	754	900	1112	1218	440
155°	801	828	906	996	1033	369
165°	874	882	908	942	953	246
175°	912	912	912	918	916	86
180°	915	915	915	915	915	



TEST NUMBER: P854862

CATALOG NUMBER: SQ2-PW1-125U-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1712.6	1712.6	1712.6	1712.6	1712.6
2.5°	1700.8	1722.5	1708.7	1710.1	1713.9
5°	1694.6	1721.7	1707.7	1709.6	1724.0
7.5°	1686.1	1713.6	1703.1	1709.0	1723.0
10°	1678.3	1707.0	1697.9	1706.4	1719.1
12.5°	1667.9	1697.9	1691.4	1701.2	1713.9
15°	1645.8	1677.6	1676.7	1688.3	1696.3
17.5°	1620.0	1651.9	1650.3	1653.3	1657.2
20°	1601.7	1633.6	1629.4	1618.0	1618.0
22.5°	1575.6	1610.0	1599.4	1568.2	1558.0
25°	1536.4	1569.9	1538.1	1473.9	1450.0
27.5°	1490.8	1517.9	1453.9	1362.8	1329.6
30°	1458.2	1478.9	1384.8	1284.5	1252.6
32.5°	1424.3	1432.2	1314.3	1210.1	1175.6
35°	1368.4	1354.1	1205.4	1100.2	1069.9
37.5°	1302.5	1259.8	1100.7	990.6	957.1
40°	1254.2	1193.6	1027.5	917.5	884.0
42.5°	1200.7	1124.9	958.4	848.3	813.6
45°	1112.3	1023.1	853.1	746.2	712.8
47.5°	1012.8	924.2	754.5	651.1	622.4
50°	941.1	855.0	693.2	589.6	554.6
52.5°	868.0	790.9	633.2	526.8	478.8
55°	768.3	694.9	546.4	428.4	401.3
57.5°	665.5	602.0	467.7	360.6	338.3
60°	600.3	544.4	414.3	324.0	301.8
62.5°	537.6	488.1	362.1	290.2	271.7
65°	443.7	406.9	301.8	242.6	226.7
67.5°	352.3	331.8	250.9	199.1	188.6
70°	293.6	287.2	217.0	174.3	166.3
72.5°	242.7	245.2	184.3	150.9	145.5
75°	172.9	185.7	141.9	118.9	115.8
77.5°	117.8	136.9	105.0	88.0	85.5
80°	86.5	105.6	81.5	68.5	68.5
82.5°	60.4	75.6	58.1	51.6	51.6
85°	29.4	37.3	31.0	21.1	19.6
87.5°	7.8	12.3	6.8	5.3	5.3
90°	0.0	3.3	7.9	6.8	6.8
92.5°	16.2	58.2	186.1	61.4	47.3
95°	47.3	144.0	641.4	228.7	140.7
97.5°	88.9	187.5	1088.7	663.0	404.7
100°	115.9	212.8	1257.0	1120.9	727.0
102.5°	146.5	239.8	1236.4	1658.3	1260.9
105°	193.6	279.4	1128.7	2155.8	2041.4
107.5°	244.4	325.2	1026.5	2199.0	2320.3
110°	281.3	355.0	977.9	2145.4	2364.4



TEST NUMBER: P854862

CATALOG NUMBER: SQ2-PW1-125U-075D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	311.9	384.8	947.4	2048.7	2331.0
115°	357.8	427.2	919.4	1894.8	2229.3
117.5°	405.1	467.6	908.6	1753.9	2086.8
120°	432.1	493.8	905.9	1667.2	1989.6
122.5°	458.2	519.0	906.8	1592.1	1892.4
125°	497.4	554.6	907.0	1496.1	1763.5
127.5°	530.9	589.5	906.8	1424.2	1647.1
130°	552.5	612.0	905.9	1383.1	1582.2
132.5°	571.4	633.5	905.0	1345.0	1531.8
135°	600.9	663.7	902.6	1291.2	1456.3
137.5°	629.8	692.9	900.1	1236.5	1383.1
140°	650.5	710.9	899.2	1199.4	1338.0
142.5°	670.2	728.1	899.2	1164.0	1287.7
145°	702.2	753.9	900.3	1112.0	1217.6
147.5°	733.3	778.2	901.9	1067.8	1149.4
150°	754.0	793.6	903.6	1041.4	1110.7
152.5°	774.7	807.3	904.5	1021.3	1076.5
155°	801.3	827.6	905.9	995.6	1033.1
157.5°	826.5	845.4	907.2	976.8	1002.9
160°	841.8	857.1	908.1	964.9	985.8
162.5°	855.2	867.2	908.1	954.9	970.5
165°	874.4	882.1	908.1	942.2	953.1
167.5°	887.9	892.8	908.4	932.6	938.3
170°	896.9	899.1	909.3	926.2	928.4
172.5°	903.3	904.5	911.1	922.6	922.2
175°	911.5	911.5	911.5	918.2	916.0
177.5°	914.9	914.0	913.1	917.5	914.0
180°	914.9	914.9	914.9	914.9	914.9



TEST NUMBER: P854862

CATALOG NUMBER: SQ2-PW1-125U-075D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.60	18.35	18.65	19.40	20.81	14.09	14.84	15.13	15.88	17.29
	3H	18.92	19.59	19.97	20.64	22.07	15.29	15.96	16.34	17.01	18.44
	4H	19.29	19.92	20.35	20.98	22.41	15.73	16.36	16.79	17.42	18.85
	6H	19.48	20.07	20.56	21.13	22.57	16.04	16.62	17.11	17.68	19.13
	8H	19.51	20.07	20.59	21.14	22.58	16.11	16.67	17.19	17.74	19.18
	12H	19.51	20.03	20.59	21.10	22.57	16.12	16.65	17.20	17.71	19.18
4H	2H	17.69	18.33	18.76	19.38	20.82	14.76	15.39	15.83	16.45	17.88
	3H	19.23	19.76	20.31	20.84	22.28	16.14	16.66	17.21	17.75	19.19
	4H	19.73	20.22	20.82	21.29	22.76	16.68	17.16	17.76	18.23	19.70
	6H	20.06	20.47	21.15	21.57	23.03	17.08	17.49	18.17	18.59	20.05
	8H	20.13	20.52	21.23	21.61	23.09	17.18	17.57	18.27	18.65	20.13
	12H	20.15	20.49	21.25	21.60	23.08	17.20	17.55	18.31	18.65	20.13
8H	4H	19.76	20.15	20.86	21.24	22.71	17.00	17.38	18.09	18.47	19.95
	6H	20.20	20.51	21.31	21.64	23.12	17.50	17.82	18.61	18.95	20.42
	8H	20.34	20.62	21.46	21.73	23.23	17.66	17.94	18.78	19.05	20.55
	12H	20.40	20.65	21.53	21.76	23.29	17.72	17.96	18.84	19.07	20.60
12H	4H	19.72	20.07	20.83	21.17	22.65	17.01	17.36	18.12	18.46	19.94
	6H	20.19	20.47	21.31	21.58	23.07	17.56	17.84	18.68	18.96	20.45
	8H	20.34	20.59	21.47	21.70	23.23	17.74	17.99	18.87	19.10	20.63