

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853716

Luminaire Tested: SQ2-F-125U-050D-930-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853716
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-F-125U-050D-930-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6806.5 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 61.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853716

CATALOG NUMBER: SQ2-F-125U-050D-930-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853716

CATALOG NUMBER: SQ2-F-125U-050D-930-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	60	59	47	46	44	32	32	31	24
2	85	77	71	66	76	70	64	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	17
4	70	60	52	46	63	54	47	42	43	38	34	32	29	26	22	20	19	15
5	64	53	45	39	57	48	41	36	38	33	29	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	25	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	17	14	13	10
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	25	21	25	21	17	20	16	14	14	12	10	8
10	44	32	25	20	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11399	11399	11399
5°	11318	11349	11443
10°	11290	11322	11401
15°	11221	11254	11366
20°	11155	11172	11270
25°	11052	11052	11120
30°	10938	10938	10974
35°	10805	10768	10843
40°	10663	10623	10663
45°	10497	10453	10497
50°	10339	10243	10268
55°	10100	10072	10018
60°	9846	9784	9720
65°	9555	9444	9333
70°	8988	8946	8762
75°	8459	8278	8041
80°	7513	7336	7066
85°	6058	5521	5169

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 10563 cd/sqm



TEST NUMBER: P853716

CATALOG NUMBER: SQ2-F-125U-050D-930-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	1.0
10°-20°	190.7	2.8
20°-30°	286.9	4.2
30°-40°	343.3	5.0
40°-50°	354.2	5.2
50°-60°	319.5	4.7
60°-70°	243.8	3.6
70°-80°	140.2	2.1
80°-90°	37.4	0.6
90°-100°	299.1	4.4
100°-110°	973.7	14.3
110°-120°	963.2	14.2
120°-130°	787.1	11.6
130°-140°	643.3	9.5
140°-150°	501.1	7.4
150°-160°	361.2	5.3
160°-170°	220.8	3.2
170°-180°	74.5	1.1
0°-30°	544.3	8.0
0°-40°	887.5	13.0
0°-60°	1561.2	22.9
0°-90°	1982.6	29.1
90°-120°	2236.0	32.9
90°-150°	4167.5	61.2
90°-180°	4824.0	70.9
0°-180°	6806.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	706	706	706	706	706	
5°	698	708	700	701	706	66
15°	671	680	673	676	680	189
25°	620	627	620	621	624	286
35°	548	552	546	548	550	343
45°	460	463	458	459	460	355
55°	359	361	358	356	356	321
65°	250	249	247	245	244	246
75°	136	135	133	130	129	143
85°	33	31	30	27	28	38
90°	0	3	7	6	6	3
95°	40	123	548	195	120	47
105°	165	239	965	1842	1744	176
115°	306	365	786	1619	1905	303
125°	425	474	775	1278	1507	378
135°	514	567	771	1103	1244	397
145°	600	644	769	950	1040	376
155°	685	707	774	851	883	315
165°	747	754	776	805	814	210
175°	779	779	779	785	783	74
180°	782	782	782	782	782	



TEST NUMBER: P853716

CATALOG NUMBER: SQ2-F-125U-050D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	706.0	706.0	706.0	706.0	706.0
2.5°	701.3	709.6	702.9	704.4	705.2
5°	698.3	707.7	700.2	701.3	706.0
7.5°	692.5	702.7	694.4	696.3	701.5
10°	688.6	698.1	690.6	691.6	695.4
12.5°	682.5	691.9	684.4	686.2	690.0
15°	671.3	679.8	673.3	676.2	680.0
17.5°	658.4	667.5	660.2	662.8	665.9
20°	649.2	656.7	650.2	651.2	655.9
22.5°	637.7	645.2	639.4	639.7	643.6
25°	620.4	626.9	620.4	621.4	624.2
27.5°	600.5	606.2	600.5	601.6	604.0
30°	586.7	592.3	586.7	587.7	588.6
32.5°	571.3	576.2	570.5	571.6	574.0
35°	548.2	552.0	546.3	548.3	550.1
37.5°	523.6	526.4	521.7	522.7	524.4
40°	505.9	508.7	504.0	505.0	505.9
42.5°	488.2	490.3	485.5	486.5	488.2
45°	459.7	462.6	457.8	458.8	459.7
47.5°	430.9	432.6	428.6	427.8	429.5
50°	411.6	412.6	407.8	407.8	408.8
52.5°	390.9	391.8	388.6	387.0	388.0
55°	358.8	360.6	357.8	355.9	355.9
57.5°	326.4	328.1	324.5	323.5	323.4
60°	304.9	305.8	303.0	302.0	301.0
62.5°	283.3	283.5	280.7	279.7	278.7
65°	250.1	249.1	247.2	245.2	244.3
67.5°	212.7	213.7	211.8	208.7	208.7
70°	190.4	191.4	189.5	185.6	185.6
72.5°	168.9	168.3	167.2	164.0	162.5
75°	135.6	134.7	132.7	129.8	128.9
77.5°	102.3	101.4	100.4	96.8	97.5
80°	80.8	79.9	78.9	76.0	76.0
82.5°	61.6	59.9	58.9	56.0	56.0
85°	32.7	30.8	29.8	27.0	27.9
87.5°	9.2	9.0	9.0	7.3	7.3
90°	0.0	2.8	6.7	5.8	5.8
92.5°	13.8	49.8	159.1	52.4	40.4
95°	40.4	123.1	548.2	195.4	120.2
97.5°	76.0	160.2	930.3	566.6	345.8
100°	99.1	181.8	1074.2	957.9	621.3
102.5°	125.2	205.0	1056.5	1417.1	1077.5
105°	165.4	238.8	964.6	1842.3	1744.5
107.5°	208.9	277.9	877.3	1879.2	1982.8
110°	240.4	303.4	835.7	1833.4	2020.5



TEST NUMBER: P853716

CATALOG NUMBER: SQ2-F-125U-050D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.6	328.8	809.5	1750.8	1992.0
115°	305.8	365.1	785.7	1619.2	1905.1
117.5°	346.2	399.6	776.5	1498.8	1783.4
120°	369.3	421.9	774.2	1424.8	1700.3
122.5°	391.6	443.5	774.9	1360.5	1617.2
125°	425.1	474.0	775.1	1278.5	1507.0
127.5°	453.7	503.7	774.9	1217.0	1407.5
130°	472.2	523.0	774.2	1181.9	1352.1
132.5°	488.3	541.4	773.4	1149.4	1309.0
135°	513.5	567.1	771.3	1103.4	1244.4
137.5°	538.2	592.1	769.2	1056.7	1181.9
140°	555.9	607.6	768.4	1025.0	1143.4
142.5°	572.8	622.2	768.4	994.7	1100.4
145°	600.1	644.3	769.4	950.3	1040.5
147.5°	626.6	665.0	770.7	912.5	982.3
150°	644.3	678.2	772.2	889.9	949.2
152.5°	662.0	689.9	773.0	872.7	920.0
155°	684.7	707.3	774.2	850.9	882.8
157.5°	706.3	722.4	775.3	834.7	857.1
160°	719.3	732.5	776.1	824.6	842.4
162.5°	730.9	741.0	776.1	816.0	829.4
165°	747.2	753.8	776.1	805.1	814.5
167.5°	758.8	762.9	776.3	797.0	801.9
170°	766.5	768.3	777.0	791.5	793.4
172.5°	771.9	773.0	778.6	788.4	788.0
175°	779.0	779.0	779.0	784.7	782.8
177.5°	781.9	781.1	780.3	784.1	781.1
180°	781.9	781.9	781.9	781.9	781.9



TEST NUMBER: P853716

CATALOG NUMBER: SQ2-F-125U-050D-930-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.10	14.80	15.21	15.91	17.46	14.02	14.73	15.14	15.84	17.38
	3H	15.87	16.50	16.99	17.62	19.17	15.75	16.38	16.87	17.50	19.06
	4H	16.52	17.12	17.65	18.24	19.80	16.36	16.97	17.50	18.09	19.65
	6H	16.98	17.53	18.12	18.65	20.23	16.79	17.35	17.94	18.47	20.04
	8H	17.11	17.64	18.26	18.78	20.34	16.91	17.44	18.06	18.57	20.14
	12H	17.18	17.68	18.33	18.81	20.40	16.96	17.46	18.11	18.59	20.18
4H	2H	14.63	15.23	15.77	16.35	17.91	14.57	15.17	15.71	16.29	17.85
	3H	16.60	17.10	17.75	18.25	19.83	16.49	17.00	17.64	18.14	19.72
	4H	17.39	17.85	18.54	18.98	20.58	17.24	17.70	18.39	18.84	20.43
	6H	17.97	18.36	19.12	19.52	21.10	17.79	18.18	18.94	19.34	20.92
	8H	18.15	18.52	19.31	19.67	21.27	17.95	18.32	19.10	19.47	21.07
	12H	18.24	18.58	19.42	19.74	21.35	18.02	18.35	19.19	19.51	21.12
8H	4H	17.62	17.99	18.78	19.14	20.74	17.49	17.86	18.65	19.01	20.61
	6H	18.33	18.64	19.51	19.83	21.43	18.16	18.47	19.34	19.66	21.26
	8H	18.60	18.86	19.78	20.03	21.65	18.40	18.67	19.59	19.84	21.46
	12H	18.76	18.99	19.94	20.16	21.81	18.53	18.76	19.72	19.93	21.58
12H	4H	17.61	17.94	18.78	19.10	20.71	17.48	17.82	18.66	18.98	20.59
	6H	18.37	18.64	19.55	19.81	21.43	18.21	18.48	19.39	19.65	21.27
	8H	18.66	18.89	19.84	20.06	21.71	18.47	18.70	19.66	19.87	21.52