

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853782

Luminaire Tested: SQ2-FA-0U-100D-930-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P853782  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-FA-0U-100D-930-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3612.5 lumens  
Efficiency: N/A  
Efficacy: 96.1 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 0.95 / 0.95  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 37.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P853782

CATALOG NUMBER: SQ2-FA-0U-100D-930-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P853782

CATALOG NUMBER: SQ2-FA-0U-100D-930-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF  | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |    |    | 20 |     |
| RC  | 80  |     |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |    |    | 10 | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0  |     |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    | 100 |
| 1   | 111 | 107 | 104 | 101 | 108 | 105 | 102 | 99  | 101 | 98  | 96  | 97  | 95  | 93  | 93  | 92  | 90  | 88  |    |    |    | 88  |
| 2   | 103 | 97  | 91  | 87  | 101 | 95  | 90  | 86  | 92  | 87  | 84  | 88  | 85  | 82  | 86  | 83  | 80  | 78  |    |    |    | 78  |
| 3   | 96  | 88  | 81  | 76  | 94  | 86  | 80  | 75  | 84  | 78  | 74  | 81  | 77  | 73  | 79  | 75  | 72  | 70  |    |    |    | 70  |
| 4   | 90  | 80  | 73  | 68  | 88  | 79  | 72  | 67  | 77  | 71  | 66  | 74  | 70  | 65  | 72  | 68  | 65  | 63  |    |    |    | 63  |
| 5   | 84  | 74  | 66  | 61  | 82  | 73  | 66  | 60  | 71  | 65  | 60  | 69  | 64  | 59  | 67  | 62  | 59  | 57  |    |    |    | 57  |
| 6   | 79  | 68  | 61  | 55  | 77  | 67  | 60  | 55  | 65  | 59  | 55  | 64  | 58  | 54  | 62  | 58  | 54  | 52  |    |    |    | 52  |
| 7   | 74  | 63  | 56  | 50  | 73  | 62  | 55  | 50  | 61  | 55  | 50  | 59  | 54  | 50  | 58  | 53  | 49  | 48  |    |    |    | 48  |
| 8   | 70  | 59  | 51  | 46  | 69  | 58  | 51  | 46  | 57  | 50  | 46  | 56  | 50  | 46  | 54  | 49  | 46  | 44  |    |    |    | 44  |
| 9   | 66  | 55  | 48  | 43  | 65  | 54  | 47  | 43  | 53  | 47  | 43  | 52  | 46  | 42  | 51  | 46  | 42  | 41  |    |    |    | 41  |
| 10  | 63  | 51  | 44  | 40  | 61  | 51  | 44  | 40  | 50  | 44  | 39  | 49  | 43  | 39  | 48  | 43  | 39  | 38  |    |    |    | 38  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    | 90°   | 180°  | 270°  |
|-----|-------|-------|-------|-------|
| 0°  | 39938 | 39938 | 39938 | 39938 |
| 5°  | 39728 | 39789 | 39577 | 39759 |
| 10° | 39667 | 39515 | 39515 | 39515 |
| 15° | 39539 | 39134 | 39228 | 39134 |
| 20° | 39232 | 37565 | 38943 | 37917 |
| 25° | 38717 | 31705 | 38450 | 32370 |
| 30° | 38361 | 18189 | 37943 | 18433 |
| 35° | 37688 | 15626 | 37211 | 15406 |
| 40° | 36644 | 8218  | 35622 | 8140  |
| 45° | 33310 | 3535  | 32118 | 3535  |
| 50° | 21976 | 4265  | 20851 | 3984  |
| 55° | 12287 | 7876  | 11657 | 7142  |
| 60° | 6626  | 11083 | 6507  | 9939  |
| 65° | 5845  | 13471 | 6128  | 15324 |
| 70° | 5462  | 16117 | 5198  | 16995 |
| 75° | 5122  | 13849 | 5234  | 14317 |
| 80° | 4333  | 9884  | 4333  | 10404 |
| 85° | 3798  | 5521  | 3464  | 6558  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 33310 cd/sqm

TEST NUMBER: P853782

CATALOG NUMBER: SQ2-FA-0U-100D-930-UNV-STD-W-4

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 232.8  | 6.4       |
| 10°-20°   | 660.4  | 18.3      |
| 20°-30°   | 900.4  | 24.9      |
| 30°-40°   | 756.7  | 20.9      |
| 40°-50°   | 429.8  | 11.9      |
| 50°-60°   | 228.0  | 6.3       |
| 60°-70°   | 210.0  | 5.8       |
| 70°-80°   | 154.1  | 4.3       |
| 80°-90°   | 40.3   | 1.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1793.6 | 49.7      |
| 0°-40°    | 2550.3 | 70.6      |
| 0°-60°    | 3208.1 | 88.8      |
| 0°-90°    | 3612.5 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3612.5 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 90°  | 180° | 270° | 360° | Flux |
|-----|------|------|------|------|------|------|
| 0°  | 2474 | 2474 | 2474 | 2474 | 2474 |      |
| 5°  | 2451 | 2455 | 2442 | 2453 | 2451 | 233  |
| 15° | 2365 | 2341 | 2347 | 2341 | 2365 | 667  |
| 25° | 2173 | 1780 | 2158 | 1817 | 2173 | 1002 |
| 35° | 1912 | 793  | 1888 | 782  | 1912 | 1194 |
| 45° | 1459 | 155  | 1407 | 155  | 1459 | 1067 |
| 55° | 436  | 280  | 414  | 254  | 436  | 420  |
| 65° | 153  | 353  | 160  | 401  | 153  | 154  |
| 75° | 82   | 222  | 84   | 230  | 82   | 85   |
| 85° | 20   | 30   | 19   | 35   | 20   | 24   |
| 90° | 0    | 0    | 0    | 0    | 0    |      |



TEST NUMBER: P853782

CATALOG NUMBER: SQ2-FA-0U-100D-930-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    | 112.5° | 135°   | 157.5° | 180°   | 202.5° | 225°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 2473.6 | 2473.6 | 2473.6 | 2473.6 | 2473.6 | 2473.6 | 2473.6 | 2473.6 | 2473.6 | 2473.6 | 2473.6 |
| 2.5°  | 2460.2 | 2496.7 | 2464.7 | 2460.5 | 2473.6 | 2470.7 | 2466.1 | 2483.4 | 2454.2 | 2483.4 | 2460.2 |
| 5°    | 2451.2 | 2493.2 | 2445.6 | 2433.1 | 2455.0 | 2440.4 | 2453.1 | 2478.4 | 2441.9 | 2474.7 | 2438.2 |
| 7.5°  | 2435.9 | 2473.1 | 2416.2 | 2408.1 | 2429.6 | 2416.8 | 2422.1 | 2457.2 | 2426.6 | 2448.1 | 2415.0 |
| 10°   | 2419.5 | 2452.3 | 2395.3 | 2390.1 | 2410.2 | 2397.4 | 2402.7 | 2439.4 | 2410.2 | 2430.2 | 2397.1 |
| 12.5° | 2401.6 | 2427.1 | 2369.9 | 2367.7 | 2384.8 | 2376.4 | 2378.8 | 2409.7 | 2386.3 | 2406.4 | 2374.7 |
| 15°   | 2365.4 | 2389.1 | 2331.8 | 2322.9 | 2341.2 | 2333.9 | 2337.4 | 2365.0 | 2346.8 | 2359.5 | 2331.8 |
| 17.5° | 2320.6 | 2339.6 | 2282.6 | 2255.7 | 2256.5 | 2265.6 | 2282.6 | 2315.8 | 2299.4 | 2316.2 | 2277.0 |
| 20°   | 2283.3 | 2305.2 | 2242.3 | 2190.0 | 2186.3 | 2195.4 | 2242.3 | 2275.7 | 2266.5 | 2284.8 | 2229.2 |
| 22.5° | 2240.1 | 2254.6 | 2197.5 | 2109.2 | 2096.8 | 2105.9 | 2191.6 | 2231.0 | 2227.7 | 2240.1 | 2171.0 |
| 25°   | 2173.3 | 2187.9 | 2083.7 | 1956.6 | 1779.7 | 1945.6 | 2087.5 | 2158.3 | 2158.3 | 2169.3 | 2078.1 |
| 27.5° | 2105.4 | 2105.7 | 1917.3 | 1256.6 | 1108.5 | 1211.3 | 1914.7 | 2068.5 | 2086.0 | 2080.5 | 1901.3 |
| 30°   | 2057.6 | 2044.8 | 1699.4 | 1015.8 | 975.6  | 1001.2 | 1701.3 | 2006.0 | 2035.2 | 2015.2 | 1656.5 |
| 32.5° | 2002.4 | 1966.3 | 1254.7 | 933.9  | 901.0  | 923.6  | 1213.3 | 1931.9 | 1983.0 | 1939.6 | 1302.8 |
| 35°   | 1912.1 | 1817.3 | 957.0  | 825.7  | 792.8  | 822.0  | 949.5  | 1785.7 | 1887.9 | 1771.1 | 988.7  |
| 37.5° | 1814.7 | 1444.5 | 842.4  | 657.6  | 586.9  | 643.4  | 838.3  | 1429.0 | 1775.2 | 1395.8 | 841.7  |
| 40°   | 1738.6 | 1134.9 | 757.4  | 481.1  | 389.9  | 453.7  | 751.8  | 1082.7 | 1690.1 | 1164.8 | 738.7  |
| 42.5° | 1637.1 | 996.9  | 608.1  | 305.5  | 239.2  | 279.6  | 583.1  | 973.9  | 1585.6 | 1009.3 | 588.0  |
| 45°   | 1458.8 | 856.9  | 360.0  | 167.6  | 154.8  | 162.1  | 332.1  | 841.1  | 1406.6 | 822.9  | 367.5  |
| 47.5° | 1155.5 | 653.5  | 231.3  | 142.5  | 156.3  | 142.5  | 224.2  | 632.7  | 1091.3 | 631.6  | 230.9  |
| 50°   | 874.9  | 510.1  | 179.1  | 144.2  | 169.8  | 144.2  | 173.5  | 492.7  | 830.1  | 538.3  | 177.2  |
| 52.5° | 648.1  | 426.3  | 146.3  | 158.1  | 204.1  | 161.0  | 142.1  | 415.0  | 615.2  | 434.3  | 138.4  |
| 55°   | 436.5  | 334.4  | 117.5  | 208.7  | 279.8  | 214.2  | 117.5  | 324.8  | 414.1  | 321.1  | 113.8  |
| 57.5° | 276.8  | 248.7  | 119.0  | 268.3  | 319.4  | 273.4  | 120.9  | 239.7  | 265.6  | 240.8  | 104.5  |
| 60°   | 205.2  | 196.1  | 132.4  | 284.9  | 343.2  | 288.5  | 134.3  | 188.7  | 201.5  | 186.9  | 111.9  |
| 62.5° | 169.4  | 154.4  | 159.3  | 308.5  | 356.7  | 300.5  | 162.7  | 147.3  | 176.1  | 141.1  | 123.9  |
| 65°   | 153.0  | 100.1  | 188.4  | 312.4  | 352.6  | 312.4  | 190.3  | 94.8   | 160.4  | 102.1  | 167.9  |
| 67.5° | 138.0  | 74.2   | 182.1  | 310.3  | 354.8  | 311.0  | 177.6  | 70.8   | 132.4  | 69.0   | 171.6  |
| 70°   | 115.7  | 66.4   | 171.6  | 315.8  | 341.4  | 304.9  | 171.6  | 64.5   | 110.1  | 62.6   | 201.5  |
| 72.5° | 96.3   | 63.1   | 159.7  | 291.6  | 302.6  | 280.7  | 161.2  | 62.7   | 96.6   | 56.5   | 189.5  |
| 75°   | 82.1   | 62.0   | 153.0  | 232.9  | 222.0  | 222.0  | 149.2  | 60.2   | 83.9   | 56.6   | 147.4  |
| 77.5° | 61.6   | 55.0   | 126.9  | 152.0  | 143.6  | 143.6  | 124.6  | 53.1   | 58.6   | 49.8   | 119.8  |
| 80°   | 46.6   | 50.3   | 104.5  | 111.8  | 106.3  | 106.3  | 100.7  | 48.5   | 46.6   | 46.6   | 98.9   |
| 82.5° | 36.2   | 42.8   | 80.6   | 82.0   | 78.0   | 76.5   | 78.3   | 42.4   | 36.2   | 39.1   | 76.5   |
| 85°   | 20.5   | 29.6   | 42.9   | 35.3   | 29.8   | 28.0   | 41.0   | 27.8   | 18.7   | 27.8   | 41.0   |
| 87.5° | 7.5    | 13.3   | 6.0    | 6.0    | 6.0    | 6.0    | 6.0    | 13.3   | 7.5    | 11.8   | 7.5    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



TEST NUMBER: P853782

CATALOG NUMBER: SQ2-FA-0U-100D-930-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

|       | 247.5° | 270°   | 292.5° | 315°   | 337.5° | 360°   |
|-------|--------|--------|--------|--------|--------|--------|
| 0°    | 2473.6 | 2473.6 | 2473.6 | 2473.6 | 2473.6 | 2473.6 |
| 2.5°  | 2454.4 | 2464.7 | 2464.7 | 2458.7 | 2487.9 | 2460.2 |
| 5°    | 2429.4 | 2453.1 | 2442.1 | 2441.9 | 2478.6 | 2451.2 |
| 7.5°  | 2411.8 | 2434.1 | 2423.8 | 2421.8 | 2457.8 | 2435.9 |
| 10°   | 2393.8 | 2410.2 | 2402.9 | 2408.3 | 2441.4 | 2419.5 |
| 12.5° | 2368.5 | 2387.8 | 2380.5 | 2388.9 | 2419.1 | 2401.6 |
| 15°   | 2324.7 | 2341.2 | 2344.8 | 2348.6 | 2383.7 | 2365.4 |
| 17.5° | 2252.5 | 2260.6 | 2278.8 | 2304.6 | 2341.1 | 2320.6 |
| 20°   | 2195.9 | 2206.8 | 2217.8 | 2262.8 | 2305.2 | 2283.3 |
| 22.5° | 2131.4 | 2127.8 | 2153.3 | 2206.1 | 2259.0 | 2240.1 |
| 25°   | 1957.4 | 1817.0 | 1972.0 | 2108.0 | 2178.7 | 2173.3 |
| 27.5° | 1362.9 | 1182.7 | 1342.1 | 1945.7 | 2094.4 | 2105.4 |
| 30°   | 1072.6 | 988.7  | 1070.8 | 1736.8 | 2032.1 | 2057.6 |
| 32.5° | 952.3  | 894.7  | 944.7  | 1321.9 | 1953.5 | 2002.4 |
| 35°   | 821.8  | 781.6  | 821.8  | 988.7  | 1799.0 | 1912.1 |
| 37.5° | 657.8  | 575.7  | 656.3  | 854.4  | 1454.3 | 1814.7 |
| 40°   | 490.1  | 386.2  | 475.5  | 764.8  | 1162.2 | 1738.6 |
| 42.5° | 326.6  | 248.9  | 309.0  | 602.2  | 1005.3 | 1637.1 |
| 45°   | 176.7  | 154.8  | 169.4  | 363.8  | 820.4  | 1458.8 |
| 47.5° | 138.6  | 146.6  | 138.6  | 229.5  | 627.6  | 1155.5 |
| 50°   | 133.0  | 158.6  | 133.0  | 177.2  | 519.2  | 874.9  |
| 52.5° | 145.0  | 172.0  | 143.5  | 139.9  | 423.7  | 648.1  |
| 55°   | 164.3  | 253.7  | 166.2  | 113.8  | 310.7  | 436.5  |
| 57.5° | 234.0  | 285.4  | 236.5  | 107.8  | 239.3  | 276.8  |
| 60°   | 240.3  | 307.8  | 238.5  | 113.8  | 185.1  | 205.2  |
| 62.5° | 284.3  | 380.9  | 283.9  | 130.2  | 137.6  | 169.4  |
| 65°   | 364.6  | 401.1  | 368.2  | 166.0  | 98.2   | 153.0  |
| 67.5° | 346.1  | 372.0  | 342.4  | 178.0  | 67.6   | 138.0  |
| 70°   | 340.0  | 360.0  | 336.3  | 203.3  | 62.8   | 115.7  |
| 72.5° | 317.2  | 319.7  | 310.6  | 188.4  | 56.5   | 96.3   |
| 75°   | 245.9  | 229.5  | 236.7  | 162.3  | 56.5   | 82.1   |
| 77.5° | 152.8  | 146.3  | 147.3  | 123.9  | 49.9   | 61.6   |
| 80°   | 115.6  | 111.9  | 110.1  | 104.5  | 46.6   | 46.6   |
| 82.5° | 85.7   | 82.1   | 80.3   | 80.6   | 39.1   | 36.2   |
| 85°   | 39.1   | 35.4   | 33.6   | 46.6   | 27.8   | 20.5   |
| 87.5° | 7.5    | 7.5    | 6.0    | 7.5    | 10.4   | 7.5    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



TEST NUMBER: P853782

CATALOG NUMBER: SQ2-FA-0U-100D-930-UNV-STD-W-4

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |       |       |       |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7   | 0.5   | 0.5   | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3   | 0.5   | 0.3   | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2   | 0.2   | 0.2   | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |       |       |       |       |
| X=2H            | Y=2H | 16.81            | 18.12 | 17.18 | 18.44 | 18.75 | 15.67          | 16.98 | 16.03 | 17.29 | 17.61 |
|                 | 3H   | 17.54            | 18.71 | 17.92 | 19.04 | 19.40 | 21.84          | 23.02 | 22.22 | 23.35 | 23.71 |
|                 | 4H   | 17.96            | 19.06 | 18.37 | 19.41 | 19.79 | 23.14          | 24.23 | 23.54 | 24.59 | 24.97 |
|                 | 6H   | 18.34            | 19.35 | 18.75 | 19.72 | 20.11 | 23.76          | 24.77 | 24.18 | 25.14 | 25.54 |
|                 | 8H   | 18.46            | 19.42 | 18.89 | 19.81 | 20.22 | 23.90          | 24.86 | 24.33 | 25.25 | 25.65 |
|                 | 12H  | 18.55            | 19.47 | 18.98 | 19.85 | 20.28 | 23.95          | 24.87 | 24.38 | 25.25 | 25.68 |
| 4H              | 2H   | 17.25            | 18.35 | 17.65 | 18.70 | 19.08 | 16.24          | 17.34 | 16.64 | 17.69 | 18.07 |
|                 | 3H   | 18.27            | 19.18 | 18.69 | 19.59 | 19.99 | 22.59          | 23.51 | 23.01 | 23.91 | 24.31 |
|                 | 4H   | 18.84            | 19.67 | 19.28 | 20.08 | 20.53 | 24.06          | 24.88 | 24.49 | 25.30 | 25.74 |
|                 | 6H   | 19.34            | 20.05 | 19.80 | 20.50 | 20.96 | 24.81          | 25.52 | 25.27 | 25.97 | 26.43 |
|                 | 8H   | 19.52            | 20.18 | 19.98 | 20.63 | 21.10 | 24.98          | 25.65 | 25.45 | 26.10 | 26.57 |
|                 | 12H  | 19.65            | 20.24 | 20.14 | 20.72 | 21.19 | 25.06          | 25.65 | 25.55 | 26.14 | 26.61 |
| 8H              | 4H   | 19.97            | 20.63 | 20.44 | 21.08 | 21.55 | 24.20          | 24.87 | 24.67 | 25.32 | 25.79 |
|                 | 6H   | 20.59            | 21.13 | 21.09 | 21.63 | 22.11 | 25.09          | 25.64 | 25.60 | 26.13 | 26.61 |
|                 | 8H   | 20.82            | 21.31 | 21.34 | 21.82 | 22.31 | 25.34          | 25.83 | 25.86 | 26.34 | 26.83 |
|                 | 12H  | 21.01            | 21.44 | 21.53 | 21.94 | 22.51 | 25.48          | 25.91 | 26.00 | 26.41 | 26.98 |
| 12H             | 4H   | 20.13            | 20.72 | 20.62 | 21.21 | 21.68 | 24.18          | 24.77 | 24.67 | 25.26 | 25.73 |
|                 | 6H   | 20.86            | 21.35 | 21.38 | 21.86 | 22.35 | 25.10          | 25.59 | 25.62 | 26.10 | 26.59 |
|                 | 8H   | 21.18            | 21.61 | 21.70 | 22.10 | 22.67 | 25.40          | 25.83 | 25.92 | 26.32 | 26.90 |