

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853875

Luminaire Tested: SQ2-FB-100U-075D-930-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853875
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-12, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FB-100U-075D-930-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6647.4 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 59.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853875
CATALOG NUMBER: SQ2-FB-100U-075D-930-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853875

CATALOG NUMBER: SQ2-FB-100U-075D-930-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	44	43	42	36
2	87	80	73	68	79	73	68	63	60	56	53	49	46	44	38	36	35	30
3	79	70	62	56	72	64	57	52	53	48	44	43	39	36	33	31	29	24
4	72	61	53	47	66	56	49	44	47	41	37	38	34	31	29	27	24	21
5	66	54	46	40	60	50	43	37	41	36	32	34	29	26	26	23	21	18
6	61	48	40	34	55	44	37	32	37	31	27	30	26	23	24	20	18	15
7	56	43	35	30	51	40	33	28	33	28	24	27	23	20	21	18	16	13
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	19	16	14	12
9	48	36	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4660	4660	4660
5°	4543	6297	8253
10°	4254	12193	16060
15°	3850	15863	18484
20°	3409	17450	19357
25°	3016	18661	19675
30°	2664	19220	19919
35°	2379	19553	21413
40°	2165	19739	22753
45°	1996	19833	23825
50°	1881	20213	24257
55°	1835	20738	24451
60°	1883	21012	24329
65°	1960	20726	23641
70°	2030	20044	17882
75°	2252	18004	9869
80°	2325	9289	9159
85°	2316	6428	3853

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 24671 cd/sqm



TEST NUMBER: P853875

CATALOG NUMBER: SQ2-FB-100U-075D-930-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	0.7
10°-20°	220.7	3.3
20°-30°	388.3	5.8
30°-40°	502.6	7.6
40°-50°	554.4	8.3
50°-60°	517.6	7.8
60°-70°	400.0	6.0
70°-80°	184.5	2.8
80°-90°	36.3	0.5
90°-100°	254.6	3.8
100°-110°	770.1	11.6
110°-120°	751.8	11.3
120°-130°	614.3	9.2
130°-140°	501.5	7.5
140°-150°	390.4	5.9
150°-160°	281.4	4.2
160°-170°	172.3	2.6
170°-180°	58.2	0.9
0°-30°	657.4	9.9
0°-40°	1160.0	17.5
0°-60°	2231.9	33.6
0°-90°	2852.8	42.9
90°-120°	1776.6	26.7
90°-150°	3282.7	49.4
90°-180°	3795.0	57.1
0°-180°	6647.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	289	289	289	289	289	
5°	280	321	388	474	509	26
15°	230	454	949	1062	1106	64
25°	169	610	1048	1094	1104	78
35°	121	589	992	1027	1086	76
45°	87	451	869	997	1043	68
55°	65	269	737	847	869	59
65°	51	152	542	608	619	50
75°	36	93	289	156	158	37
85°	12	27	35	24	21	13
90°	0	2	12	7	6	2
95°	32	100	480	178	112	37
105°	134	188	756	1436	1365	141
115°	238	284	612	1266	1486	236
125°	333	370	603	1000	1176	296
135°	399	441	599	862	970	309
145°	466	501	599	742	811	292
155°	531	549	603	665	690	244
165°	581	588	606	629	636	164
175°	608	608	609	614	612	58
180°	610	610	610	610	610	



TEST NUMBER: P853875

CATALOG NUMBER: SQ2-FB-100U-075D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	288.6	288.6	288.6	288.6	288.6
2.5°	286.4	298.3	311.9	327.6	334.1
5°	280.3	321.0	388.5	473.9	509.2
7.5°	269.4	352.2	565.0	793.6	864.1
10°	259.5	374.8	743.7	941.6	979.6
12.5°	248.4	404.9	855.8	994.9	1033.9
15°	230.3	454.2	949.0	1062.4	1105.8
17.5°	211.7	509.6	992.3	1104.1	1127.7
20°	198.4	548.4	1015.6	1111.7	1126.6
22.5°	186.2	577.5	1032.3	1105.1	1121.1
25°	169.3	610.2	1047.5	1093.6	1104.4
27.5°	152.9	618.8	1040.9	1071.1	1081.7
30°	142.9	616.4	1030.9	1053.4	1068.4
32.5°	134.0	609.7	1016.5	1038.3	1070.6
35°	120.7	588.7	992.0	1026.7	1086.4
37.5°	109.3	555.1	959.9	1030.8	1088.3
40°	102.7	530.0	936.5	1030.6	1079.5
42.5°	96.0	500.6	909.9	1019.5	1068.4
45°	87.4	451.0	868.6	997.3	1043.4
47.5°	79.4	395.2	830.3	966.4	1000.1
50°	74.9	357.1	804.7	938.5	965.7
52.5°	70.5	320.1	779.2	905.2	930.2
55°	65.2	268.7	736.7	846.8	868.6
57.5°	60.5	224.6	688.5	782.4	800.0
60°	58.3	200.7	650.7	735.8	753.4
62.5°	54.9	178.9	608.5	686.9	703.4
65°	51.3	151.7	542.5	608.0	618.8
67.5°	46.3	131.5	472.3	512.3	492.0
70°	43.0	121.7	424.6	437.1	378.8
72.5°	40.8	110.8	372.4	339.4	228.9
75°	36.1	93.1	288.6	155.5	158.2
77.5°	29.4	72.0	189.8	119.4	121.8
80°	25.0	58.9	99.9	97.2	98.5
82.5°	20.5	45.8	68.8	71.6	69.7
85°	12.5	27.4	34.7	23.5	20.8
87.5°	4.4	10.2	7.8	6.9	6.7
90°	0.0	1.9	11.5	6.7	5.7
92.5°	10.7	43.3	155.4	51.6	37.1
95°	31.6	99.9	480.5	177.5	112.0
97.5°	61.1	127.1	757.3	501.1	305.1
100°	79.4	144.0	846.1	818.0	549.4
102.5°	100.1	162.4	827.8	1147.3	914.7
105°	134.0	188.3	756.2	1436.0	1364.9
107.5°	166.2	218.0	687.2	1464.6	1547.0
110°	187.6	237.2	652.8	1428.6	1578.4



TEST NUMBER: P853875

CATALOG NUMBER: SQ2-FB-100U-075D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	208.3	256.4	632.1	1368.3	1557.7
115°	238.3	284.2	611.6	1265.6	1486.5
117.5°	268.2	311.6	604.4	1169.4	1395.5
120°	288.1	329.3	602.1	1113.3	1330.5
122.5°	306.5	345.4	602.1	1063.9	1264.6
125°	333.1	369.6	603.0	999.5	1176.3
127.5°	354.7	392.5	602.1	950.8	1101.7
130°	368.5	407.8	602.1	922.9	1059.6
132.5°	380.8	420.8	601.3	897.4	1023.6
135°	399.1	441.3	599.2	862.0	969.6
137.5°	419.6	459.7	599.2	824.1	923.8
140°	432.6	471.9	599.2	799.5	894.0
142.5°	445.7	483.5	598.4	777.0	859.5
145°	466.1	500.8	599.2	741.5	810.7
147.5°	486.6	516.0	600.3	712.2	765.3
150°	499.6	526.8	601.1	695.9	740.8
152.5°	511.9	536.0	601.9	681.9	718.6
155°	531.2	549.0	603.0	664.8	690.1
157.5°	548.1	562.5	604.2	652.2	669.8
160°	558.0	570.2	604.9	644.5	657.6
162.5°	568.0	577.1	605.7	637.5	648.4
165°	581.0	587.5	605.9	629.0	636.5
167.5°	592.1	595.5	607.0	622.4	625.6
170°	598.2	600.1	607.8	619.3	620.2
172.5°	602.1	603.2	607.8	616.2	616.4
175°	607.8	607.8	608.8	613.5	611.6
177.5°	610.5	609.7	608.9	611.2	609.7
180°	609.7	609.7	609.7	609.7	609.7

TEST NUMBER: P853875

CATALOG NUMBER: SQ2-FB-100U-075D-930-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.72	12.55	12.73	13.57	14.94	20.46	21.28	21.47	22.31	23.67
	3H	12.45	13.19	13.47	14.22	15.61	22.08	22.82	23.10	23.85	25.24
	4H	12.75	13.45	13.78	14.48	15.88	22.26	22.96	23.29	23.99	25.39
	6H	12.96	13.61	14.01	14.65	16.05	22.34	22.99	23.39	24.02	25.43
	8H	13.02	13.63	14.07	14.69	16.09	22.35	22.96	23.39	24.01	25.42
	12H	13.05	13.63	14.10	14.68	16.11	22.32	22.90	23.37	23.95	25.37
4H	2H	16.12	16.82	17.16	17.85	19.25	20.90	21.60	21.94	22.63	24.03
	3H	17.05	17.63	18.10	18.69	20.10	22.72	23.30	23.77	24.37	25.77
	4H	17.33	17.86	18.38	18.92	20.35	22.96	23.49	24.01	24.54	25.97
	6H	17.46	17.92	18.52	18.99	20.42	23.10	23.56	24.17	24.64	26.06
	8H	17.48	17.91	18.54	18.98	20.42	23.12	23.55	24.19	24.62	26.06
	12H	17.47	17.85	18.55	18.94	20.39	23.10	23.48	24.18	24.57	26.01
8H	4H	18.50	18.93	19.57	20.00	21.44	23.07	23.50	24.14	24.57	26.01
	6H	18.74	19.09	19.83	20.20	21.64	23.27	23.63	24.36	24.74	26.18
	8H	18.81	19.12	19.90	20.21	21.67	23.34	23.64	24.43	24.74	26.20
	12H	18.83	19.10	19.93	20.19	21.69	23.33	23.60	24.43	24.69	26.19
12H	4H	18.52	18.90	19.60	19.99	21.43	23.02	23.41	24.11	24.49	25.94
	6H	18.83	19.14	19.93	20.23	21.69	23.26	23.57	24.35	24.66	26.12
	8H	18.93	19.20	20.03	20.29	21.79	23.32	23.59	24.42	24.69	26.18