

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853887

Luminaire Tested: SQ2-FB-125U-075D-930-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P853887  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-FB-125U-075D-930-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7654.5 lumens  
Efficiency: N/A  
Efficacy: 108.4 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 70.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P853887

CATALOG NUMBER: SQ2-FB-125U-075D-930-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P853887

CATALOG NUMBER: SQ2-FB-125U-075D-930-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37
1	95	91	87	83	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	86	79	73	67	78	71	66	62	58	54	51	46	43	41	34	32	31	26
3	78	69	61	56	71	63	56	51	51	46	42	40	37	34	30	28	26	21
4	71	61	53	47	64	55	48	43	45	40	36	35	32	29	26	24	22	18
5	65	54	45	39	59	49	42	36	40	34	30	31	28	25	23	21	19	15
6	60	48	40	34	54	44	36	31	36	30	26	28	24	21	21	18	16	13
7	55	43	35	29	50	39	32	27	32	27	23	25	21	18	19	16	14	11
8	51	39	31	26	46	35	28	24	29	24	20	23	19	16	17	15	13	10
9	47	35	28	23	43	32	25	21	26	21	18	21	17	14	16	13	11	9
10	44	32	25	20	40	29	23	19	24	19	16	19	15	13	15	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4660	4660	4660
5°	4543	6297	8253
10°	4254	12193	16060
15°	3850	15863	18484
20°	3409	17450	19357
25°	3016	18661	19675
30°	2664	19220	19919
35°	2379	19553	21413
40°	2165	19739	22753
45°	1996	19833	23825
50°	1881	20213	24257
55°	1835	20738	24451
60°	1883	21012	24329
65°	1960	20726	23641
70°	2030	20044	17882
75°	2252	18004	9869
80°	2325	9289	9159
85°	2316	6428	3853

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 24671 cd/sqm



TEST NUMBER: P853887

CATALOG NUMBER: SQ2-FB-125U-075D-930-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.4	0.6
10°-20°	220.7	2.9
20°-30°	388.3	5.1
30°-40°	502.6	6.6
40°-50°	554.4	7.2
50°-60°	517.6	6.8
60°-70°	400.0	5.2
70°-80°	184.5	2.4
80°-90°	36.1	0.5
90°-100°	297.7	3.9
100°-110°	969.3	12.7
110°-120°	958.8	12.5
120°-130°	783.5	10.2
130°-140°	640.4	8.4
140°-150°	498.8	6.5
150°-160°	359.5	4.7
160°-170°	219.7	2.9
170°-180°	74.1	1.0
0°-30°	657.4	8.6
0°-40°	1160.0	15.2
0°-60°	2231.9	29.2
0°-90°	2852.6	37.3
90°-120°	2225.8	29.1
90°-150°	4148.5	54.2
90°-180°	4802.0	62.7
0°-180°	7654.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	289	289	289	289	289	
5°	280	321	388	474	509	26
15°	230	454	949	1062	1106	64
25°	169	610	1048	1094	1104	78
35°	121	589	992	1027	1086	76
45°	87	451	869	997	1043	68
55°	65	269	737	847	869	59
65°	51	152	542	608	619	50
75°	36	93	289	156	158	37
85°	12	27	35	24	21	13
90°	0	3	7	6	6	2
95°	40	123	546	194	120	47
105°	165	238	960	1834	1737	176
115°	304	363	782	1612	1896	301
125°	423	472	772	1273	1500	377
135°	511	565	768	1098	1239	395
145°	597	641	766	946	1036	374
155°	682	704	771	847	879	314
165°	744	750	772	802	811	209
175°	775	775	775	781	779	74
180°	778	778	778	778	778	

TEST NUMBER: P853887

CATALOG NUMBER: SQ2-FB-125U-075D-930-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	288.6	288.6	288.6	288.6	288.6
2.5°	286.4	298.3	311.9	327.6	334.1
5°	280.3	321.0	388.5	473.9	509.2
7.5°	269.4	352.2	565.0	793.6	864.1
10°	259.5	374.8	743.7	941.6	979.6
12.5°	248.4	404.9	855.8	994.9	1033.9
15°	230.3	454.2	949.0	1062.4	1105.8
17.5°	211.7	509.6	992.3	1104.1	1127.7
20°	198.4	548.4	1015.6	1111.7	1126.6
22.5°	186.2	577.5	1032.3	1105.1	1121.1
25°	169.3	610.2	1047.5	1093.6	1104.4
27.5°	152.9	618.8	1040.9	1071.1	1081.7
30°	142.9	616.4	1030.9	1053.4	1068.4
32.5°	134.0	609.7	1016.5	1038.3	1070.6
35°	120.7	588.7	992.0	1026.7	1086.4
37.5°	109.3	555.1	959.9	1030.8	1088.3
40°	102.7	530.0	936.5	1030.6	1079.5
42.5°	96.0	500.6	909.9	1019.5	1068.4
45°	87.4	451.0	868.6	997.3	1043.4
47.5°	79.4	395.2	830.3	966.4	1000.1
50°	74.9	357.1	804.7	938.5	965.7
52.5°	70.5	320.1	779.2	905.2	930.2
55°	65.2	268.7	736.7	846.8	868.6
57.5°	60.5	224.6	688.5	782.4	800.0
60°	58.3	200.7	650.7	735.8	753.4
62.5°	54.9	178.9	608.5	686.9	703.4
65°	51.3	151.7	542.5	608.0	618.8
67.5°	46.3	131.5	472.3	512.3	492.0
70°	43.0	121.7	424.6	437.1	378.8
72.5°	40.8	110.8	372.4	339.4	228.9
75°	36.1	93.1	288.6	155.5	158.2
77.5°	29.4	72.0	189.8	119.4	121.8
80°	25.0	58.9	99.9	97.2	98.5
82.5°	20.5	45.8	68.8	71.6	69.7
85°	12.5	27.4	34.7	23.5	20.8
87.5°	4.4	10.4	6.9	6.7	6.7
90°	0.0	2.8	6.7	5.7	5.7
92.5°	13.8	49.5	158.3	52.2	40.2
95°	40.2	122.6	545.7	194.5	119.7
97.5°	75.6	159.5	926.1	564.0	344.2
100°	98.6	181.0	1069.3	953.5	618.4
102.5°	124.6	204.0	1051.7	1410.7	1072.6
105°	164.7	237.7	960.2	1833.9	1736.6
107.5°	207.9	276.6	873.3	1870.6	1973.8
110°	239.3	302.0	831.9	1825.0	2011.3



TEST NUMBER: P853887

CATALOG NUMBER: SQ2-FB-125U-075D-930-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	265.4	327.3	805.9	1742.8	1983.0
115°	304.4	363.4	782.1	1611.9	1896.4
117.5°	344.6	397.8	772.9	1492.0	1775.2
120°	367.6	420.0	770.6	1418.3	1692.5
122.5°	389.8	441.5	771.4	1354.3	1609.8
125°	423.1	471.8	771.6	1272.6	1500.1
127.5°	451.7	501.5	771.4	1211.5	1401.1
130°	470.0	520.6	770.6	1176.5	1346.0
132.5°	486.1	538.9	769.9	1144.1	1303.1
135°	511.2	564.6	767.8	1098.3	1238.8
137.5°	535.7	589.4	765.7	1051.8	1176.5
140°	553.3	604.8	764.9	1020.3	1138.2
142.5°	570.2	619.4	764.9	990.1	1095.3
145°	597.4	641.4	765.8	945.9	1035.8
147.5°	623.8	662.0	767.2	908.3	977.8
150°	641.4	675.1	768.7	885.9	944.9
152.5°	659.0	686.7	769.5	868.8	915.8
155°	681.6	704.1	770.6	847.0	878.8
157.5°	703.0	719.1	771.8	830.9	853.1
160°	716.1	729.2	772.5	820.8	838.6
162.5°	727.6	737.7	772.5	812.3	825.6
165°	743.8	750.4	772.5	801.5	810.8
167.5°	755.3	759.4	772.7	793.3	798.2
170°	763.0	764.8	773.5	787.9	789.8
172.5°	768.3	769.5	775.0	784.8	784.4
175°	775.4	775.4	775.4	781.1	779.2
177.5°	778.3	777.5	776.8	780.5	777.5
180°	778.3	778.3	778.3	778.3	778.3



TEST NUMBER: P853887

CATALOG NUMBER: SQ2-FB-125U-075D-930-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.11	11.89	12.17	12.95	14.39	19.85	20.63	20.91	21.69	23.13
	3H	11.84	12.53	12.90	13.60	15.06	21.47	22.16	22.53	23.23	24.69
	4H	12.13	12.79	13.21	13.87	15.33	21.64	22.30	22.72	23.37	24.84
	6H	12.35	12.95	13.43	14.03	15.51	21.72	22.33	22.81	23.41	24.88
	8H	12.40	12.98	13.49	14.07	15.54	21.73	22.30	22.82	23.40	24.87
	12H	12.43	12.98	13.52	14.06	15.56	21.69	22.24	22.79	23.33	24.82
4H	2H	15.50	16.16	16.59	17.23	18.70	20.28	20.94	21.37	22.01	23.48
	3H	16.43	16.98	17.52	18.08	19.55	22.10	22.65	23.19	23.75	25.23
	4H	16.71	17.21	17.80	18.30	19.80	22.33	22.84	23.43	23.93	25.43
	6H	16.83	17.27	17.94	18.38	19.87	22.48	22.91	23.58	24.02	25.51
	8H	16.85	17.26	17.96	18.36	19.87	22.50	22.90	23.60	24.01	25.51
	12H	16.84	17.20	17.96	18.32	19.84	22.47	22.83	23.59	23.95	25.46
8H	4H	17.87	18.28	18.98	19.38	20.89	22.44	22.85	23.55	23.95	25.46
	6H	18.11	18.44	19.23	19.59	21.09	22.65	22.98	23.77	24.13	25.63
	8H	18.18	18.47	19.31	19.60	21.12	22.71	23.00	23.84	24.13	25.65
	12H	18.20	18.46	19.34	19.58	21.14	22.70	22.95	23.83	24.08	25.64
12H	4H	17.89	18.25	19.01	19.37	20.88	22.39	22.76	23.51	23.88	25.39
	6H	18.20	18.49	19.33	19.62	21.15	22.63	22.92	23.76	24.05	25.57
	8H	18.30	18.56	19.44	19.68	21.24	22.69	22.95	23.83	24.07	25.63