

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854052

Luminaire Tested: SQ2-PH1-125U-050D-930-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P854052  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PH1-125U-050D-930-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7060.7 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 61.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P854052

CATALOG NUMBER: SQ2-PH1-125U-050D-930-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P854052

CATALOG NUMBER: SQ2-PH1-125U-050D-930-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	46	35	34	33	27
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	26	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21	17
5	65	54	46	41	59	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16	13
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16322	16322	16322
5°	16415	15433	14917
10°	16038	14050	13562
15°	16109	13215	13295
20°	15534	12807	13402
25°	15250	12748	13090
30°	14919	12713	13198
35°	14806	12569	15469
40°	14819	12488	12265
45°	14824	12013	10563
50°	14616	12248	9904
55°	14429	13292	9503
60°	14286	11648	8913
65°	14036	9444	7752
70°	13256	8035	5537
75°	11822	6057	4198
80°	9661	3933	3933
85°	6058	3557	2668

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14824 cd/sqm



TEST NUMBER: P854052

CATALOG NUMBER: SQ2-PH1-125U-050D-930-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.9	1.3
10°-20°	234.0	3.3
20°-30°	343.1	4.9
30°-40°	415.5	5.9
40°-50°	408.5	5.8
50°-60°	355.6	5.0
60°-70°	247.2	3.5
70°-80°	117.2	1.7
80°-90°	26.7	0.4
90°-100°	299.1	4.2
100°-110°	973.7	13.8
110°-120°	963.2	13.6
120°-130°	787.1	11.1
130°-140°	643.3	9.1
140°-150°	501.1	7.1
150°-160°	361.2	5.1
160°-170°	220.8	3.1
170°-180°	74.5	1.1
0°-30°	666.0	9.4
0°-40°	1081.4	15.3
0°-60°	1845.6	26.1
0°-90°	2236.8	31.7
90°-120°	2236.0	31.7
90°-150°	4167.5	59.0
90°-180°	4824.0	68.3
0°-180°	7060.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1011	1011	1011	1011	1011	
5°	1013	1012	952	922	920	95
15°	964	858	791	785	795	269
25°	856	728	716	738	735	394
35°	751	607	638	693	785	471
45°	649	481	526	544	463	499
55°	513	374	472	340	338	458
65°	367	257	247	203	203	361
75°	190	131	97	69	67	201
85°	33	21	19	15	14	44
90°	0	3	7	6	6	3
95°	40	123	548	195	120	47
105°	165	239	965	1842	1744	176
115°	306	365	786	1619	1905	303
125°	425	474	775	1278	1507	378
135°	514	567	771	1103	1244	397
145°	600	644	769	950	1040	376
155°	685	707	774	851	883	315
165°	747	754	776	805	814	210
175°	779	779	779	785	783	74
180°	782	782	782	782	782	



TEST NUMBER: P854052

CATALOG NUMBER: SQ2-PH1-125U-050D-930-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1010.9	1010.9	1010.9	1010.9	1010.9
2.5°	1008.5	1019.1	995.5	986.2	984.7
5°	1012.8	1011.8	952.2	922.3	920.4
7.5°	994.3	965.2	893.9	861.0	859.5
10°	978.2	934.0	857.0	827.2	827.2
12.5°	974.3	904.5	827.0	804.9	809.5
15°	963.7	858.4	790.6	785.1	795.4
17.5°	928.7	815.3	762.3	774.9	786.9
20°	904.1	792.2	745.4	768.7	780.0
22.5°	883.3	769.9	733.1	758.6	764.6
25°	856.0	728.1	715.6	737.6	734.8
27.5°	823.3	689.8	698.1	711.6	713.3
30°	800.2	666.7	681.9	695.7	707.9
32.5°	777.9	639.9	664.2	696.8	724.8
35°	751.2	607.3	637.7	692.7	784.8
37.5°	723.1	568.9	610.9	657.2	686.5
40°	703.1	541.3	592.5	649.6	581.9
42.5°	681.5	519.8	564.8	638.5	524.2
45°	649.2	480.9	526.1	544.4	462.6
47.5°	611.1	450.7	499.9	454.0	422.0
50°	581.9	430.5	487.6	415.0	394.3
52.5°	553.4	409.5	479.2	382.9	368.9
55°	512.6	374.4	472.2	340.4	337.6
57.5°	469.4	338.6	417.6	303.5	308.4
60°	442.4	315.5	360.7	281.7	276.0
62.5°	414.0	293.0	307.6	254.0	248.3
65°	367.4	257.4	247.2	202.9	202.9
67.5°	316.2	220.3	200.2	166.1	143.5
70°	280.8	196.2	170.2	132.4	117.3
72.5°	243.1	170.5	139.5	108.5	91.2
75°	189.5	131.2	97.1	69.2	67.3
77.5°	137.0	94.5	65.4	51.4	51.6
80°	103.9	71.9	42.3	41.4	42.3
82.5°	73.1	49.4	31.5	32.9	33.1
85°	32.7	21.4	19.2	15.4	14.4
87.5°	6.9	6.7	5.2	5.0	5.0
90°	0.0	2.8	6.7	5.8	5.8
92.5°	13.8	49.8	159.1	52.4	40.4
95°	40.4	123.1	548.2	195.4	120.2
97.5°	76.0	160.2	930.3	566.6	345.8
100°	99.1	181.8	1074.2	957.9	621.3
102.5°	125.2	205.0	1056.5	1417.1	1077.5
105°	165.4	238.8	964.6	1842.3	1744.5
107.5°	208.9	277.9	877.3	1879.2	1982.8
110°	240.4	303.4	835.7	1833.4	2020.5



TEST NUMBER: P854052

CATALOG NUMBER: SQ2-PH1-125U-050D-930-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	266.6	328.8	809.5	1750.8	1992.0
115°	305.8	365.1	785.7	1619.2	1905.1
117.5°	346.2	399.6	776.5	1498.8	1783.4
120°	369.3	421.9	774.2	1424.8	1700.3
122.5°	391.6	443.5	774.9	1360.5	1617.2
125°	425.1	474.0	775.1	1278.5	1507.0
127.5°	453.7	503.7	774.9	1217.0	1407.5
130°	472.2	523.0	774.2	1181.9	1352.1
132.5°	488.3	541.4	773.4	1149.4	1309.0
135°	513.5	567.1	771.3	1103.4	1244.4
137.5°	538.2	592.1	769.2	1056.7	1181.9
140°	555.9	607.6	768.4	1025.0	1143.4
142.5°	572.8	622.2	768.4	994.7	1100.4
145°	600.1	644.3	769.4	950.3	1040.5
147.5°	626.6	665.0	770.7	912.5	982.3
150°	644.3	678.2	772.2	889.9	949.2
152.5°	662.0	689.9	773.0	872.7	920.0
155°	684.7	707.3	774.2	850.9	882.8
157.5°	706.3	722.4	775.3	834.7	857.1
160°	719.3	732.5	776.1	824.6	842.4
162.5°	730.9	741.0	776.1	816.0	829.4
165°	747.2	753.8	776.1	805.1	814.5
167.5°	758.8	762.9	776.3	797.0	801.9
170°	766.5	768.3	777.0	791.5	793.4
172.5°	771.9	773.0	778.6	788.4	788.0
175°	779.0	779.0	779.0	784.7	782.8
177.5°	781.9	781.1	780.3	784.1	781.1
180°	781.9	781.9	781.9	781.9	781.9

-----



TEST NUMBER: P854052

CATALOG NUMBER: SQ2-PH1-125U-050D-930-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.04	15.75	16.14	16.85	18.36	13.71	14.43	14.81	15.52	17.03
	3H	17.05	17.69	18.16	18.80	20.32	14.73	15.37	15.84	16.48	18.01
	4H	17.78	18.38	18.90	19.49	21.02	14.94	15.55	16.06	16.65	18.19
	6H	18.25	18.81	19.38	19.92	21.47	15.08	15.63	16.21	16.74	18.29
	8H	18.37	18.90	19.51	20.03	21.57	15.10	15.63	16.24	16.76	18.30
	12H	18.41	18.92	19.55	20.03	21.60	15.10	15.60	16.23	16.72	18.28
4H	2H	15.40	16.00	16.52	17.11	18.64	14.33	14.94	15.46	16.05	17.58
	3H	17.49	17.99	18.62	19.12	20.67	15.50	16.00	16.63	17.14	18.68
	4H	18.30	18.76	19.43	19.88	21.45	15.77	16.23	16.91	17.35	18.92
	6H	18.87	19.27	20.02	20.41	21.97	15.97	16.36	17.11	17.51	19.07
	8H	19.04	19.41	20.18	20.55	22.12	16.02	16.39	17.16	17.53	19.10
	12H	19.10	19.43	20.26	20.58	22.16	16.02	16.36	17.18	17.51	19.08
8H	4H	18.30	18.67	19.44	19.81	21.38	15.97	16.34	17.12	17.48	19.05
	6H	18.95	19.25	20.11	20.43	22.00	16.24	16.54	17.40	17.72	19.29
	8H	19.17	19.44	20.34	20.60	22.19	16.34	16.61	17.51	17.76	19.36
	12H	19.28	19.51	20.45	20.67	22.29	16.38	16.61	17.55	17.77	19.39
12H	4H	18.25	18.58	19.41	19.73	21.31	15.96	16.30	17.12	17.45	19.02
	6H	18.92	19.19	20.09	20.34	21.94	16.27	16.53	17.44	17.69	19.28
	8H	19.15	19.38	20.32	20.53	22.16	16.38	16.61	17.55	17.76	19.39