

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853905

Luminaire Tested: SQ2-FB-150U-125D-930-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P853905  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-14, G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-FB-150U-125D-930-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10444.7 lumens  
Efficiency: N/A  
Efficacy: 98.7 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 105.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P853905

CATALOG NUMBER: SQ2-FB-150U-125D-930-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P853905

CATALOG NUMBER: SQ2-FB-150U-125D-930-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	97	92	88	85	89	85	81	78	71	68	66	58	56	55	46	45	44	38
2	88	80	74	69	80	74	68	64	62	58	54	50	48	45	40	38	36	31
3	80	70	63	57	73	64	58	53	54	49	45	44	41	38	35	32	30	26
4	73	62	54	47	66	57	50	44	47	42	38	39	35	32	31	28	26	22
5	66	55	46	40	61	50	43	38	42	37	32	35	30	27	28	24	22	19
6	61	49	40	34	56	45	38	32	38	32	28	31	27	23	25	22	19	16
7	56	44	36	30	51	40	33	28	34	28	24	28	24	20	22	19	17	14
8	52	39	32	26	47	36	29	24	31	25	21	25	21	18	20	17	15	12
9	48	36	28	23	44	33	26	22	28	23	19	23	19	16	19	15	13	11
10	45	33	25	20	41	30	24	19	26	20	17	21	17	14	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7800	7800	7800
5°	7605	10541	13817
10°	7122	20412	26886
15°	6445	26557	30945
20°	5708	29215	32407
25°	5049	31242	32938
30°	4460	32175	33346
35°	3983	32735	35847
40°	3623	33046	38088
45°	3341	33202	39884
50°	3150	33840	40609
55°	3074	34719	40932
60°	3152	35179	40729
65°	3282	34697	39580
70°	3399	33555	29934
75°	3768	30137	16519
80°	3887	15546	15332
85°	3872	10763	6447

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 41301 cd/sqm



TEST NUMBER: P853905

CATALOG NUMBER: SQ2-FB-150U-125D-930-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.9	0.8
10°-20°	369.5	3.5
20°-30°	650.1	6.2
30°-40°	841.5	8.1
40°-50°	928.1	8.9
50°-60°	866.5	8.3
60°-70°	669.7	6.4
70°-80°	308.9	3.0
80°-90°	60.0	0.6
90°-100°	350.0	3.4
100°-110°	1146.0	11.0
110°-120°	1133.0	10.8
120°-130°	926.2	8.9
130°-140°	755.8	7.2
140°-150°	588.2	5.6
150°-160°	423.5	4.1
160°-170°	259.1	2.5
170°-180°	87.5	0.8
0°-30°	1100.5	10.5
0°-40°	1942.0	18.6
0°-60°	3736.5	35.8
0°-90°	4775.1	45.7
90°-120°	2629.1	25.2
90°-150°	4899.3	46.9
90°-180°	5670.0	54.3
0°-180°	10444.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	483	483	483	483	483	
5°	469	537	650	793	852	44
15°	386	760	1589	1779	1851	107
25°	283	1022	1754	1831	1849	130
35°	202	986	1661	1719	1819	127
45°	146	755	1454	1670	1747	113
55°	109	450	1233	1418	1454	98
65°	86	254	908	1018	1036	84
75°	60	156	483	260	265	62
85°	21	46	58	39	35	22
90°	1	3	8	7	8	3
95°	49	142	636	227	147	56
105°	199	284	1138	2161	2053	210
115°	359	429	924	1910	2242	354
125°	499	557	911	1506	1769	444
135°	601	665	904	1299	1464	465
145°	703	755	902	1117	1224	441
155°	802	828	907	1000	1038	369
165°	875	883	911	946	956	247
175°	915	915	916	922	920	87
180°	919	919	919	919	919	



TEST NUMBER: P853905

CATALOG NUMBER: SQ2-FB-150U-125D-930-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	483.1	483.1	483.1	483.1	483.1
2.5°	479.4	499.4	522.2	548.4	559.3
5°	469.2	537.3	650.4	793.4	852.5
7.5°	451.1	589.6	945.8	1328.5	1446.6
10°	434.4	627.4	1245.0	1576.3	1639.9
12.5°	415.8	677.9	1432.7	1665.5	1730.9
15°	385.6	760.3	1588.8	1778.6	1851.3
17.5°	354.5	853.2	1661.3	1848.4	1888.0
20°	332.2	918.1	1700.3	1861.1	1886.1
22.5°	311.7	966.7	1728.2	1850.0	1876.8
25°	283.4	1021.5	1753.7	1830.8	1848.9
27.5°	256.0	1035.9	1742.6	1793.1	1810.9
30°	239.2	1031.9	1725.8	1763.6	1788.6
32.5°	224.4	1020.7	1701.7	1738.2	1792.3
35°	202.1	985.6	1660.8	1718.8	1818.7
37.5°	183.0	929.3	1606.9	1725.7	1822.0
40°	171.9	887.3	1567.9	1725.4	1807.1
42.5°	160.7	838.0	1523.3	1706.8	1788.6
45°	146.3	755.0	1454.1	1669.5	1746.7
47.5°	132.9	661.6	1390.0	1617.9	1674.3
50°	125.4	597.8	1347.2	1571.2	1616.7
52.5°	118.0	535.9	1304.5	1515.4	1557.2
55°	109.2	449.8	1233.4	1417.7	1454.1
57.5°	101.3	376.1	1152.6	1309.8	1339.3
60°	97.6	336.0	1089.4	1231.8	1261.3
62.5°	92.0	299.6	1018.8	1149.9	1177.7
65°	85.9	254.0	908.2	1017.8	1036.0
67.5°	77.6	220.2	790.7	857.7	823.7
70°	72.0	203.7	710.8	731.8	634.1
72.5°	68.3	185.5	623.4	568.1	383.3
75°	60.4	155.8	483.1	260.3	264.8
77.5°	49.2	120.6	317.8	199.9	203.9
80°	41.8	98.6	167.2	162.6	164.9
82.5°	34.4	76.6	115.2	119.8	116.6
85°	20.9	45.9	58.1	39.4	34.8
87.5°	7.6	17.1	10.8	10.6	10.8
90°	0.9	2.8	7.6	6.6	7.6
92.5°	16.0	58.5	179.7	58.5	46.8
95°	49.1	142.3	636.3	226.7	147.3
97.5°	89.1	187.7	1091.7	660.4	409.3
100°	117.1	211.2	1263.1	1128.0	747.7
102.5°	148.8	240.7	1244.3	1662.1	1288.4
105°	199.2	284.1	1137.6	2161.3	2053.3
107.5°	248.9	326.8	1033.5	2208.0	2326.7
110°	281.3	357.0	983.7	2153.7	2374.3



TEST NUMBER: P853905

CATALOG NUMBER: SQ2-FB-150U-125D-930-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	312.3	385.8	953.5	2059.2	2341.8
115°	358.7	428.9	924.2	1909.8	2242.1
117.5°	403.9	469.4	913.1	1763.0	2100.5
120°	433.3	495.2	910.1	1677.5	2006.1
122.5°	459.8	520.1	910.1	1603.7	1908.7
125°	499.4	556.6	911.0	1506.1	1769.2
127.5°	533.0	591.4	909.9	1434.1	1663.0
130°	554.2	613.2	909.1	1390.6	1597.3
132.5°	573.0	633.6	906.9	1353.1	1540.7
135°	601.4	665.1	903.5	1299.0	1464.2
137.5°	631.2	694.3	901.4	1242.6	1391.9
140°	652.3	713.3	900.6	1206.9	1348.1
142.5°	673.5	730.7	900.6	1168.8	1296.8
145°	703.3	755.0	901.6	1117.4	1224.4
147.5°	734.7	777.7	902.9	1072.6	1153.4
150°	754.3	792.1	904.4	1046.6	1114.9
152.5°	773.9	807.3	905.2	1025.2	1081.7
155°	801.5	828.3	907.2	999.7	1038.5
157.5°	826.2	845.6	909.3	979.6	1007.7
160°	842.1	857.8	910.1	968.2	990.3
162.5°	855.7	868.4	910.1	959.0	975.2
165°	875.1	883.4	911.0	946.2	956.3
167.5°	891.6	895.6	912.1	936.2	941.8
170°	900.6	902.5	912.9	930.9	932.7
172.5°	907.4	908.5	915.2	927.1	927.4
175°	914.8	914.8	915.7	922.3	920.5
177.5°	918.6	917.8	917.1	921.5	918.6
180°	918.6	918.6	918.6	918.6	918.6

-----



TEST NUMBER: P853905

CATALOG NUMBER: SQ2-FB-150U-125D-930-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.79	14.64	14.78	15.65	16.97	22.53	23.38	23.52	24.38	25.71
	3H	14.52	15.28	15.52	16.30	17.65	24.15	24.91	25.15	25.93	27.28
	4H	14.82	15.54	15.84	16.56	17.92	24.33	25.05	25.34	26.07	27.43
	6H	15.04	15.70	16.06	16.72	18.09	24.42	25.08	25.44	26.10	27.47
	8H	15.10	15.73	16.13	16.77	18.13	24.42	25.05	25.45	26.09	27.46
	12H	15.12	15.72	16.16	16.76	18.15	24.39	24.99	25.43	26.02	27.42
4H	2H	18.19	18.91	19.21	19.93	21.29	22.97	23.69	23.99	24.71	26.07
	3H	19.12	19.72	20.15	20.77	22.14	24.80	25.40	25.82	26.44	27.81
	4H	19.41	19.95	20.44	20.99	22.39	25.03	25.58	26.07	26.62	28.01
	6H	19.54	20.01	20.58	21.07	22.46	25.18	25.65	26.22	26.71	28.10
	8H	19.56	20.00	20.60	21.05	22.46	25.20	25.64	26.25	26.70	28.10
	12H	19.55	19.95	20.61	21.01	22.42	25.18	25.57	26.24	26.64	28.05
8H	4H	20.58	21.02	21.63	22.07	23.48	25.15	25.59	26.20	26.64	28.05
	6H	20.82	21.18	21.89	22.27	23.68	25.36	25.72	26.43	26.81	28.22
	8H	20.89	21.21	21.97	22.28	23.71	25.42	25.74	26.50	26.81	28.24
	12H	20.91	21.19	22.00	22.27	23.73	25.41	25.69	26.49	26.76	28.23
12H	4H	20.60	20.99	21.66	22.06	23.47	25.10	25.50	26.17	26.57	27.98
	6H	20.91	21.23	21.99	22.31	23.73	25.34	25.66	26.42	26.74	28.16
	8H	21.01	21.29	22.10	22.37	23.83	25.41	25.69	26.49	26.76	28.22