

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854082

Luminaire Tested: SQ2-PP3-025U-100D-930-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854082
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PP3-025U-100D-930-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5409.4 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854082

CATALOG NUMBER: SQ2-PP3-025U-100D-930-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854082

CATALOG NUMBER: SQ2-PP3-025U-100D-930-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20				20			20
RC	80				70				50			30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	115	115	115	115	110	110	110	110	101	101	101	93	93	93	86	86	86		82
1	106	102	98	95	101	98	94	91	90	88	85	84	81	80	77	76	74		71
2	97	90	84	79	93	86	81	76	80	76	72	74	71	68	69	66	64		61
3	89	80	72	67	85	77	70	65	71	66	62	66	62	58	62	58	55		52
4	82	71	63	57	78	69	61	56	64	58	53	60	55	51	56	51	48		45
5	76	64	56	50	72	62	54	48	58	51	46	54	48	44	50	46	42		40
6	70	58	49	43	67	56	48	43	52	46	41	49	43	39	46	41	37		35
7	65	52	44	38	62	51	43	38	48	41	36	45	39	35	42	37	33		31
8	60	48	40	34	58	46	39	34	44	37	32	41	35	31	39	34	30		28
9	56	44	36	31	54	43	35	30	40	34	29	38	32	28	36	31	27		25
10	53	40	33	28	51	39	32	27	37	31	27	35	30	26	33	28	25		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	28493	28493	28493
5°	28269	28511	28783
10°	28412	28627	28994
15°	28344	28625	29061
20°	28142	28816	29649
25°	27982	29179	31206
30°	27824	29770	31858
35°	27429	29857	31915
40°	26698	29803	29489
45°	25898	28453	22448
50°	24882	24272	18696
55°	23159	20428	13444
60°	19940	17531	9639
65°	16821	13540	9478
70°	14002	10655	9069
75°	11871	9195	8497
80°	10060	7978	7634
85°	7947	6558	4150

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 28453 cd/sqm



TEST NUMBER: P854082

CATALOG NUMBER: SQ2-PP3-025U-100D-930-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.0	3.1
10°-20°	486.3	9.0
20°-30°	761.9	14.1
30°-40°	939.9	17.4
40°-50°	884.9	16.4
50°-60°	626.5	11.6
60°-70°	357.0	6.6
70°-80°	176.6	3.3
80°-90°	43.6	0.8
90°-100°	62.9	1.2
100°-110°	195.6	3.6
110°-120°	191.4	3.5
120°-130°	156.3	2.9
130°-140°	127.8	2.4
140°-150°	99.8	1.8
150°-160°	72.0	1.3
160°-170°	44.0	0.8
170°-180°	14.8	0.3
0°-30°	1416.2	26.2
0°-40°	2356.1	43.6
0°-60°	3867.5	71.5
0°-90°	4444.7	82.2
90°-120°	450.0	8.3
90°-150°	833.8	15.4
90°-180°	965.0	17.8
0°-180°	5409.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1765	1765	1765	1765	1765	
5°	1744	1775	1759	1763	1776	166
15°	1696	1719	1712	1730	1739	478
25°	1571	1611	1638	1704	1752	723
35°	1392	1430	1515	1601	1619	868
45°	1134	1220	1246	1056	983	873
55°	823	872	726	547	478	726
65°	440	464	354	250	248	442
75°	190	210	147	138	136	206
85°	43	39	35	28	22	50
90°	0	1	3	3	3	2
95°	9	25	115	43	28	10
105°	34	48	193	368	351	36
115°	61	72	156	323	378	60
125°	85	94	154	254	298	75
135°	102	113	154	219	246	79
145°	119	128	154	189	206	75
155°	136	141	154	170	176	63
165°	150	151	155	160	162	42
175°	155	155	155	156	155	15
180°	155	155	155	155	155	



TEST NUMBER: P854082

CATALOG NUMBER: SQ2-PP3-025U-100D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1764.7	1764.7	1764.7	1764.7	1764.7
2.5°	1751.3	1776.1	1760.3	1763.3	1766.2
5°	1744.2	1775.2	1759.1	1763.2	1775.9
7.5°	1737.5	1769.2	1753.5	1760.2	1775.9
10°	1733.0	1760.4	1746.1	1755.7	1768.5
12.5°	1719.6	1745.5	1732.6	1745.2	1756.5
15°	1695.7	1719.4	1712.5	1729.5	1738.6
17.5°	1663.3	1692.1	1692.0	1716.1	1725.6
20°	1637.9	1672.5	1677.1	1707.3	1725.6
22.5°	1611.0	1651.5	1659.1	1704.6	1736.0
25°	1570.7	1610.9	1637.9	1704.3	1751.7
27.5°	1523.7	1563.5	1619.2	1693.6	1731.2
30°	1492.4	1530.7	1596.8	1674.1	1708.8
32.5°	1453.6	1493.3	1564.0	1647.2	1678.9
35°	1391.6	1429.9	1514.8	1601.0	1619.2
37.5°	1320.4	1363.8	1458.8	1507.0	1508.0
40°	1266.7	1323.2	1414.0	1422.8	1399.1
42.5°	1214.4	1287.0	1351.3	1312.0	1206.6
45°	1134.2	1219.9	1246.1	1056.1	983.1
47.5°	1048.8	1133.4	1091.7	885.7	835.4
50°	990.6	1070.8	966.3	791.7	744.3
52.5°	924.9	996.4	854.4	701.6	629.4
55°	822.7	871.9	725.7	546.9	477.6
57.5°	699.6	734.2	620.5	410.5	332.8
60°	617.5	644.8	542.9	336.8	298.5
62.5°	542.9	567.3	462.3	292.6	279.1
65°	440.3	464.0	354.4	249.9	248.1
67.5°	350.3	376.2	272.0	218.2	216.0
70°	296.6	324.0	225.7	195.8	192.1
72.5°	251.8	277.7	191.4	171.9	169.8
75°	190.3	210.3	147.4	138.0	136.2
77.5°	138.0	150.8	109.7	104.8	103.0
80°	108.2	113.7	85.8	83.9	82.1
82.5°	81.3	79.5	64.9	63.0	59.7
85°	42.9	39.3	35.4	27.9	22.4
87.5°	13.4	13.6	6.5	5.0	5.0
90°	0.0	0.9	2.9	2.9	2.9
92.5°	3.1	10.7	36.4	12.0	9.7
95°	8.6	25.4	115.4	42.6	27.7
97.5°	15.6	33.0	191.1	119.0	75.0
100°	21.0	36.8	215.5	201.6	134.5
102.5°	26.3	41.4	210.9	287.9	226.0
105°	34.3	48.3	192.6	367.7	350.9
107.5°	42.3	55.4	175.1	373.8	392.3
110°	47.7	60.7	165.9	365.1	401.5



TEST NUMBER: P854082

CATALOG NUMBER: SQ2-PP3-025U-100D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	53.0	65.3	161.3	349.3	395.4
115°	61.0	72.2	156.4	322.6	377.6
117.5°	68.8	79.1	154.3	297.1	353.4
120°	73.4	83.7	153.5	282.5	336.6
122.5°	78.0	88.3	154.3	270.2	319.8
125°	84.9	94.2	154.5	253.7	297.5
127.5°	90.4	99.9	154.5	241.3	278.6
130°	93.5	103.7	154.5	234.4	268.0
132.5°	97.3	107.5	153.7	228.2	259.6
135°	102.0	113.2	153.5	219.0	246.0
137.5°	107.6	117.8	153.5	209.8	234.4
140°	110.6	120.9	153.5	203.6	226.0
142.5°	114.4	123.9	153.5	197.5	217.6
145°	119.2	128.5	153.5	189.2	206.0
147.5°	124.9	132.9	154.5	181.5	194.7
150°	128.7	135.3	154.5	177.6	187.9
152.5°	131.8	137.6	154.5	173.8	182.5
155°	136.4	141.0	154.5	169.9	175.5
157.5°	140.9	144.5	154.5	166.4	169.9
160°	144.0	146.8	154.5	164.1	166.9
162.5°	146.3	148.3	154.5	162.5	164.6
165°	149.7	150.6	155.4	160.2	162.1
167.5°	151.8	152.0	154.5	158.9	159.8
170°	152.6	153.5	154.5	157.4	158.3
172.5°	154.1	154.3	155.2	156.6	156.8
175°	155.4	155.4	155.4	156.4	155.4
177.5°	155.4	155.4	155.4	155.4	155.4
180°	155.4	155.4	155.4	155.4	155.4



TEST NUMBER: P854082

CATALOG NUMBER: SQ2-PP3-025U-100D-930-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.79	22.98	22.42	23.61	24.34	18.19	19.37	18.81	20.01	20.73
	3H	22.91	23.97	23.55	24.62	25.38	19.32	20.38	19.96	21.02	21.78
	4H	23.27	24.26	23.93	24.92	25.70	19.79	20.79	20.46	21.45	22.22
	6H	23.50	24.42	24.17	25.09	25.88	20.16	21.07	20.83	21.74	22.53
	8H	23.56	24.43	24.24	25.12	25.91	20.25	21.12	20.94	21.81	22.61
	12H	23.58	24.41	24.27	25.10	25.92	20.28	21.11	20.97	21.79	22.61
4H	2H	21.94	22.93	22.60	23.59	24.37	18.94	19.94	19.60	20.59	21.37
	3H	23.28	24.10	23.96	24.80	25.59	20.22	21.04	20.90	21.74	22.54
	4H	23.76	24.51	24.46	25.21	26.03	20.79	21.53	21.48	22.23	23.06
	6H	24.12	24.76	24.83	25.49	26.32	21.25	21.89	21.96	22.62	23.45
	8H	24.22	24.82	24.94	25.54	26.39	21.37	21.97	22.09	22.70	23.54
	12H	24.27	24.81	25.01	25.56	26.41	21.42	21.95	22.15	22.70	23.55
8H	4H	23.81	24.41	24.52	25.13	25.98	21.08	21.69	21.80	22.41	23.25
	6H	24.25	24.74	25.00	25.51	26.36	21.64	22.14	22.39	22.90	23.75
	8H	24.40	24.85	25.17	25.62	26.48	21.83	22.27	22.59	23.04	23.90
	12H	24.50	24.90	25.27	25.65	26.58	21.91	22.31	22.68	23.06	23.99
12H	4H	23.78	24.32	24.52	25.07	25.92	21.11	21.65	21.85	22.39	23.24
	6H	24.24	24.68	25.00	25.45	26.31	21.69	22.14	22.46	22.91	23.77
	8H	24.42	24.81	25.18	25.57	26.50	21.92	22.31	22.68	23.07	23.99