

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854355

Luminaire Tested: SQ2-WBM-075U-075D-930-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854355
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-11, G3-2104-222-6)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-WBM-075U-075D-930-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6003.3 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.18 / 1.17
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 50.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854355

CATALOG NUMBER: SQ2-WBM-075U-075D-930-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854355

CATALOG NUMBER: SQ2-WBM-075U-075D-930-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	100	97	93	90	93	90	87	85	77	75	73	65	64	63	54	54	53	48
2	93	87	82	77	86	81	76	73	70	67	64	60	57	56	50	49	48	43
3	86	78	72	67	80	73	68	63	63	59	56	55	52	49	46	45	43	39
4	80	70	64	58	74	66	60	56	58	53	50	50	47	44	43	41	39	35
5	74	64	57	52	69	60	54	49	53	48	44	46	43	40	40	37	35	32
6	69	58	51	46	64	55	48	44	48	43	40	42	39	36	37	34	32	29
7	64	53	46	41	60	50	44	39	45	40	36	39	35	33	34	31	29	27
8	60	49	42	37	56	46	40	36	41	36	33	36	32	30	32	29	27	25
9	56	45	38	34	52	43	36	32	38	33	30	34	30	27	30	27	25	23
10	53	42	35	31	49	39	33	29	35	30	27	31	28	25	28	25	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	32411	32411	32411
5°	32707	32302	32692
10°	33037	32723	33023
15°	33588	33153	32991
20°	33747	32953	32459
25°	33054	32076	31545
30°	31362	30464	29496
35°	28206	27618	26613
40°	23123	22778	21905
45°	14458	16459	13579
50°	5657	9595	5172
55°	2790	4470	2764
60°	1305	2144	1182
65°	1177	1249	1104
70°	1138	1180	1090
75°	1142	1142	1023
80°	1069	1069	986
85°	1074	889	889

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 16459 cd/sqm



TEST NUMBER: P854355

CATALOG NUMBER: SQ2-WBM-075U-075D-930-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.9	3.2
10°-20°	561.2	9.3
20°-30°	829.8	13.8
30°-40°	858.6	14.3
40°-50°	516.4	8.6
50°-60°	123.6	2.1
60°-70°	33.8	0.6
70°-80°	18.9	0.3
80°-90°	6.4	0.1
90°-100°	174.9	2.9
100°-110°	579.7	9.7
110°-120°	575.3	9.6
120°-130°	468.6	7.8
130°-140°	380.8	6.3
140°-150°	295.8	4.9
150°-160°	213.1	3.5
160°-170°	130.5	2.2
170°-180°	44.1	0.7
0°-30°	1582.9	26.4
0°-40°	2441.5	40.7
0°-60°	3081.5	51.3
0°-90°	3140.5	52.3
90°-120°	1329.9	22.2
90°-150°	2475.1	41.2
90°-180°	2863.0	47.7
0°-180°	6003.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2007	2007	2007	2007	2007	
5°	2018	2011	1993	2020	2017	192
15°	2009	2024	1983	1983	1974	566
25°	1855	1870	1800	1781	1771	848
35°	1431	1429	1401	1369	1350	878
45°	633	719	721	685	595	490
55°	99	111	159	106	98	99
65°	31	32	33	31	29	31
75°	18	18	18	17	16	19
85°	6	6	5	5	5	6
90°	0	1	3	4	4	1
95°	25	74	317	113	76	28
105°	102	144	580	1094	1023	107
115°	181	216	467	972	1137	179
125°	253	281	458	764	901	225
135°	302	333	455	656	740	234
145°	351	378	454	564	618	220
155°	401	415	457	504	523	185
165°	440	445	458	477	482	124
175°	460	460	461	464	463	44
180°	462	462	462	462	462	

TEST NUMBER: P854355

CATALOG NUMBER: SQ2-WBM-075U-075D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2007.4	2007.4	2007.4	2007.4	2007.4
2.5°	2017.4	2012.2	1995.9	2012.7	2009.0
5°	2018.0	2011.4	1993.0	2019.9	2017.1
7.5°	2015.9	2013.1	1999.0	2019.3	2014.9
10°	2015.1	2016.1	1995.9	2017.0	2014.2
12.5°	2014.4	2022.1	1992.8	2009.2	2002.6
15°	2009.4	2024.4	1983.4	1983.2	1973.7
17.5°	1988.0	2005.9	1951.0	1936.0	1924.5
20°	1964.1	1982.0	1917.9	1893.8	1889.1
22.5°	1926.4	1945.8	1877.1	1850.6	1842.9
25°	1855.4	1870.4	1800.5	1781.0	1770.7
27.5°	1760.7	1769.0	1703.3	1681.1	1666.8
30°	1682.2	1685.9	1634.0	1604.7	1582.1
32.5°	1589.0	1592.8	1547.0	1519.3	1501.2
35°	1431.0	1429.1	1401.2	1369.0	1350.2
37.5°	1233.3	1236.0	1213.9	1188.4	1169.4
40°	1097.1	1098.9	1080.7	1044.0	1039.3
42.5°	930.8	959.0	934.4	905.8	883.8
45°	633.2	718.8	720.8	685.1	594.7
47.5°	357.6	455.1	511.4	408.8	299.1
50°	225.2	291.1	382.0	242.6	205.9
52.5°	159.7	193.2	288.1	170.7	151.3
55°	99.1	111.4	158.8	105.7	98.2
57.5°	58.9	71.5	90.3	71.5	59.7
60°	40.4	50.8	66.4	46.9	36.6
62.5°	35.0	39.4	52.5	37.1	33.5
65°	30.8	31.7	32.7	30.8	28.9
67.5°	27.1	28.1	27.3	27.1	25.4
70°	24.1	25.0	25.0	24.0	23.1
72.5°	21.7	22.7	21.9	21.7	20.0
75°	18.3	18.3	18.3	17.3	16.4
77.5°	13.9	14.8	13.9	13.8	12.9
80°	11.5	12.5	11.5	11.5	10.6
82.5°	9.2	9.4	9.2	9.2	8.3
85°	5.8	5.8	4.8	4.8	4.8
87.5°	1.5	2.5	2.1	2.3	2.3
90°	0.0	0.9	2.9	3.8	3.8
92.5°	7.7	29.6	87.1	28.2	23.7
95°	24.9	73.6	316.9	113.1	75.6
97.5°	45.8	96.7	553.1	322.6	203.9
100°	60.3	109.0	640.4	550.1	364.7
102.5°	76.4	123.6	635.1	840.6	635.1
105°	101.5	144.5	580.1	1094.5	1023.3
107.5°	127.1	165.5	527.5	1120.3	1174.4
110°	141.7	180.1	500.7	1094.8	1204.3



TEST NUMBER: P854355

CATALOG NUMBER: SQ2-WBM-075U-075D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	157.0	194.6	484.6	1049.5	1189.0
115°	180.9	216.5	467.2	972.5	1137.3
117.5°	204.7	236.3	460.8	899.0	1071.8
120°	219.2	250.1	458.5	852.9	1020.5
122.5°	232.2	262.4	458.5	815.1	969.9
125°	252.7	280.8	458.5	764.2	900.8
127.5°	269.6	297.1	457.4	725.6	842.4
130°	279.5	308.5	456.6	703.1	808.0
132.5°	288.7	318.5	455.9	684.5	778.9
135°	302.5	333.4	454.7	655.7	740.0
137.5°	317.4	347.2	453.6	628.0	702.3
140°	327.4	356.4	452.8	609.4	677.8
142.5°	336.6	364.9	453.6	590.9	651.7
145°	351.3	377.5	453.8	564.1	617.5
147.5°	367.2	389.1	453.9	541.4	581.1
150°	377.2	396.8	454.7	528.2	561.9
152.5°	386.4	405.3	455.5	517.4	544.3
155°	401.1	415.1	456.6	504.0	522.7
157.5°	415.5	426.3	457.8	494.5	507.7
160°	423.1	432.5	458.5	487.5	497.8
162.5°	430.8	437.9	458.5	482.9	490.9
165°	440.4	445.0	458.5	476.8	481.5
167.5°	449.2	451.6	459.5	471.4	473.9
170°	453.8	454.7	459.5	469.1	470.0
172.5°	456.8	457.8	460.3	466.8	467.0
175°	460.5	460.5	461.4	464.3	463.3
177.5°	462.4	462.4	461.6	463.1	461.6
180°	462.4	462.4	462.4	462.4	462.4



TEST NUMBER: P854355

CATALOG NUMBER: SQ2-WBM-075U-075D-930-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.22	5.95	6.19	6.91	8.16	4.87	5.60	5.84	6.56	7.81
	3H	5.72	6.36	6.70	7.33	8.61	5.38	6.03	6.36	7.00	8.27
	4H	5.98	6.59	6.97	7.56	8.85	5.62	6.23	6.62	7.21	8.49
	6H	6.21	6.77	7.21	7.75	9.04	5.83	6.39	6.83	7.37	8.66
	8H	6.29	6.82	7.30	7.81	9.10	5.89	6.42	6.90	7.42	8.71
	12H	6.34	6.84	7.35	7.83	9.14	5.92	6.43	6.94	7.42	8.73
4H	2H	5.22	5.83	6.22	6.81	8.09	4.91	5.52	5.91	6.49	7.77
	3H	5.93	6.44	6.94	7.44	8.73	5.63	6.13	6.64	7.14	8.43
	4H	6.33	6.79	7.35	7.79	9.11	6.01	6.46	7.02	7.46	8.78
	6H	6.71	7.10	7.73	8.12	9.44	6.35	6.74	7.38	7.76	9.08
	8H	6.85	7.21	7.87	8.23	9.56	6.47	6.84	7.50	7.85	9.18
	12H	6.94	7.27	7.98	8.30	9.63	6.54	6.86	7.58	7.89	9.23
8H	4H	6.42	6.78	7.44	7.79	9.12	6.12	6.48	7.14	7.49	8.82
	6H	6.92	7.22	7.97	8.28	9.60	6.59	6.89	7.63	7.94	9.27
	8H	7.15	7.41	8.20	8.45	9.80	6.79	7.05	7.84	8.09	9.44
	12H	7.33	7.56	8.38	8.59	9.98	6.92	7.15	7.97	8.18	9.58
12H	4H	6.39	6.71	7.43	7.74	9.08	6.09	6.42	7.13	7.45	8.78
	6H	6.94	7.20	7.99	8.24	9.59	6.62	6.88	7.67	7.92	9.27
	8H	7.19	7.42	8.25	8.46	9.85	6.84	7.07	7.89	8.10	9.49