

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854100

Luminaire Tested: SQ2-PP3-075U-050D-930-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854100
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-11, G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PP3-075U-050D-930-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5167.8 lumens
Efficiency: N/A
Efficacy: 125.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 41.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854100

CATALOG NUMBER: SQ2-PP3-075U-050D-930-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854100

CATALOG NUMBER: SQ2-PP3-075U-050D-930-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33				
3	81	72	65	60	74	66	60	55	56	51	48	46	43	40	37	34	33	28				
4	74	64	56	51	68	59	52	47	50	45	41	41	37	34	33	30	28	25				
5	68	57	49	43	62	53	46	41	45	39	35	37	33	30	30	27	25	21				
6	63	51	43	38	58	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17				
8	54	42	34	29	49	39	32	28	33	28	24	28	24	21	23	20	18	15				
9	50	38	31	26	46	36	29	25	30	25	22	26	22	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14691	14691	14691
5°	14575	14700	14840
10°	14649	14759	14949
15°	14614	14758	14984
20°	14510	14857	15287
25°	14427	15045	16089
30°	14344	15349	16425
35°	14142	15394	16454
40°	13765	15365	15205
45°	13353	14671	11574
50°	12828	12514	9640
55°	11941	10531	6930
60°	10282	9038	4970
65°	8672	6980	4886
70°	7218	5495	4678
75°	6120	4741	4379
80°	5188	4110	3933
85°	4094	3390	2130

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 14671 cd/sqm



TEST NUMBER: P854100

CATALOG NUMBER: SQ2-PP3-075U-050D-930-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.6	1.7
10°-20°	250.7	4.9
20°-30°	392.8	7.6
30°-40°	484.6	9.4
40°-50°	456.2	8.8
50°-60°	323.0	6.3
60°-70°	184.0	3.6
70°-80°	91.1	1.8
80°-90°	22.7	0.4
90°-100°	175.7	3.4
100°-110°	582.3	11.3
110°-120°	578.0	11.2
120°-130°	470.8	9.1
130°-140°	382.6	7.4
140°-150°	297.1	5.7
150°-160°	214.1	4.1
160°-170°	131.1	2.5
170°-180°	44.3	0.9
0°-30°	730.2	14.1
0°-40°	1214.8	23.5
0°-60°	1994.0	38.6
0°-90°	2291.9	44.3
90°-120°	1336.0	25.9
90°-150°	2486.4	48.1
90°-180°	2876.0	55.7
0°-180°	5167.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	910	910	910	910	910	
5°	899	915	907	909	916	86
15°	874	886	883	892	896	246
25°	810	830	844	879	903	373
35°	718	737	781	825	835	447
45°	585	629	642	544	507	450
55°	424	450	374	282	246	374
65°	227	239	183	129	128	228
75°	98	108	76	71	70	106
85°	22	20	18	14	12	26
90°	0	1	3	4	4	2
95°	25	74	318	114	76	29
105°	102	145	583	1100	1028	107
115°	182	218	469	977	1142	180
125°	254	282	461	768	905	226
135°	304	335	457	659	743	235
145°	353	379	456	567	620	221
155°	403	417	459	506	525	186
165°	442	447	461	479	484	125
175°	463	463	464	466	466	44
180°	464	464	464	464	464	



TEST NUMBER: P854100

CATALOG NUMBER: SQ2-PP3-075U-050D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	909.9	909.9	909.9	909.9	909.9
2.5°	902.9	915.7	907.6	909.1	910.6
5°	899.3	915.3	907.0	909.1	915.6
7.5°	895.8	912.2	904.1	907.6	915.6
10°	893.5	907.6	900.2	905.2	911.8
12.5°	886.6	899.9	893.3	899.8	905.6
15°	874.3	886.5	882.9	891.7	896.4
17.5°	857.5	872.4	872.4	884.8	889.7
20°	844.5	862.3	864.7	880.3	889.7
22.5°	830.6	851.5	855.4	878.9	895.1
25°	809.8	830.5	844.5	878.7	903.1
27.5°	785.6	806.1	834.8	873.2	892.6
30°	769.4	789.2	823.3	863.1	881.0
32.5°	749.4	769.9	806.4	849.3	865.6
35°	717.5	737.3	781.0	825.4	834.8
37.5°	680.8	703.1	752.1	777.0	777.5
40°	653.1	682.2	729.0	733.6	721.4
42.5°	626.1	663.6	696.7	676.5	622.1
45°	584.8	629.0	642.5	544.5	506.9
47.5°	540.7	584.4	562.8	456.7	430.7
50°	510.7	552.1	498.2	408.2	383.8
52.5°	476.9	513.7	440.5	361.8	324.5
55°	424.2	449.5	374.1	282.0	246.2
57.5°	360.7	378.5	319.9	211.6	171.6
60°	318.4	332.5	279.9	173.6	153.9
62.5°	279.9	292.5	238.3	150.8	143.9
65°	227.0	239.2	182.7	128.9	127.9
67.5°	180.6	194.0	140.2	112.5	111.4
70°	152.9	167.0	116.4	100.9	99.1
72.5°	129.8	143.2	98.7	88.7	87.5
75°	98.1	108.4	76.0	71.2	70.2
77.5°	71.2	77.8	56.6	54.0	53.1
80°	55.8	58.6	44.2	43.3	42.3
82.5°	41.9	41.0	33.5	32.5	30.8
85°	22.1	20.2	18.3	14.4	11.5
87.5°	6.9	7.1	3.7	3.1	3.1
90°	0.0	0.9	2.9	3.8	3.8
92.5°	7.7	29.7	87.5	28.4	23.8
95°	25.0	73.9	318.3	113.6	76.0
97.5°	46.0	97.1	555.7	324.1	204.8
100°	60.6	109.5	643.4	552.6	366.4
102.5°	76.7	124.1	638.0	844.5	638.0
105°	101.9	145.2	582.8	1099.5	1028.0
107.5°	127.7	166.3	529.9	1125.4	1179.8
110°	142.3	180.9	503.0	1099.8	1209.8



TEST NUMBER: P854100

CATALOG NUMBER: SQ2-PP3-075U-050D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	157.7	195.5	486.8	1054.3	1194.4
115°	181.8	217.5	469.3	977.0	1142.5
117.5°	205.6	237.4	463.0	903.1	1076.7
120°	220.2	251.3	460.6	856.8	1025.1
122.5°	233.3	263.6	460.6	818.8	974.4
125°	253.9	282.1	460.6	767.7	904.9
127.5°	270.8	298.5	459.5	728.9	846.3
130°	280.8	310.0	458.7	706.3	811.7
132.5°	290.0	319.9	458.0	687.6	782.4
135°	303.9	334.9	456.8	658.7	743.4
137.5°	318.9	348.8	455.6	630.8	705.5
140°	328.9	358.0	454.9	612.2	680.9
142.5°	338.1	366.5	455.6	593.6	654.7
145°	352.9	379.3	455.8	566.7	620.3
147.5°	368.9	390.9	456.0	543.9	583.7
150°	378.9	398.6	456.8	530.7	564.5
152.5°	388.1	407.1	457.6	519.7	546.8
155°	402.9	417.0	458.7	506.3	525.1
157.5°	417.4	428.3	459.9	496.7	510.1
160°	425.1	434.5	460.6	489.7	500.1
162.5°	432.8	439.9	460.6	485.1	493.1
165°	442.4	447.1	460.6	479.0	483.7
167.5°	451.2	453.7	461.6	473.6	476.0
170°	455.8	456.8	461.6	471.2	472.2
172.5°	458.9	459.9	462.4	468.9	469.1
175°	462.6	462.6	463.5	466.4	465.5
177.5°	464.5	464.5	463.7	465.2	463.7
180°	464.5	464.5	464.5	464.5	464.5



TEST NUMBER: P854100

CATALOG NUMBER: SQ2-PP3-075U-050D-930-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.33	17.11	17.34	18.13	19.48	12.72	13.51	13.73	14.53	15.88
	3H	17.42	18.12	18.44	19.14	20.52	13.82	14.52	14.84	15.55	16.92
	4H	17.76	18.42	18.79	19.45	20.83	14.28	14.94	15.32	15.97	17.35
	6H	17.97	18.58	19.01	19.61	21.00	14.62	15.23	15.67	16.27	17.66
	8H	18.01	18.59	19.06	19.64	21.03	14.71	15.29	15.76	16.34	17.72
	12H	18.03	18.58	19.08	19.62	21.03	14.72	15.27	15.77	16.31	17.72
4H	2H	16.43	17.09	17.47	18.12	19.50	13.43	14.09	14.47	15.12	16.50
	3H	17.73	18.28	18.78	19.33	20.73	14.67	15.22	15.72	16.28	17.67
	4H	18.20	18.70	19.25	19.75	21.17	15.22	15.73	16.28	16.77	18.19
	6H	18.53	18.96	19.60	20.03	21.45	15.66	16.09	16.72	17.16	18.57
	8H	18.62	19.03	19.69	20.09	21.52	15.78	16.18	16.84	17.25	18.67
	12H	18.66	19.02	19.74	20.10	21.53	15.80	16.17	16.89	17.25	18.68
8H	4H	18.21	18.61	19.28	19.68	21.10	15.49	15.89	16.56	16.96	18.38
	6H	18.64	18.97	19.73	20.08	21.50	16.03	16.37	17.12	17.47	18.90
	8H	18.80	19.09	19.89	20.18	21.62	16.22	16.51	17.31	17.60	19.04
	12H	18.88	19.14	19.98	20.22	21.70	16.29	16.55	17.39	17.63	19.11
12H	4H	18.17	18.53	19.25	19.61	21.04	15.50	15.86	16.58	16.94	18.37
	6H	18.63	18.92	19.72	20.01	21.45	16.09	16.38	17.18	17.47	18.91
	8H	18.80	19.05	19.89	20.14	21.62	16.29	16.55	17.39	17.63	19.12