

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854127

Luminaire Tested: SQ2-PP3-100U-075D-930-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854127
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-12, G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PP3-100U-075D-930-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7101.2 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 59.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854127

CATALOG NUMBER: SQ2-PP3-100U-075D-930-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854127

CATALOG NUMBER: SQ2-PP3-100U-075D-930-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	42	41	39	34
3	82	73	66	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	50	45	41	42	38	35	34	32	29	26
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	47	39	33	54	43	36	32	37	32	28	31	27	24	26	23	20	18
8	54	42	35	30	50	39	33	28	34	28	25	29	24	21	24	21	18	16
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21191	21191	21191
5°	21026	21206	21409
10°	21133	21292	21564
15°	21081	21290	21615
20°	20931	21431	22051
25°	20811	21702	23209
30°	20694	22143	23694
35°	20402	22206	23737
40°	19857	22167	21933
45°	19262	21162	16696
50°	18505	18053	13906
55°	17225	15192	9999
60°	14832	13039	7169
65°	12508	10071	7049
70°	10414	7926	6746
75°	8827	6837	6319
80°	7485	5932	5672
85°	5910	4891	3075

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 21162 cd/sqm



TEST NUMBER: P854127

CATALOG NUMBER: SQ2-PP3-100U-075D-930-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.0	1.8
10°-20°	361.7	5.1
20°-30°	566.7	8.0
30°-40°	699.0	9.8
40°-50°	658.1	9.3
50°-60°	466.0	6.6
60°-70°	265.5	3.7
70°-80°	131.4	1.8
80°-90°	33.2	0.5
90°-100°	254.6	3.6
100°-110°	770.1	10.8
110°-120°	751.8	10.6
120°-130°	614.3	8.7
130°-140°	501.5	7.1
140°-150°	390.4	5.5
150°-160°	281.4	4.0
160°-170°	172.3	2.4
170°-180°	58.2	0.8
0°-30°	1053.3	14.8
0°-40°	1752.4	24.7
0°-60°	2876.5	40.5
0°-90°	3306.6	46.6
90°-120°	1776.6	25.0
90°-150°	3282.7	46.2
90°-180°	3795.0	53.4
0°-180°	7101.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1312	1312	1312	1312	1312	
5°	1297	1320	1308	1311	1321	124
15°	1261	1279	1274	1286	1293	355
25°	1168	1198	1218	1268	1303	538
35°	1035	1064	1127	1191	1204	646
45°	844	907	927	786	731	649
55°	612	648	540	407	355	540
65°	327	345	264	186	184	329
75°	142	156	110	103	101	153
85°	32	29	26	21	17	37
90°	0	2	12	7	6	3
95°	32	100	480	178	112	37
105°	134	188	756	1436	1365	141
115°	238	284	612	1266	1486	236
125°	333	370	603	1000	1176	296
135°	399	441	599	862	970	309
145°	466	501	599	742	811	292
155°	531	549	603	665	690	244
165°	581	588	606	629	636	164
175°	608	608	609	614	612	58
180°	610	610	610	610	610	



TEST NUMBER: P854127

CATALOG NUMBER: SQ2-PP3-100U-075D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1312.5	1312.5	1312.5	1312.5	1312.5
2.5°	1302.6	1321.0	1309.2	1311.5	1313.7
5°	1297.3	1320.3	1308.4	1311.4	1320.9
7.5°	1292.3	1315.9	1304.2	1309.2	1320.9
10°	1289.0	1309.3	1298.7	1305.8	1315.3
12.5°	1279.0	1298.2	1288.7	1298.0	1306.4
15°	1261.2	1278.8	1273.7	1286.3	1293.1
17.5°	1237.1	1258.5	1258.4	1276.4	1283.4
20°	1218.2	1244.0	1247.3	1269.8	1283.4
22.5°	1198.2	1228.3	1234.0	1267.8	1291.2
25°	1168.2	1198.1	1218.2	1267.6	1302.8
27.5°	1133.3	1162.9	1204.3	1259.6	1287.6
30°	1110.0	1138.5	1187.7	1245.1	1270.9
32.5°	1081.1	1110.7	1163.3	1225.1	1248.7
35°	1035.1	1063.5	1126.6	1190.8	1204.3
37.5°	982.1	1014.3	1085.0	1120.8	1121.6
40°	942.1	984.1	1051.7	1058.2	1040.6
42.5°	903.2	957.2	1005.1	975.8	897.4
45°	843.6	907.3	926.8	785.5	731.2
47.5°	780.0	843.0	811.9	658.8	621.3
50°	736.7	796.4	718.7	588.9	553.6
52.5°	687.9	741.1	635.5	521.9	468.1
55°	611.9	648.5	539.7	406.7	355.2
57.5°	520.3	546.1	461.5	305.3	247.5
60°	459.3	479.6	403.8	250.5	222.0
62.5°	403.8	421.9	343.8	217.6	207.6
65°	327.4	345.1	263.6	185.9	184.5
67.5°	260.6	279.8	202.3	162.3	160.7
70°	220.6	241.0	167.9	145.6	142.9
72.5°	187.3	206.6	142.4	127.9	126.3
75°	141.5	156.4	109.6	102.6	101.3
77.5°	102.7	112.2	81.6	77.9	76.6
80°	80.5	84.5	63.8	62.4	61.0
82.5°	60.5	59.1	48.3	46.8	44.4
85°	31.9	29.2	26.4	20.7	16.6
87.5°	10.0	10.4	6.7	4.7	4.5
90°	0.0	1.9	11.5	6.7	5.7
92.5°	10.7	43.3	155.4	51.6	37.1
95°	31.6	99.9	480.5	177.5	112.0
97.5°	61.1	127.1	757.3	501.1	305.1
100°	79.4	144.0	846.1	818.0	549.4
102.5°	100.1	162.4	827.8	1147.3	914.7
105°	134.0	188.3	756.2	1436.0	1364.9
107.5°	166.2	218.0	687.2	1464.6	1547.0
110°	187.6	237.2	652.8	1428.6	1578.4



TEST NUMBER: P854127

CATALOG NUMBER: SQ2-PP3-100U-075D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	208.3	256.4	632.1	1368.3	1557.7
115°	238.3	284.2	611.6	1265.6	1486.5
117.5°	268.2	311.6	604.4	1169.4	1395.5
120°	288.1	329.3	602.1	1113.3	1330.5
122.5°	306.5	345.4	602.1	1063.9	1264.6
125°	333.1	369.6	603.0	999.5	1176.3
127.5°	354.7	392.5	602.1	950.8	1101.7
130°	368.5	407.8	602.1	922.9	1059.6
132.5°	380.8	420.8	601.3	897.4	1023.6
135°	399.1	441.3	599.2	862.0	969.6
137.5°	419.6	459.7	599.2	824.1	923.8
140°	432.6	471.9	599.2	799.5	894.0
142.5°	445.7	483.5	598.4	777.0	859.5
145°	466.1	500.8	599.2	741.5	810.7
147.5°	486.6	516.0	600.3	712.2	765.3
150°	499.6	526.8	601.1	695.9	740.8
152.5°	511.9	536.0	601.9	681.9	718.6
155°	531.2	549.0	603.0	664.8	690.1
157.5°	548.1	562.5	604.2	652.2	669.8
160°	558.0	570.2	604.9	644.5	657.6
162.5°	568.0	577.1	605.7	637.5	648.4
165°	581.0	587.5	605.9	629.0	636.5
167.5°	592.1	595.5	607.0	622.4	625.6
170°	598.2	600.1	607.8	619.3	620.2
172.5°	602.1	603.2	607.8	616.2	616.4
175°	607.8	607.8	608.8	613.5	611.6
177.5°	610.5	609.7	608.9	611.2	609.7
180°	609.7	609.7	609.7	609.7	609.7



TEST NUMBER: P854127

CATALOG NUMBER: SQ2-PP3-100U-075D-930-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.82	18.62	18.81	19.62	20.95	14.22	15.02	15.21	16.02	17.34
	3H	18.91	19.63	19.92	20.64	21.98	15.32	16.03	16.32	17.04	18.39
	4H	19.25	19.93	20.27	20.94	22.29	15.78	16.45	16.79	17.47	18.82
	6H	19.46	20.09	20.49	21.10	22.47	16.12	16.74	17.15	17.76	19.12
	8H	19.51	20.10	20.54	21.14	22.50	16.20	16.80	17.24	17.83	19.19
	12H	19.52	20.09	20.56	21.11	22.50	16.22	16.78	17.25	17.81	19.19
4H	2H	17.92	18.60	18.95	19.61	20.96	14.92	15.60	15.95	16.61	17.96
	3H	19.23	19.79	20.26	20.83	22.19	16.17	16.73	17.20	17.77	19.14
	4H	19.70	20.21	20.74	21.24	22.63	16.72	17.23	17.76	18.27	19.66
	6H	20.03	20.47	21.08	21.53	22.91	17.16	17.60	18.21	18.65	20.04
	8H	20.12	20.54	21.17	21.58	22.98	17.28	17.69	18.33	18.74	20.14
	12H	20.16	20.53	21.22	21.59	23.00	17.30	17.67	18.37	18.74	20.14
8H	4H	19.71	20.12	20.76	21.17	22.57	16.99	17.40	18.04	18.45	19.85
	6H	20.14	20.48	21.21	21.57	22.97	17.53	17.87	18.61	18.96	20.36
	8H	20.30	20.60	21.38	21.67	23.09	17.72	18.02	18.80	19.09	20.51
	12H	20.38	20.64	21.46	21.71	23.17	17.79	18.05	18.87	19.12	20.58
12H	4H	19.67	20.04	20.73	21.10	22.51	17.00	17.37	18.06	18.43	19.83
	6H	20.13	20.43	21.21	21.50	22.92	17.59	17.88	18.67	18.96	20.37
	8H	20.30	20.56	21.38	21.63	23.09	17.79	18.05	18.87	19.12	20.58