

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854385

Luminaire Tested: SQ2-WBM-100U-125D-930-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854385
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-12, G3-2104-222-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-WBM-100U-125D-930-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8996.8 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.18 / 1.17
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 82.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854385

CATALOG NUMBER: SQ2-WBM-100U-125D-930-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854385

CATALOG NUMBER: SQ2-WBM-100U-125D-930-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58																			
1	102	98	95	92	95	92	89	87	80	78	76	69	68	67	59	59	58	53																			
2	94	88	83	79	88	83	79	75	73	70	67	64	61	59	55	54	52	48																			
3	88	80	74	69	82	75	70	65	66	62	59	58	55	53	51	49	47	44																			
4	81	72	65	60	76	68	62	58	61	56	52	54	50	47	47	45	43	39																			
5	76	66	58	53	71	62	56	51	55	51	47	49	46	43	44	41	39	36																			
6	70	60	53	48	66	57	50	46	51	46	42	45	42	39	40	37	35	33																			
7	66	55	48	43	62	52	46	41	47	42	38	42	38	35	38	34	32	30																			
8	61	50	43	39	58	48	42	37	43	38	35	39	35	32	35	32	29	27																			
9	58	46	40	35	54	44	38	34	40	35	32	36	32	29	33	29	27	25																			
10	54	43	36	32	51	41	35	31	37	32	29	34	30	27	30	27	25	23																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	54077	54077	54077
5°	54501	53848	54579
10°	55085	54502	55100
15°	55968	55231	55005
20°	56244	54974	53983
25°	55184	53440	52533
30°	52361	50696	49264
35°	46952	45835	44415
40°	38545	37696	36320
45°	24103	27371	21866
50°	9530	16189	8518
55°	4622	7355	4569
60°	2170	3597	1986
65°	1945	2090	1872
70°	1902	1950	1770
75°	1859	1859	1678
80°	1785	1785	1609
85°	1593	1593	1593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 27371 cd/sqm



TEST NUMBER: P854385

CATALOG NUMBER: SQ2-WBM-100U-125D-930-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	320.0	3.6
10°-20°	935.4	10.4
20°-30°	1382.8	15.4
30°-40°	1428.9	15.9
40°-50°	859.8	9.6
50°-60°	206.6	2.3
60°-70°	56.4	0.6
70°-80°	31.4	0.3
80°-90°	10.9	0.1
90°-100°	252.6	2.8
100°-110°	764.0	8.5
110°-120°	745.8	8.3
120°-130°	609.5	6.8
130°-140°	497.5	5.5
140°-150°	387.3	4.3
150°-160°	279.2	3.1
160°-170°	170.9	1.9
170°-180°	57.7	0.6
0°-30°	2638.2	29.3
0°-40°	4067.2	45.2
0°-60°	5133.6	57.1
0°-90°	5232.4	58.2
90°-120°	1762.4	19.6
90°-150°	3256.6	36.2
90°-180°	3764.0	41.8
0°-180°	8996.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3349	3349	3349	3349	3349	
5°	3363	3352	3322	3369	3368	321
15°	3348	3374	3304	3305	3291	944
25°	3098	3121	3000	2957	2949	1416
35°	2382	2376	2325	2281	2253	1466
45°	1056	1198	1199	1133	958	818
55°	164	185	261	176	162	167
65°	51	54	55	51	49	52
75°	30	32	30	29	27	31
85°	9	10	9	9	9	10
90°	0	2	11	7	6	2
95°	31	99	477	176	111	37
105°	133	187	750	1425	1354	140
115°	236	282	607	1256	1475	234
125°	330	367	598	992	1167	294
135°	396	438	594	855	962	307
145°	462	497	594	736	804	290
155°	527	545	598	660	685	243
165°	576	583	601	624	631	162
175°	603	603	604	609	607	57
180°	605	605	605	605	605	



TEST NUMBER: P854385

CATALOG NUMBER: SQ2-WBM-100U-125D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3349.3	3349.3	3349.3	3349.3	3349.3
2.5°	3361.6	3353.3	3327.0	3357.6	3352.4
5°	3362.7	3352.4	3322.4	3369.4	3367.5
7.5°	3362.2	3356.7	3331.2	3367.4	3360.1
10°	3359.9	3362.7	3324.3	3363.6	3360.8
12.5°	3358.3	3370.9	3320.5	3348.2	3340.8
15°	3348.3	3373.7	3304.2	3304.8	3290.7
17.5°	3311.8	3342.6	3252.5	3225.8	3207.9
20°	3273.4	3303.5	3199.5	3159.7	3141.8
22.5°	3213.5	3241.3	3125.7	3085.2	3070.4
25°	3097.6	3121.1	2999.7	2957.2	2948.8
27.5°	2941.5	2951.4	2839.8	2798.2	2783.8
30°	2808.5	2809.5	2719.2	2669.6	2642.4
32.5°	2654.1	2647.5	2577.8	2528.1	2494.1
35°	2382.1	2376.4	2325.4	2280.6	2253.4
37.5°	2062.4	2061.5	2012.8	1974.2	1946.8
40°	1828.8	1835.4	1788.5	1740.1	1723.2
42.5°	1549.1	1597.8	1557.9	1505.1	1494.2
45°	1055.6	1198.4	1198.7	1133.3	957.6
47.5°	603.8	757.8	862.7	667.9	495.8
50°	379.4	495.9	644.5	406.7	339.1
52.5°	269.5	326.6	477.0	286.1	253.0
55°	164.2	184.9	261.3	176.4	162.3
57.5°	99.5	118.9	151.4	118.3	99.9
60°	67.2	85.1	111.4	78.4	61.5
62.5°	59.6	66.1	87.6	61.7	55.3
65°	50.9	53.7	54.7	50.9	49.0
67.5°	45.0	46.8	45.9	44.9	42.1
70°	40.3	42.2	41.3	40.3	37.5
72.5°	35.7	37.6	36.7	35.7	33.6
75°	29.8	31.7	29.8	28.8	26.9
77.5°	23.1	24.7	23.8	23.0	21.1
80°	19.2	20.1	19.2	19.2	17.3
82.5°	15.4	15.6	14.6	14.6	13.4
85°	8.6	9.6	8.6	8.6	8.6
87.5°	3.1	3.4	5.4	4.4	3.4
90°	0.0	1.9	11.4	6.6	5.7
92.5°	10.6	42.9	154.2	51.1	36.8
95°	31.3	99.1	476.7	176.1	111.1
97.5°	60.6	126.1	751.3	497.1	302.7
100°	78.8	142.9	839.4	811.5	545.0
102.5°	99.3	161.2	821.2	1138.2	907.4
105°	132.9	186.8	750.1	1424.6	1354.1
107.5°	164.8	216.3	681.8	1453.0	1534.7
110°	186.1	235.3	647.6	1417.2	1565.8



TEST NUMBER: P854385

CATALOG NUMBER: SQ2-WBM-100U-125D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	206.6	254.3	627.1	1357.4	1545.3
115°	236.4	281.9	606.8	1255.5	1474.6
117.5°	266.1	309.1	599.5	1160.1	1384.4
120°	285.8	326.7	597.3	1104.5	1319.9
122.5°	304.0	342.7	597.3	1055.5	1254.5
125°	330.4	366.7	598.2	991.5	1167.0
127.5°	351.9	389.4	597.3	943.3	1092.9
130°	365.6	404.6	597.3	915.6	1051.1
132.5°	377.7	417.5	596.5	890.3	1015.4
135°	396.0	437.7	594.4	855.1	961.9
137.5°	416.3	456.0	594.4	817.5	916.5
140°	429.2	468.2	594.4	793.1	886.9
142.5°	442.1	479.6	593.7	770.8	852.7
145°	462.4	496.8	594.4	735.6	804.3
147.5°	482.7	511.9	595.6	706.5	759.3
150°	495.7	522.6	596.3	690.4	734.9
152.5°	507.8	531.8	597.1	676.5	712.9
155°	527.0	544.6	598.2	659.6	684.6
157.5°	543.7	558.0	599.4	647.0	664.5
160°	553.6	565.7	600.1	639.3	652.3
162.5°	563.5	572.6	600.9	632.5	643.2
165°	576.4	582.9	601.1	624.0	631.4
167.5°	587.4	590.7	602.2	617.5	620.6
170°	593.5	595.3	603.0	614.4	615.3
172.5°	597.3	598.4	603.0	611.3	611.5
175°	603.0	603.0	603.9	608.6	606.8
177.5°	605.6	604.9	604.1	606.3	604.9
180°	604.9	604.9	604.9	604.9	604.9



TEST NUMBER: P854385

CATALOG NUMBER: SQ2-WBM-100U-125D-930-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.51	8.28	8.43	9.19	10.35	7.18	7.95	8.10	8.86	10.02
	3H	8.03	8.70	8.96	9.63	10.82	7.69	8.37	8.62	9.29	10.48
	4H	8.29	8.93	9.24	9.86	11.06	7.93	8.56	8.87	9.49	10.69
	6H	8.52	9.10	9.48	10.04	11.25	8.13	8.71	9.08	9.64	10.85
	8H	8.59	9.14	9.55	10.09	11.30	8.19	8.75	9.16	9.69	10.90
	12H	8.63	9.15	9.59	10.10	11.32	8.23	8.76	9.20	9.70	10.93
4H	2H	7.53	8.16	8.48	9.09	10.29	7.23	7.86	8.18	8.79	9.99
	3H	8.26	8.78	9.21	9.74	10.95	7.95	8.47	8.90	9.43	10.64
	4H	8.66	9.14	9.63	10.09	11.33	8.32	8.79	9.28	9.74	10.98
	6H	9.03	9.44	10.01	10.41	11.65	8.66	9.06	9.63	10.04	11.27
	8H	9.16	9.54	10.14	10.51	11.76	8.78	9.16	9.76	10.12	11.37
	12H	9.24	9.58	10.23	10.56	11.81	8.86	9.20	9.85	10.18	11.43
8H	4H	8.74	9.12	9.72	10.09	11.34	8.42	8.80	9.40	9.77	11.02
	6H	9.24	9.55	10.24	10.56	11.80	8.89	9.20	9.89	10.21	11.46
	8H	9.45	9.72	10.46	10.72	11.99	9.09	9.37	10.11	10.37	11.63
	12H	9.61	9.85	10.62	10.84	12.15	9.25	9.49	10.26	10.48	11.80
12H	4H	8.71	9.05	9.71	10.04	11.29	8.40	8.74	9.39	9.72	10.98
	6H	9.25	9.53	10.26	10.53	11.79	8.92	9.19	9.93	10.19	11.46
	8H	9.49	9.74	10.50	10.73	12.04	9.15	9.39	10.16	10.38	11.70